

# T-1 3/4 (5mm) BI-COLOR INDICATOR LAMP

Part Number: L-59EGW

High Efficiency Red


#### **Features**

- Uniform light output.
- Low power consumption.
- 3 leads with one common lead.
- Long life-solid state reliability.
- High glass transition temperature epoxy.
- RoHS compliant.

## **Description**

- The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.
- The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

# **Package Dimensions**



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.25(0.01") unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.4. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

SPEC NO: DSAA4041 APPROVED: WYNEC **REV NO: V.23A CHECKED: Allen Liu** 

DATE: JUN/07/2014 DRAWN: L.Q.Xie

PAGE: 1 OF 7 ERP: 1101005755

### **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
L-59EGW	High Efficiency Red (GaAsP/GaP)	White Diffused	30	60	- 60°
			*20	*40	
	Green (GaP)		20	60	
			*20	*60	

- 1.  $\theta$ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

## Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red Green	627 565		nm	Ir=20mA
λD [1]	Dominant Wavelength	High Efficiency Red Green	617 568		nm	Ir=20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red Green	45 30		nm	Ir=20mA
С	Capacitance	High Efficiency Red Green	15 15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	High Efficiency Red Green	2 2.2	2.5 2.5	V	Ir=20mA
lR	Reverse Current	High Efficiency Red Green		10 10	uA	V <sub>R</sub> = 5V

#### Notes:

- 1.Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.
  3. Wavelength value is traceable to the CIE127-2007 compliant national standards.


# Absolute Maximum Ratings at TA=25°C

Parameter	High Efficiency Red	Green	Units		
Power dissipation	75	62.5	mW		
DC Forward Current	30	25	mA		
Peak Forward Current [1]	160	140	mA		
Reverse Voltage	5				
Operating / Storage Temperature	-40°C To +85°C				
Lead Solder Temperature [2]	260°C For 3 Seconds				
Lead Solder Temperature [3]	260°C For 5 Seconds				

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.


DATE: JUN/07/2014 PAGE: 2 OF 7 SPEC NO: DSAA4041 **REV NO: V.23A APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: L.Q.Xie ERP: 1101005755


Luminous intensity/ luminous Flux: +/-15%.
 \*Luminous intensity value is traceable to the CIE127-2007 compliant national standards.





wavelength > (nm)
RELATIVE INTENSITY Vs. WAVELENGTH


# L-59EGW High Efficiency Red














 SPEC NO: DSAA4041
 REV NO: V.23A
 DATE: JUN/07/2014
 PAGE: 3 OF 7


 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: L.Q.Xie
 ERP: 1101005755


## Green












SPATIAL DISTRIBUTION

SPEC NO: DSAA4041 REV NO: V.23A DATE: JUN/07/2014 PAGE: 4 OF 7
APPROVED: WYNEC CHECKED: Allen Liu DRAWN: L.Q.Xie ERP: 1101005755



### Terms and conditions for the usage of this document


- 1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2.The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6.All design applications should refer to Kingbright application notes available at <a href="http://www.kingbright.com/application">http://www.kingbright.com/application</a> notes

 SPEC NO: DSAA4041
 REV NO: V.23A
 DATE: JUN/07/2014
 PAGE: 5 OF 7


 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: L.Q.Xie
 ERP: 1101005755

#### **PRECAUTIONS**

1. The lead pitch of the LED must match the pitch of the mounting holes on the PCB during component placement. Lead—forming may be required to insure the lead pitch matches the hole pitch. Refer to the figure below for proper lead forming procedures. (Fig. 1)




- "( )" Correct mounting method "imes" Incorrect mounting method
- 2. When soldering wire to the LED, use individual heat—shrink tubing to insulate the exposed leads to prevent accidental contact short—circuit. (Fig.2)
- 3. Use stand—offs (Fig.3) or spacers (Fig.4) to securely position the LED above the PCB.




- 4. Maintain a minimum of 3mm clearance between the base of the LED lens and the first lead bend. (Fig. 5 and 6)
- 5. During lead forming, use tools or jigs to hold the leads securely so that the bending force will not be transmitted to the LED lens and its internal structures. Do not perform lead forming once the component has been mounted onto the PCB. (Fig. 7)

SPEC NO: DSAA4041 APPROVED: WYNEC REV NO: V.23A CHECKED: Allen Liu DATE: JUN/07/2014 DRAWN: L.Q.Xie PAGE: 6 OF 7 ERP: 1101005755


6. Do not bend the leads more than twice. (Fig. 8)



7. During soldering, component covers and holders should leave clearance to avoid placing damaging stress on the LED during soldering.



- 8. The tip of the soldering iron should never touch the lens epoxy.
- 9. Through—hole LEDs are incompatible with reflow soldering.
- 10. If the LED will undergo multiple soldering passes or face other processes where the part may be subjected to intense heat, please check with Kingbright for compatibility.
- 11. Recommended Wave Soldering Profiles:



### Notes:

- 1.Recommend pre-heat temperature of 105°C or less (as measured with a thermocouple attached to the LED pins) prior to immersion in the solder wave with a maximum solder bath temperature of  $260^{\circ}$ C
- 2.Peak wave soldering temperature between 245°C  $\sim$  255°C for 3 sec (5 sec max).
- 3.Do not apply stress to the epoxy resin while the temperature is above 85°C.
- 4.Fixtures should not incur stress on the component when mounting and during soldering process. 5.SAC 305 solder alloy is recommended.
- 6.No more than one wave soldering pass.

 SPEC NO: DSAA4041
 REV NO: V.23A
 DATE: JUN/07/2014
 PAGE: 7 OF 7

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: L.Q.Xie
 ERP: 1101005755