

Product Overview


The Qorvo T2G6003028-FS is a 30W (P_{3dB}) discrete GaN on SiC HEMT which operates from DC to 6 GHz. The device is constructed with Qorvo's proven QGaN25 process, which features advanced field plate techniques to optimize power and efficiency at high drain bias operating conditions. This optimization can potentially lower system costs in terms of fewer amplifier line-ups and lower thermal management costs.

Lead-free and ROHS compliant

Evaluation boards are available upon request.



Functional Block Diagram



Pin Configuration

| Pin No. | Label |
|---------|----------------|
| 1 | V_D / RF OUT |
| 2 | V_G / RF IN |
| 3 | Flange/Source |

Key Features ¹

- Frequency: DC to 6 GHz
 - Output Power (P_{3dB}): 42.7 W
 - Linear Gain: >14 dB
 - Operating Voltage: 28 V
 - Low thermal resistance package
 - Pulse capable
- Note 1: @ 3 GHz

Applications

- Military radar
- Civilian radar
- Professional and military radio communications
- Test instrumentation
- Wideband or narrowband amplifiers
- Jammers

Ordering info

| Part No. | Description |
|-------------------|-----------------------------------|
| T2G6003028-FS | Packaged part Flangeless |
| T2G6003028-FSEVB | 5.4 – 5.9 GHz Evaluation Board |
| T2G6003028-FSEVB2 | 1.3 – 1.9 GHz Evaluation Board |

Absolute Maximum Ratings

| Parameter | Rating | Units |
|---|-------------|------------------|
| Breakdown Voltage, BV_{DG} | 100 | V |
| Gate Voltage Range, V_G | -7 to +2 | V |
| Drain Current, $I_{D_{MAX}}$ | 5.5 | A |
| Gate Current Range, I_G | -10 to 28 | mA |
| Power Dissipation, Pulsed, P_{DISS}^2 | 47.5 | W |
| RF Input Power, CW, $T = 25^\circ\text{C}$ (P_{IN}) | 40 | dBm |
| Channel Temperature (T_{CH}) | 275 | $^\circ\text{C}$ |
| Mounting Temperature (30 Seconds) | 320 | $^\circ\text{C}$ |
| Storage Temperature | -40 to +150 | $^\circ\text{C}$ |

Operation of this device outside the parameter ranges given above may cause permanent damage. These are stress ratings only, and functional operation of the device at these conditions is not implied.

Recommended Operating Conditions ^{1, 2}

| Parameter | Min | Typ | Max | Units |
|------------------------------|-----|------|-----|-------|
| Drain Voltage Range, V_D | 12 | | 40 | V |
| Drain Bias Current, I_{DQ} | | 200 | | mA |
| Gate Voltage, V_G | - | -3.0 | - | V |

Electrical Specifications ^{1, 2}

| Parameter | Min | Typ | Max | Units |
|---|------|------|-----|-------|
| Linear Gain, G_{LIN} | 12 | 14 | - | dB |
| Output Power at 3dB compression point, P_{3dB} | 43.0 | 44.6 | - | W |
| Drain Efficiency at 3dB compression point, $DEFF_{3dB}$ | 45.0 | 54.0 | - | % |
| Gain at 3dB compression point, G_{3dB} | 9.0 | 11.0 | - | dB |
| Gate Leakage ($V_D = +10\text{ V}$, $V_G = -3.7\text{ V}$) | -11 | - | - | mA |

Notes:

- Performance at 5.6 GHz in the 5.4 to 5.9 GHz Evaluation Board
- $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$; Pulse: 100 μs , 20%

RF Characterization – Mismatch Ruggedness at 5.6 GHz ¹

| Symbol | Parameter | dB Compression | Typical |
|--------|-------------------------------|----------------|---------|
| VSWR | Impedance Mismatch Ruggedness | 3 | 10:1 |

Notes:

- P_{1dB} CW Input Power under matched condition.

Power-Matched Load Pull Performance

Test conditions unless otherwise noted: T = 25°C.

| Parameter | Typical Value | | | | | | Units |
|--|---------------|------|------|------|------|------|-------|
| | 1 | 2 | 3 | 4 | 5 | 6 | |
| Frequency (F) | 1 | 2 | 3 | 4 | 5 | 6 | GHz |
| Drain Voltage (V _D) | 28 | 28 | 28 | 28 | 28 | 28 | V |
| Bias Current (I _{DQ}) | 200 | 200 | 200 | 200 | 200 | 200 | mA |
| Output P3dB (P _{3dB}) | 45.7 | 46 | 46.3 | 46.5 | 46.8 | 46.2 | dBm |
| PAE @ P _{3dB} (PAE _{3dB}) | 64.9 | 64.2 | 68.1 | 54.6 | 55.9 | 54.7 | % |
| Gain @ P3dB (G _{3dB}) | 19.9 | 15.7 | 11.3 | 10.1 | 10.7 | 12.1 | dB |

Notes:

1. V_D = 28 V, I_{DQ} = 200 mA, Pulse Width = 100 uS, Duty Cycle = 20%
2. Characteristic Impedance (Z₀) = 10 Ω. See pg. 14 for Load Pull Reference Planes.

Efficiency-Matched Load Pull Performance

Test conditions unless otherwise noted: T = 25°C.

| Parameter | Typical Value | | | | | | Units |
|--|---------------|------|------|------|------|------|-------|
| | 1 | 2 | 3 | 4 | 5 | 6 | |
| Frequency (F) | 1 | 2 | 3 | 4 | 5 | 6 | GHz |
| Drain Voltage (V _D) | 28 | 28 | 28 | 28 | 28 | 28 | V |
| Bias Current (I _{DQ}) | 200 | 200 | 200 | 200 | 200 | 200 | mA |
| Output P3dB (P _{3dB}) | 43.1 | 43.1 | 44.6 | 44.1 | 44.9 | 45.7 | dBm |
| PAE @ P _{3dB} (PAE _{3dB}) | 73 | 76 | 46.1 | 65.1 | 69.5 | 60 | % |
| Gain @ P3dB (G _{3dB}) | 19.7 | 16.2 | 11.7 | 10.8 | 12.4 | 12.9 | dB |

Notes:

1. V_D = 28 V, I_{DQ} = 200 mA, Pulse Width = 100 uS, Duty Cycle = 20%.
2. Characteristic Impedance (Z₀) = 10 Ω. See pg. 14 for Load Pull Reference Planes.

Thermal Information – CW ^{1,2}

| Parameter | Test Conditions | Value | Units |
|--|---|--------|--------------------|
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 30\text{ W}$, $T_{base} = 85^\circ\text{C}$ | 2.51 | $^\circ\text{C/W}$ |
| Maximum Channel Temperature, T_{CH} | | 160.65 | $^\circ\text{C}$ |
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 35\text{ W}$, $T_{base} = 85^\circ\text{C}$ | 2.58 | $^\circ\text{C/W}$ |
| Maximum Channel Temperature, T_{CH} | | 175.20 | $^\circ\text{C}$ |
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 40\text{ W}$, $T_{base} = 85^\circ\text{C}$ | 2.67 | $^\circ\text{C/W}$ |
| Maximum Channel Temperature, T_{CH} | | 191.68 | $^\circ\text{C}$ |
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 45\text{ W}$, $T_{base} = 85^\circ\text{C}$ | 2.75 | $^\circ\text{C/W}$ |
| Maximum Channel Temperature, T_{CH} | | 208.73 | $^\circ\text{C}$ |

Notes:

1. Thermal resistance calculated to bottom of package.
2. Refer to the following document: [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)

Thermal Information – Pulsed ^{1,2}

| Parameter | Test Conditions | Value | Units |
|--|--|--------|--------------------|
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 40\text{ W}$, $T_{base} = 85^\circ\text{C}$ Pulse Width = 100 μS Duty Cycle = 5% | 1.56 | $^\circ\text{C/W}$ |
| Peak Channel Temperature, T_{CH} | | 147.37 | $^\circ\text{C}$ |
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 40\text{ W}$, $T_{base} = 85^\circ\text{C}$ Pulse Width = 100 μS Duty Cycle = 10% | 1.62 | $^\circ\text{C/W}$ |
| Peak Channel Temperature, T_{CH} | | 149.83 | $^\circ\text{C}$ |
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 40\text{ W}$, $T_{base} = 85^\circ\text{C}$ Pulse Width = 100 μS Duty Cycle = 20% | 1.77 | $^\circ\text{C/W}$ |
| Peak Channel Temperature, T_{CH} | | 155.89 | $^\circ\text{C}$ |
| Thermal Resistance, IR^2 (θ_{JC}) | $P_D = 40\text{ W}$, $T_{base} = 85^\circ\text{C}$ Pulse Width = 100 μS Duty Cycle = 50% | 2.07 | $^\circ\text{C/W}$ |
| Peak Channel Temperature, T_{CH} | | 167.69 | $^\circ\text{C}$ |

Notes:


1. Thermal resistance calculated to bottom of package.
2. Refer to the following document: [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)

Load Pull Contours 1, 2, 3

Notes:

1. Test Conditions: $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$
2. Test Signal: Pulse Width = 100 μsec , Duty Cycle = 20%
3. See pg. 14 for load pull reference planes.

1GHz, Load-pull




Load Pull Contours 1, 2, 3

Notes:

1. Test Conditions: $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$
2. Test Signal: Pulse Width = 100 μsec , Duty Cycle = 20%
3. See pg. 14 for load pull reference planes.

2GHz, Load-pull




Load Pull Contours ^{1, 2, 3}

Notes:

1. Test Conditions: $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$
2. Test Signal: Pulse Width = 100 μsec , Duty Cycle = 20%
3. See pg. 14 for load pull reference planes.

3GHz, Load-pull




Load Pull Contours 1, 2, 3

Notes:

1. Test Conditions: $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$
2. Test Signal: Pulse Width = 100 μsec , Duty Cycle = 20%
3. See pg. 14 for load pull reference planes.

4GHz, Load-pull




Load Pull Contours 1, 2, 3

Notes:

1. Test Conditions: $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$
2. Test Signal: Pulse Width = 100 μsec , Duty Cycle = 20%
3. See pg. 14 for load pull reference planes.

5GHz, Load-pull




Load Pull Contours 1, 2, 3

Notes:

1. Test Conditions: $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$
2. Test Signal: Pulse Width = 100 μsec , Duty Cycle = 20%
3. See pg. 14 for load pull reference planes.







6GHz, Load-pull



Load Pull Drive-up ^{1, 2}

Notes:







1. $V_d = 28\text{ V}$, $I_{dq} = 200\text{ mA}$, Pulse Width = 100 μs , Duty Cycle = 20%
2. NaN means the parameter is either unavailable or undefined.




Load Pull Drive-up ^{1, 2}

Notes:

1. $V_d = 28\text{ V}$, $I_{dq} = 200\text{ mA}$, Pulse Width = 100 μs , Duty Cycle = 20%
2. NaN means the parameter is either unavailable or undefined.



Package Marking and Pin Configuration ¹



Note:


The T2G6003028-FS will be marked with the “30282” designator and a lot code marked below the part designator. The “YY” represents the last two digits of the calendar year the part was manufactured, the “WW” is the work week of the assembly lot start, and the “ZZZ” is an auto-generated number.

| Pin | Symbol | Description |
|-----|----------------|--|
| 1 | V_D / RF OUT | Drain voltage / RF Output matched to 50 ohms; see EVB Layout on page 17 as an example. |
| 2 | V_G / RF IN | Gate voltage / RF Input matched to 50 ohms; see EVB Layout on page 17 as an example. |
| 3 | Flange | Source connected to ground; see EVB Layout on page 17 as an example. |

Notes:

Thermal resistance measured to bottom of package


Package Dimensions



Notes:

- Material:
Package Base: Ceramic/Metal
Package Lid: Ceramic
- Package exposed metallization is gold plated
- Part is epoxy sealed
- Part meets industry NI200 footprint
- Body dimensions do not include lid shift or epoxy run out which can be up to 0.020 per side.
- Dimensions are in inches. General tolerance is ±0.005".

Application Circuit




Bias Procedure

| Bias-up Procedure | Bias-down Procedure |
|--|--|
| 1. Set V_G to -5 V. | 1. Turn off RF signal. |
| 2. Set I_D current limit to 220 mA. | 2. Turn off V_D |
| 3. Apply 28 V V_D . | 3. Wait 1 seconds to allow drain capacitor to discharge. |
| 4. Slowly adjust V_G until I_D is set to 200 mA. | 4. Turn off V_G |
| 5. Set I_D to 2.8 A. | |
| 6. Apply RF signal | |

5.4 – 5.9 GHz Evaluation Board– Layout ^{1, 2, 3}

Notes:



1. Top RF layer is 0.020" thick Rogers RO4350B, $\epsilon_r = 3.48$
2. The pad pattern shown has been developed and tested for optimized assembly at Qorvo Semiconductor.
3. The PCB land pattern has been developed to accommodate lead and package tolerances



5.4 – 5.9 GHz Application Circuit – Bill of Materials EVB1

| Ref Des | Qty | Description | Mfg Name | Mfg Part # |
|--------------------|-----|-------------|----------------------|-----------------------|
| C1 | 1 | 0.3 pF | ATC | ATC600S0R3 |
| C2 | 1 | 0.2 pF | ATC | ATC600S0R2 |
| L1, L2 | 2 | 8.8 nH | COILCRAFT | 1606-8 |
| C3, C4, C6, C7, C8 | 5 | 3 pF | ATC | ATC600S3R0 |
| C5 | 1 | 0.4 pF | ATC | ATC600S0R5 |
| R1 | 1 | 97.6 Ohms | Venkel | CR0604-16w-97R6FT |
| R2 | 1 | 4.7 Ohms | Newark | 37C0064 |
| R3 | 1 | 330 Ohms | Newark | TNPW1206330RBT9ET1-E3 |
| R4 | 1 | 50 Ohms | ATC | CRCW120651R0FKEA |
| C9, C10 | 2 | 220 pF | AVX | AVX06035C22KAT2A |
| C11, C12 | 2 | 2200 pF | Vitramon | VJ1206Y222KXA |
| C13, C14 | 2 | 22000 pF | Vitramon | VJ1206Y223KXA |
| C15 | 1 | 220 uF | United Chemi-Con | EMVY500ADA221MJA0G |
| C16 | 1 | 1.0 uF | Allied | 541-1231 |
| L3 | 1 | 48 Ohm | Ferrite, Laird Tech. | 28F0121-0SR-10 |

Evaluation Board Performance ^{1, 2, 3}







Notes:

1. Test Conditions: $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$
2. Test Signal: Pulse Width = $100\text{ }\mu\text{s}$, Duty Cycle = 20 %
3. Performance at 3dB compression.


Performance over Temperatures of 5.4 – 5.9 GHz EVB ^{1, 2}

Notes:

1. Test Conditions: $V_D = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$, 100 us Pulse Width, 20% Duty Cycle.
2. Performance at 3dB compression.



Recommended Solder Temperature Profile



Handling Precautions

| Parameter | Rating | Standard |
|----------------------------------|------------------|-------------------|
| ESD – Human Body Model (HBM) | Class 1A (250V) | JEDEC JESD22-A114 |
| ESD – Charged Device Model (CDM) | Class C3 (1000V) | JEDEC JS-002 |
| MSL – Moisture Sensitivity Level | MSL3 | JESD J-STD-020 |



Caution!
ESD-Sensitive Device

Solderability

Compatible with both lead-free (260°C max. reflow temp.) and tin/lead (245°C max. reflow temp.) soldering processes.

Solder profiles available upon request.

The use of no-clean solder to avoid washing after soldering is recommended.

Contact plating: NiAu. Minimum Au thickness is 60 µinches.

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- PFOS Free
- SVHC Free



Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2021 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)

[T2G6003028-FS](#) [T2G6003028-FS EVAL BOARD](#) [T2G6003028-FS-EVB2](#)