

## D SUB MIXED FE S CRIMP COAX 50 OHMS-PL3




Image is for illustration purposes only. Please refer to product description.

Part number	09 69 181 7140
Specification	D SUB MIXED FE S CRIMP COAX 50 OHMS-PL3
HARTING eCatalogue	<a href="https://b2b.harting.com/09691817140">https://b2b.harting.com/09691817140</a>

### Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Coaxial contact
Description of the contact	Straight for cables RG 174 U, 188 AU, 316 U
Features	Outer ferrule: crimp in tool cavity B

### Version

Termination method	Solder/crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Operating current	$\leq 2$ A
Rated voltage	250 V
Insulation resistance	$> 10^9$ $\Omega$
Contact resistance	$\leq 10$ m $\Omega$
Impedance	50 $\Omega$
Limiting temperature	-55 ... +135 °C
Insertion force	$\leq 7$ N
Withdrawal force	$\leq 7$ N
Performance level	3



Pushing Performance

## Technical characteristics

Mating cycles	≥50
Test voltage $U_{r.m.s.}$	0.75 kV @ 50 Hz
Frequency	0 ... 2 GHz

## Material properties

Material (contacts)	Copper alloy PBFE / PBTP / PI
Surface (contacts)	Gold plated
Material (locking)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

## Commercial data

Packaging size	20
Net weight	1 g
Country of origin	Czechia
European customs tariff number	85366910
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09691817140](#)