Kingbright

2.5x5mm RECTANGULAR SOLID LAMP

The Green source color devices are made with

Gallium Phosphide Green Light Emitting Diode.

L-383GDT


Description

GREEN

Features

- LOW POWER CONSUMPTION.
- RELIABLE AND RUGGED.
- EXCELLENT UNIFORMITY OF LIGHT OUTPUT.
- SUITABLE FOR LEVEL INDICATOR.
- LONG LIFE SOLID STATE RELIABILITY.
- RoHS COMPLIANT.

Package Dimensions



SPEC NO.: DSAA4982

REV NO.: V.4

APPROVED: J. Lu

CHECKED: Allen Liu

DATE: MAR/20/2005 DRAWN: S.M.TANG PAGE: 1 OF 3

Kingbright

Selection Guide)				
Part No.	Dice	Lens Type	lv (mcd) @ 10mA		Viewing Angle
			Min.	Тур.	201/2
L-383GDT	GREEN (GaP)	GREEN DIFFUSED	1	4	110°

Note:

1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	565		nm	IF=20mA
λD	Dominant Wavelength	Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	30		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
Vf	Forward Voltage	Green	2.2	2.5	V	IF=20mA
IR	Reverse Current	Green		10	uA	VR = 5V

Absolute Maximum Ratings at TA=25°C

Parameter	Green	Units		
Power dissipation	105	mW		
DC Forward Current	25	mA		
Peak Forward Current [1]	140	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	260°C For 3 Seconds			
Lead Solder Temperature [3]	260°C For 5 Seconds			


Notes:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.

2. 2mm below package base.

3. 5mm below package base.

Kingbright



SPEC NO.: DSAA4982 APPROVED: J. Lu

CHECKED: Allen Liu

REV NO.: V.4

DATE: MAR/20/2005 DRAWN: S.M.TANG