

T2800D



Description

Designed primarily for full-wave ac control applications, such as light dimmers, motor controls, heating controls and power supplies.

Features


- Blocking Voltage to 400 V
- All Diffused and Glass Passivated Junctions for Greater Parameter Uniformity and Stability
- Four Quadrant Gating

Po


- Pb–Free Package is Available
- Small, Rugged, Thermowatt Construction for Low Thermal Resistance, High Heat Dissipation and Durability

Pin Out





Functional Diagram



Additional Information







Samples

© 2019 Littelfuse, Inc. Specifications are subject to change without notice. Revised: 07/16/19



Maximum Ratings (T = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Peak Repetitive Off-State Voltage (Note 1) (Sine Wave 50 to 60 Hz, $T_{\rm J}$ = -40 to +100°C, Gate Open)	V _{drm} , V _{rrm}	400	V
On-State RMS Current (All Conduction Angles, $T_c = +80^{\circ}C$)	I _{T (RMS)}	6.0	A
Peak Non–Repetitive Surge Current (One Full Cycle, Sine Wave 60 Hz, T _j = +80°C)	I _{TSM}	100	А
Circuit Fusing Considerations (t = 8.3 ms)	l²t	40	A2s
Peak Gate Power (Pulse Width = 10 μ sec, T _c = +80°C)	P _{GM}	16	W
Average Gate Power (t = 8.3 msec, $T_c = +80^{\circ}C$)	P _{GM (AV)}	0.35	W
Peak Gate Current (Pulse Width = 10 μ sec, T _c = +80°C)	I _{GM}	4.0	А
Operating Junction Temperature Range @ Rated $\rm V_{_{RRM}}$ and $\rm V_{_{DRM}}$	Tj	-40 to +125	°C
Storage Temperature Range	T _{stg}	-40 to +150	°C

Thermal Characteristics

Rating	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	R _{ejc}	2.2	°C/W
Maximum Device Temperature for Soldering Purposes for 10 Sec	TL	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. V_{prix} and V_{prix} for all types can be applied on a continuous basis. Ratings apply for zero or negative gate voltage; however, positive gate voltage shall not be applied concurrent with negative potential on the anode. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.

Electrical Characteristics \cdot **OFF** (T₁ = 25°C unless otherwise noted ; Electricals apply in both directions)

Characteristic		Symbol	Min	Тур	Мах	Unit
Peak Repetitive Blocking Current	T ₁ = 25°C	I _{DRM} ,	-	-	1.0	-
$(V_{D} = V_{DRM} = V_{RRM}; \text{ Gate Open})$	T_ = 125°C	I	-	-	2.0	mA

Electrical Characteristics · **ON** ($T_1 = 25^{\circ}$ C unless otherwise noted; Electricals apply in both directions)

Characteristic		Symbol	Min	Тур	Мах	Unit
Peak Forward On-State Voltage (Note 3) ($I_{TM} = \pm 30 \text{ A}$)		V _{TM}	-	1.7	2.0	V
	MT2(+), G(+)		-	10	25	
Gate Trigger Current (Continuous dc)	MT2(+), G(-)		_	20	60	
$(V_{\rm D} = 12 \text{ V}, \text{ R}_{\rm L} = 100 \Omega)$	MT2(-), G(-)	GT	_	15	25	mA
	MT2(-), G(+)		_	30	60	
Gate Trigger Voltage (Continuous dc) (All Four Quadrants) (V_{_{D}} = 12 Vdc, R_{_{L}} = 100 Ω)		V _{gt}	-	1.25	2.5	V
Gate Non-Trigger Voltage (Continuous dc) ($V_p = 12 \text{ Vdc}, R_L = 100 \Omega, T_c = 100^{\circ}\text{C}$)		V _{gD}	0.2	_	_	V
Holding Current (MainTerminal Voltage = 12 Vdc, Gate Open , Initiating Current) = ±200 mA)		I _H	_	15	30	mA
Gate Controlled Turn-On Time (Rated V_{DRM} , $I_{_{T}} = 10$ A , $I_{_{GT}} = 160$ mA, Rise Time = 0.1 µs)		t _{gt}	_	1.6	_	μs




Dynamic	Charac	teristics
	onarao	

·					
Characteristic	Symbol	Min	Тур	Max	Unit
Critical Rate-of-Rise of Commutation Voltage (V _D = Rated V _{DRM} , I _{T(RMS)} = 8 A, Commutating di/dt = 4.1 A/ms, Gate Unenergized, T _C = 80°C)	(di/dt)c	-	10	_	A/ms
Critical Rate-of-Rise of Off-State Voltage (V_{D} = Rated V_{DRM} , Exponential Voltage Rise, Gate Open, T_{C} = 100°C)	dv/dt	60	-	-	V/µs


2. Pulse Test: Pulse Width \leq 2.0 ms, Duty Cycle \leq 2%.

Voltage Current Characteristic of SCR

Symbol	Parameter	
V _{DRM}	Peak Repetitive Forward Off State Voltage	
I _{DRM}	Peak Forward Blocking Current	
V _{RRM}	Peak Repetitive Reverse Off State Voltage	
I	Peak Reverse Blocking Current	
V _{TM}	Maximum On State Voltage	
I _H	Holding Current	



Quadrant Definitions for a Triac



All polarities are referenced to MT1.

With in -phase signals (using standard AC lines) quadrants I and III are used

Figure 1. Current Derating





Figure 2. Power Dissipation



^{© 2019} Littelfuse, Inc. Specifications are subject to change without notice. Revised: 07/16/19




Thyristors Surface Mount – 400V > T2800D


S


.1

Dimensions



Part Marking System





Dim		Millim	neters	
Dim	Min	Мах	Min	Мах
Α	0.590	0.620	14.99	15.75
В	0.380	0.420	9.65	10.67
С	0.178	0.188	4.52	4.78
D	0.025	0.035	0.64	0.89
F	0.142	0.147	3.61	3.73
G	0.095	0.105	2.41	2.67
Н	0.110	0.130	2.79	3.30
J	0.018	0.024	0.46	0.61
К	0.540	0.575	13.72	14.61
L	0.060	0.075	1.52	1.91
Ν	0.195	0.205	4.95	5.21
٥	0.105	0.115	2.67	2.92
R	0.085	0.095	2.16	2.41
S	0.045	0.060	1.14	1.52
Т	0.235	0.255	5.97	6.47
U	0.000	0.050	0.00	1.27
v	0.045		1.15	
Z		0.080		2.04

Pin Assignment		
1 Main Terminal 1		
2	Main Terminal 2	
3	Gate	
4	No Connection	

Ordering Information				
Device	Package	Shipping		
T2800D	TO-220AB			
T2800DG	TO-220AB (Pb-Free)	500 Units/ Box		

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

2. CONTROLLING DIMENSION: INCH.

3. DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at http://www.littelfuse.com/disclaimer-electronics.