

## Description

The F2976 is a single-pole double-throw (SP2T) reflective RF switch featuring high linearity and wide bandwidth. This device is optimized from 5MHz to 1.8GHz to support downstream cable modem future migration for DOCSIS 3.1 applications, and operates at up to 10GHz to support a multitude of wireless RF applications. Superb performance is achieved when used in either 50Ω or 75Ω terminating impedance applications.

The F2976 uses a single positive supply voltage of either +3.3V or +5.0V and is compatible with either 1.8V or 3.3V control logic.

## Competitive Advantage

The F2976 provides extremely low insertion loss across the entire bandwidth while providing superb distortion performance.

- Optimized for DOCSIS 3.1 applications up to 1.8GHz
- Optimized for Wi-Fi applications up to 5.9GHz
- Low insertion loss
- High isolation
- Fast switching
- No external matching required

## Typical Applications

- Broadband Cable DOCSIS 3.0 / 3.1
- Set top box
- CATV filter bank switching
- Wi-Fi
- Cellular BTS
- General purpose

## General Features

- Supply voltage: +2.5V to +5.25V
- 1.8V and 3.3V compatible control logic
- 2mm x 2mm, 12-pin TQFN package
- -40°C to +105°C operating temperature range

## Features (75Ω)


- Low insertion loss:
  - 0.23dB at 204MHz
  - 0.34dB at 1.8GHz
- High Isolation: 40dB at 1.8GHz
- P0.1dB compression of +37dBm at 204MHz
- Second Harmonic: -100dBc at 204MHz
- Third Harmonic: -120dBc at 204MHz
- Composite Second Order Distortion > 100dBc
- Composite Triple Beat Distortion > 100dBc

## Features (50Ω)

- Low insertion loss:
  - 0.40dB at 2.4GHz
  - 0.55dB at 8GHz
- High Isolation:
  - 34dB at 2.4GHz
- High Linearity:
  - IIP2 +125dBm at 2.4GHz
  - IIP3 +77dBm at 2.4GHz
- P0.1dB compression of +40dBm at 2.4GHz
- Second Harmonic: -100dBc at 2.4GHz
- Third Harmonic: -110dBc at 2.4GHz


## Block Diagram

**Figure 1. Block Diagram**



## Pin Assignments

Figure 2. Pin Assignments for 2mm x 2mm x 0.5mm 12-pin TQFN, NEG12 – Top View



## Pin Descriptions

Table 1. Pin Descriptions

| Number | Name             | Description  |
|--------|------------------|--|
| 1      | GND              | Internally grounded. Connect pin directly to paddle ground or as close as possible to pin with thru vias.  |
| 2      | RF2              | RF2 Port. If this pin is not 0V DC, then an external coupling capacitor must be used.  |
| 3      | GND              | Internally grounded. Connect pin directly to paddle ground or as close as possible to pin with thru vias.  |
| 4      | GND              | Internally grounded. Connect pin directly to paddle ground or as close as possible to pin with thru vias.  |
| 5      | RFC              | RF Common Port. If this pin is not 0V DC, then an external coupling capacitor must be used.  |
| 6      | GND              | Internally grounded. Connect pin directly to paddle ground or as close as possible to pin with thru vias.  |
| 7      | GND              | Internally grounded. Connect pin directly to paddle ground or as close as possible to pin with thru vias.  |
| 8      | RF1              | RF1 Port. If this pin is not 0V DC, then an external coupling capacitor must be used.  |
| 9      | GND              | Internally grounded. Connect pin directly to paddle ground or as close as possible to pin with thru vias.  |
| 10     | V <sub>CTL</sub> | Logic control pin (see Table 9).   |
| 11     | LS               | Truth Table select pin. Defines V <sub>CTL</sub> logic for RF switching (see Table 9). Pin is internally pulled up to 2.5V through a 500kΩ resistor.   |
| 12     | V <sub>CC</sub>  | Power supply. Bypass to GND with capacitors shown in the Typical Application Circuit as close as possible to pin.  |
|        | EP               | Exposed Pad. Internally connected to GND. Solder this exposed pad to a PCB pad that uses multiple ground vias to provide heat transfer out of the device into the PCB ground planes. These multiple ground vias are also required to achieve the specified RF performance. |

## Absolute Maximum Ratings

Stresses beyond those listed below may cause permanent damage to the device. Functional operation of the device at these or any other conditions beyond those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

**Table 2. Absolute Maximum Ratings**

| Parameter  | Symbol                             | Minimum             | Maximum                               | Units |
|--|------------------------------------|---------------------|---------------------------------------|-------|
| V <sub>CC</sub> to GND   | V <sub>CC</sub>                    | -0.3                | +5.5                                  | V     |
| V <sub>CTL</sub> , LS  | V <sub>LOGIC</sub>                 | -0.3                | Lower of (V <sub>CC</sub> + 0.3, 3.9) | V     |
| RF1, RF2, RFC  | V <sub>RF</sub>                    | -0.3                | +0.3                                  | V     |
| Maximum Input CW Power, 50Ω, T <sub>EP</sub> = 25°C, V <sub>CC</sub> = 5.25V (any port, insertion loss state) [a, b] | 5MHz ≤ f <sub>RF</sub> ≤ 10MHz     | P <sub>ABSCW1</sub> | 30                                    | dBm   |
|  | 10MHz < f <sub>RF</sub> ≤ 25MHz    | P <sub>ABSCW2</sub> | 32                                    |       |
|  | 25MHz < f <sub>RF</sub> ≤ 200MHz   | P <sub>ABSCW3</sub> | 33                                    |       |
|  | 200MHz < f <sub>RF</sub> ≤ 6000MHz | P <sub>ABSCW4</sub> | 34                                    |       |
|  | f <sub>RF</sub> > 6000MHz          | P <sub>ABSCW5</sub> | 33                                    |       |
| Maximum Peak Power, 50Ω, T <sub>EP</sub> = 25°C, V <sub>CC</sub> = 5.25V (any port, insertion loss state) [a, b, c]  | 5MHz ≤ f <sub>RF</sub> ≤ 10MHz     | P <sub>ABSPK1</sub> | 35                                    | dBm   |
|  | 10MHz < f <sub>RF</sub> ≤ 25MHz    | P <sub>ABSPK2</sub> | 37                                    |       |
|  | 25MHz < f <sub>RF</sub> ≤ 200MHz   | P <sub>ABSPK3</sub> | 38                                    |       |
|  | 200MHz < f <sub>RF</sub> ≤ 6000MHz | P <sub>ABSPK4</sub> | 39                                    |       |
|  | f <sub>RF</sub> > 6000MHz          | P <sub>ABSPK5</sub> | 38                                    |       |
| Maximum Junction Temperature   | T <sub>JMAX</sub>                  |                     | +140                                  | °C    |
| Storage Temperature Range  | T <sub>ST</sub>                    | -65                 | +150                                  | °C    |
| Lead Temperature (soldering, 10s)  | T <sub>LEAD</sub>                  |                     | +260                                  | °C    |
| Electrostatic Discharge – HBM (JEDEC/ESDA JS-001-2012)   | V <sub>ESDHBM</sub>                |                     | 2500 (Class 2)                        | V     |
| Electrostatic Discharge – CDM (JEDEC 22-C101F)   | V <sub>ESDCDM</sub>                |                     | 1000 (Class C3)                       | V     |

- a. In a 50Ω system, dBmV = dBm [50Ω] + 47.  
In a 75Ω system, dBmV = dBm [75Ω] + 48.75.
- b. T<sub>EP</sub> = Temperature of the exposed paddle.
- c. 5% duty cycle of a 4.6ms period.


## Recommended Operating Conditions

**Table 3. Recommended Operating Conditions**

| Parameter                      | Symbol    | Condition                                      | Minimum | Typical | Maximum          | Units |
|--------------------------------|-----------|--|---------|---------|------------------|-------|
| Supply Voltage                 | $V_{CC}$  |  | 2.5     | 3.3     | 5.25             | V     |
| Operating Temperature Range    | $T_{EP}$  | Exposed Paddle                                 | -40     |         | +105             | °C    |
| RF Frequency Range             | $f_{RF}$  | 75Ω  | 0.005   |         | 1.8              | GHz   |
|                                |           | 50Ω  | 0.005   |         | 10               |       |
| Maximum Operating Input Power  | $P_{MAX}$ | Insertion Loss State<br>$Z_S = Z_L = 50\Omega$ |         |         | See Figure 3 [a] | dBm   |
| Port Impedance (RFC, RF1, RF2) | $Z_{RF}$  | 75Ω System                                     |         | 75      |                  | Ω     |
|                                |           | 50Ω System                                     |         | 50      |                  |       |

a. In a 50Ω system, dBmV = dBm [50Ω] + 47. In a 75Ω system, dBmV = dBm [75Ω] + 48.75.

**Figure 3. Maximum Operating RF Input Power ( $Z_S = Z_L = 50\Omega$ )**



## General Specifications

**Table 4. General Specifications**

See F2976 Typical Application Circuit. Specifications apply when operated with  $V_{CC} = +3.3V$ ,  $T_{EP} = +25^{\circ}C$ , LS = HIGH, single tone signal applied at RF1 or RF2 and measured at RFC, unless otherwise noted.

| Parameter                            | Symbol              | Condition  | Minimum        | Typical | Maximum                    | Units   |
|--------------------------------------|---------------------|--|----------------|---------|----------------------------|---------|
| Logic Input High Threshold           | $V_{IH}$            | $V_{CTL}$ , LS pins  | 1.17 [b]       |         | Lower of ( $V_{CC}$ , 3.6) | V       |
| Logic Input Low Threshold            | $V_{IL}$            | $V_{CTL}$ , LS pins  | -0.3           |         | 0.6                        | V       |
| Logic Current                        | $I_{IH}$ , $I_{IL}$ | $V_{CTL}$ , LS pins (each pin)   | <b>-10</b> [a] |         | <b>+10</b>                 | $\mu A$ |
| DC Current ( $V_{CC}$ )              | $I_{CC}$            |  |                | 80      | <b>150</b>                 | $\mu A$ |
| Switching Rate                       | $SW_{RATE}$         |  |                |         | 25                         | kHz     |
| Maximum Video Feed-Through, RFC Port | $VID_{FT}$          | Peak transient during switching. $Z_S = Z_L = 75\Omega$ . Measured with 20ns rise time, 0V to 3.3V (3.3V to 0V) control pulse applied to $V_{CTL}$ . |                | 5       |                            | mVp-p   |
| Switching Time [c]                   | $SW_{TIME}$         | 50% $V_{CTL}$ to 90% or 10% RF   |                | 1.5     | 3                          | $\mu s$ |

- Items in min/max columns in **bold italics** are guaranteed by test.
- Items in min/max columns that are not bold italics are guaranteed by design characterization.
- Measured at  $f_{RF} = 1GHz$ .

## Electrical Characteristics

**Table 5. Electrical Characteristics - 75Ω SPECIFICATION**

See F2976 75Ω Application Circuit. Specifications apply when operated with  $V_{CC} = +3.3V$ ,  $T_{EP} = +25^{\circ}C$ .  $Z_S = Z_L = 75\Omega$ , LS = HIGH, single tone signal applied at RF1 or RF2 and measured at RFC, EVKit trace and connector losses are de-embedded, unless otherwise noted.

| Parameter  | Symbol | Condition                              | Minimum | Typical | Maximum  | Units |
|--|--------|--|---------|---------|----------|-------|
| Insertion Loss (RFC to RF1, RF2)                       | IL     | $f_{RF} = 5MHz$                        |         | 0.20    |          | dB    |
|  |        | $5MHz < f_{RF} \leq 204MHz$            |         | 0.23    | 0.43 [b] |       |
|  |        | $204MHz < f_{RF} \leq 1.2GHz$          |         | 0.32    | 0.52     |       |
|  |        | $1.2GHz < f_{RF} \leq 1.8GHz$          |         | 0.34    | 0.54     |       |
| Isolation (All Paths)                                  | ISO1   | $f_{RF} = 5MHz$                        |         | 77      |          | dB    |
|  |        | $5MHz < f_{RF} \leq 204MHz$            |         | 60      |          |       |
|  |        | $204MHz < f_{RF} \leq 1.2GHz$          |         | 44      |          |       |
|  |        | $1.2GHz < f_{RF} \leq 1.8GHz$          |         | 40      |          |       |
| Return Loss (RFC, RF1, RF2)<br>(Insertion Loss States) | RL     | $f_{RF} = 5MHz$                        |         | 35      |          | dB    |
|  |        | $5MHz < f_{RF} \leq 204MHz$            |         | 30      |          |       |
|  |        | $204MHz < f_{RF} \leq 1.2GHz$          |         | 17      |          |       |
|  |        | $1.2GHz < f_{RF} \leq 1.8GHz$          |         | 16      |          |       |
| 2 <sup>nd</sup> Harmonic                               | H2     | $f_{IN} = 27MHz$ $P_{OUT} = 20dBm$ [c] |         | -80     | -70      | dBc   |
|  |        | $f_{IN} = 204MHz$ $P_{OUT} = 20dBm$    |         | -100    | -90      |       |
|  |        | $f_{IN} = 800MHz$ $P_{OUT} = 20dBm$    |         | -120    | -110     |       |
| 3 <sup>rd</sup> Harmonic                               | H3     | $f_{IN} = 17MHz$ $P_{OUT} = 20dBm$     |         | -95     | -80      | dBc   |
|  |        | $f_{IN} = 204MHz$ $P_{OUT} = 20dBm$    |         | -120    | -105     |       |
|  |        | $f_{IN} = 800MHz$ $P_{OUT} = 20dBm$    |         | -115    | -100     |       |
| Input 0.1dB Compression Point [d]<br>(RFC to RF1, RF2) | P0.1dB | $f_{RF} = 5MHz$                        |         | 37      |          | dBm   |
|  |        | $f_{RF} = 204MHz$                      |         | 37      |          |       |
|  |        | $f_{RF} = 1.8GHz$                      |         | 38      |          |       |
| Composite Second Order                                 | CSO    | 41dBmV / channel                       |         | >100    |          | dBc   |
| Composite Triple Beat                                  | CTB    | 137 channels [e]                       |         | >100    |          |       |

- Items in min/max columns in **bold italics** are guaranteed by test.
- Items in min/max columns that are not bold italics are guaranteed by design characterization.
- $dBmV = dBm [75\Omega] + 48.75$ .
- The input 0.1dB compression point is a linearity figure of merit. Refer to Figure 3 for the maximum operating RF input power levels.
- Total power =  $-7.75 dBm [75\Omega] + 10 \cdot \log(137) = +13.62 dBm [75\Omega]$ .

## Electrical Characteristics

**Table 6. Electrical Characteristics - 50Ω SPECIFICATION**

See F2976 50Ω Application Circuit. Specifications apply when operated with  $V_{CC} = +3.3V$ ,  $T_{EP} = +25^{\circ}C$ .  $Z_S = Z_L = 50\Omega$ , LS = HIGH, single tone signal applied at RF1 or RF2 and measured at RFC, EVKit trace and connector losses are de-embedded, unless otherwise noted.

| Parameter  | Symbol | Condition                     | Minimum | Typical | Maximum         | Units |
|--|--------|-------------------------------|---------|---------|-----------------|-------|
| Insertion Loss<br>(RFC to RF1, RF2)                    | IL     | $f_{RF} = 5MHz$               |         | 0.25    | 0.45 [b]        | dB    |
|  |        | $5MHz < f_{RF} \leq 1GHz$     |         | 0.33    | 0.53            |       |
|  |        | $1GHz < f_{RF} \leq 2GHz$ [c] |         | 0.36    | <b>0.56</b> [a] |       |
|  |        | $2GHz < f_{RF} \leq 3GHz$     |         | 0.40    |                 |       |
|  |        | $3GHz < f_{RF} \leq 6GHz$     |         | 0.45    |                 |       |
|  |        | $6GHz < f_{RF} \leq 8GHz$     |         | 0.55    |                 |       |
|  |        | $8GHz < f_{RF} \leq 9GHz$     |         | 0.65    |                 |       |
|  |        | $9GHz < f_{RF} \leq 10GHz$    |         | 0.80    |                 |       |
| Isolation<br>(RFC to RF1, RF2)                         | ISO1   | $5MHz < f_{RF} \leq 1GHz$     | 43      | 48      |                 | dB    |
|  |        | $1GHz < f_{RF} \leq 2GHz$     | 36      | 42      |                 |       |
|  |        | $2GHz < f_{RF} \leq 3GHz$     | 31      | 37      |                 |       |
|  |        | $3GHz < f_{RF} \leq 6GHz$     |         | 27      |                 |       |
|  |        | $6GHz < f_{RF} \leq 8GHz$     |         | 22      |                 |       |
|  |        | $8GHz < f_{RF} \leq 10GHz$    |         | 18      |                 |       |
| Isolation<br>(RF1 to RF2, RF2 to RF1)                  | ISO2   | $5MHz < f_{RF} \leq 1GHz$     | 40      | 45      |                 | dB    |
|  |        | $1GHz < f_{RF} \leq 2GHz$     | 33      | 38      |                 |       |
|  |        | $2GHz < f_{RF} \leq 3GHz$     | 29      | 34      |                 |       |
|  |        | $3GHz < f_{RF} \leq 6GHz$     |         | 26      |                 |       |
|  |        | $6GHz < f_{RF} \leq 8GHz$     |         | 21      |                 |       |
|  |        | $8GHz < f_{RF} \leq 10GHz$    |         | 18      |                 |       |
| Return Loss (RFC, RF1, RF2)<br>(Insertion loss states) | RL     | $5MHz < f_{RF} \leq 1GHz$     |         | 28      |                 | dB    |
|  |        | $1GHz < f_{RF} \leq 2GHz$     |         | 26      |                 |       |
|  |        | $2GHz < f_{RF} \leq 3GHz$     |         | 26      |                 |       |
|  |        | $3GHz < f_{RF} \leq 6GHz$     |         | 25      |                 |       |
|  |        | $6GHz < f_{RF} \leq 8GHz$     |         | 23      |                 |       |
|  |        | $8GHz < f_{RF} \leq 9GHz$     |         | 18      |                 |       |
|  |        | $9GHz < f_{RF} \leq 10GHz$    |         | 16      |                 |       |

- Items in min/max columns in **bold italics** are guaranteed by test.
- Items in min/max columns that are not bold italics are guaranteed by design characterization.
- Minimum or maximum specification guaranteed by test at 2GHz and by design characterization over the whole frequency range.

## Electrical Characteristics

**Table 7. Electrical Characteristics - 50Ω SPECIFICATION**

See F2976 50Ω Application Circuit. Specifications apply when operated with  $V_{CC} = +3.3V$ ,  $T_{EP} = +25^{\circ}C$ .  $Z_S = Z_L = 50\Omega$ , LS = HIGH, single tone signal applied at RF1 or RF2 and measured at RFC, EVKit trace and connector losses are de-embedded, unless otherwise noted.

| Parameter                            | Symbol      | Condition   | Minimum | Typical | Maximum | Units |
|--------------------------------------|-------------|---|---------|---------|---------|-------|
| Input 0.1dB Compression [a]          | P0.1dB      | $f_{RF} = 2.4GHz$   |         | 40      |         | dBm   |
|                                      |             | $f_{RF} = 6.0GHz$   |         | 40      |         |       |
|                                      |             | $f_{RF} = 8.0GHz$   |         | 40      |         |       |
| Input IP3<br>(RF1, RF2 to RFC)       | IIP3        | $f_{RF} = 2.4GHz$<br>$P_{IN} = +24dBm/$ tone<br>100MHz spacing                        |         | 77      |         | dBm   |
| Input IP2<br>(RF1, RF2 to RFC)       | IIP2        | $f_1 = 700MHz$<br>$f_2 = 1.7GHz$<br>$P_{IN} = +24dBm/$ tone<br>Measure 2.4GHz product |         | 125     |         | dBm   |
|                                      |             | $f_1 = 2.4GHz$<br>$f_2 = 3.5GHz$<br>$P_{IN} = +24dBm/$ tone<br>Measure 5.9GHz product |         | 120     |         |       |
| Second Harmonic<br>(RF1, RF2 to RFC) | H2          | $f_{IN} = 2.4GHz$ , $P_{IN} = +24dBm$   |         | -100    | -90 [b] | dBc   |
|                                      |             | $f_{IN} = 5.9GHz$ , $P_{IN} = +24dBm$   |         | -90     | -80     |       |
| Third Harmonic<br>(RF1, RF2 to RFC)  | H3          | $f_{IN} = 2.4GHz$ , $P_{IN} = +24dBm$   |         | -110    | -95     | dBc   |
|                                      |             | $f_{IN} = 5.9GHz$ , $P_{IN} = +24dBm$   |         | -100    | -85     |       |
| Spurious Output<br>(No RF Applied)   | $P_{SPUR1}$ | $f_{OUT} \geq 5MHz$<br>All unused ports terminated                                    |         | -133    |         | dBm   |
|                                      | $P_{SPUR2}$ | $f_{OUT} < 5 MHz$<br>All unused ports terminated                                      |         | -120    |         |       |

- Items in min/max columns in **bold italics** are guaranteed by test.
- Items in min/max columns that are not bold italics are guaranteed by design characterization.
- The input 0.1dB compression point is a linearity figure of merit. Refer to Figure 3 for the maximum RF operating input power levels.



## Thermal Characteristics

**Table 8. Package Thermal Characteristics**

| Parameter  | Symbol             | Value | Units |
|--|--------------------|-------|-------|
| Junction to Ambient Thermal Resistance   | $\theta_{JA}$      | 102   | °C/W  |
| Junction to Case Thermal Resistance<br>(Case is defined as the exposed paddle) | $\theta_{JC\_BOT}$ | 56    | °C/W  |
| Moisture Sensitivity Rating (Per J-STD-020)                                    |                    | MSL 1 |       |


## Typical Operating Conditions (TOCs)

Unless otherwise noted:


- $V_{CC} = +3.3V$
- LS = HIGH
- $Z_L = Z_S = 75\Omega$
- $Z_L = Z_S = 50\Omega$
- All temperatures are referenced to the exposed paddle
- Evaluation Kit traces and connector losses are de-embedded

## Typical Performance Characteristics - 75Ω Performance


**Figure 4. RF1 to RFC Insertion Loss**




**Figure 5. RF2 to RFC Insertion Loss**




**Figure 6. RF1 to RFC Isolation [RF2 On State]**




**Figure 7. RF2 to RFC Isolation [RF1 On State]**



**Figure 8. RF1 to RF2 Isolation [RF1 On State]**



**Figure 9. RF1 to RF2 Isolation [RF2 On State]**



## Typical Performance Characteristics - 75Ω Performance

Figure 10. RFC Return Loss [RF1 On State]




Figure 11. RFC Return Loss [RF2 On State]




Figure 12. RF1 Return Loss [RF1 On State]





Figure 13. RF2 Return Loss [RF2 On State]



## Typical Performance Characteristics - 50Ω Performance

Figure 14. RF1 to RFC Insertion Loss




Figure 15. RF2 to RFC Insertion Loss




Figure 16. RF1 to RFC Isolation [RF2 On State]




Figure 17. RF2 to RFC Isolation [RF1 On State]




Figure 18. RF1 to RF2 Isolation [RF1 On State]





Figure 19. RF1 to RF2 Isolation [RF2 On State]



## Typical Performance Characteristics - 50Ω Performance

Figure 20. RFC Return Loss [RF1 On State]




Figure 21. RFC Return Loss [RF2 On State]




Figure 22. RF1 Return Loss [RF1 On State]




Figure 23. RF2 Return Loss [RF2 On State]




Figure 24. Switching Time [Isolation to Insertion Loss State]





Figure 25. Switching Time [Insertion Loss to Isolation State]



## Control Mode

**Table 9. Switch Control Truth Table**

| V <sub>CTL</sub> (pin 10) | LS (pin 11) | Switch State                    |
|---------------------------|-------------|---------------------------------|
| HIGH                      | HIGH        | RFC to RF2 Insertion Loss State |
| LOW                       | HIGH        | RFC to RF1 Insertion Loss State |
| HIGH                      | LOW         | RFC to RF1 Insertion Loss State |
| LOW                       | LOW         | RFC to RF2 Insertion Loss State |

## Application Information


### Power Supplies

A common V<sub>CC</sub> power supply should be used for all pins requiring DC power. All supply pins should be bypassed with external capacitors to minimize noise and fast transients. Supply noise can degrade noise figure and fast transients can trigger ESD clamps and cause them to fail. Supply voltage change or transients should have a slew rate smaller than 1V / 20μs. In addition, all control pins should remain at 0V (+/-0.3V) while the supply voltage ramps up or while it returns to zero.

### Control Pin Interface

If control signal integrity is a concern and clean signals cannot be guaranteed due to overshoot, undershoot, ringing, etc., the following circuit at the input of each control pin is recommended. This applies to control pins 7 and 8 as shown below.

**Figure 26. Control Pin Interface Schematic**



## 75Ω Evaluation Kit Picture

Figure 27. Top View (75Ω)





Figure 28. Bottom View (75Ω)



## 50Ω Evaluation Kit Picture

Figure 29. Top View (50Ω)




Figure 30. Bottom View (50Ω)








## 50Ω Evaluation Kit / Applications Circuit

Figure 32. Electrical Schematic (50Ω)



Note: The F2976 50Ω EVKit reuses the 50Ω PCB from the F2972 and requires pin 1 of the F2976 to be rotated by 90 degrees clockwise from the F2972 PCB pin 1 marking, for proper assembly.

**Table 10. 75Ω Bill of Material (BOM)**

| Part Reference | QTY | Description                                    | Manufacturer Part # | Manufacturer |
|----------------|-----|--|---------------------|--------------|
| C1             | 1   | 0.1μF ±10%, 16V, X7R, Ceramic Capacitor (0402) | GRM155R71C104KA88D  | Murata       |
| C2, C4         | 2   | 100pF ±5% 50V, C0G, Ceramic Capacitor (0402)   | GRM1555C1H101JA01D  | Murata       |
| C3             | 1   | 0.01μF ±5% 50V, X7R, Ceramic Capacitor (0603)  | GRM188R71H103JA01D  | Murata       |
| R2, R3         | 2   | 100Ω 1/10W, Resistor (0402)                    | ERJ-2RKF1000X       | Panasonic    |
| J1 – J5        | 5   | F-Type Edge Mount                              | 222181              | Amphenol RF  |
| J6             | 1   | Conn Header Vert 5x1 Pos Gold                  | 68002-205HLF        | Amphenol FCI |
| U1             | 1   | SP2T Switch 2mm x 2mm 12-pin TQFN              | F2976NEGK           | IDT          |
|                | 1   | Printed Circuit Board <sup>[a]</sup>           | F2972 75Ω PCB       | IDT          |

- a. The F2976 75Ω EVKit reuses the 75Ω PCB from the F2972 and requires pin 1 of the F2976 to be rotated by 90 degrees clockwise from the F2972 PCB pin 1 marking, for proper assembly.

**Table 11. 50Ω Bill of Material (BOM)**

| Part Reference          | QTY | Description                          | Manufacturer Part # | Manufacturer       |
|-------------------------|-----|--------------------------------------|---------------------|--------------------|
| C1 – C7                 | 0   | Not Installed (0402)                 |                     |                    |
| R1– R3                  | 3   | 0Ω 1/10 W, Resistor (0402)           | ERJ-2GE0R00X        | Panasonic          |
| J1 – J5                 | 5   | SMA Edge Mount                       | 142-0761-881        | Cinch Connectivity |
| J6                      | 1   | Conn Header 10 Pos 0.100" Str 15 Au  | 68602-210HLF        | Amphenol FCI       |
| TP1, TP2, TP3, TP4, TP5 | 0   | Not Installed Test Point Loop        |                     |                    |
| U1                      | 1   | SP2T Switch 2mm x 2mm 12-pin TQFN    | F2976NEGK           | IDT                |
|                         | 1   | Printed Circuit Board <sup>[a]</sup> | F2972 50Ω PCB       | IDT                |

- a. The F2976 50Ω EVKit reuses the 50Ω PCB from the F2972 and requires pin 1 of the F2976 to be rotated by 90 degrees clockwise from the F2972 PCB pin 1 marking, for proper assembly.

## Evaluation Kit (EVKit) Operation

### External Supply Setup

Set up a  $V_{CC}$  power supply in the voltage range of 2.5V to 5.25V with the power supply output disabled.

For the 75 $\Omega$  EVKit, connect the disabled  $V_{CC}$  supply connection to J6 pin 2 and GND to J6 pins 1 or 5.

For the 50 $\Omega$  EVKit, connect the disabled  $V_{CC}$  supply connection to J6 pin 3 and GND to J6 pin 1, 2, 4, 6, 8, 9, or 10.

### Logic Control Setup

With the logic control lines disabled set the HIGH and LOW logic levels to satisfy the levels stated in the electrical specifications table.

For the 75 $\Omega$  EVKit, connect the disabled logic control lines to J6 EN (pin 3) and  $V_{CTL}$  (pin 4).

For the 50 $\Omega$  EVKit, connect the disabled logic control lines to J6 EN / LS (pin 5) and  $V_{CTL}$  (pin 7).

See Table 9 for the logic truth table.

### Turn On Procedure

Setup the supplies and EVKit as noted in the External Supply Setup and Logic Control Setup sections above.

Enable the  $V_{CC}$  supply.

Enable the logic control signals.

Set the logic settings to achieve the desired Table 9 configuration. Note that external control logic should not be applied without  $V_{CC}$  being present.


### Turn Off Procedure

Set the logic control pins to a logic LOW.

Disable the  $V_{CC}$  supply.


Package Drawings

Figure 33. Package Outline Drawing NEG12 PSC-4642




# Recommended Land Pattern

Figure 34. Recommended Land Pattern NEG12 PSC-4642



## Marking Diagram



Line 1 - 2976 = Abbreviated part number.  
 Line 2 - Y = Year code.  
 Line 2 - W = Work week code.  
 Line 2 - \*\* = Sequential alpha for lot traceability.

## Ordering Information

| Orderable Part Number | Package                      | MSL Rating | Shipping Packaging | Temperature     |
|-----------------------|------------------------------|------------|--------------------|-----------------|
| F2976NEGK             | 2mm x 2mm x 0.5mm 12-VFQFP-N | MSL1       | Cut Reel           | -40°C to +105°C |
| F2976NEGK8            | 2mm x 2mm x 0.5mm 12-VFQFP-N | MSL1       | Tape and Reel      | -40°C to +105°C |
| F2976EVBI-75OHM       | 75Ω Evaluation Board         |            |                    |                 |
| F2976EVBI-50OHM       | 50Ω Evaluation Board         |            |                    |                 |

## Revision History

| Revision | Revision Date | Description of Change |
|----------|---------------|-----------------------|
| Rev 0    | 2017-Apr-19   | Initial Release       |



## IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Rev.1.0 Mar 2020)

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:  
[www.renesas.com/contact/](http://www.renesas.com/contact/)

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renesas Electronics:](#)

[F2976NEGK](#) [F2976EVBI-50OHM](#) [F2976EVBI-75OHM](#) [F2976NEGK8](#)