







SCT616/816 Series 16A SCRs

Circuit Diagram





Description

With high ability to withstand the shock loading of large current, SCT616/816 series of silicon controlled rectifiers provide high dv/dt rate with strong resistance to electromagnetic interference. They are especially recommended for use on solid state relay, motorcycle, power charger, T-tools etc.

Maximum Ratings:

Characteristics	Symbol	Condition	Max.	Units
Storage junction temperature range	TJ	-	-40 to +125	°C
Operating junction temperature range	T _{stg}	-	-40 to +150	°C
Repetitive peak off-state voltage	V_{DRM}	-	600/800	V
Repetitive peak reverse voltage	V_{RRM}	-	600/800	V
Non repetitive peak off-state voltage	V _{DSM}	-	V _{DRM} +100	V
Non repetitive peak reverse voltage	V _{RSM}	-	V _{RRM} +100	V
RMS on-state current	I _(TRMS)	TO-220B(Non-Ins)(T _C =110℃)	16	А
Non repetitive surge peak on-state current (tp=10ms)	I _{TSM}	-	180	А
I ² t value for fusing (tp=10ms)	I ² t	-	162	A ² s
Critical rate of rise of on-state current $(I_G=2\times I_{GT})$	dI/dt	-	50	A/µs
Peak gate current	I _{GM}	-	4	А
Average gate power dissipation	P _{G(AV)}	-	1	W
Peak gate power	P _{GM}	-	5	W

[•] http://www.smc-diodes.com - sales@ smc-diodes.com •







Electrical Characteristics(Tj=25℃ unless otherwise specified)

Symbol	Test Condition		Unit		
	rest Condition	MIN.	TYP.	MAX.	Offic
I _{GT}	· V _D =12V R _L =33Ω	-	1	15	mA
V_{GT}	VD-12V NL-3322	-	1	1.3	V
V_{GD}	$V_D=V_{DRM}T_j=125^{\circ}C$ R _L =3.3K Ω	0.2	-	-	V
lι	I _G =1.2I _{GT}	-	-	60	mA
I _H	I _T =500mA	-	-	50	mA
dV/dt	V _D =2/3V _{DRM} Gate Open T _j =125°C	200	-	-	V/µs


Static Characteristics

Symbol	Condition	Max.	Units
V_{TM}	I _T =32A tp=380μs,Tj=25℃	1.55	V
I _{DRM}	V _D =V _{DRM} V _R =V _{RRM} , Tj=25°C	5	μA
I _{RRM}	V _D =V _{DRM} V _R =V _{RRM} , Tj=125°C	2	mA

Thermal Resistances

Symbol	Cond	dition	Value	Units
Rth(j-c)	Junction to case(AC)	TO-220B(Non-Ins)	1.1	°C/W

Ordering Information



Device	Package	Shipping	
SCT616/816 Series	TO-220B(Non-Ins)	50pcs/ Tube	


- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •







Marking Diagram



Where XXXXX is YYWWL


 SCT616B
 = Part name

 YY
 = Year

 WW
 = Week

 L
 = Lot Number

Mechanical Dimensions TO-220B(Non-Ins)



SYMBOL	Millimeters			Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	4.40		4.60	0.17		0.18
В	0.61		0.88	0.02		0.03
С	0.46		0.70	0.01		0.02
C2	1.21		1.32	0.04		0.05
C3	2.40		2.72	0.09		0.10
D	8.60		9.70	0.33		0.38
E	9.60		10.4	0.37		0.40
F	6.20		6.60	0.24		0.26
G		2.54			0.1	
Н	28.0		29.8	1.10		1.17
L1		3.75			0.14	
L2	1.14		1.70	0.04		0.06
L3	2.65		2.95	0.10		0.11
V1		45°			45°	

Ratings and Characteristics Curves

FIG.1 Maximum power dissipation versus RMS on-state current





FIG.2: RMS on-state current versus case temperature



- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •







FIG.3: Surge peak on-state current versus number of cycles




FIG.4: On-state characteristics (maximum values)




FIG.5: Non-repetitive surge peak on-state current for a sinusoidal pulse with width tp<10ms, and corresponging value of f t (dl/dt<50A/µs)





FIG.6: Relative variations of gate trigger current, holding current and latching current versus junction temperature



- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •







DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Diode Solutions sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall SMC Diode Solutions be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Diode Solution assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall SMC Diode Solutions be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Diode Solutions.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Diode Solutions.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations..