

- [▶ 8-bit PIC® Microcontrollers](#)
- [▶ 16-bit PIC®MCUs & dsPIC®DSCs](#)
- [▶ 32-bit PIC Microcontrollers](#)
- [▶ Touch and Input Sensing](#)
- [▶ Analog](#)
- [▶ Interface](#)
- [▶ Data and Video Transceivers](#)
- [▶ PC Systems & I/O Controllers](#)
- [▶ Memory](#)
- [▶ Wi-Fi, Bluetooth, RF and Security](#)
- [▶ Development Tools](#)
- [▶ Automotive Grade](#)
- [▶ Discount Parts](#)

Search



 **CART / CHECKOUT (0)**

Advanced Search

Found 1 matches total.

Items 1 to 1 displayed.

Part Number ARD00514 - MCP19035 High Voltage Buck Converter Eval Board



The MCP19035 600 kHz Synchronous Buck Converter Controller Board is a compact, highly efficient, step-down voltage converter that converts the input voltage rail (typically 24V) to a regulated 5V output voltage. The maximum output current for this demo board is 5A. [More Info >>](#)

Standard Pricing:

| Quantity | USD per Unit |
|----------|--------------|
| 1+ | 45.99 |

In stock (processes immediately): 26

When can I get more?

Quantity:

ADD TO CART

Page 1

FEEDBACK

GET VOLUME PRICING

UPGRADE TO A BUSINESS ACCOUNT

FREE PROGRAMMED SAMPLES

 WITH AN ORDER TODAY

SMSC PRODUCTS

NOW AVAILABLE

GET CONNECTED EMBEDDED WIRELESS

 **WiFi** **Bluetooth**