





# MLF1005VR33JT000

Applications		Commercial Grade
Feature		Multilayer
		Magnetic Shield
		Ferrite Core
Series	MLF Series / MLF1005 Type	
Status	PROD	



Size	
Length(L)	1.00mm +/-0.05mm
Width(W)	0.50mm +/-0.05mm
Thickness(T)	0.50mm +/-0.05mm
Recommended Land Pattern (A)	0.50mm Nom.
Recommended Land Pattern (B)	0.40mm Nom.
Recommended Land Pattern (C)	0.50mm Nom.


Electrical Characteristics	
Inductance	330nH +/-5% at 25MHz
Rated Current	140mA
Self-Resonant Frequency [Min.]	230MHz
Self-Resonant Frequency [Typ.]	380MHz
Q [Min.]	15 at 25MHz
Q [Typ.]	30 at 25MHz
DC Resistance [Nom.]	800mΩ
DC Resistance [Max.]	1.05Ω

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000Pcs Min.
Weight	0.0012g


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# MLF1005VR33JT000


**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




**MLF1005VR33JT000**



**MLF1005VR33JT000**



**MLF1005VR33JT000**






**MLF1005VR33JT000**

- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.

# MLF1005VR33JT000

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.  
•All specifications are subject to change without notice.