

# **10BASE-T/100BASE-TX Physical Layer Transceiver**

#### Features

- Single-Chip 10BASE-T/100BASE-TX IEEE 802.3 Compliant Ethernet Transceiver
- MII Interface Support (KSZ8091MNX)
- RMII v1.2 interface support with a 50 MHz reference clock output to MAC, and an option to input a 50 MHz reference clock (KSZ8091RNB)
- Back-to-Back Mode Support for a 100 Mbps Copper Repeater
- MDC/MDIO Management Interface for PHY Register Configuration
- Programmable Interrupt Output
- LED Outputs for Link and Activity Status Indication, plus speed indication for KSZ8091RNB
- On-Chip Termination Resistors for the Differential Pairs
- Baseline Wander Correction
- HP Auto MDI/MDI-X to Reliably Detect and Correct Straight-Through and Crossover Cable Connections with Disable and Enable Option
- Auto-Negotiation to Automatically Select the Highest Link-Up Speed (10/100 Mbps) and Duplex (Half/Full)
- Energy Efficient Ethernet (EEE) Support with Low-Power Idle (LPI) Mode and Clock Stoppage (MII Version Only) for 100BASE-TX and Transmit Amplitude Reduction with 10BASE-Te Option
- Wake-on-LAN (WOL) Support with Either Magic Packet, Link Status Change, or Robust Custom-Packet Detection
- HBM ESD Rating (6 kV)
- · Power-Down and Power-Saving Modes
- LinkMD<sup>®</sup> TDR-Based Cable Diagnostics to Identify Faulty Copper Cabling
- Parametric NAND Tree Support for Fault Detection Between Chip I/Os and the Board
- · Loopback Modes for Diagnostics
- Single 3.3V Power Supply with  $V_{DD}$  I/O Options for 1.8V, 2.5V, or 3.3V
- Built-In 1.2V Regulator for Core
- Available in 32-pin 5 mm x 5 mm QFN Package

#### **Target Applications**

- Game Consoles
- IP Phones
- IP Set-Top Boxes
- IP TVs
- LOM
- Printers

## TO OUR VALUED CUSTOMERS

It is our intention to provide our valued customers with the best documentation possible to ensure successful use of your Microchip products. To this end, we will continue to improve our publications to better suit your needs. Our publications will be refined and enhanced as new volumes and updates are introduced.

If you have any questions or comments regarding this publication, please contact the Marketing Communications Department via E-mail at docerrors@microchip.com. We welcome your feedback.

#### **Most Current Data Sheet**

To obtain the most up-to-date version of this data sheet, please register at our Worldwide Web site at:

#### http://www.microchip.com

You can determine the version of a data sheet by examining its literature number found on the bottom outside corner of any page. The last character of the literature number is the version number, (e.g., DS3000000A is version A of document DS30000000).

#### Errata

An errata sheet, describing minor operational differences from the data sheet and recommended workarounds, may exist for current devices. As device/documentation issues become known to us, we will publish an errata sheet. The errata will specify the revision of silicon and revision of document to which it applies.

To determine if an errata sheet exists for a particular device, please check with one of the following:

- Microchip's Worldwide Web site; http://www.microchip.com
- Your local Microchip sales office (see last page)

When contacting a sales office, please specify which device, revision of silicon and data sheet (include -literature number) you are using.

#### **Customer Notification System**

Register on our web site at www.microchip.com to receive the most current information on all of our products.

### **Table of Contents**

1.0 Introduction	4
2.0 Pin Description and Configuration	. 15
4.0 Register Descriptions	. 40
5.0 Operational Characteristics	. 57
6.0 Electrical Characteristics	58
7.0 Timing Diagrams	. 60
8.0 Reset Circuit	. 69
9.0 Reference Circuits — LED Strap-In Pins	. 70
10.0 Reference Clock - Connection and Selection	
11.0 Magnetic - Connection and Selection	. 72
11.0 Magnetic - Connection and Selection	. 74
Appendix A: Data Sheet Revision History	. 75
The Microchip Web Site	. 76
Customer Change Notification Service	
Customer Support	. 76
Product Identification System	. 77

<sup>© 2016</sup> Microchip Technology Inc.

# 1.0 INTRODUCTION

### 1.1 General Description

The KSZ8091 is a single-supply 10BASE-T/100BASE-TX Ethernet physical-layer transceiver for transmission and reception of data over standard CAT-5 unshielded twisted pair (UTP) cable.


The KSZ8091 is a highly integrated PHY solution. It reduces board cost and simplifies board layout by using on-chip termination resistors for the differential pairs, by integrating a low-noise regulator to supply the 1.2V core, and by offering a flexible 1.8/2.5/3.3V digital I/O interface.

The KSZ8091MNX offers the Media Independent Interface (MII) and the KSZ8091RNB offers the Reduced Media Independent Interface (RMII) for direct connection with MII/RMII-compliant Ethernet MAC processors and switches.

Energy Efficient Ethernet (EEE) provides further power saving during idle traffic periods and Wake-on-LAN (WOL) provides a mechanism for the KSZ8091 to wake up a system that is in standby power mode.

The KSZ8091 provides diagnostic features to facilitate system bring-up and debugging in production testing and in product deployment. Parametric NAND tree support enables fault detection between KSZ8091 I/Os and the board. LinkMD<sup>®</sup> TDR-based cable diagnostics identify faulty copper cabling.

The KSZ8091MNX and KSZ8091RNB are available in 32-pin, lead-free QFN packages.



#### FIGURE 1-1: SYSTEM BLOCK DIAGRAM

### 2.0 PIN DESCRIPTION AND CONFIGURATION

FIGURE 2-1: 32-PIN 5 MM X 5 MM QFN ASSIGNMENT, KSZ8091MNX (TOP VIEW)




TABLE 2-1:	SIGNALS - KSZ8091MNX
------------	----------------------

Pin Number	Pin Name	Type Note 2-1	Description	
1	GND	GND	Ground.	
2	VDD_1.2	Р	1.2V core $V_{DD}$ (power supplied by KSZ8091MNX) Decouple with 2.2 $\mu$ F and 0.1 $\mu$ F capacitors to ground.	
3	VDDA_3.3	Р	3.3V analog V <sub>DD</sub>	
4	RXM	I/O	Physical receive or transmit signal (– differential)	
5	RXP	I/O	Physical receive or transmit signal (+ differential)	

© 2016 Microchip Technology Inc.

### TABLE 2-1: SIGNALS - KSZ8091MNX (CONTINUED)

Pin Number	Pin Name	Type Note 2-1	Description	
6	ТХМ	I/O	Physical transmit or receive signal (– differential)	
7	TXP	I/O	Physical transmit or receive signal (+ differential)	
8	хо	0	Crystal feedback for 25 MHz crystal This pin is a no connect if an oscillator or external clock source is used.	
9	XI	I	Crystal/Oscillator/External Clock input 25 MHz ±50 ppm	
10	REXT	I	Set PHY transmit output current Connect a 6.49 $k\Omega$ resistor to ground on this pin.	
11	MDIO	lpu/ Opu	Management Interface (MII) Data I/O This pin has a weak pull-up, is open-drain, and requires an external 1.0 $k\Omega$ pull-up resistor.	
12	MDC	lpu	Management Interface (MII) Clock input This clock pin is synchronous to the MDIO data pin.	
13	RXD3/ PHYAD0	lpu/O	MII mode: MII Receive Data Output[3] (Note 2-2) Config mode: The pull-up/pull-down value is latched as PHYADDR[0] at the de assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
14	RXD2/ PHYAD1	lpd/O	MII mode: MII Receive Data Output[2] (Note 2-2) Config mode: The pull-up/pull-down value is latched as PHYADDR[1] at the deassertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
15	RXD1/ PHYAD2	lpd/O	MII mode: MII Receive Data Output[1] (Note 2-2) Config mode: The pull-up/pull-down value is latched as PHYADDR[2] at the de assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
16	RXD0/ DUPLEX	lpu/O	MII mode: MII Receive Data Output[0] (Note 2-2) Config mode: The pull-up/pull-down value is latched as DUPLEX at the de- assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
17	VDDIO	Р	3.3V, 2.5V, or 1.8V digital V <sub>DD</sub>	
18	RXDV/ CONFIG2	lpd/O	MII mode: MII Receive Data Valid output Config mode: The pull-up/pull-down value is latched as CONFIG2 at the de- assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
19	RXC/ B-CAST_OFF	lpd/O	MII mode: MII Receive Clock output Config mode: The pull-up/pull-down value is latched as B-CAST_OFF at the de assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
20	RXER/ISO	lpd/O	MII mode: MII Receive Error output Config mode: The pull-up/pull-down value is latched as ISOLATE at the de- assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	

Pin Number	Pin Name	Type Note 2-1	Description	
21	INTRP/ PME_N2/ NAND_Tree#	lpu/ Opu	Interrupt output: Programmable interrupt output, with Register 1Bh as the Interrupt Control/Status register, for programming the interrupt conditions and reading the interrupt status. Register 1Fh, bit [9] sets the interrupt output to active low (default) or active high. PME_N output: Programmable PME_N output (pin option 2). When asserted low, this pin signals that a WOL event has occurred. Config mode: The pull-up/pull-down value is latched as NAND Tree# at the deassertion of reset. See the Strap-In Options - KSZ8091MNX section for details. This pin has a weak pull-up and is an open-drain. For Interrupt (when active low) and PME functions, this pin requires an external 1.0 k $\Omega$ pull-up resistor to V <sub>DDIO</sub> (digital V <sub>DD</sub> ).	
22	TXC/ PME_EN	lpd/O	MII mode: MII Transmit Clock output MII back-to-back mode: No connection Config mode: The pull-up/pull-down value is latched as PME_EN at the de- assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
23	TXEN	Ι	MII mode: MII Transmit Enable input	
24	TXD0	I	MII mode: MII Transmit Data Input[0] (Note 2-3)	
25	TXD1	I	MII mode: MII Transmit Data Input[1] (Note 2-3)	
26	TXD2	I	MII mode: MII Transmit Data Input[2] (Note 2-3)	
27	TXD3	I	MII Mode: MII Transmit Data Input[3] (Note 2-3)	
28	COL/ CONFIG0	lpd/O	MII mode: MII Collision Detect output Config mode: The pull-up/pull-down value is latched as CONFIG0 at the de- assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	
29	CRS/ CONFIG1	lpd/O	MII mode: MII Carrier Sense output Config mode: The pull-up/pull-down value is latched as CONFIG1 at the de- assertion of reset. See the Strap-In Options - KSZ8091MNX section for details.	

#### TABLE 2-1: SIGNALS - KSZ8091MNX (CONTINUED)

Pin Number	Pin Name	Type Note 2-1	Description				
			LED output: Programmable LED0 output PME_N Output: Programmable PME_N Output (pin option 1) In this mode, this pin has a weak pull-up, is an open-drain, and requires an external 1.0 k $\Omega$ pull-up resistor to V <sub>DDIO</sub> (digital V <sub>DD</sub> ). Config mode: Latched as auto-negotiation enable (Register 0h, bit [12]) at the de-assertion of reset. See the Strap-In Options - KSZ8091MNX section for details. The LED0 pin is programmable using Register 1Fh bits [5:4], and is defined as follows.				
			LED Mode = [00]				
30	LED0/ PME_N1/	lpu/O	Link/Activity	Pin State	LED Definition		
- 50	NWAYEN	ipu/O	No Link	High	OFF		
			Link	Low	ON		
			Activity	Toggle	Blinking		
			LED Mode = [01]				
			Link	Pin State	LED Definition		
					No Link	High	OFF
			Link	Low	ON		
			LED Mode = [10], [11]: F	Reserved			
31	TXER	lpd	MII mode: MII Transmit Error input For EEE mode, this pin is driven by the EEEMAC to pull up this pin for KSZ8091MNX transmit into the LPI state. For non-EEE mode, this pin is not defined for error transmission from MAC to KSZ8091MNX and can be left as a no connect. For NAND Tree testing, this pin should be pulled high by a pull-up resistor.				
32	RST#	lpu	Chip reset (active low)				
PADDLE	GND	GND	Ground				

**Note 2-1** P = power supply

GND = ground

I = input

O = output

I/O = bi-directional

Ipu = Input with internal pull-up (see Electrical Characteristics for value).

lpd = Input with internal pull-down (see Electrical Characteristics for value).

Ipu/O = Input with internal pull-up (see Electrical Characteristics for value) during power-up/reset; output pin otherwise.

Ipd/O = Input with internal pull-down (see Electrical Characteristics for value) during power-up/reset; output pin otherwise.

Ipu/Opu = Input with internal pull-up (see Electrical Characteristics for value) and output with internal pull-up (see Electrical Characteristics for value).

**Note 2-2** MII RX Mode: The RXD[3:0] bits are synchronous with RXC. When RXDV is asserted, RXD[3:0] presents valid data to the MAC.

**Note 2-3** MII TX Mode: The TXD[3:0] bits are synchronous with TXC. When TXEN is asserted, TXD[3:0] presents valid data from the MAC.

The strap-in pins are latched at the de-assertion of reset. In some systems, the MAC MII receive input pins may drive high/low during power-up or reset, and consequently cause the PHY strap-in pins on the MII signals to be latched to unintended high/low states. In this case, external pull-ups ( $4.7 \text{ k}\Omega$ ) or pull-downs ( $1.0 \text{ k}\Omega$ ) should be added on these PHY strap-in pins to ensure that the intended values are strapped-in correctly.

Pin Number	Pin Name	Type Note 2-4		Description		
15	PHYAD2	lpd/O		latched at de-assertion of reset and is configurable to		
14	PHYAD1 PHYAD0	Ipd/O Ipu/O	any value from 0 to 7 with PHY Address 1 as the default value. PHY Address 0 is assigned by default as the broadcast PHY address, but it can be assigned as a unique PHY address after pull ing the B-CAST_OFF strapping pin high or writing a '1' to Register 16h, bit [9]. PHY Address bits [4:3] are set to 00 by default.			
18	CONFIG2		The CONFIG[2 reset.	2:0] strap-in pins are latched at the de-assertion of		
			CONFIG[2:0]	Mode		
29	CONFIG1	lpd/O	000	MII (default)		
			110	MII back-to-back		
28	CONFIG0		001 – 101, 111	Reserved, not used		
22	PME_EN	lpd/O	PME output for Wake-on-LAN Pull-up = Enable Pull-down (default) = Disable At the de-assertion of reset, this pin value is latched into Register 16h, bit [15].			
20	ISO	lpd/O	Isolate mode Pull-up = Enable Pull-down (default) = Disable At the de-assertion of reset, this pin value is latched into Register 0h bit [10].			
16	DUPLEX	lpu/O	Duplex Mode: Pull-up (default) = Half-duplex Pull-down = Full-duplex At the de-assertion of reset, this pin value is latched into Register 0h Bit [8].			
30	NWAYEN	lpu/O	Nway Auto-Negotiation Enable: Pull-up (default) = Enable auto-negotiation Pull-down = Disable auto-negotiation At the de-assertion of reset, this pin value is latched into Register 0 Bit [12].			
19	B-CAST_OFF	lpd/O	Broadcast Off – for PHY Address 0: Pull-up = PHY Address 0 is set as an unique PHY address Pull-down (default) = PHY Address 0 is set as a broadcast PHY address At the de-assertion of reset, this pin value is latched by the chip.			
21 Note 2-4	NAND_Tree#	lpu/Opu	NAND Tree Mode: Pull-up (default) = Disable Pull-down = Enable At the de-assertion of reset, this pin value is latched by the chip.			

TABLE 2-2:STRAP-IN OPTIONS - KSZ8091MNX

Ipd/O = Input with internal pull-down during power-up/reset; output pin otherwise.

Ipu/Opu = Input with internal pull-up and output with internal pull-up.

© 2016 Microchip Technology Inc.




TABLE 2-3: SIG	NALS - KSZ8091RNB
----------------	-------------------

Pin Number	Pin Name	Type Note 2-1	Description	
1	GND	GND	Ground.	
2	VDD_1.2	Р	1.2V core $V_{DD}$ (power supplied by KSZ8091RNB) Decouple with 2.2 $\mu$ F and 0.1 $\mu$ F capacitors to ground.	
3	VDDA_3.3	Р	3.3V analog V <sub>DD</sub>	
4	RXM	I/O	Physical receive or transmit signal (– differential)	
5	RXP	I/O	Physical receive or transmit signal (+ differential)	
6	TXM	I/O	Physical transmit or receive signal (– differential)	
7	TXP	I/O	Physical transmit or receive signal (+ differential)	
8	хо	0	Crystal feedback for 25 MHz crystal This pin is a no connect if an oscillator or external clock source is used.	

Pin Number	Pin Name	Type Note 2-1	Description	
9	ХІ	I	25 MHz Mode:25 MHz ±50 ppm Crystal/Oscillator/External Clock Input 50 MHz Mode: 50 MHz ±50 ppm Oscillator/External Clock Input	
10	REXT	I	Set PHY transmit output current Connect a 6.49 k $\Omega$ resistor to ground on this pin.	
11	MDIO	lpu/Opu	Management Interface (MII) Data I/O This pin has a weak pull-up, is open-drain, and requires an external 1.0 $k\Omega$ pull-up resistor.	
12	MDC	lpu	Management Interface (MII) Clock input This clock pin is synchronous to the MDIO data pin.	
13	PHYAD0	lpu/O	The pull-up/pull-down value is latched as PHYADDR[0] at the de-assertion of reset. See the Strap-In Options - KSZ8091RNB section for details.	
14	PHYAD1	lpd/O	The pull-up/pull-down value is latched as PHYADDR[1] at the de-assertion of reset. See the Strap-In Options - KSZ8091RNB section for details.	
15	RXD1/ PHYAD2	Ipd/O	RMII mode: RMII Receive Data Output[1] (Note 2-2) Config mode: The pull-up/pull-down value is latched as PHYADDR[2] at the de-assertion of reset. See the Strap-In Options - KSZ8091RNB section for details.	
16	RXD0/ DUPLEX	lpu/O	RMII mode: RMII Receive Data Output[0] (Note 2-2) Config mode: The pull-up/pull-down value is latched as DUPLEX at the de- assertion of reset. See the Strap-In Options - KSZ8091RNB section for details.	
17	VDDIO	Р	3.3V, 2.5V, or 1.8V digital V <sub>DD</sub>	
18	CRS_DV/ CONFIG2	lpd/O	RMII mode: RMII Carrier Sense/Receive Data Valid output Config mode: The pull-up/pull-down value is latched as CONFIG2 at the de- assertion of reset. See the Strap-In Options - KSZ8091RNB section for details.	
19	REF_CLK/ B-CAST_OFF	lpd/O	RMII mode: 25 MHz mode: This pin provides the 50 MHz RMII reference clo output to the MAC. See also XI (pin 9). 50 MHz mode: This pin is a no connect. See also XI (pin 9). Config mode: The pull-up/pull-down value is latched as B-CAST_OFF at th de-assertion of reset. See the Strap-In Options - KSZ8091RNB section for details.	
20	RXER/ISO	Ipd/O	RMII mode: RMII Receive Error output Config mode: The pull-up/pull-down value is latched as ISOLATE at the de- assertion of reset. See the Strap-In Options - KSZ8091RNB section for details.	
21	INTRP/ PME_N2/ NAND_Tree#	lpu/Opu	Interrupt output: Programmable interrupt output, with Register 1Bh as the Interrupt Control/Status register, for programming the interrupt conditions a reading the interrupt status. Register 1Fh, bit [9] sets the interrupt output to active low (default) or active high. PME_N output: Programmable PME_N output (pin option 2). When asserted low, this pin signals that a WOL event has occurred	

TABLE 2-3:	SIGNALS - KSZ8091RNB	(CONTINUED)
IADLL Z-J.		

© 2016 Microchip Technology Inc.

Pin Number	Pin Name	Type Note 2-1		Description		
22	PME_EN	lpd/O	reset.			
				- KSZ8091RNB section fo	or details.	
23	TXEN	 	RMII Transmit Enable inp			
24	TXD0		RMII Transmit Data Inpu			
25	TXD1		RMII Transmit Data Inpu		t flagting	
26	NC	NC	· · · · ·	not bonded and can be lef		
27	NC	NC		No connect – This pin is not bonded and can be left floating. The pull-up/pull-down value is latched as CONFIG0 at the de-assertion of		
28	CONFIG0	lpd/O	reset.	- KSZ8091RNB section for		
29	CONFIG1	lpd/O	reset.	lue is latched as CONFIG <sup>2</sup> - KSZ8091RNB section for		
	LED0/		LED output: Programmable LED0 output PME_N Output: Programmable PME_N Output (pin option 1). In this mode, this pin has a weak pull-up, is an open-drain, and requires an external 1.0 kΩ pull-up resistor to V <sub>DDIO</sub> (digital V <sub>DD</sub> ). Config mode: Latched as auto-negotiation enable (Register 0h, bit [12]) at the de-assertion of reset. See the Strap-In Options - KSZ8091RNB section for details. The LED0 pin is programmable using Register 1Fh bits [5:4], and is defined as follows.			
30	PME N1/	lpu/O	LED Mode = [00] Link/Activity	Pin State	LED Definition	
	NWAYEN	P	No Link	High	OFF	
			Link	Low	ON	
			Activity	Toggle	Blinking	
			LED Mode = [01]	00	Ŭ	
			Link	Pin State	LED Definition	
			No Link	High	OFF	
			Link	Low	ON	
			LED Mode = [10], [11]: 8	Reserved	·	
			LED output: Programmable LED1 output Config mode: Latched as SPEED (Register 0h, bit [13]) at the de-assertion o reset. See the Strap-In Options - KSZ8091RNB section for details. The LED1 pin is programmable using Register 1Fh bits [5:4], and is defined as follows.			
			LED Mode = [00]			
31	LED1/	lpu/O	Speed	Pin State	LED Definition	
	SPEED		10BASE-T	High	OFF	
			100BASE-TX	Low	ON	
			LED Mode = [01]	Din State		
			Activity	Pin State	LED Definition	
			No Activity	High	OFF	
			Activity	Toggle	Blinking	
			LED Mode = [10], [11]: {	Reserved		

### TABLE 2-3: SIGNALS - KSZ8091RNB (CONTINUED)

Pin Number	Pin Name	Type Note 2-1	Description	
32	RST#	lpu	Chip reset (active low)	
PADDLE	GND	GND	Ground	
Note 2-1	Ipu/O = Inp output pin c Ipd/O = Inp output pin c Ipu/Opu = In pull-up (see	und. ectional. with interna out with intervise. ut with inte otherwise. nput with inte e Electrical	al pull-up (see Electrical Characteristics for value). ernal pull-up (see Electrical Characteristics for value) during power-up/reset; rnal pull-down (see Electrical Characteristics for value) during power-up/reset; tternal pull-up (see Electrical Characteristics for value) and output with internal Characteristics for value). d to the die.	
Note 2-2			XD[1:0] bits are synchronous with the 50 MHz RMII Reference Clock. For each CRS_DV is asserted, two bits of recovered data are sent by the PHY to the	
Note 2-3			(D[1:0] bits are synchronous with the 50 MHz RMII Reference Clock. For each IXEN is asserted, two bits of data are received by the PHY from the MAC.	

TABLE 2-3: SIGNALS - KSZ8091RNB (CONTINUED)

The strap-in pins are latched at the de-assertion of reset. In some systems, the MAC RMII receive input pins may drive high/low during power-up or reset, and consequently cause the PHY strap-in pins on the RMII signals to be latched to unintended high/low states. In this case, external pull-ups (4.7 k $\Omega$ ) or pull-downs (1.0 k $\Omega$ ) should be added on these PHY strap-in pins to ensure that the intended values are strapped-in correctly.

Pin Number	Pin Name	Type Note 2-4		Description
15	PHYAD2	lpd/O	PHYAD[2:0] is	latched at de-assertion of reset and is configurable to
14	PHYAD1	Ipd/O		0 to 7 with PHY Address 1 as the default value.
13	PHYAD0	lpu/O	address, but it ing the B-CAS 16h, bit [9].	0 is assigned by default as the broadcast PHY can be assigned as a unique PHY address after pull- T_OFF strapping pin high or writing a '1' to Register bits [4:3] are set to 00 by default.
18	CONFIG2		The CONFIG[2 reset.	2:0] strap-in pins are latched at the de-assertion of
29	CONFIG1		CONFIG[2:0]	Mode
29	CONFIGI	Ipd/O	000	RMII (default)
			110	RMII back-to-back
28	CONFIG0		001 – 101, 111	Reserved, not used
22	PME_EN	lpd/O	Pull-up = Enat Pull-down (def	r Wake-on-LAN ole ault) = Disable rtion of reset, this pin value is latched into Register

TABLE 2-4: STRAP-IN OPTIONS - KSZ8091RNB

r			
Pin Number	Pin Name	Type Note 2-4	Description
20	ISO	lpd/O	Isolate mode Pull-up = Enable Pull-down (default) = Disable At the de-assertion of reset, this pin value is latched into Register 0h, bit [10].
31	SPEED	lpu/O	Speed mode Pull-up (default) = 100 Mbps Pull-down = 10 Mbps At the de-assertion of reset, this pin value is latched into Register 0h, bit [13] as the speed select, and also is latched into Register 4h (auto-negotiation advertisement) as the speed capability support.
16	DUPLEX	lpu/O	Duplex Mode: Pull-up (default) = Half-duplex Pull-down = Full-duplex At the de-assertion of reset, this pin value is latched into Register 0h, Bit [8].
30	NWAYEN	lpu/O	Nway Auto-Negotiation Enable: Pull-up (default) = Enable auto-negotiation Pull-down = Disable auto-negotiation At the de-assertion of reset, this pin value is latched into Register 0h, Bit [12].
19	B-CAST_OFF	lpd/O	Broadcast Off – for PHY Address 0: Pull-up = PHY Address 0 is set as an unique PHY address Pull-down (default) = PHY Address 0 is set as a broadcast PHY address At the de-assertion of reset, this pin value is latched by the chip.
21	NAND_Tree#	lpu/Opu	NAND Tree Mode: Pull-up (default) = Disable Pull-down = Enable At the de-assertion of reset, this pin value is latched by the chip.

#### TABLE 2-4: STRAP-IN OPTIONS - KSZ8091RNB (CONTINUED)

**Note 2-4** Ipu/O = Input with internal pull-up during power-up/reset; output pin otherwise. Ipd/O = Input with internal pull-down during power-up/reset; output pin otherwise. Ipu/Opu = Input with internal pull-up and output with internal pull-up.

### 3.0 FUNCTIONAL DESCRIPTION

The KSZ8091 is an integrated single 3.3V supply Fast Ethernet transceiver. It is fully compliant with the IEEE 802.3 Specification, and reduces board cost and simplifies board layout by using on-chip termination resistors for the two differential pairs and by integrating the regulator to supply the 1.2V core.

On the copper media side, the KSZ8091 supports 10BASE-T and 100BASE-TX for transmission and reception of data over a standard CAT-5 unshielded twisted pair (UTP) cable, and HP Auto MDI/MDI-X for reliable detection of and correction for straight-through and crossover cables.

On the MAC processor side, the KSZ8091MNX offers the Media Independent Interface (MII) and the KSZ8091RNB offers the Reduced Media Independent Interface (RMII) for direct connection with MII and RMII compliant Ethernet MAC processors and switches, respectively.

The MII management bus option gives the MAC processor complete access to the KSZ8091 control and status registers. Additionally, an interrupt pin eliminates the need for the processor to poll for PHY status change.

The KSZ8091MNX/RNB is used to refer to both KSZ8091MNX and KSZ8091RNB versions in this data sheet.

#### 3.1 10BASE-T/100BASE-TX Transceiver

#### 3.1.1 100BASE-TX TRANSMIT

The 100BASE-TX transmit function performs parallel-to-serial conversion, 4B/5B encoding, scrambling, NRZ-to-NRZI conversion, and MLT3 encoding and transmission.

The circuitry starts with a parallel-to-serial conversion, which converts the MII/RMII data from the MAC into a 125 MHz serial bit stream. The data and control stream is then converted into 4B/5B coding and followed by a scrambler. The serialized data is further converted from NRZ-to-NRZI format, and then transmitted in MLT3 current output. The output current is set by an external 6.49 k $\Omega$  1% resistor for the 1:1 transformer ratio.

The output signal has a typical rise/fall time of 4ns and complies with the ANSI TP-PMD standard regarding amplitude balance, overshoot, and timing jitter. The wave-shaped 10BASE-T output is also incorporated into the 100BASE-TX transmitter.

#### 3.1.2 100BASE-TX RECEIVE

The 100BASE-TX receiver function performs adaptive equalization, DC restoration, MLT3-to-NRZI conversion, data and clock recovery, NRZI-to-NRZ conversion, de-scrambling, 4B/5B decoding, and serial-to-parallel conversion.

The receiving side starts with the equalization filter to compensate for inter-symbol interference (ISI) over the twisted pair cable. Because the amplitude loss and phase distortion is a function of the cable length, the equalizer must adjust its characteristics to optimize performance. In this design, the variable equalizer makes an initial estimation based on comparisons of incoming signal strength against some known cable characteristics, then tunes itself for optimization. This is an ongoing process and self-adjusts against environmental changes such as temperature variations.

Next, the equalized signal goes through a DC-restoration and data-conversion block. The DC-restoration circuit compensates for the effect of baseline wander and improves the dynamic range. The differential data-conversion circuit converts MLT3 format back to NRZI. The slicing threshold is also adaptive.

The clock-recovery circuit extracts the 125 MHz clock from the edges of the NRZI signal. This recovered clock is then used to convert the NRZI signal to NRZ format. This signal is sent through the de-scrambler, then the 4B/5B decoder. Finally, the NRZ serial data is converted to MII/RMII format and provided as the input data to the MAC.

#### 3.1.3 SCRAMBLER/DE-SCRAMBLER (100BASE-TX ONLY)

The scrambler spreads the power spectrum of the transmitted signal to reduce electromagnetic interference (EMI) and baseline wander. The de-scrambler recovers the scrambled signal.

#### 3.1.4 10BASE-T TRANSMIT

The 10BASE-T drivers are incorporated with the 100BASE-TX drivers to allow for transmission using the same magnetic. The drivers perform internal wave-shaping and pre-emphasis, and output 10BASE-T signals with a typical amplitude of 2.5V peak for standard 10BASE-T mode and 1.75V peak for energy-efficient 10BASE-Te mode. The 10BASE-T/10BASE-Te signals have harmonic contents that are at least 27 dB below the fundamental frequency when driven by an all-ones Manchester-encoded signal.

<sup>© 2016</sup> Microchip Technology Inc.

#### 3.1.5 10BASE-T RECEIVE

On the receive side, input buffer and level detecting squelch circuits are used. A differential input receiver circuit and a phase-locked loop (PLL) performs the decoding function. The Manchester-encoded data stream is separated into clock signal and NRZ data. A squelch circuit rejects signals with levels less than 400 mV, or with short pulse widths, to prevent noise at the RXP and RXM inputs from falsely triggering the decoder. When the input exceeds the squelch limit, the PLL locks onto the incoming signal and the KSZ8091MNX/RNB decodes a data frame. The receive clock is kept active during idle periods between data receptions.

#### 3.1.6 SQE AND JABBER FUNCTION (10BASE-T ONLY)

In 10BASE-T operation, a short pulse is put out on the COL pin after each frame is transmitted. This SQE test is needed to test the 10BASE-T transmit/receive path. If transmit enable (TXEN) is high for more than 20 ms (jabbering), the 10BASE-T transmitter is disabled and COL is asserted high. If TXEN is then driven low for more than 250 ms, the 10BASE-T transmitter is re-enabled and COL is de-asserted (returns to low).

#### 3.1.7 PLL CLOCK SYNTHESIZER

The KSZ8091MNX/RNB generates all internal clocks and all external clocks for system timing from an external 25 MHz crystal, oscillator, or reference clock. For the KSZ8091RNB in RMII 50 MHz clock mode, these clocks are generated from an external 50 MHz oscillator or system clock.

#### 3.1.8 AUTO-NEGOTIATION

The KSZ8091MNX/RNB conforms to the auto-negotiation protocol, defined in Clause 28 of the IEEE 802.3 Specification.

Auto-negotiation allows unshielded twisted pair (UTP) link partners to select the highest common mode of operation.

During auto-negotiation, link partners advertise capabilities across the UTP link to each other and then compare their own capabilities with those they received from their link partners. The highest speed and duplex setting that is common to the two link partners is selected as the mode of operation.

The following list shows the speed and duplex operation mode from highest to lowest priority.

- Priority 1: 100BASE-TX, full-duplex
- Priority 2: 100BASE-TX, half-duplex
- Priority 3: 10BASE-T, full-duplex
- Priority 4: 10BASE-T, half-duplex


If auto-negotiation is not supported or the KSZ8091MNX/RNB link partner is forced to bypass auto-negotiation, then the KSZ8091MNX/RNB sets its operating mode by observing the signal at its receiver. This is known as parallel detection, which allows the KSZ8091MNX/RNB to establish a link by listening for a fixed signal protocol in the absence of the auto-negotiation advertisement protocol.

Auto-negotiation is enabled by either hardware pin strapping (NWAYEN, pin 30) or software (Register 0h, bit [12]).

By default, auto-negotiation is enabled after power-up or hardware reset. After that, auto-negotiation can be enabled or disabled by Register 0h, bit [12]. If auto-negotiation is disabled, the speed is set by Register 0h, bit [13], and the duplex is set by Register 0h, bit [8].

The auto-negotiation link-up process is shown in Figure 3-1.





#### 3.2 MII Data Interface (KSZ8091MNX Only)

The Media Independent Interface (MII) is compliant with the IEEE 802.3 Specification. It provides a common interface between MII PHYs and MACs, and has the following key characteristics:

- Pin count is 16 pins (7 pins for data transmission, 7 pins for data reception, and 2 pins for carrier and collision indication).
- 10 Mbps and 100 Mbps data rates are supported at both half- and full-duplex.
- Data transmission and reception are independent and belong to separate signal groups.
- Transmit data and receive data are each 4 bits wide, a nibble.

By default, the KSZ8091MNX is configured to MII mode after it is powered up or hardware reset with the following:

- A 25 MHz crystal connected to XI, XO (pins 9, 8), or an external 25 MHz clock source (oscillator) connected to XI.
- The CONFIG[2:0] strapping pins (pins 18, 29, 28) set to 000 (default setting).

#### 3.2.1 MII SIGNAL DEFINITION

Table 3-1 describes the MII signals. Refer to Clause 22 of the IEEE 802.3 Specification for detailed information.

MII Signal Name	Direction with Respect to PHY, KSZ8091MNX Signal	Direction with Respect to MAC	Description
ТХС	Output	Input	Transmit Clock (2.5 MHz for 10 Mbps; 25 MHz for 100 Mbps)
TXEN	Input	Output	Transmit Enable
TXD[3:0]	Input	Output	Transmit Data[3:0]
TXER	Input	Output or not implemented	Transmit Error (KSZ8091MNX implements only the EEE function for this pin. See Transmit Error (TXER) for details.)
RXC	Output	Input	Receive Clock (2.5 MHz for 10 Mbps; 25 MHz for 100 Mbps)
RXDV	Output	Input	Receive Data Valid
RXD[3:0]	Output	Input	Receive Data[3:0]
RXER	Output	Input or not required	Receive Error
CRS	Output	Input	Carrier Sense
COL	Output	Input	Collision Detection

#### TABLE 3-1: MII SIGNAL DEFINITION

#### 3.2.1.1 Transmit Clock (TXC)

TXC is sourced by the PHY. It is a continuous clock that provides the timing reference for TXEN, TXD[3:0], and TXER.

TXC is 2.5 MHz for 10 Mbps operation and 25 MHz for 100 Mbps operation.

#### 3.2.1.2 Transmit Enable (TXEN)

TXEN indicates that the MAC is presenting nibbles on TXD[3:0] for transmission. It is asserted synchronously with the first nibble of the preamble and remains asserted while all nibbles to be transmitted are presented on the MII. It is negated before the first TXC following the final nibble of a frame.

TXEN transitions synchronously with respect to TXC.

#### 3.2.1.3 Transmit Data[3:0] (TXD[3:0])

When TXEN is asserted, TXD[3:0] are the data nibbles presented by the MAC and accepted by the PHY for transmission.

When TXEN is de-asserted, the MAC drives TXD[3:0] to either 0000 for the idle state (non-EEE mode) or 0001 for the LPI state (EEE mode).

TXD[3:0] transitions synchronously with respect to TXC.

#### 3.2.1.4 Transmit Error (TXER)

TXER is implemented only for the EEE function.

For EEE mode, this pin is driven by the EEE-MAC to put the KSZ8091MNX transmit into the LPI state.

For non-EEE mode, this pin is not defined for error transmission from MAC to KSZ8091MNX and can be left as a no connect.

TXER transitions synchronously with respect to TXC.

#### 3.2.1.5 Receive Clock (RXC)

RXC provides the timing reference for RXDV, RXD[3:0], and RXER.

In 10 Mbps mode, RXC is recovered from the line while the carrier is active. When the line is idle or the link is down, RXC is derived from the PHY's reference clock.

In 100 Mbps mode, RXC is continuously recovered from the line. If the link is down, RXC is derived from the PHY's reference clock.

RXC is 2.5 MHz for 10 Mbps operation and 25 MHz for 100 Mbps operation.

#### 3.2.1.6 Receive Data Valid (RXDV)

RXDV is driven by the PHY to indicate that the PHY is presenting recovered and decoded nibbles on RXD[3:0].

In 10 Mbps mode, RXDV is asserted with the first nibble of the start-of-frame delimiter (SFD), 5D, and remains asserted until the end of the frame.

In 100 Mbps mode, RXDV is asserted from the first nibble of the preamble to the last nibble of the frame.

RXDV transitions synchronously with respect to RXC.

#### 3.2.1.7 Receive Data[3:0] (RXD[3:0])

For each clock period in which RXDV is asserted, RXD[3:0] transfers a nibble of recovered data from the PHY.

When RXDV is de-asserted, the PHY drives RXD[3:0] to either 0000 for the idle state (non-EEE mode) or 0001 for the LPI state (EEE mode).

RXD[3:0] transitions synchronously with respect to RXC.

#### 3.2.1.8 Receive Error (RXER)

When RXDV is asserted, RXER is asserted for one or more RXC periods to indicate that a symbol error (for example, a coding error that a PHY can detect that may otherwise be undetectable by the MAC sub-layer) is detected somewhere in the frame that is being transferred from the PHY to the MAC.

In EEE mode only, when RXDV is de-asserted, RXER is driven by the PHY to inform the MAC that the KSZ8091MNX receive is in the LPI state.

RXER transitions synchronously with respect to RXC.

#### 3.2.1.9 Carrier Sense (CRS)

CRS is asserted and de-asserted as follows:

- In 10 Mbps mode, CRS assertion is based on the reception of valid preambles. CRS de-assertion is based on the reception of an end-of-frame (EOF) marker.
- In 100 Mbps mode, CRS is asserted when a start-of-stream delimiter or /J/K symbol pair is detected. CRS is deasserted when an end-of-stream delimiter or /T/R symbol pair is detected. Additionally, the PMA layer de-asserts CRS if IDLE symbols are received without /T/R.

#### 3.2.1.10 Collision Detection (COL)


COL is asserted in half-duplex mode whenever the transmitter and receiver are simultaneously active on the line. This informs the MAC that a collision has occurred during its transmission to the PHY.

COL transitions asynchronously with respect to TXC and RXC.

#### 3.2.2 MII SIGNAL DIAGRAM

The KSZ8091MNX MII pin connections to the MAC are shown in Figure 3-2.

#### FIGURE 3-2: KSZ8091MNX MII INTERFACE



#### 3.3 RMII Data Interface (KSZ8091RNB Only)

The Reduced Media Independent Interface (RMII) specifies a low pin count Media Independent Interface (MII). It provides a common interface between physical layer and MAC layer devices, and has the following key characteristics:

- Pin count is 8 pins (3 pins for data transmission, 4 pins for data reception, and 1 pin for the 50 MHz reference clock).
- 10 Mbps and 100 Mbps data rates are supported at both half- and full-duplex.
- Data transmission and reception are independent and belong to separate signal groups.
- · Transmit data and receive data are each 2 bits wide, a dibit.

#### 3.3.1 RMII - 25 MHZ CLOCK MODE

The KSZ8091RNB is configured to RMII - 25 MHz clock mode after it is powered up or hardware reset with the following:

- A 25 MHz crystal connected to XI, XO (pins 9, 8), or an external 25 MHz clock source (oscillator) connected to XI.
- The CONFIG[2:0] strap-in pins (pins 18, 29, 28) set to 001.
- Register 1Fh, bit [7] is set to 0 (default value) to select 25 MHz clock mode.

#### 3.3.2 RMII - 50 MHZ CLOCK MODE

The KSZ8091RNB is configured to RMII - 50 MHz clock mode after it is powered up or hardware reset with the following:

- An external 50 MHz clock source (oscillator) connected to XI (pin 9).
- The CONFIG[2:0] strap-in pins (pins 18, 29, 28) set to 001.
- Register 1Fh, bit [7] is set to 1 to select 50 MHz clock mode.

#### 3.3.3 RMII SIGNAL DEFINITION

Table 3-2 describes the RMII signals. Refer to RMII Specification v1.2 for detailed information.

RMII Signal Name	Direction with Respect to PHY KSZ8091RNB Signal	Direction with Respect to MAC	Description
REF_CLK	Output (25 MHz clock mode)/ <no connect=""> (50 MHz clock mode)</no>	Input/Input or <no connect=""></no>	Synchronous 50 MHz reference clock for receive, transmit, and control interface
TXEN	Input	Output	Transmit Enable
TXD[1:0]	Input	Output	Transmit Data[1:0]
CRS_DV	Output	Input	Carrier Sense/Receive Data Valid
RXD[1:0]	Output	Input	Receive Data[1:0]
RXER	Output	Input or not required	Receive Error

#### TABLE 3-2: RMII SIGNAL DEFINITION

#### 3.3.4 REFERENCE CLOCK (REF\_CLK)

REF\_CLK is a continuous 50 MHz clock that provides the timing reference for TXEN, TXD[1:0], CRS\_DV, RXD[1:0] and RX\_ER.

For 25 MHz clock mode, the KSZ8091RNB generates and outputs the 50 MHz RMII REF\_CLK to the MAC at REF\_CLK (pin 19).

For 50 MHz clock mode, the KSZ8091RNB takes in the 50 MHz RMII REF\_CLK from the MAC or system board at XI (pin 9) and leaves the REF\_CLK (pin 19) as a no connect.

#### 3.3.5 TRANSMIT ENABLE (TXEN)

TXEN indicates that the MAC is presenting dibits on TXD[1:0] for transmission. It is asserted synchronously with the first dibit of the preamble and remains asserted while all dibits to be transmitted are presented on the RMII. It is negated before the first REF\_CLK following the final dibit of a frame.

TXEN transitions synchronously with respect to REF\_CLK.

#### 3.3.6 TRANSMIT DATA[1:0] (TXD[1:0])

When TXEN is asserted, TXD[1:0] are the data dibits presented by the MAC and accepted by the PHY for transmission.

When TXEN is de-asserted, the MAC drives TXD[1:0] to either 00 for the idle state (non-EEE mode) or 01 for the LPI state (EEE mode).

TXD[1:0] transitions synchronously with respect to REF\_CLK.

#### 3.3.7 CARRIER SENSE/RECEIVE DATA VALID (CRS\_DV)

The PHY asserts CRS\_DV when the receive medium is non-idle. It is asserted asynchronously when a carrier is detected. This happens when squelch is passed in 10 Mbps mode, and when two non-contiguous 0s in 10 bits are detected in 100 Mbps mode. Loss of carrier results in the de-assertion of CRS\_DV.

While carrier detection criteria are met, CRS\_DV remains asserted continuously from the first recovered dibit of the frame through the final recovered dibit. It is negated before the first REF\_CLK that follows the final dibit. The data on RXD[1:0] is considered valid after CRS\_DV is asserted. However, because the assertion of CRS\_DV is asynchronous relative to REF\_CLK, the data on RXD[1:0] is 00 until receive signals are properly decoded.

#### 3.3.8 RECEIVE DATA[1:0] (RXD[1:0])

For each clock period in which CRS\_DV is asserted, RXD[1:0] transfers a dibit of recovered data from the PHY.

When CRS\_DV is de-asserted, the PHY drives RXD[1:0] to either 00 for the idle state (non-EEE mode) or 01 for the LPI state (EEE mode).

RXD[1:0] transitions synchronously with respect to REF\_CLK.

<sup>© 2016</sup> Microchip Technology Inc.

#### 3.3.9 RECEIVE ERROR (RXER)

When CRS\_DV is asserted, RXER is asserted for one or more REF\_CLK periods to indicate that a symbol error (for example, a coding error that a PHY can detect that may otherwise be undetectable by the MAC sub-layer) is detected somewhere in the frame that is being transferred from the PHY to the MAC.

RXER transitions synchronously with respect to REF\_CLK.


#### 3.3.10 COLLISION DETECTION (COL)


The MAC regenerates the COL signal of the MII from TXEN and CRS\_DV.

#### 3.3.11 RMII SIGNAL DIAGRAM

The KSZ8091RNB RMII pin connections to the MAC for 25 MHz clock mode are shown in Figure 3-3. The connections for 50 MHz clock mode are shown in Figure 3-4.

#### FIGURE 3-3: KSZ8091RNB RMII INTERFACE (25 MHZ CLOCK MODE)






#### FIGURE 3-4: KSZ8091RNB RMII INTERFACE (50 MHZ CLOCK MODE)

#### 3.4 Back-to-Back Mode – 100 Mbps Copper Repeater

Two KSZ8091MNX/RNB devices can be connected back-to-back to form a 100BASE-TX copper repeater.

#### FIGURE 3-5: KSZ8091MNX/RNB TO KSZ8091MNX/RNB BACK-TO-BACK COPPER REPEATER



© 2016 Microchip Technology Inc.

#### 3.4.1 MII BACK-TO-BACK MODE (KSZ8091MNX ONLY)

In MII back-to-back mode, a KSZ8091MNX interfaces with another KSZ8091MNX to provide a complete 100 Mbps copper repeater solution.

The KSZ8091MNX devices are configured to MII back-to-back mode after power-up or reset with the following:

- Strap-in pin CONFIG[2:0] (pins 18, 29, 28) set to 110.
- A common 25 MHz reference clock connected to XI (Pin 9) of both KSZ8091MNX devices.
- MII signals connected as shown in Table 3-3.

# TABLE 3-3:MII SIGNAL CONNECTION FOR MII BACK-TO-BACK MODE (100BASE-TX COPPER<br/>REPEATER)

KSZ809 <sup>2</sup>	IMNX (100BASE-TX [Device 1]	Copper)	KSZ8091MNX (100BASE-TX Copper) [Device 2]		
Pin Name	Pin Number	Pin Type	Pin Name	Pin Number	Pin Type
RXDV	18	Output	TXEN	23	Input
RXD3	13	Output	TXD3	27	Input
RXD2	14	Output	TXD2	26	Input
RXD1	15	Output	TXD1	25	Input
RXD0	16	Output	TXD0	24	Input
TXEN	23	Input	RXDV	18	Output
TXD3	27	Input	RXD3	13	Output
TXD2	26	Input	RXD2	14	Output
TXD1	25	Input	RXD1	15	Output
TXD0	24	Input	RXD0	16	Output

#### 3.4.2 RMII BACK-TO-BACK MODE (KSZ8091RNB ONLY)

In RMII back-to-back mode, a KSZ8091RNB interfaces with another KSZ8091RNB to provide a complete 100 Mbps copper repeater solution.

The KSZ8091RNB devices are configured to RMII back-to-back mode after power-up or reset with the following:

- Strap-in pin CONFIG[2:0] (pins 18, 29, 28) set to 101.
- A common 50 MHz reference clock connected to XI (pin 9) of both KSZ8091RNB devices.
- RMII signals connected as shown in Table 3-4.

# TABLE 3-4:RMII SIGNAL CONNECTION FOR RMII BACK-TO-BACK MODE (100BASE-TX<br/>COPPER REPEATER)

KSZ809 <sup>,</sup>	KSZ8091RNB (100BASE-TX Copper) [Device 1]			RNB (100BASE-TX [Device 2]	(Copper)
Pin Name	Pin Number	Pin Type	Pin Name	Pin Number	Pin Type
CRSDV	18	Output	TXEN	23	Input
RXD1	15	Output	TXD1	25	Input
RXD0	16	Output	TXD0	24	Input
TXEN	23	Input	CRSDV	18	Output
TXD1	25	Input	RXD1	15	Output
TXD0	24	Input	RXD0	16	Output

#### 3.5 MII Management (MIIM) Interface

The KSZ8091MNX/RNB supports the IEEE 802.3 MII management interface, also known as the Management Data Input/Output (MDIO) interface. This interface allows an upper-layer device, such as a MAC processor, to monitor and control the state of the KSZ8091MNX/RNB. An external device with MIIM capability is used to read the PHY status and/ or configure the PHY settings. More details about the MIIM interface can be found in Clause 22.2.4 of the IEEE 802.3 Specification.

The MIIM interface consists of the following:

- A physical connection that incorporates the clock line (MDC) and the data line (MDIO).
- A specific protocol that operates across the physical connection mentioned earlier, which allows the external controller to communicate with one or more PHY devices.
- A 32-register address space for direct access to IEEE-defined registers and vendor-specific registers, and for indirect access to MMD addresses and registers. See the Register Descriptions section.

As the default, the KSZ8091MNX/RNB supports unique PHY addresses 1 to 7, and broadcast PHY address 0. The latter is defined in the IEEE 802.3 Specification, and can be used to read/write to a single KSZ8091MNX/RNB device, or write to multiple KSZ8091MNX/RNB devices simultaneously.

PHY address 0 can optionally be disabled as the broadcast address by either hardware pin strapping (B-CAST\_OFF, pin 19) or software (Register 16h, bit [9]), and assigned as a unique PHY address.

The PHYAD[2:0] strapping pins are used to assign a unique PHY address between 0 and 7 to each KSZ8091MNX/RNB device.

The MIIM interface can operates up to a maximum clock speed of 10 MHz MAC clock.

Table 3-5 shows the MII management frame format for the KSZ8091MNX/RNB.

	Preamble	Start of Frame	Read/ Write OP Code	PHY Address Bits[4:0]	REG Address Bits[4:0]	ТА	Data Bits[15:0]	Idle
Read	32 1's	01	10	00AAA	RRRRR	Z0	DDDDDDD_DDDDDDD	Ζ
Write	32 1's	01	01	00AAA	RRRRR	10	DDDDDDD_DDDDDDD	Z

TABLE 3-5: MII MANAGEMENT FRAME FORMAT FOR THE KSZ8091MNX/RNB

#### 3.6 Interrupt (INTRP)

INTRP (pin 21) is an optional interrupt signal that is used to inform the external controller that there has been a status update to the KSZ8091MNX/RNB PHY Register. Bits [15:8] of Register 1Bh are the interrupt control bits to enable and disable the conditions for asserting the INTRP signal. Bits [7:0] of Register 1Bh are the interrupt status bits to indicate which interrupt conditions have occurred. The interrupt status bits are cleared after reading Register 1Bh.

Bit [9] of Register 1Fh sets the interrupt level to active high or active low. The default is active low.

The MII management bus option gives the MAC processor complete access to the KSZ8091MNX/RNB control and status registers. Additionally, an interrupt pin eliminates the need for the processor to poll the PHY for status change.

#### 3.7 HP Auto MDI/MDI-X

HP Auto MDI/MDI-X configuration eliminates the need to decide whether to use a straight cable or a crossover cable between the KSZ8091MNX/RNB and its link partner. This feature allows the KSZ8091MNX/RNB to use either type of cable to connect with a link partner that is in either MDI or MDI-X mode. The auto-sense function detects transmit and receive pairs from the link partner and assigns transmit and receive pairs to the KSZ8091MNX/RNB accordingly.

HP Auto MDI/MDI-X is enabled by default. It is disabled by writing a '1' to Register 1Fh, bit [13]. MDI and MDI-X mode is selected by Register 1Fh, bit [14] if HP Auto MDI/MDI-X is disabled.

An isolation transformer with symmetrical transmit and receive data paths is recommended to support Auto MDI/MDI-X.

Table 3-6 shows how the IEEE 802.3 Standard defines MDI and MDI-X.

<sup>© 2016</sup> Microchip Technology Inc.


TABLE 3-6: MDI/MDI-X PIN DESCRIPT	ON
-----------------------------------	----

M	DI	MD	N-X
RJ-45 Pin	Signal	RJ-45 Pin	Signal
1	TX+	1	RX+
2	TX–	2	RX–
3	RX+	3	TX+
6	RX–	6	TX–

#### 3.7.1 STRAIGHT CABLE


A straight cable connects an MDI device to an MDI-X device, or an MDI-X device to an MDI device. Figure 3-6 shows a typical straight cable connection between a NIC card (MDI device) and a switch or hub (MDI-X device).

FIGURE 3-6: TYPICAL STRAIGHT CABLE CONNECTION



#### 3.7.2 CROSSOVER CABLE

A crossover cable connects an MDI device to another MDI device, or an MDI-X device to another MDI-X device. Figure 3-7 shows a typical crossover cable connection between two switches or hubs (two MDI-X devices).



#### FIGURE 3-7: TYPICAL CROSSOVER CABLE CONNECTION

#### 3.8 Loopback Mode

The KSZ8091MNX/RNB supports the following loopback operations to verify analog and/or digital data paths.

- Local (digital) loopback
- Remote (analog) loopback


#### 3.8.1 LOCAL (DIGITAL) LOOPBACK

This loopback mode checks the MII/RMII transmit and receive data paths between the KSZ8091MNX/RNB and the external MAC, and is supported for both speeds (10/100 Mbps) at full-duplex.

The loopback data path is shown in Figure 3-8.

- 1. The MII/RMII MAC transmits frames to the KSZ8091MNX/RNB.
- 2. Frames are wrapped around inside the KSZ8091MNX/RNB.
- 3. The KSZ8091MNX/RNB transmits frames back to the MII/RMII MAC.
- 4. Except the frames back to the RMII MAC, the transmit frames also go out from the copper port.

### FIGURE 3-8: LOCAL (DIGITAL) LOOPBACK



The following programming action and register settings are used for local loopback mode:

For 10/100 Mbps loopback:

Set Register 0h,

- Bit [14] = 1 // Enable local loopback mode
- Bit [13] = 0/1 // Select 10 Mbps/100 Mbps speed
- Bit [12] = 0 // Disable auto-negotiation
- Bit [8] = 1 // Select full-duplex mode


### 3.8.2 REMOTE (ANALOG) LOOPBACK

This loopback mode checks the line (differential pairs, transformer, RJ-45 connector, Ethernet cable) transmit and receive data paths between the KSZ8091MNX/RNB and its link partner, and is supported for 100BASE-TX full-duplex mode only.

The loopback data path is shown in Figure 3-9.

- 1. The Fast Ethernet (100BASE-TX) PHY link partner transmits frames to the KSZ8091MNX/RNB.
- 2. Frames are wrapped around inside the KSZ8091MNX/RNB.
- 3. The KSZ8091MNX/RNB transmits frames back to the Fast Ethernet (100BASE-TX) PHY link partner.

#### FIGURE 3-9: REMOTE (ANALOG) LOOPBACK



The following programming steps and register settings are used for remote loopback mode:

1. Set Register 0h,

Bits [13] = 1 // Select 100 Mbps speed

Bit [12] = 0 // Disable auto-negotiation

Bit [8] = 1 // Select full-duplex mode

Or just auto-negotiate and link up at 100BASE-TX full-duplex mode with the link partner.

2. Set Register 1Fh,

Bit [2] = 1 // Enable remote loopback mode

#### 3.9 LinkMD<sup>®</sup> Cable Diagnostic

The LinkMD function uses time-domain reflectometry (TDR) to analyze the cabling plant for common cabling problems. These include open circuits, short circuits, and impedance mismatches.

LinkMD works by sending a pulse of known amplitude and duration down the MDI or MDI-X pair, then analyzing the shape of the reflected signal to determine the type of fault. The time duration for the reflected signal to return provides the approximate distance to the cabling fault. The LinkMD function processes this TDR information and presents it as a numerical value that can be translated to a cable distance.

LinkMD is initiated by accessing register 1Dh, the LinkMD Cable Diagnostic register, in conjunction with Register 1Fh, the PHY Control 2 Register. The latter register is used to disable Auto MDI/MDI-X and to select either MDI or MDI-X as the cable differential pair for testing.

#### 3.9.1 USAGE

The following is a sample procedure for using LinkMD with Registers 1Dh and 1Fh:

- 1. Disable auto MDI/MDI-X by writing a '1' to Register 1Fh, bit [13].
- 2. Start cable diagnostic test by writing a '1' to Register 1Dh, bit [15]. This enable bit is self-clearing.
- 3. Wait (poll) for Register 1Dh, bit [15] to return a '0', and indicating cable diagnostic test is completed.
- 4. Read cable diagnostic test results in Register 1Dh, bits [14:13]. The results are as follows:
  - 00 = normal condition (valid test)
  - 01 = open condition detected in cable (valid test)
  - 10 = short condition detected in cable (valid test)

© 2016 Microchip Technology Inc.

11 = cable diagnostic test failed (invalid test)

The '11' case, invalid test, occurs when the device is unable to shut down the link partner. In this instance, the test is not run because it would be impossible for the device to determine if the detected signal is a reflection of the signal generated or a signal from another source.

5. Get distance to fault by concatenating Register 1Dh, bits [8:0] and multiplying the result by a constant of 0.38. The distance to the cable fault can be determined by the following formula:

#### EQUATION 3-1:

 $D(Distance \text{ to cable fault in meters}) = 0.38 \times (Register 1Dh, bits[8:0])$ 

Concatenated value of Registers 1Dh bits [8:0] should be converted to decimal before multiplying by 0.38.

The constant (0.38) may be calibrated for different cabling conditions, including cables with a velocity of propagation that varies significantly from the norm.

#### 3.10 NAND Tree Support

The KSZ8091MNX/RNB provides parametric NAND tree support for fault detection between chip I/Os and board. The NAND tree is a chain of nested NAND gates in which each KSZ8091MNX/RNB digital I/O (NAND tree input) pin is an input to one NAND gate along the chain. At the end of the chain, the CRS/CONFIG1 pin provides the output for the nested NAND gates.

The NAND tree test process includes:

- · Enabling NAND tree mode
- · Pulling all NAND tree input pins high
- Driving each NAND tree input pin low, sequentially, according to the NAND tree pin order
- Checking the NAND tree output to make sure there is a toggle high-to-low or low-to-high for each NAND tree input driven low

Table 3-7 and Table 3-8 list the NAND tree pin orders for KSZ8091MNX and KSZ8091RNB, respectively.

Pin Number	Pin Name	NAND Tree Description	
11	MDIO	Input	
12	MDC	Input	
13	RXD3	Input	
14	RXD2	Input	
15	RXD1	Input	
16	RXD0	Input	
18	RXDV	Input	
18	RXC	Input	
20	RXER	Input	
21	INTRP	Input	
22	TXC	Input	
23	TXEN	Input	
24	TXD0	Input	
25	TXD1	Input	
26	TXD2	Input	
27	TXD3	Input	

TABLE 3-7:NAND TREE TEST PIN ORDER FOR KSZ8091MNX

Pin Number	Pin Name	NAND Tree Description
30	LED0	Input
28	COL	Input
29	CRS	Output

#### TABLE 3-8:NAND TREE TEST PIN ORDER FOR KSZ8091RNB

Pin Number	Pin Name	NAND Tree Description
11	MDIO	Input
12	MDC	Input
15	RXD1	Input
16	RXD0	Input
18	CRS_DV	Input
19	REF_CLK	Input
20	RXER	Input
21	INTRP	Input
22	PME_EN	Input
23	TXEN	Input
24	TXD0	Input
25	TXD1	Input
30	LED0	Input
31	LED1	Input
28	CONFIG0	Input
29	CONFIG1	Output

#### 3.10.1 NAND TREE I/O TESTING

Use the following procedure to check for faults on the KSZ8091MNX/RNB digital I/O pin connections to the board:

- 1. Enable NAND tree mode using either a hardware strap-in pin (NAND\_Tree#, Pin 21) or software (Register 16h, Bit [5]).
- 2. Use board logic to drive all KSZ8091MNX/RNB NAND tree input pins high.
- 3. Use board logic to drive each NAND tree input pin, in KSZ8091MNX/RNB NAND tree pin order, as follows:
  - a) Toggle the first pin (MDIO) from high to low, and verify that the CRS/CONFIG1 pin switches from high to low to indicate that the first pin is connected properly.
  - b) Leave the first pin (MDIO) low.
  - c) Toggle the second pin (MDC) from high to low, and verify that the CRS/CONFIG1 pin switches from low to high to indicate that the second pin is connected properly.
  - d) Leave the first pin (MDIO) and the second pin (MDC) low.
  - e) Toggle the third pin (RXD3/PHYAD0) from high to low, and verify that the CRS/CONFIG1 pin switches from high to low to indicate that the third pin is connected properly.
  - f) Continue with this sequence until all KSZ8091MNX/RNB NAND tree input pins have been toggled.

Each KSZ8091MNX/RNB NAND tree input pin must cause the CRS/CONFIG1 output pin to toggle high-to-low or lowto-high to indicate a good connection. If the CRS/CONFIG1 pin fails to toggle when the KSZ8091MNX/RNB input pin toggles from high to low, the input pin has a fault.

#### 3.11 Power Management

The KSZ8091MNX/RNB incorporates a number of power-management modes and features that provide methods to consume less energy. These are discussed in the following sections.

#### 3.11.1 POWER-SAVING MODE

Power-saving mode is used to reduce the transceiver power consumption when the cable is unplugged. It is enabled by writing a '1' to Register 1Fh, bit [10], and is in effect when auto-negotiation mode is enabled and the cable is disconnected (no link).

In this mode, the KSZ8091MNX/RNB shuts down all transceiver blocks, except for the transmitter, energy detect, and PLL circuits.

By default, power-saving mode is disabled after power-up.

#### 3.11.2 ENERGY-DETECT POWER-DOWN MODE

Energy-detect power-down (EDPD) mode is used to further reduce transceiver power consumption when the cable is unplugged. It is enabled by writing a '0' to Register 18h, bit [11], and is in effect when auto-negotiation mode is enabled and the cable is disconnected (no link).

EDPD mode works with the PLL off (set by writing a '1' to Register 10h, bit [4] to automatically turn the PLL off in EDPD mode) to turn off all KSZ8091MNX/RNB transceiver blocks except the transmitter and energy-detect circuits.

Power can be reduced further by extending the time interval between transmissions of link pulses to check for the presence of a link partner. The periodic transmission of link pulses is needed to ensure the KSZ8091MNX/RNB and its link partner, when operating in the same low-power state and with Auto MDI/MDI-X disabled, can wake up when the cable is connected between them.

By default, energy-detect power-down mode is disabled after power-up.

#### 3.11.3 POWER-DOWN MODE

Power-down mode is used to power down the KSZ8091MNX/RNB device when it is not in use after power-up. It is enabled by writing a '1' to Register 0h, bit [11].

In this mode, the KSZ8091MNX/RNB disables all internal functions except the MII management interface. The KSZ8091MNX/RNB exits (disables) power-down mode after Register 0h, bit [11] is set back to '0'.

#### 3.11.4 SLOW-OSCILLATOR MODE

Slow-oscillator mode is used to disconnect the input reference crystal/clock on XI (pin 9) and select the on-chip slow oscillator when the KSZ8091MNX/RNB device is not in use after power-up. It is enabled by writing a '1' to Register 11h, bit [5].

Slow-oscillator mode works in conjunction with power-down mode to put the KSZ8091MNX/RNB device in the lowest power state, with all internal functions disabled except the MII management interface. To properly exit this mode and return to normal PHY operation, use the following programming sequence:

- 1. Disable slow-oscillator mode by writing a '0' to Register 11h, Bit [5].
- 2. Disable power-down mode by writing a '0' to Register 0h, Bit [11].
- 3. Initiate software reset by writing a '1' to Register 0h, Bit [15].

### 3.12 Energy Efficient Ethernet (EEE)

The KSZ8091MNX implements Energy Efficient Ethernet (EEE) for the Media Independent Interface (MII) as described in IEEE Standard 802.3az. The Standard is defined around an EEE-compliant MAC on the host side and an EEE-compliant link partner on the line side that support special signaling associated with EEE. EEE saves power by keeping the AC signal on the copper Ethernet cable at approximately 0V peak-to-peak as often as possible during periods of no traffic activity, while maintaining the link-up status. This is referred to as low-power idle (LPI) mode or state.

Similarly, the KSZ8091RNB implements EEE for the Reduced Media Independent Interface (RMII) as described in IEEE Standard 802.3az for line signaling by the two differential pairs (analog side) and according to the multi-source agreement (MSA) of collaborating Fast Ethernet chip vendors for the RMII (digital side). This agreement is based on the IEEE Standard's EEE implementation for MII (100 Mbps).

During LPI mode, the copper link responds automatically when it receives traffic and resumes normal PHY operation immediately, without blockage of traffic or loss of packet. This involves exiting LPI mode and returning to normal 100 Mbps operating mode. Wake-up time is <30 µs for 100BASE-TX.

The LPI state is controlled independently for transmit and receive paths, allowing the LPI state to be active (enabled) for:

- Transmit cable path only
- Receive cable path only
- Both transmit and receive cable paths


The KSZ8091MNX/RNB has the EEE function disabled as the power-up default setting. To enable the EEE function for 100 Mbps mode, use the following programming sequence:

- 1. Enable 100 Mbps EEE mode advertisement by writing a '1' to MMD address 7h, Register 3Ch, bit [1].
- 2. Restart auto-negotiation by writing a '1' to standard Register 0h, bit [9].

For standard (non-EEE) 10BASE-T mode, normal link pulses (NLPs) with long periods of no AC signal transmission are used to maintain the link during the idle period when there is no traffic activity. To save more power, the KSZ8091MNX/ RNB provides the option to enable 10BASE-Te mode, which saves additional power by reducing the transmitted signal amplitude from 2.5V to 1.75V. To enable 10BASE-Te mode, write a '1' to standard Register 13h, bit [4].

During LPI mode, refresh transmissions are used to maintain the link; power savings occur in quiet periods. Approximately every 20 to 22 milliseconds, a refresh transmission of 200 to 220 microseconds is sent to the link partner. The refresh transmissions and quiet periods are shown in Figure 3-10.

#### FIGURE 3-10: LPI MODE (REFRESH TRANSMISSIONS AND QUIET PERIODS)



#### 3.12.1 TRANSMIT DIRECTION CONTROL (MAC-TO-PHY)


The KSZ8091MNX enters LPI mode for the transmit direction when its attached EEE-compliant MII MAC de-asserts TXEN, asserts TXER, and sets TXD[3:0] to 0001. The KSZ8091MNX remains in the LPI transmit state while the MAC maintains the states of these signals. When the MAC changes any of the TXEN, TXER, or TX data signals from their LPI state values, the KSZ8091MNX exits the LPI transmit state.

The TXC clock is not stopped, because it is sourced from the PHY and is used by the MAC for MII transmit.

Figure 3-11 shows the LPI transition for MII (100 Mbps) transmit.

<sup>© 2016</sup> Microchip Technology Inc.


### FIGURE 3-11: LPI TRANSITION - MII (100 MBPS) TRANSMIT



Similarly, the KSZ8091RNB enters LPI mode for the transmit direction when its attached EEE-compliant RMII MAC deasserts TXEN and sets TXD [1:0] to 01. The KSZ8091RNB remains in the LPI transmit state while the RMII MAC maintains the states of these signals. When the RMII MAC changes any of the TXEN or TX data signals from their LPI state values, the KSZ8091RNB exits the LPI transmit state.

Figure 3-12 shows the LPI transition for RMII (100 Mbps) transmit.

### FIGURE 3-12: LPI TRANSITION - RMII (100 MBPS) TRANSMIT




#### 3.12.2 RECEIVE DIRECTION CONTROL (PHY-TO-MAC)

The KSZ8091MNX enters LPI mode for the receive direction when it receives the /P/ code bit pattern (Sleep/Refresh) from its EEE-compliant link partner. It then de-asserts RXDV, asserts RXER, and drives RXD[3:0] to 0001. The KSZ8091MNX remains in the LPI receive state while it continues to receive the refresh from its link partner, so it will continue to maintain and drive the LPI output states for the MII receive signals to inform the attached EEE-compliant MII MAC that it is in the LPI receive state. When the KSZ8091MNX receives a non /P/ code bit pattern (non-refresh), it exits the LPI receive state and sets the RXDV, RXER, and RX data signals to set a normal frame or normal idle.

The KSZ8091MNX stops the RXC clock output to the MAC after nine or more RXC clock cycles have occurred in the LPI receive state, to save more power. By default, RXC clock stoppage is enabled. It is disabled by writing a '0' to MMD address 3h, Register 0h, Bit [10].

Figure 3-13 shows the LPI transition for MII (100 Mbps) receive.






Similarly, the KSZ8091RNB enters LPI mode for the receive direction when it receives the /P/ code bit pattern (Sleep/ Refresh) from its EEE-compliant link partner. It then de-asserts CRS\_DV and drives RXD[1:0] to 01. The KSZ8091RNB remains in the LPI receive state while it continues to receive the refresh from its link partner, so it will continue to maintain and drive the LPI output states for the RMII receive signals to inform the attached EEE-compliant RMII MAC that it is in the LPI receive state. When the KSZ8091RNB receives a non /P/ code bit pattern (non-refresh), it exits the LPI receive state and sets the CRS\_DV and RX data signals to set a normal frame or normal idle.

Figure 3-14 shows the LPI transition for RMII (100 Mbps) receive.





#### 3.12.3 REGISTERS ASSOCIATED WITH EEE

The following registers are provided for EEE configuration and management:

- Standard Register 13h AFE Control 4 (to enable 10BASE-Te mode)
- MMD address 1h, Register 0h PMA/PMD Control 1 (to enable LPI)
- MMD address 1h, Register 1h PMA/PMD Status 1 (for LPI status)
- MMD address 3h, Register 0h EEE PCS Control 1 (to stop RXC clock for KSZ8091MNX only)
- MMD address 7h, Register 3Ch EEE Advertisement
- MMD address 7h, Register 3Dh EEE Link Partner Advertisement

### 3.13 Wake-On-LAN

Wake-On-LAN (WOL) is normally a MAC-based function to wake up a host system (for example, an Ethernet end device, such as a PC) that is in standby power mode. Wake-up is triggered by receiving and detecting a special packet (commonly referred to as the "magic packet") that is sent by the remote link partner. The KSZ8091MNX/RNB can perform the same WOL function if the MAC address of its associated MAC device is entered into the KSZ8091MNX/RNB PHY registers for magic-packet detection. When the KSZ8091MNX/RNB detects the magic packet, it wakes up the host by driving its power management event (PME) output pin low.

By default, the WOL function is disabled. It is enabled by setting the enabling bit and configuring the associated registers for the selected PME wake-up detection method.

The KSZ8091MNX/RNB provides three methods to trigger a PME wake-up:

- Magic-packet detection
- · Customized-packet detection
- Link status change detection

#### 3.13.1 MAGIC-PACKET DETECTION

The magic packet's frame format starts with 6 bytes of 0xFFh and is followed by 16 repetitions of the MAC address of its associated MAC device (local MAC device).

When the magic packet is detected from its link partner, the KSZ8091MNX/RNB asserts its PME output pin low.

The following MMD address 1Fh registers are provided for magic-packet detection:

- Magic-packet detection is enabled by writing a '1' to MMD address 1Fh, Register 0h, bit [6]
- The MAC address (for the local MAC device) is written to and stored in MMD address 1Fh, Registers 19h 1Bh

The KSZ8091MNX/RNB does not generate the magic packet. The magic packet must be provided by the external system.

#### 3.13.2 CUSTOMIZED-PACKET DETECTION

The customized packet has associated register/bit masks to select which byte, or bytes, of the first 64 bytes of the packet to use in the CRC calculation. After the KSZ8091MNX/RNB receives the packet from its link partner, the selected bytes for the received packet are used to calculate the CRC. The calculated CRC is compared to the expected CRC value that was previously written to and stored in the KSZ8091MNX/RNB PHY Registers. If there is a match, the KSZ8091MNX/RNB asserts its PME output pin low.

Four customized packets are provided to support four types of wake-up scenarios. A dedicated set of registers is used to configure and enable each customized packet.

The following MMD Registers are provided for customized-packet detection:

- Each of the four customized packets is enabled via MMD address 1Fh, Register 0h,
  - Bit [2] // For customized packets, type 0
  - Bit [3] // For customized packets, type 1
  - Bit [4] // For customized packets, type 2
  - Bit [5] // For customized packets, type 3
- Masks to indicate which of the first 64-bytes to use in the CRC calculation are set in:
  - MMD address 1Fh, Registers 1h 4h // For customized packets, type 0
  - MMD address 1Fh, Registers 7h Ah // For customized packets, type 1
  - MMD address 1Fh, Registers Dh 10h // For customized packets, type 2
  - MMD address 1Fh, Registers 13h 16h // For customized packets, type 3
- · 32-bit expected CRCs are written to and stored in:
  - MMD address 1Fh, Registers 5h 6h // For customized packets, type 0
  - MMD address 1Fh, Registers Bh Ch // For customized packets, type 1
  - MMD address 1Fh, Registers 11h 12h // For customized packets, type 2
  - MMD address 1Fh, Registers 17h 18h // For customized packets, type 3

### 3.13.3 LINK STATUS CHANGE DETECTION

If link status change detection is enabled, the KSZ8091MNX/RNB asserts its PME output pin low whenever there is a link status change, using the following MMD address 1Fh register bits and their enabled (1) or disabled (0) settings:


- MMD address 1Fh, Register 0h, bit [0] // For link-up detection
- MMD address 1Fh, Register 0h, bit [1] // For link-down detection

The PME output signal is available on either INTRP/PME\_N2 (pin 21) or LED0/PME\_N1 (pin 30), and is enabled using standard Register 16h, bit [15]. MMD address 1Fh, Register 0h, bits [15:14] defines and selects the output functions for pins 21 and 30.

The PME output is active low and requires a 1 k $\Omega$  pull-up to the V<sub>DDIO</sub> supply. When asserted, the PME output is cleared by disabling the register bit that enabled the PME trigger source (magic packet, customized packet, link status change).

### 3.14 Reference Circuit for Power and Ground Connections

The KSZ8091MNX/RNB is a single 3.3V supply device with a built-in regulator to supply the 1.2V core. The power and ground connections are shown in Figure 3-15 and Table 3-9 for  $3.3V V_{DDIO}$ .



#### FIGURE 3-15: KSZ8091MNX/RNB POWER AND GROUND CONNECTIONS

Power Pin	Pin Number	Description
VDD_1.2	2	Decouple with 2.2 µF and 0.1 µF capacitors to ground.
VDDA_3.3	3	Connect to board's 3.3V supply through a ferrite bead. Decouple with 22 µF and 0.1 µF capacitors to ground.
VDDIO	17	Connect to board's 3.3V supply for 3.3V V <sub>DDIO</sub> . Decouple with 22 $\mu$ F and 0.1 $\mu$ F capacitors to ground.

<sup>© 2016</sup> Microchip Technology Inc.

## 3.15 Typical Current/Power Consumption

Table 3-10, Table 3-11, and Table 3-12 show typical values for current consumption by the transceiver (VDDA\_3.3) and digital I/O (VDDIO) power pins, and typical values for power consumption by the KSZ8091MNX/RNB device for the indicated nominal operating voltages. These current and power consumption values include the transmit driver current and on-chip regulator current for the 1.2V core.

Condition	3.3V Transceiver (VDDA_3.3)	3.3V Digital I/Os (VDDIO)	Total Chip Power
100BASE-TX Link-up (no traffic)	34 mA	12 mA	152 mW
100BASE-TX Full-duplex @ 100% utilization	34 mA	13 mA	155 mW
10BASE-T Link-up (no traffic)	14 mA	11 mA	82.5 mW
10BASE-T Full-duplex @ 100% utilization	30 mA	11 mA	135 mW
EEE 100 Mbps Link-up mode (transmit and receive in LPI state with no traffic)	13 mA	10 mA	75.9 mW
Power-saving mode (Reg. 1Fh, Bit [10] = 1)	13 mA	10 mA	75.9 mW
EDPD mode (Reg. 18h, Bit [11] = 0)	10 mA	10 mA	66 mW
EDPD mode (Reg. 18h, Bit [11] = 0) and PLL off (Reg. 10h, Bit [4] = 1)	3.77 mA	1.54 mA	17.5 mW
Software power-down mode (Reg. 0h, Bit [11] =1)	2.59 mA	1.51 mA	13.5 mW
Software power-down mode (Reg. 0h, Bit [11] =1) and slow-oscillator mode (Reg. 11h, Bit [5] =1)	1.36 mA	0.45 mA	5.97 mW

#### TABLE 3-10:TYPICAL CURRENT/POWER CONSUMPTION (VDDA\_3.3 = 3.3V, VDDIO = 3.3V)

### TABLE 3-11:TYPICAL CURRENT/POWER CONSUMPTION (VDDA\_3.3 = 3.3V, VDDIO = 2.5V)

Condition	3.3V Transceiver (VDDA_3.3)	2.5V Digital I/Os (VDDIO)	Total Chip Power
100BASE-TX Link-up (no traffic)	34 mA	11 mA	140 mW
100BASE-TX Full-duplex @ 100% utilization	34 mA	12 mA	142 mW
10BASE-T Link-up (no traffic)	15 mA	10 mA	74.5 mW
10BASE-T Full-duplex @ 100% utilization	27 mA	10 mA	114 mW
EEE 100 Mbps Link-up mode (transmit and receive in LPI state with no traffic)	13 mA	10 mA	67.9 mW
Power-saving mode (Reg. 1Fh, Bit [10] = 1)	13 mA	10 mA	67.9 mW
EDPD mode (Reg. 18h, Bit [11] = 0)	11 mA	10 mA	61.3 mW
EDPD mode (Reg. 18h, Bit [11] = 0) and PLL off (Reg. 10h, Bit [4] = 1)	3.55 mA	1.35 mA	15.1 mW
Software power-down mode (Reg. 0h, Bit [11] =1)	2.29 mA	1.34 mA	10.9 mW
Software power-down mode (Reg. 0h, Bit [11] =1) and slow-oscillator mode (Reg. 11h, Bit [5] =1)	1.15 mA	0.29 mA	4.52 mW

### TABLE 3-12:TYPICAL CURRENT/POWER CONSUMPTION (VDDA\_3.3 = 3.3V, VDDIO = 1.8V)

Condition	3.3V Transceiver (VDDA_3.3)	1.8V Digital I/Os (VDDIO)	Total Chip Power
100BASE-TX Link-up (no traffic)	34 mA	11 mA	132 mW
100BASE-TX Full-duplex @ 100% utilization	34 mA	12 mA	134 mW
10BASE-T Link-up (no traffic)	15 mA	9 mA	65.7 mW
10BASE-T Full-duplex @ 100% utilization	27 mA	9 mA	105 mW

Condition	3.3V Transceiver (VDDA_3.3)	1.8V Digital I/Os (VDDIO)	Total Chip Power
EEE 100 Mbps Link-up mode (transmit and receive in LPI state with no traffic)	13 mA	9 mA	59.1 mW
Power-saving mode (Reg. 1Fh, Bit [10] = 1)	13 mA	9 mA	59.1 mW
EDPD mode (Reg. 18h, Bit [11] = 0)	11 mA	9 mA	52.5 mW
EDPD mode (Reg. 18h, Bit [11] = 0) and PLL off (Reg. 10h, Bit [4] = 1)	4.05 mA	1.21 mA	15.5 mW
Software power-down mode (Reg. 0h, Bit [11] =1)	2.79 mA	1.21 mA	11.4 mW
Software power-down mode (Reg. 0h, Bit [11] =1) and slow-oscillator mode (Reg. 11h, Bit [5] =1)	1.65 mA	0.19 mA	5.79 mW

## TABLE 3-12: TYPICAL CURRENT/POWER CONSUMPTION (VDDA\_3.3 = 3.3V, VDDIO = 1.8V)

<sup>© 2016</sup> Microchip Technology Inc.

## 4.0 **REGISTER DESCRIPTIONS**

The register space within the KSZ8091MNX/RNB consists of two distinct areas.

- Standard registers
   // Direct register access
- MDIO manageable device (MMD) registers // Indirect register access

The KSZ8091MNX/RNB supports the following standard registers.

## 4.1 Register Map

#### TABLE 4-1: STANDARD REGISTERS SUPPORTED BY KSZ8091MNX/RNB

Register Number (hex)	Description		
EEE Defined Registers			
0h	Basic Control		
1h	Basic Status		
2h	PHY Identifier 1		
3h	PHY Identifier 2		
4h	Auto-Negotiation Advertisement		
5h	Auto-Negotiation Link Partner Ability		
6h	Auto-Negotiation Expansion		
7h	Auto-Negotiation Next Page		
8h	Auto-Negotiation Link Partner Next Page Ability		
9h - Ch	Reserved		
Dh	MMD Access - Control		
Eh	MMD Access - Register/Data		
Fh	Reserved		
Vendor Specific Registers			
10h	Digital Reserved Control		
11h	AFE Control 1		
12h	Reserved		
13h	AFE Control 4		
14h	Reserved		
15h	RXER Counter		
16h	Operation Mode Strap Override		
17h	Operation Mode Strap Status		
18h	Expanded Control		
19h - 1Ah	Reserved		
1Bh	Interrupt Control/Status		
1Ch	Reserved		
1Dh	LinkMD Cable Diagnostic		
1Eh	PHY Control 1		
1Fh	PHY Control 2		

The KSZ8091MNX/RNB supports the following MMD device addresses and their associated register addresses, which make up the indirect MMD registers.

Device Address (Hex)	Register Address (Hex)	Description		
1h	0h	PMA/PMD Control 1		
111	1h	PMA/PMD Status 1		
3h	0h	EEE PCS Control 1		
7h	3Ch EEE Advertisement			
711	3Dh	EEE Link Partner Advertisement		
	0h	Wake-On-LAN – Control		
	1h	Wake-On-LAN – Customized Packet, Type 0, Mask 0		
	2h	Wake-On-LAN – Customized Packet, Type 0, Mask 1		
	3h	Wake-On-LAN – Customized Packet, Type 0, Mask 2		
	4h	Wake-On-LAN – Customized Packet, Type 0, Mask 3		
	5h	Wake-On-LAN – Customized Packet, Type 0, Expected CRC 0		
	6h	Wake-On-LAN – Customized Packet, Type 0, Expected CRC 1		
	7h	Wake-On-LAN – Customized Packet, Type 1, Mask 0		
	8h	Wake-On-LAN – Customized Packet, Type 1, Mask 1		
	9h	Wake-On-LAN – Customized Packet, Type 1, Mask 2		
	Ah	Wake-On-LAN – Customized Packet, Type 1, Mask 3		
	Bh	Wake-On-LAN – Customized Packet, Type 1, Expected CRC 0		
	Ch	Wake-On-LAN – Customized Packet, Type 1, Expected CRC 1		
1Fh	Dh	Wake-On-LAN – Customized Packet, Type 2, Mask 0		
1611	Eh	Wake-On-LAN – Customized Packet, Type 2, Mask 1		
	Fh	Wake-On-LAN – Customized Packet, Type 2, Mask 2		
	10h	Wake-On-LAN – Customized Packet, Type 2, Mask 3		
	11h	Wake-On-LAN – Customized Packet, Type 2, Expected CRC 0		
	12h	Wake-On-LAN – Customized Packet, Type 2, Expected CRC 1		
	13h	Wake-On-LAN – Customized Packet, Type 3, Mask 0		
	14h	Wake-On-LAN – Customized Packet, Type 3, Mask 1		
	15h	Wake-On-LAN – Customized Packet, Type 3, Mask 2		
	16h	Wake-On-LAN – Customized Packet, Type 3, Mask 3		
	17h	Wake-On-LAN – Customized Packet, Type 3, Expected CRC 0		
	18h	Wake-On-LAN – Customized Packet, Type 3, Expected CRC 1		
	19h	Wake-On-LAN – Magic Packet, MAC-DA-0		
	1Ah	Wake-On-LAN – Magic Packet, MAC-DA-1		
	1Bh	Wake-On-LAN – Magic Packet, MAC-DA-2		

<sup>© 2016</sup> Microchip Technology Inc.

## 4.2 Standard Registers

Standard registers provide direct read/write access to a 32-register address space, as defined in Clause 22 of the IEEE 802.3 Specification. Within this address space, the first 16 registers (Registers 0h to Fh) are defined according to the IEEE specification, while the remaining 16 registers (Registers 10h to 1Fh) are defined specific to the PHY vendor.

Address	Name	Description	Mode Note 4-1	Default
Register 0h	- Basic Contro	bl		
0.15	Reset	1 = Software reset 0 = Normal operation This bit is self-cleared after a '1' is written to it.	RW/SC	0
0.14	Loopback	1 = Loopback mode 0 = Normal operation	RW	0
0.13	Speed Select	1 = 100 Mbps 0 = 10 Mbps This bit is ignored if auto-negotiation is enabled (Register 0.12 = 1).	RW	Set by the SPEED strapping pin (KSZ8091RNB only). See the Strap-In Options - KSZ8091RNB section for details.
0.12	Auto-Negoti- ation Enable	1 = Enable auto-negotiation process 0 = Disable auto-negotiation process If enabled, the auto-negotiation result overrides the settings in Registers 0.13 and 0.8.	RW	Set by the NWAYEN strapping pin. See the Strap-In Options - KSZ8091MNX sec- tion for details.
0.11	Power-Down	1 = Power-down mode 0 = Normal operation If software reset (Register 0.15) is used to exit power-down mode (Register 0.11 = 1), two soft- ware reset writes (Register 0.15 = 1) are required. The first write clears power-down mode; the sec- ond write resets the chip and re-latches the pin strapping pin values.	RW	0
0.10	Isolate	1 = Electrical isolation of PHY from MII 0 = Normal operation	RW	Set by the ISO strap- ping pin. See the Strap-In Options - KSZ8091MNX_sec- tion for details.
0.9	Restart Auto- Negotiation	<ul> <li>1 = Restart auto-negotiation process</li> <li>0 = Normal operation.</li> <li>This bit is self-cleared after a '1' is written to it.</li> </ul>	RW/SC	0
0.8	Duplex Mode	1 = Full-duplex 0 = Half-duplex	RW	The inverse of the DUPLEX strapping pin value. See the Strap-In Options - KSZ8091MNX sec- tion for details.
0.7	Collision Test	1 = Enable COL test 0 = Disable COL test	RW	0
0.6:0	Reserved	Reserved	RO	000_0000

TABLE 4-3: IEEE DEFINED REGISTER DESCRIPTIONS

Address	Name	Description	Mode Note 4-1	Default
Register 1h	- Basic Status			
1.15	100BASE-T4	1 = T4 capable 0 = Not T4 capable	RO	0
1.14	100BASE-TX Full-Duplex	1 = Capable of 100 Mbps full-duplex 0 = Not capable of 100 Mbps full-duplex	RO	1
1.13	100BASE-TX Half-Duplex	1 = Capable of 100 Mbps half-duplex 0 = Not capable of 100 Mbps half-duplex	RO	1
1.12	10BASE-T Full-Duplex	1 = Capable of 10 Mbps full-duplex 0 = Not capable of 10 Mbps full-duplex	RO	1
1.11	10BASE-T Half-Duplex	1 = Capable of 10 Mbps half-duplex 0 = Not capable of 10 Mbps half-duplex	RO	1
1.10:7	Reserved	Reserved	RO	000_0
1.6	No Preamble	1 = Preamble suppression 0 = Normal preamble	RO	1
1.5	Auto-Negoti- ation Com- plete	1 = Auto-negotiation process completed 0 = Auto-negotiation process not completed	RO	0
1.4	Remote Fault	1 = Remote fault 0 = No remote fault	RO/LH	0
1.3	Auto-Negoti- ation Ability	<ul><li>1 = Can perform auto-negotiation</li><li>0 = Cannot perform auto-negotiation</li></ul>	RO	1
1.2	Link Status	1 = Link is up 0 = Link is down	RO/LL	0
1.1	Jabber Detect	1 = Jabber detected 0 = Jabber not detected (default is low)	RO/LH	0
1.0	Extended Capability	1 = Supports extended capability registers	RO	1
Register 2h	- PHY Identifie	r 1		
2.15:0	PHY ID Number	Assigned to the 3rd through 18th bits of the Organi- zationally Unique Identifier (OUI). KENDIN Com- munication's OUI is 0010A1 (hex).	RO	0022h
Register 3h	- PHY Identifie	r 2		
3.15:10	PHY ID Num- ber	Assigned to the 19th through 24th bits of the Orga- nizationally Unique Identifier (OUI). KENDIN Com- munication's OUI is 0010A1 (hex).	RO	0001_01
3.9:4	Model Num- ber	Six-bit manufacturer's model number	RO	01_0110
3.3:0	Revision Number	Four-bit manufacturer's revision number	RO	Indicates silicon revision.
Register 4h	- Auto-Negotia	tion Advertisement		
4.15	Next Page	1 = Next page capable 0 = No next page capability	RW	1
4.14	Reserved	Reserved	RO	0
4.13	Remote Fault	1 = Remote fault supported 0 = No remote fault	RW	0
4.12	Reserved	Reserved	RO	0

TABLE 4-3: IEEE DEFINED REGISTER DESCRIPTIONS (CONTINUED)

<sup>© 2016</sup> Microchip Technology Inc.

Address	Name	Description	Mode Note 4-1	Default
4.11:10	Pause	[00] = No pause [10] = Asymmetric pause [01] = Symmetric pause [11] = Asymmetric and symmetric pause	RW	00
4.9	100BASE-T4	1 = T4 capable 0 = No T4 capability	RO	0
4.8	100BASE-TX Full-Duplex	1 = 100 Mbps full-duplex capable 0 = No 100 Mbps full-duplex capability	RW	Set by the SPEED strapping pin (KSZ8091RNB only). See the Strap-In Options - KSZ8091RNB section for details.
4.7	100BASE-TX Half-Duplex	1 = 100 Mbps half-duplex capable 0 = No 100 Mbps half-duplex capability	RW	Set by the SPEED strapping pin (KSZ8091RNB only). See the Strap-In Options - KSZ8091RNB section for details.
4.6	10BASE-T Full-Duplex	1 = 10 Mbps full-duplex capable 0 = No 10 Mbps full-duplex capability	RW	1
4.5	10BASE-T Half-Duplex	1 = 10 Mbps half-duplex capable 0 = No 10 Mbps half-duplex capability	RW	1
4.4:0	Selector Field	[00001] = IEEE 802.3	RW	0_0001
Register 5h	- Auto-Negotia	ation Link Partner Ability		
5.15	Next Page	1 = Next page capable 0 = No next page capability	RO	0
5.14	Acknowledge	<ul><li>1 = Link code word received from partner</li><li>0 = Link code word not yet received</li></ul>	RO	0
5.13	Remote Fault	1 = Remote fault detected 0 = No remote fault	RO	0
5.12	Reserved	Reserved	RO	0
5.11:10	Pause	<ul> <li>[00] = No pause</li> <li>[10] = Asymmetric pause</li> <li>[01] = Symmetric pause</li> <li>[11] = Asymmetric and symmetric pause</li> </ul>	RO	00
5.9	100BASE-T4	1 = T4 capable 0 = No T4 capability	RO	0
5.8	100BASE-TX Full-Duplex	1 = 100 Mbps full-duplex capable 0 = No 100 Mbps full-duplex capability	RO	0
5.7	100BASE-TX Half-Duplex	1 = 100 Mbps half-duplex capable 0 = No 100 Mbps half-duplex capability	RO	0
5.6	10BASE-T Full-Duplex	1 = 10 Mbps full-duplex capable 0 = No 10 Mbps full-duplex capability	RO	0
5.5	10BASE-T Half-Duplex	1 = 10 Mbps half-duplex capable 0 = No 10 Mbps half-duplex capability	RO	0
5.4:0	Selector Field	[00001] = 802.3 after AN completes.	RO	0_000

### TABLE 4-3: IEEE DEFINED REGISTER DESCRIPTIONS (CONTINUED)

Address	Name	Description	Mode Note 4-1	Default
Register 6h	- Auto-Negotia	tion Expansion		
6.15:5	Reserved	Reserved	RO	000_0000_000
6.4	Parallel Detection Fault	<ul><li>1 = Fault detected by parallel detection</li><li>0 = No fault detected by parallel detection</li></ul>	RO/LH	0
6.3	Link Partner Next Page Able	<ul><li>1 = Link partner has next page capability</li><li>0 = Link partner does not have next page capability</li></ul>	RO	0
6.2	Next Page Able	<ul><li>1 = Local device has next page capability</li><li>0 = Local device does not have next page capabil- ity</li></ul>	RO	1
6.1	Page Received	1 = New page received 0 = New page not received yet	RO/LH	0
6.0	Link Partner Auto-Negoti- ation Able	<ul> <li>1 = Link partner has auto-negotiation capability</li> <li>0 = Link partner does not have auto-negotiation capability</li> </ul>	RO	0
Register 7h	- Auto-Negotia	tion Next Page		
7.15	Next Page	1 = Additional next pages will follow 0 = Last page	RW	0
7.14	Reserved	Reserved	RO	0
7.13	Message Page	1 = Message page 0 = Unformatted page	RW	1
7.12	Acknowl- edge2	<ul><li>1 = Will comply with message</li><li>0 = Cannot comply with message</li></ul>	RW	0
7.11	Toggle	1 = Previous value of the transmitted link code word equaled logic 1 0 = Logic 0	RO	0
7.10:0	Message Field	11-bit wide field to encode 2048 messages	RW	000_0000_0001
Register 8h	- Link Partner	Next Page Ability		
8.15	Next Page	1 = Additional next pages will follow 0 = Last page	RO	0
8.14	Acknowledge	<ul><li>1 = Successful receipt of link word</li><li>0 = No successful receipt of link word</li></ul>	RO	0
8.13	Message Page	1 = Message page 0 = Unformatted page	RO	0
8.12	Acknowl- edge2	1 = Can act on the information 0 = Cannot act on the information	RO	0
8.11	Toggle	<ul> <li>1 = Previous value of transmitted link code word equal to logic 0</li> <li>0 = Previous value of transmitted link code word equal to logic 1</li> </ul>	RO	0
8.10:0	Message Field	11-bit wide field to encode 2048 messages	RO	000_0000_0000

TABLE 4-3: IEEE DEFINED REGISTER DESCRIPTIONS (CONTINUED)

<sup>© 2016</sup> Microchip Technology Inc.

Address	Name	Description	Mode Note 4-1	Default
Register Dh	- MMD Acces	s - Control		
D.15:14	MMD – Operation Mode	For the selected MMD device address (bits [4:0] of this register), these two bits select one of the fol- lowing register or data operations and the usage for MMD Access – Register/Data (Reg. Eh). 00 = Register 01 = Data, no post increment 10 = Data, post increment on reads and writes 11 = Data, post increment on writes only	RW	00
D.13:5	Reserved	Reserved	RW	00_0000_000
D.4:0	MMD – Device Address	These five bits set the MMD device address.	RW	0_000
Register Eh	- MMD Acces	s - Register/Data		
E.15:0	MMD – Register/ Data	For the selected MMD device address (Reg. Dh, bits [4:0]), When Reg. Dh, bits [15:14] = 00, this register con- tains the read/write register address for the MMD device address. Otherwise, this register contains the read/write data value for the MMD device address and its selected register address. See also Reg. Dh, bits [15:14], for descriptions of post increment reads and writes of this register for data operation.	RW	0000_0000_0000_ 0000

## TABLE 4-3: IEEE DEFINED REGISTER DESCRIPTIONS (CONTINUED)

**Note 4-1** RW = Read/Write; RO = Read Only; SC = Self-Cleared; LH = Latch High; LL = Latch Low.

### TABLE 4-4: VENDOR SPECIFIC REGISTER DESCRIPTIONS

Address	Name	Description	Mode Note 4-1	Default		
Register 10h – Digital Reserved Control						
10.15:5	Reserved	Reserved	RW	0000_0000_000		
10.4	PLL Off	1 = Turn PLL off automatically in EDPD mode 0 = Keep PLL on in EDPD mode. See also Register 18h, Bit [11] for EDPD mode	RW	0		
10.3:0	Reserved	Reserved	RW	0000		
Register 11h	n – AFE Contro	bl 1				
11.15:6	Reserved	Reserved	RW	0000_0000_00		
11.5	Slow-Oscilla- tor Mode Enable	Slow-oscillator mode is used to disconnect the input reference crystal/clock on the XI pin and select the on-chip slow oscillator when the KSZ8091MNX/RNB device is not in use after power-up. 1 = Enable 0 = Disable This bit automatically sets software power-down to the analog side when enabled.	RW	0		
11.4:0	Reserved	Reserved	RW	0_000		

Address	Name	Description	Mode Note 4-1	Default
Register 15	h – RXER Cou	nter		
15.15:0	RXER Counter	Receive error counter for symbol error frames	RO/SC	0000h
Register 16	h – Operation	Mode Strap Override		
16.15	PME Enable	PME for Wake-on-LAN 1 = Enable 0 = Disable This bit works in conjunction with MMD Address 1Fh, Reg. 0h, Bits [15:14] to define the output for pins 21 and 30.	RW	Set by the PME_EN strapping pin. See the Strap-In Options - KSZ8091MNX sec- tion for details.
16.14:11	Reserved	Reserved	RW	000_0
16.10	Reserved	Reserved	RO	0
16.9	B- CAST_OFF Override	1 = Override strap-in for B-CAST_OFF If bit is '1', PHY Address 0 is non-broadcast.	RW	0
16.8	Reserved	Reserved	RW	0
16.7	MII B-to-B Override	1 = Override strap-in for MII back-to-back mode (also set bit 0 of this register to '1') This bit applies only to KSZ8091MNX.	RW	0
16.6	RMII B-to-B Override	1 = Override strap-in for RMII back-to-back mode (also set bit 1 of this register to '1') This bit applies only to KSZ8091RNB.	RW	0
16.5	NAND Tree Override	1 = Override strap-in for NAND tree mode	RW	0
16.4:2	Reserved	Reserved	RW	0_00
16.1	RMII Override	1 = Override strap-in for RMII mode This bit applies only to KSZ8091RNB.	RW	0
16.0	MII Override	1 = Override strap-in for MII mode This bit applies only to KSZ8091MNX.	RW	1
Register 17	h - Operation I	Node Strap Status		
17.15:13	PHYAD[2:0] Strap-In Sta- tus	[000] = Strap to PHY Address 0 [001] = Strap to PHY Address 1 [010] = Strap to PHY Address 2 [011] = Strap to PHY Address 3 [100] = Strap to PHY Address 4 [101] = Strap to PHY Address 5 [110] = Strap to PHY Address 6 [111] = Strap to PHY Address 7	RO	_
17.12:10	Reserved	Reserved	RO	_
17.9	B- CAST_OFF Strap-In Status	1 = Strap to B-CAST_OFF If bit is '1', PHY Address 0 is non-broadcast.	RO	_
17.8	Reserved	Reserved	RO	_
17.7	MII B-to-B Strap-In Status	1 = Strap to MII back-to-back mode This bit applies only to KSZ8091MNX.	RO	
17.6	RMII B-to-B Strap-In Status	1 = Strap to RMII back-to-back mode This bit applies only to KSZ8091RNB.	RO	_

TABLE 4-4:	VENDOR SPECIFIC REGISTER DESCRIPTIONS (	CONTINUED)	,

© 2016 Microchip Technology Inc.

Address	Name	Description	Mode Note 4-1	Default
17.5	NAND Tree Strap-In Status	1 = Strap to NAND tree mode	RO	_
17.4:2	Reserved	Reserved	RO	—
17.1	RMII Strap-In Status	1 = Strap to RMII mode This bit applies only to KSZ8091RNB.	RO	_
17.0	MII Strap-In Status	1 = Strap to MII mode This bit applies only to KSZ8091MNX.	RO	_
Register 18	h - Expanded C	Control	-	•
18.15:12	Reserved	Reserved	RW	0000
18.11	EDPD Disabled	Energy-detect power-down mode 1 = Disable 0 = Enable See also Register 10h, Bit [4] for PLL off.	RW	1
18.10	100BASE-TX Latency	<ul> <li>1 = MII output is random latency</li> <li>0 = MII output is fixed latency</li> <li>For both settings, all bytes of received preamble are passed to the MII output.</li> <li>This bit applies only to the KSZ8091MNX.</li> </ul>	RW	0
18.9:7	Reserved	Reserved	RW	00_0
18.6	10BASE-T Preamble Restore	1 = Restore received preamble to MII output 0 = Remove all seven bytes of preamble before sending frame (starting with SFD) to MII output This bit applies only to the KSZ8091MNX.	RW	0
18.5:0	Reserved	Reserved	RW	00_0001
Register 1B	h – Interrupt C	ontrol/Status		
1B.15	Jabber Inter- rupt Enable	1 = Enable jabber interrupt 0 = Disable jabber interrupt	RW	0
1B.14	Receive Error Inter- rupt Enable	1 = Enable receive error interrupt 0 = Disable receive error interrupt	RW	0
1B.13	Page Received Interrupt Enable	<ul><li>1 = Enable page received interrupt</li><li>0 = Disable page received interrupt</li></ul>	RW	0
1B.12	Parallel Detect Fault Interrupt Enable	<ul><li>1 = Enable parallel detect fault interrupt</li><li>0 = Disable parallel detect fault interrupt</li></ul>	RW	0
1B.11	Link Partner Acknowl- edge Inter- rupt Enable	<ul><li>1 = Enable link partner acknowledge interrupt</li><li>0 = Disable link partner acknowledge interrupt</li></ul>	RW	0
1B.10	Link-Down Interrupt Enable	1= Enable link-down interrupt 0 = Disable link-down interrupt	RW	0
1B.9	Remote Fault Interrupt Enable	1 = Enable remote fault interrupt 0 = Disable remote fault interrupt	RW	0

### TABLE 4-4: VENDOR SPECIFIC REGISTER DESCRIPTIONS (CONTINUED)

Address	Name	Description	Mode Note 4-1	Default
1B.8	Link-Up Interrupt Enable	1 = Enable link-up interrupt 0 = Disable link-up interrupt	RW	0
1B.7	Jabber Interrupt	1 = Jabber occurred 0 = Jabber did not occur	RO/SC	0
1B.6	Receive Error Interrupt	1 = Receive error occurred 0 = Receive error did not occur	RO/SC	0
1B.5	Page Receive Interrupt	1 = Page receive occurred 0 = Page receive did not occur	RO/SC	0
1B.4	Parallel Detect Fault Interrupt	<ul><li>1 = Parallel detect fault occurred</li><li>0 = Parallel detect fault did not occur</li></ul>	RO/SC	0
1B.3	Link Partner Acknowl- edge Inter- rupt	<ul><li>1 = Link partner acknowledge occurred</li><li>0 = Link partner acknowledge did not occur</li></ul>	RO/SC	0
1B.2	Link-Down Interrupt	1 = Link-down occurred 0 = Link-down did not occur	RO/SC	0
1B.1	Remote Fault Interrupt	1 = Remote fault occurred 0 = Remote fault did not occur	RO/SC	0
1B.0	Link-Up Interrupt	1 = Link-up occurred 0 = Link-up did not occur	RO/SC	0
Register 1D	h – LinkMD Co	ntrol/Status		
1D.15	Cable Diag- nostic Test Enable	<ul> <li>1 = Enable cable diagnostic test. After test has completed, this bit is self-cleared.</li> <li>0 = Indicates cable diagnostic test (if enabled) has completed and the status information is valid for read.</li> </ul>	RW/SC	0
1D.14:13	Cable Diag- nostic Test Result	<ul> <li>[00] = Normal condition</li> <li>[01] = Open condition has been detected in cable</li> <li>[10] = Short condition has been detected in cable</li> <li>[11] = Cable diagnostic test has failed</li> </ul>	RO	00
1D.12	Short Cable Indicator	1 = Short cable (<10 meter) has been detected by LinkMD	RO	0
1D.11:9	Reserved	Reserved	RW	000
1D.8:0	Cable Fault Counter	Distance to fault	RO	0_0000_0000
Register 1E	h – PHY Contro	ol 1		
1E.15:10	Reserved	Reserved	RO	0000_00
1E.9	Enable Pause (Flow Control)	1 = Flow control capable 0 = No flow control capability	RO	0
1E.8	Link Status	1 = Link is up 0 = Link is down	RO	0
1E.7	Polarity Status	1 = Polarity is reversed 0 = Polarity is not reversed	RO	_
1E.6	Reserved	Reserved	RO	0

TABLE 4-4:	VENDOR SPECIFIC REGISTER DESCRIPTIONS	(CONTINUED)

© 2016 Microchip Technology Inc.

Address	Name	Description	Mode Note 4-1	Default
1E.5	MDI/MDI-X State	1 = MDI-X 0 = MDI	RO	_
1E.4	Energy Detect	<ul><li>1 = Signal present on receive differential pair</li><li>0 = No signal detected on receive differential pair</li></ul>	RO	0
1E.3	PHY Isolate	1 = PHY in isolate mode 0 = PHY in normal operation	RW	0
1E.2:0	Operation Mode Indication	[000] = Still in auto-negotiation [001] = 10BASE-T half-duplex [010] = 100BASE-TX half-duplex [011] = Reserved [100] = Reserved [101] = 10BASE-T full-duplex [110] = 100BASE-TX full-duplex [111] = Reserved	RO	000
Register 1F	h – PHY Contr	ol 2		
1F.15	HP_MDIX	1 = HP Auto MDI/MDI-X mode 0 = Microchip Auto MDI/MDI-X mode	RW	1
1F.14	MDI/MDI-X Select	When Auto MDI/MDI-X is disabled, 1 = MDI-X mode Transmit on RXP, RXM (Pins 5, 4) and Receive on TXP, TXM (Pins 7, 6) 0 = MDI mode Transmit on TXP, TXM (Pins 7, 6) and Receive on RXP, RXM (Pins 5, 4)	RW	0
1F.13	Pair Swap Disable	1 = Disable Auto MDI/MDI-X 0 = Enable Auto MDI/MDI-X	RW	0
1F.12	Reserved	Reserved	RW	0
1F.11	Force Link	<ul> <li>1 = Force link pass</li> <li>0 = Normal link operation</li> <li>This bit bypasses the control logic and allows the transmitter to send a pattern even if there is no link.</li> </ul>	RW	0
1F.10	Power Saving	1 = Enable power saving 0 = Disable power saving	RW	0
1F.9	Interrupt Level	<ul><li>1 = Interrupt pin active high</li><li>0 = Interrupt pin active low</li></ul>	RW	0
1F.8	Enable Jabber	<ul><li>1 = Enable jabber counter</li><li>0 = Disable jabber counter</li></ul>	RW	1
1F.7	RMII Refer- ence Clock Select	<ul> <li>1 = RMII 50 MHz clock mode; clock input to XI (pin</li> <li>9) is 50 MHz</li> <li>0 = RMII 25 MHz clock mode; clock input to XI (pin</li> <li>9) is 25 MHz</li> <li>This bit applies only to KSZ8091RNB.</li> </ul>	RW	0
1F.6	Reserved	Reserved	RW	0
1F.5:4	LED Mode	<ul> <li>[00] = LED1: Speed LED0: Link/Activity</li> <li>[01] = LED1: Activity LED0: Link</li> <li>[10], [11] = Reserved The LED1 pin applies only to the KSZ8091RNB.</li> </ul>	RW	00
1F.3	Disable Transmitter	1 = Disable transmitter 0 = Enable transmitter	RW	0

### TABLE 4-4: VENDOR SPECIFIC REGISTER DESCRIPTIONS (CONTINUED)

Address	Name	Description	Mode Note 4-1	Default
1F.2	Remote Loopback	1 = Remote (analog) loopback is enabled 0 = Normal mode	RW	0
1F.1	Enable SQE Test	1 = Enable SQE test 0 = Disable SQE test	RW	0
1F.0	Disable Data Scrambling	1 = Disable scrambler 0 = Enable scrambler	RW	0

TABLE 4-4: VENDOR SPECIFIC REGISTER DESCRIPTIONS (CONTINUED)

Note 4-1 RW = Read/Write; RO = Read Only; SC = Self-Cleared.

### 4.3 MMD Registers

MMD registers provide indirect read/write access to up to 32 MMD Device Addresses with each device supporting up to 65,536 16-bit registers, as defined in Clause 22 of the IEEE 802.3 Specification. The KSZ8091MNX/RNB, however, uses only a small fraction of the available registers. See the Register Descriptions section for a list of supported MMD device addresses and their associated register addresses.

The following two standard registers serve as the portal registers to access the indirect MMD registers.

- Standard register Dh MMD Access Control
- · Standard register Eh MMD Access Register/Data

#### TABLE 4-5: PORTAL REGISTERS (ACCESS TO INDIRECT MMD REGISTERS)

Address	Name	Description	Mode	Default	
Register Dh - MMD Access - Control					
D.15:14	MMD – Operation Mode	For the selected MMD device address (bits [4:0] of this register), these two bits select one of the fol- lowing register or data operations and the usage for MMD Access – Register/Data (Reg. Eh). 00 = Register 01 = Data, no post increment 10 = Data, post increment on reads and writes 11 = Data, post increment on writes only	RW	00	
D.13:5	Reserved	Reserved	RW	00_0000_000	
D.4:0	MMD – Device Address	These five bits set the MMD device address.	RW	0_000	
<b>Register Eh</b>	- MMD Acces	ss - Register/Data			
E.15:0	MMD – Register/ Data	For the selected MMD device address (Reg. Dh, bits [4:0]), When Reg. Dh, bits [15:14] = 00, this register con- tains the read/write register address for the MMD device address. Otherwise, this register contains the read/write data value for the MMD device address and its selected register address. See also Reg. Dh, bits [15:14], for descriptions of post increment reads and writes of this register for data operation.	RW	0000_0000_0000_ 0000	

Examples:

#### **MMD Register Write**

Write MMD – Device Address 1Fh, Register 0h = 0001h to enable link-up detection to trigger PME for WOL.

- 1. Write Register Dh with 001Fh // Set up register address for MMD Device Address 1Fh.
  - Write Register Eh with 0000h // Select register 0h of MMD Device Address 1Fh.
- 3. Write Register Dh with 401Fh // Select register data for MMD Device Address 1Fh, Register 0h.
- 4. Write Register Eh with 0001h // Write value 0001h to MMD Device Address 1Fh, Register 0h.

#### **MMD Register Read**

2.

1. 2.

Read MMD – Device Address 1Fh, Register 19h – 1Bh for the magic packet's MAC address

- Write Register Dh with 001Fh // Set up register address for MMD Device Address 1Fh.
- Write Register Eh with 0019h // Select Register 19h of MMD Device Address 1Fh.
- Write Register Dh with 801Fh // Select register data for MMD Device Address 1Fh, Register 19h // with post increments
- 4. Read Register Eh // Read data in MMD Device Address 1Fh, Register 19h.
- 5. Read Register Eh // Read data in MMD Device Address 1Fh, Register 1Ah.
- 6. Read Register Eh // Read data in MMD Device Address 1Fh, Register 1Bh.

### TABLE 4-6: MMD REGISTER DESCRIPTIONS

Address	Name	Description	Mode	Default
MMD Addre	ss 1h, Registe	r 0h – PMA/PMD Control 1		
1.0.15:13	Reserved	Reserved	RW	000
1.0.12	LPI enable	Lower Power Idle enable	RW	0
1.0.11:0	Reserved	Reserved	RW	0000_0000_0000
MMD Addre	ss 1h, Registe	r 1h – PMA/PMD Status 1		
1.1.15:9	Reserved	Reserved	RO	0000_000
1.1.8	LPI State Entered	1 = PMA/PMD has entered LPI state 0 = PMA/PMD has not entered LPI state	RO/LH	0
1.1.7:4	Reserved	Reserved	RO	0000
1.1.3	LPI State Indication	1 = PMA/PMD is currently in LPI state 0 = PMA/PMD is currently not in LPI state	RO	0
1.1.2:0	Reserved	Reserved	RO	000
MMD Addre	ss 3h, Registe	r 0h – EEE PCS Control 1		
3.0.15:12	Reserved	Reserved	RO	0000
3.0.11	Reserved	Reserved	RW	1
3.0.10	100BASE-TX RXC Clock Stoppable	During receive lower-power idle mode, 1 = RXC clock is stoppable for 100BASE-TX 0 = RXC clock is not stoppable for 100BASE-TX This bit applies only to KSZ8091MNX.	RW	1
3.0.9:4	Reserved	Reserved	RW	00_0001
3.0.3:2	Reserved	Reserved	RO	00
3.0.1:0	Reserved	Reserved	RW	00
MMD Addre	ss 7h, Registe	r 3Ch – EEE Advertisement		
7.3C.15:3	Reserved	Reserved	RO	0000_0000_0000_0
7.3C.2	1000BASE-T EEE Capable	0 = 1000 Mbps EEE is not supported	RO	0
7.3C.1	100BASE-TX EEE Capable	1 = 100 Mbps EEE capable 0 = No 100 Mbps EEE capability This bit is set to '0' as the default after power-up or reset. Set this bit to '1' to enable 100 Mbps EEE mode.	RW	0
7.3C.0	Reserved	Reserved	RO	0
MMD Addre	ss 7h, Registe	r 3Dh – EEE Link Partner Advertisement	•	•
7.3D.15:3	Reserved	Reserved	RO	0000_0000_0000_0

Address	Name	Description	Mode	Default							
7.3D.2		1 = 1000 Mbps EEE capable 0 = No 1000 Mbps EEE capability	RO	0							
7.3D.1		1 = 100 Mbps EEE capable 0 = No 100 Mbps EEE capability	RO	0							
7.3D.0	Reserved	eserved RO 0									
MMD Addre	IMD Address 1Fh, Register 0h – Wake-On-LAN – Control										
1F.0.15:14	PME Output Select	These two bits work in conjunction with Reg. 16h, Bit [15] for PME enable to define the output for pins 21 and 30. INTRP/PME_N2 (pin 21) 00 = INTRP output 01 = PME_N2 output 10 = INTRP and PME_N2 output 11 = Reserved LED0/PME_N1 (pin 30) 00 = PME_N1 output 01 = LED0 output 10 = LED0 output 11 = PME_N1 output	RW	00							
1F.0.13:7	Reserved	Reserved	RO	00_0000_0							
1F.0.6	Magic Packet Detect Enable	<ul><li>1 = Enable magic-packet detection</li><li>0 = Disable magic-packet detection</li></ul>	RW	0							
1F.0.5	Custom- Packet Type 3 Detect Enable	<ul><li>1 = Enable custom-packet, Type 3 detection</li><li>0 = Disable custom-packet, Type 3 detection</li></ul>	RW	0							
1F.0.4	Custom- Packet Type 2 Detect Enable	<ul><li>1 = Enable custom-packet, Type 2 detection</li><li>0 = Disable custom-packet, Type 2 detection</li></ul>	RW	0							
1F.0.3	Custom- Packet Type 1 Detect Enable	1 = Enable custom-packet, Type 1 detection 0 = Disable custom-packet, Type 1 detection	RW	0							
1F.0.2	Custom- Packet Type 0 Detect Enable	<ul><li>1 = Enable custom-packet, Type 0 detection</li><li>0 = Disable custom-packet, Type 0 detection</li></ul>	RW	0							
1F.0.1	Link-Down Detect Enable	1 = Enable link-down detection 0 = Disable link-down detection	RW	0							
1F.0.0	Link-Up Detect Enable	1 = Enable link-up detection 0 = Disable link-up detection	RW	0							

TABLE 4-6:	MMD REGISTER DESCRIPTIONS	(CONTINUED)	)
			,

<sup>© 2016</sup> Microchip Technology Inc.

TABLE 4-6:									
Address	Name	Description	Mode	Default					
MMD Address 1Fh, Register 1h – Wake-On-LAN – Customized Packet, Type 0, Mask 0 MMD Address 1Fh, Register 7h – Wake-On-LAN – Customized Packet, Type 1, Mask 0 MMD Address 1Fh, Register Dh – Wake-On-LAN – Customized Packet, Type 2, Mask 0 MMD Address 1Fh, Register 13h – Wake-On-LAN – Customized Packet, Type 3, Mask 0									
1F.1.15:0 1F.7.15:0 1F.D.15:0 1F.13.15:0	Custom Packet Type X Mask 0	This register selects the bytes in the first 16 bytes of the packet (bytes 1 thru 16) that will be used for CRC calculation. For each bit in this register, 1 = Byte is selected for CRC calculation 0 = Byte is not selected for CRC calculation The register-bit to packet-byte mapping is as fol- lows: Bit [15]: byte-16 : Bit [1]: byte-2 Bit [0]: byte-1	RW	0000_0000_0000_ 0000					
MMD Addres	ss 1Fh, Regist ss 1Fh, Regist	er 2h – Wake-On-LAN – Customized Packet, Type er 8h – Wake-On-LAN – Customized Packet, Type er Eh – Wake-On-LAN – Customized Packet, Type er 14h – Wake-On-LAN – Customized Packet, Typ	1, Mask 1 2, Mask 1						
1F.2.15:0 1F.8.15:0 1F.E.15:0 1F.14.15:0	Custom Packet Type X Mask 1	This register selects the bytes in the second 16 bytes of the packet (bytes 17 thru 32) that will be used for CRC calculation. For each bit in this register, 1 = Byte is selected for CRC calculation 0 = Byte is not selected for CRC calculation The register-bit to packet-byte mapping is as fol- lows: Bit [15]: byte-32	RW	0000_0000_0000_ 0000					
MMD Addres	ss 1Fh, Regist ss 1Fh, Regist	: Bit [1]: byte-18 Bit [0]: byte-17 er 3h – Wake-On-LAN – Customized Packet, Type er 9h – Wake-On-LAN – Customized Packet, Type er Fh – Wake-On-LAN – Customized Packet, Type	1, Mask 2 2, Mask 2						
MMD Addres 1F.3.15:0 1F.9.15:0 1F.F.15:0 1F.15.15:0	Custom Packet Type X Mask 2	This register selects the bytes in the third 16 bytes of the packet (bytes 33 thru 48) that will be used for CRC calculation. For each bit in this register, 1 = Byte is selected for CRC calculation 0 = Byte is not selected for CRC calculation The register-bit to packet-byte mapping is as fol- lows: Bit [15]: byte-48 i	RW	0000_0000_0000_ 0000					
		Bit [1]: byte-34 Bit [0]: byte-33							

## TABLE 4-6: MMD REGISTER DESCRIPTIONS (CONTINUED)

TABLE 4-6:         MMD REGISTER DESCRIPTIONS (CONTINUED)								
Address	Name	Description	Mode	Default				
MMD Address 1Fh, Register 4h – Wake-On-LAN – Customized Packet, Type 0, Mask 3 MMD Address 1Fh, Register Ah – Wake-On-LAN – Customized Packet, Type 1, Mask 3 MMD Address 1Fh, Register 10h – Wake-On-LAN – Customized Packet, Type 2, Mask 3 MMD Address 1Fh, Register 16h – Wake-On-LAN – Customized Packet, Type 3, Mask 3								
1F.4.15:0 1F.A.15:0 1F.10.15:0 1F.16.15:0	Custom Packet Type X Mask 3	This register selects the bytes in the fourth 16 bytes of the packet (bytes 49 thru 64) that will be used for CRC calculation. For each bit in this register, 1 = Byte is selected for CRC calculation 0 = Byte is not selected for CRC calculation The register-bit to packet-byte mapping is as fol- lows: Bit [15]: byte-64 : Bit [1]: byte-50 Bit [0]: byte-49	RW	0000_0000_0000_ 0000				
MMD Addres	ss 1Fh, Regist ss 1Fh, Regist	er 5h – Wake-On-LAN – Customized Packet, Type er Bh – Wake-On-LAN – Customized Packet, Type er 11h – Wake-On-LAN – Customized Packet, Typ er 17h – Wake-On-LAN – Customized Packet, Typ	e 1, Expected e 2, Expecte	d CRC 0 ed CRC 0				
1F.5.15:0 1F.B.15:0 1F.11.15:0 1F.17.15:0	Custom Packet Type X CRC 0	This register stores the lower two bytes for the expected CRC. Bit [15:8] = Byte 2 (CRC [15:8]) Bit [7:0] = Byte 1 (CRC [7:0]) The upper two bytes for the expected CRC are stored in the following register.	RW	0000_0000_0000_ 0000				
MMD Addres	ss 1Fh, Regist ss 1Fh, Regist	er 6h – Wake-On-LAN – Customized Packet, Type er Ch – Wake-On-LAN – Customized Packet, Type er 12h – Wake-On-LAN – Customized Packet, Typ er 18h – Wake-On-LAN – Customized Packet, Typ	e 1, Expecte e 2, Expecte	d CRC 1 ed CRC 1				
1F.6.15:0 1F.C.15:0 1F.12.15:0 1F.18.15:0	Custom Packet Type X CRC 1	This register stores the upper two bytes for the expected CRC. Bit [15:8] = Byte 4 (CRC [31:24]) Bit [7:0] = Byte 3 (CRC [23:16]) The lower two bytes for the expected CRC are stored in the previous register.	RW	0000_0000_0000_ 0000				
MMD Addres	ss 1Fh, Regist	er 19h – Wake-On-LAN – Magic Packet, MAC-DA-(	0	1				
1F.19.15:0	Magic Packet MAC-DA-0	This register stores the lower two bytes of the des- tination MAC address for the magic packet. Bit [15:8] = Byte 2 (MAC Address [15:8]) Bit [7:0] = Byte 1 (MAC Address [7:0]) The upper four bytes of the destination MAC address are stored in the following two registers.	RW	0000_0000_0000_ 0000				
MMD Addres	ss 1Fh, Regist	er 1Ah – Wake-On-LAN – Magic Packet, MAC-DA-	1	·				
1F.1A.15:0	Magic Packet MAC-DA-1	This register stores the middle two bytes of the destination MAC address for the magic packet. Bit [15:8] = Byte 4 (MAC Address [31:24]) Bit [7:0] = Byte 3 (MAC Address [23:16]) The lower two bytes and upper two bytes of the destination MAC address are stored in the previous and following registers, respectively.	RW	0000_0000_0000_ 0000				

TABLE 4-6:	MMD REGISTER DESCRIPTIONS (CONTINUED)
IADLL = 0.	

<sup>© 2016</sup> Microchip Technology Inc.

TABLE 4-6:	MMD REGISTER DESCRIPTIONS (CONTINUED)

Address	Name	Description	Mode	Default						
MMD Addres	MMD Address 1Fh, Register 1Bh – Wake-On-LAN – Magic Packet, MAC-DA-2									
1F.1B.15:0	Magic Packet MAC-DA-2	This register stores the upper two bytes of the des- tination MAC address for the magic packet. Bit [15:8] = Byte 6 (MAC Address [47:40]) Bit [7:0] = Byte 5 (MAC Address [39:32]) The lower four bytes of the destination MAC address are stored in the previous two registers.	RW	0000_0000_0000_ 0000						

**Note 4-1** RW = Read/Write; RO = Read Only; LH = Latch High.

# 5.0 OPERATIONAL CHARACTERISTICS

## 5.1 Absolute Maximum Ratings\*

Supply Voltage (V <sub>IN</sub> )	
(V <sub>DD_1.2</sub> )	–0.5V to +1.8V
(V <sub>DDIO</sub> , V <sub>DDA_3.3</sub> )	–0.5V to +5.0V
Input Voltage (all inputs)	–0.5V to +5.0V
Output Voltage (all outputs)	–0.5V to +5.0V
Lead Temperature (soldering, 10s)	+260°C
Storage Temperature (T <sub>S</sub> )	–55°C to +150°C

\*Exceeding the absolute maximum rating may damage the device. Stresses greater than the absolute maximum rating may cause permanent damage to the device. Operation of the device at these or any other conditions above those specified in the operating sections of this specification is not implied. Maximum conditions for extended periods may affect reliability.

## 5.2 Operating Ratings\*\*

Supply Voltage

(V <sub>DDIO_3.3</sub> , V <sub>DDA_3.3</sub> )	+3.135V to +3.465V
(V <sub>DDIO_2.5</sub> )	+2.375V to +2.625V
(V <sub>DDIO 1.8</sub> )	+1.710V to +1.890V
Ambient Temperature	
(T <sub>A</sub> Commercial)	0°C to +70°C
(T <sub>A</sub> Industrial)	40°C to +85°C
Maximum Junction Temperature (T <sub>J</sub> max.)	+125°C
Thermal Resistance ( $\Theta_{JA}$ )	+45.87°C/W
Thermal Resistance ( $\Theta_{JC}$ )	+15.85°C/W
**The device is not guaranteed to function outside its operating ratings.	

Note: Do not drive input signals without power supplied to the device.

# 6.0 ELECTRICAL CHARACTERISTICS

 $T_A = 25^{\circ}C$ . Specification is for packaged product only.

#### TABLE 6-1: ELECTRICAL CHARACTERISTICS

Parameters	Symbol	Min.	Тур.	Max.	Units	Note
Supply Current (V <sub>DDIO</sub> , V <sub>DI</sub>	<sub>DA 3.3</sub> = 3.3V	/), Note 6	i-1	•		
10BASE-T	I <sub>DD1_3.3V</sub>	—	41	_	mA	Full-duplex traffic @ 100% utilization
100BASE-TX	I <sub>DD2 3.3V</sub>		47	_	mA	Full-duplex traffic @ 100% utilization
EEE (100 Mbps) Mode	I <sub>DD3_3.3V</sub>	_	23	_	mA	TX and RX paths in LPI state with no traffic
EDPD Mode	I <sub>DD4_3.3V</sub>	_	20	_	mA	Ethernet cable disconnected (Reg. 18h.11 = 0)
Power-Down Mode	I <sub>DD5_3.3V</sub>	_	4	—	mA	Software power-down (Reg. 0h.11 = 1)
CMOS Level Inputs						
		2.0		_	V	V <sub>DDIO</sub> = 3.3V
Input High Voltage	V <sub>IH</sub>	1.8		_	V	V <sub>DDIO</sub> = 2.5V
		1.3	—	—	V	V <sub>DDIO</sub> = 1.8V
		—		0.8	V	V <sub>DDIO</sub> = 3.3V
Input Low Voltage	V <sub>IL</sub>	_		0.7	V	V <sub>DDIO</sub> = 2.5V
		_		0.5	V	V <sub>DDIO</sub> = 1.8V
Input Current	I <sub>IN</sub>	_		10	μA	V <sub>IN</sub> = GND ~ V <sub>DDIO</sub>
CMOS Level Outputs						
		2.4		_	V	V <sub>DDIO</sub> = 3.3V
Output High Voltage	V <sub>OH</sub>	2.0		_	V	V <sub>DDIO</sub> = 2.5V
		1.5		_	V	V <sub>DDIO</sub> = 1.8V
		—	—	0.4	V	V <sub>DDIO</sub> = 3.3V
Output Low Voltage	V <sub>OL</sub>	—	_	0.4	V	V <sub>DDIO</sub> = 2.5V
		—	—	0.3	V	V <sub>DDIO</sub> = 1.8V
Output Tri-State Leakage	I <sub>oz</sub>	—		10	μA	—
LED Output						
Output Drive Current	I <sub>LED</sub>	_	8		mA	Each LED pin (LED0, LED1)
All Pull-Up/Pull-Down Pins	(including	Strap-In	Pins)			
		30	45	73	kΩ	V <sub>DDIO</sub> = 3.3V
Internal Pull-Up Resistance	pu	39	61	102	kΩ	V <sub>DDIO</sub> = 2.5V
		48	99	178	kΩ	V <sub>DDIO</sub> = 1.8V
		26	43	79	kΩ	V <sub>DDIO</sub> = 3.3V
Internal Pull-Down Resistance	pd	34	59	113	kΩ	V <sub>DDIO</sub> = 2.5V
Redictance		53	99	200	kΩ	V <sub>DDIO</sub> = 1.8V
100BASE-TX Transmit (me	asured diffe	erentially	after 1:1	transfo	rmer)	
Peak Differential Output Voltage	V <sub>O</sub>	0.95	_	1.05	V	100Ω termination across differential output
Output Voltage Imbalance	V <sub>IMB</sub>	_	_	2	%	100 $\Omega$ termination across differential output
Rise/Fall Time	t <sub>r</sub> /t <sub>f</sub>	3		5	ns	—
Rise/Fall Time Imbalance		0		0.5	ns	
Duty Cycle Distortion	_			±0.25	ns	
Overshoot		_		5	%	_

Parameters	Symbol	Min.	Тур.	Max.	Units	Note
Output Jitter	—		0.7		ns	Peak-to-peak
10BASE-T Transmit (meas	ured differe	ntially af	ter 1:1 tr	ansform	er)	•
Peak Differential Output Voltage	V <sub>P</sub>	2.2	_	2.8	V	100Ω termination across differential output
Jitter Added	—			3.5	ns	Peak-to-peak
Rise/Fall Time	t <sub>r</sub> /t <sub>f</sub>		25	_	ns	—
10BASE-T Receive						
Squelch Threshold	V <sub>SQ</sub>		400	—	mV	5 MHz square wave
Transmitter - Drive Setting						
Reference Voltage of I <sub>SET</sub>	V <sub>SET</sub>	_	0.65	—	V	R(I <sub>SET</sub> ) = 6.49 kΩ
REF_CLK Output						
50 Mhz RMII Clock Output Jitter	_	_	300	_	ps	Peak-to-peak (Applies only to KSZ8091RNB in RMII - 25 MHz Clock Mode)
100 Mbps Mode - Industria	I Applicatio	ns Paran	neters			
Clock Phase Delay – XI Input to MII TXC Output	_	15	20	25	ns	XI (25 MHz clock input) to MII TXC (25 MHz clock output) delay, refer- enced to rising edges of both clocks. (Applies only to KSZ8091MNX in MII mode)
Link Loss Reaction (Indication) Time	tıır		4.4		μs	Link loss detected at receive differen tial inputs to PHY signal indication time for each of the following: 1. For LED mode 00 (KSZ8091RNB only), Speed LED output changes from low (100 Mbps) to high (10 Mbps default state for link-down). 2. For LED mode 01, Link LED outpu changes from low (link-up) to high (link-down). 3. INTRP pin asserts for link-down status change.


## TABLE 6-1: ELECTRICAL CHARACTERISTICS (CONTINUED)

**Note 6-1** Current consumption is for the single 3.3V supply KSZ8091MNX/RNB device only, and includes the transmit driver current and the 1.2V supply voltage (V<sub>DD\_1.2</sub>) that are supplied by the KSZ8091MNX/ RNB.

## 7.0 TIMING DIAGRAMS

## 7.1 MII SQE Timing (10BASE-T)


## FIGURE 7-1: MII SQE TIMING (10BASE-T)



### TABLE 7-1: MII SQE TIMING (10BASE-T) PARAMETERS

Parameter	Description	Min.	Тур.	Max.	Units
t <sub>P</sub>	TXC period	_	400	_	ns
t <sub>WL</sub>	TXC pulse width low		200	_	ns
t <sub>WH</sub>	TXC pulse width high	_	200	_	ns
t <sub>SQE</sub>	COL (SQE) delay after TXEN de-asserted	_	2.2	_	μs
t <sub>SQEP</sub>	COL (SQE) pulse duration		1.0	_	μs

# 7.2 MII Transmit Timing (10BASE-T)




## TABLE 7-2: MII TRANSMIT TIMING (10BASE-T) PARAMETERS

Parameter	Description	Min.	Тур.	Max.	Units
t <sub>P</sub>	TXC period	—	400	_	ns
t <sub>WL</sub>	TXC pulse width low	—	200		ns
t <sub>WH</sub>	TXC pulse width high	—	200		ns
t <sub>SU1</sub>	TXD[3:0] setup to rising edge of TXC	120	—	_	ns
t <sub>SU2</sub>	TXEN setup to rising edge of TXC	120	_		ns
t <sub>HD1</sub>	TXD[3:0] hold from rising edge of TXC	0	_	_	ns
t <sub>HD2</sub>	TXEN hold from rising edge of TXC	0			ns
t <sub>CRS1</sub>	TXEN high to CRS asserted latency	—	600		ns
t <sub>CRS2</sub>	TXEN low to CRS de-asserted latency	—	1.0		μs

<sup>© 2016</sup> Microchip Technology Inc.

## 7.3 MII Receive Timing (10BASE-T)






#### TABLE 7-3: MII RECEIVE TIMING (10BASE-T) PARAMETERS

Parameter	Description	Min.	Тур.	Max.	Units
t <sub>P</sub>	RXC period	_	400	—	ns
t <sub>WL</sub>	RXC pulse width low		200	—	ns
t <sub>WH</sub>	RXC pulse width high	_	200	—	ns
t <sub>OD</sub>	(RXDV, RXD[3:0], RXER) output delay from rising edge of RXC	_	205	_	ns
t <sub>RLAT</sub>	CRS to (RXDV, RXD[3:0]) latency		7.2	—	μs

## 7.4 MII Transmit Timing (100BASE-TX)




## FIGURE 7-4: MII TRANSMIT TIMING (100BASE-TX)

<b>TABLE 7-4:</b>	MII TRANSMIT TIMING (100BASE-TX) PARAMETERS

Parameter	Description	Min.	Тур.	Max.	Units
t <sub>P</sub>	TXC period	—	40	_	ns
t <sub>WL</sub>	TXC pulse width low	—	20	—	ns
t <sub>WH</sub>	TXC pulse width high	—	20	—	ns
t <sub>SU1</sub>	TXD[3:0] setup to rising edge of TXC	10	_	—	ns
t <sub>SU2</sub>	TXEN setup to rising edge of TXC	10	_	—	ns
t <sub>HD1</sub>	TXD[3:0] hold from rising edge of TXC	0	_	—	ns
t <sub>HD2</sub>	TXEN hold from rising edge of TXC	0	_	—	ns
t <sub>CRS1</sub>	TXEN high to CRS asserted latency	—	72	_	ns
t <sub>CRS2</sub>	TXEN low to CRS de-asserted latency	—	72	_	ns

## 7.5 MII Receive Timing (100BASE-TX)




## FIGURE 7-5: MII RECEIVE TIMING (100BASE-TX)

## TABLE 7-5: MII RECEIVE TIMING (10BASE-T) PARAMETERS


Parameter	Description	Min.	Тур.	Max.	Units
t <sub>P</sub>	RXC period	_	40		ns
t <sub>WL</sub>	RXC pulse width low	—	20	_	ns
t <sub>WH</sub>	RXC pulse width high	—	20		ns
t <sub>OD</sub>	(RXDV, RXD[3:0], RXER) output delay from rising edge of RXC	16	21	25	ns
t <sub>RLAT</sub>	CRS to (RXDV, RXD[3:0]) latency	_	170		ns

## 7.6 RMII Timing



#### FIGURE 7-6: RMII TIMING - DATA RECEIVED FROM RMII

## FIGURE 7-7: RMII TIMING - DATA INPUT TO RMII



#### TABLE 7-6: RMII TIMING PARAMETERS - KSZ8091RNB (Note 7-1)

Timing Parameter	Description	Min.	Тур.	Max.	Units
t <sub>CYC</sub>	Clock cycle		20	—	ns
t <sub>1</sub>	Setup time	4	—	—	ns
t <sub>2</sub>	Hold time	2	—	—	ns
t <sub>OD</sub>	Output delay	7	10	13	ns

**Note 7-1** 25 MHz input to XI pin, 50 MHz output from REF\_CLK pin.


## TABLE 7-7: RMII TIMING PARAMETERS - KSZ8091RNB (Note 7-1)

Timing Parameter	Description	Min.	Тур.	Max.	Units
t <sub>CYC</sub>	Clock cycle	_	20		ns
t <sub>1</sub>	Setup time	4	_	-	ns
t <sub>2</sub>	Hold time	2	_	-	ns
t <sub>OD</sub>	Output delay	8	11	13	ns

Note 7-1 50 MHz input to XI pin.

<sup>© 2016</sup> Microchip Technology Inc.

## 7.7 Auto-Negotiation Timing




## FIGURE 7-8: AUTO-NEGOTIATION FAST LINK PULSE (FLP) TIMING

### TABLE 7-8: AUTO-NEGOTIATION FAST LINK PULSE TIMING PARAMETERS

Parameter	Description	Min.	Тур.	Max.	Units
t <sub>BTB</sub>	FLP burst to FLP burst	8	16	24	ms
t <sub>FLPW</sub>	FLP burst width	—	2	_	ms
t <sub>PW</sub>	Clock/Data pulse width	—	100		ns
t <sub>CTD</sub>	Clock pulse to data pulse	55.5	64	69.5	μs
t <sub>CTC</sub>	Clock pulse to clock pulse	111	128	139	μs
—	Number of clock/data pulses per FLP burst	17	_	33	—

## 7.8 MDC/MDIO Timing




## TABLE 7-9: MDC/MDIO TIMING PARAMETERS

Parameter	Description	Min.	Тур.	Max.	Units
f <sub>c</sub>	MDC Clock Frequency		2.5	10	MHz
t <sub>P</sub>	MDC period	_	400	—	ns
t <sub>MD1</sub>	MDIO (PHY input) setup to rising edge of MDC	10	—	—	ns
t <sub>MD2</sub>	MDIO (PHY input) hold from rising edge of MDC	4	—	—	ns
t <sub>MD3</sub>	MDIO (PHY output) delay from rising edge of MDC	5	222	_	ns

<sup>© 2016</sup> Microchip Technology Inc.

## 7.9 Power-Up/Reset Timing

The KSZ8091MNX/RNB reset timing requirement is summarized in Figure 7-10 and Table 7-10.



#### FIGURE 7-10: POWER-UP/RESET TIMING

TABLE 7-10: PC	OWER-UP/RESET TIMING PARAMETERS
----------------	---------------------------------

Parameter	Description	Min.	Тур.	Max.	Units
t <sub>VR</sub>	Supply voltage (V <sub>DDIO</sub> , V <sub>DDA_3.3</sub> ) rise time	300	—	_	μs
t <sub>SR</sub>	Stable supply voltage ( $V_{DDIO}$ , $V_{DDA_{3.3}}$ ) to reset high	10	_	—	ms
t <sub>CS</sub>	Configuration setup time	5	—	_	ns
t <sub>CH</sub>	Configuration hold time	5	—	—	ns
t <sub>RC</sub>	Reset to strap-in pin output	6	—	—	ns

The supply voltage ( $V_{DDIO}$  and  $V_{DDA_{3.3}}$ ) power-up waveform should be monotonic. The 300 µs minimum rise time is from 10% to 90%.

For warm reset, the reset (RST#) pin should be asserted low for a minimum of 500  $\mu$ s. The strap-in pin values are read and updated at the de-assertion of reset.

After the de-assertion of reset, wait a minimum of 100  $\mu$ s before starting programming on the MIIM (MDC/MDIO) interface.

## 8.0 RESET CIRCUIT

Figure 8-1 shows a reset circuit recommended for powering up the KSZ8091MNX/RNB if reset is triggered by the power supply.







Figure 8-2 shows a reset circuit recommended for applications where reset is driven by another device (for example, the CPU or an FPGA). The reset out RST\_OUT\_n from CPU/FPGA provides the warm reset after power up reset. D2 is used if using different  $V_{DDIO}$  between the switch and CPU/FPGA, otherwise, the different  $V_{DDIO}$  will fight each other. If different  $V_{DDIO}$  have to use in a special case, a low  $V_F$  (<0.3V) diode is required (for example, Vishay's BAT54, MSS1P2L and so on), or a level shifter device can be used too. If Ethernet device and CPU/FPGA use same  $V_{DDIO}$  voltage, D2 can be removed to connect both devices directly. Usually, Ethernet device and CPU/FPGA should use same  $V_{DDIO}$  voltage.


#### FIGURE 8-2: RECOMMENDED RESET CIRCUIT FOR CPU/FPGA RESET OUTPUT



<sup>© 2016</sup> Microchip Technology Inc.

# 9.0 REFERENCE CIRCUITS — LED STRAP-IN PINS

The pull-up, float, and pull-down reference circuits for the LED1/SPEED and LED0/PME\_N1/NWAYEN strapping pins are shown in Figure 9-1 for 3.3V and 2.5V  $V_{DDIO}$ .



## FIGURE 9-1: REFERENCE CIRCUITS FOR LED STRAPPING PINS


For 1.8V V<sub>DDIO</sub>, LED indication support is not recommended due to the low voltage. Without the LED indicator, the SPEED and NWAYEN strap-in pins are functional with a 4.7 k $\Omega$  pull-up to 1.8V V<sub>DDIO</sub> or float for a value of '1', and with a 1.0 k $\Omega$  pull-down to ground for a value of '0'.

If using RJ45 jacks with integrated LEDs and 1.8V  $V_{DDIO}$ , a level shifting is required from LED 3.3V to 1.8V. For example, use a bipolar transistor or a level shift device.

# **10.0 REFERENCE CLOCK - CONNECTION AND SELECTION**

A crystal or external clock source, such as an oscillator, is used to provide the reference clock for the KSZ8091MNX/ RNB. For the KSZ8091MNX/RNB in all operating modes and for the KSZ8091RNB in RMII - 25 MHz Clock Mode, the reference clock is 25 MHz. The reference clock connections to XI (Pin 9) and XO (Pin 8), and the reference clock selection criteria, are provided in Figure 10-1 and Table 10-1.

### FIGURE 10-1: 25 MHZ CRYSTAL/OSCILLATOR REFERENCE CLOCK CONNECTION




#### TABLE 10-1: 25 MHZ CRYSTAL/REFERENCE CLOCK SELECTION CRITERIA

Value
25 MHz
±50 ppm
40Ω
16 pF

**Note 10-1** ±60 ppm for overtemperature crystal.

For the KSZ8091RNB in RMII - 50 MHz Clock Mode, the reference clock is 50 MHz. The reference clock connections to XI (Pin 9), and the reference clock selection criteria are provided in Figure 10-2 and Table 10-2.

### FIGURE 10-2: 50 MHZ OSCILLATOR REFERENCE CLOCK CONNECTION



#### TABLE 10-2: 50 MHZ OSCILLATOR/REFERENCE CLOCK SELECTION CRITERIA

Characteristics	Value
Frequency	50 MHz
Frequency Tolerance (max.)	±50 ppm

© 2016 Microchip Technology Inc.

# 11.0 MAGNETIC - CONNECTION AND SELECTION

A 1:1 isolation transformer is required at the line interface. Use one with integrated common-mode chokes for designs exceeding FCC requirements.

The KSZ8091MNX/RNB design incorporates voltage-mode transmit drivers and on-chip terminations.

With the voltage-mode implementation, the transmit drivers supply the common-mode voltages to the two differential pairs. Therefore, the two transformer center tap pins on the KSZ8091MNX/RNB side should not be connected to any power supply source on the board; instead, the center tap pins should be separated from one another and connected through separate 0.1  $\mu$ F common-mode capacitors to ground. Separation is required because the common-mode voltage is different between transmitting and receiving differential pairs.

Figure 11-1 shows the typical magnetic interface circuit for the KSZ8091MNX/RNB.




FIGURE 11-1: TYPICAL MAGNETIC INTERFACE CIRCUIT

Table 11-1 lists recommended magnetic characteristics.

## TABLE 11-1: MAGNETICS SELECTION CRITERIA

Parameter	Value	Test Conditions
Turns Ratio	1 CT : 1 CT	—
Open-Circuit Inductance (min.)	350 µH	100 mV, 100 kHz, 8 mA
Insertion Loss (max.)	–1.1 dB	100 kHz to 100 MHz
HIPOT (min.)	1500 V <sub>RMS</sub>	—

Table 11-2 is a list of compatible single-port magnetics with separated transformer center tap pins on the PHY chip side that can be used with the KSZ8091MNX/RNB.


Manufacturer	Part Number	Temperature Range	Magnetic + RJ-45
Bel Fuse	S558-5999-U7	0°C to 70°C	No
Bel Fuse	SI-46001-F	0°C to 70°C	Yes
Bel Fuse	SI-50170-F	0°C to 70°C	Yes
Delta	LF8505	0°C to 70°C	No
HALO	HFJ11-2450E	0°C to 70°C	Yes
HALO	TG110-E055N5	-40°C to 85°C	No
LANKom	LF-H41S-1	0°C to 70°C	No
Pulse	H1102	0°C to 70°C	No
Pulse	H1260	0°C to 70°C	No
Pulse	HX1188	-40°C to 85°C	No
Pulse	J00-0014	0°C to 70°C	Yes
Pulse	JX0011D21NL	-40°C to 85°C	Yes
TDK	TLA-6T718A	0°C to 70°C	Yes
Transpower	HB726	0°C to 70°C	No
Wurth/Midcom	000-7090-37R-LF1	-40°C to 85°C	No

TABLE 11-2: COMPATIBLE SINGLE-PORT 10/100 MAGNETICS

<sup>© 2016</sup> Microchip Technology Inc.

# 12.0 PACKAGE OUTLINE

#### FIGURE 12-1: 32-LEAD QFN 5 MM X 5 MM PACKAGE



# APPENDIX A: DATA SHEET REVISION HISTORY

Revision	Section/Figure/Entry	Correction
DS00002275A (09-15-16)		Converted Micrel data sheet KSZ8091MNX/RNB to Microchip DS00002275A. Minor text changes throughout.

<sup>© 2016</sup> Microchip Technology Inc.

# THE MICROCHIP WEB SITE

Microchip provides online support via our WWW site at www.microchip.com. This web site is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the web site contains the following information:

- **Product Support** Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- **General Technical Support** Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

# **CUSTOMER CHANGE NOTIFICATION SERVICE**

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip web site at www.microchip.com. Under "Support", click on "Customer Change Notification" and follow the registration instructions.

# **CUSTOMER SUPPORT**

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Field Application Engineer (FAE)
- Technical Support

Customers should contact their distributor, representative or field application engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the web site at: http://microchip.com/support

## **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO. Device Int	X X X XX — XX I I I I terface Package Special Temperature Media Type Attribute	Examples: a) KSZ8091MNXCA MII Interface 32-pin QFN
Device:	KSZ8091	No Special Attribute Commercial Temperature Tray b) KSZ8091MNXIA
Interface:	M = MII R = RMII	MII Interface 32-pin QFN No Special Attribute Industrial Temperature
Package:	N = 32-pin QFN	Tray c) KSZ8091MNXCA-TR MII Interface
Special Attribute:	B = 25 MHz In/50 MHz Out Clocks X = None	32-pin QFN No Special Attribute Commercial Temperature Tape & Reel
Temperature:	CA = 0°C to +70°C (Commercial) IA = -40°C to +85°C (Industrial)	d) KSZ8091MNXIA-TR MII Interface 32-pin QFN No Special Attribute
Media Type:	blank = Tray TR = Tape & Reel	Industrial Temperature Tape & Reel e) KSZ8091RNBCA RMII Interface 32-pin QFN 25 MHz In/50 MHz Out Clocks Commercial Temperature Tray f) KSZ8091RNBIA RMII Interface 32-pin QFN 25 MHz In/50 MHz Out Clocks Industrial Temperature Tray g) KSZ8091RNBCA-TR RMII Interface 32-pin QFN 25 MHz In/50 MHz Out Clocks Commercial Temperature Tape & Reel h) KSZ8091RNBIA-TR RMII Interface 32-pin QFN 25 MHz In/50 MHz Out Clocks Industrial Temperature Tape & Reel

<sup>© 2016</sup> Microchip Technology Inc.

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### Trademarks

The Microchip name and logo, the Microchip logo, AnyRate, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KeeLoq, KeeLoq logo, Kleer, LANCheck, LINK MD, MediaLB, MOST, MOST logo, MPLAB, OptoLyzer, PIC, PICSTART, PIC32 logo, RightTouch, SpyNIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, ETHERSYNCH, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and QUIET-WIRE are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, RightTouch logo, REAL ICE, Ripple Blocker, Serial Quad I/O, SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2016, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-0944-1

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and mulfacture of development systems is ISO 9001:2000 certified.

© 2016 Microchip Technology Inc.



# **Worldwide Sales and Service**

#### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

**Chicago** Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

**Cleveland** Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway

Harbour City, Kowloon Hong Kong Tel: 852-2943-5100 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

**China - Beijing** Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

**China - Chengdu** Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

**China - Hangzhou** Tel: 86-571-8792-8115 Fax: 86-571-8792-8116

China - Hong Kong SAR Tel: 852-2943-5100

**China - Nanjing** Tel: 86-25-8473-2460 Fax: 86-25-8473-2470

Fax: 852-2401-3431

China - Qingdao Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

**China - Shanghai** Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

**China - Shenzhen** Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

**China - Wuhan** Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

**China - Xian** Tel: 86-29-8833-7252 Fax: 86-29-8833-7256 ASIA/PACIFIC China - Xiamen Tel: 86-592-2388138

Fax: 86-592-2388130 China - Zhuhai Tel: 86-756-3210040 Fax: 86-756-3210049

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-3019-1500

Japan - Osaka Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

**Japan - Tokyo** Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

**Korea - Daegu** Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

**Singapore** Tel: 65-6334-8870 Fax: 65-6334-8850

**Taiwan - Hsin Chu** Tel: 886-3-5778-366 Fax: 886-3-5770-955

**Taiwan - Kaohsiung** Tel: 886-7-213-7828

**Taiwan - Taipei** Tel: 886-2-2508-8600

Fax: 886-2-2508-0102 Thailand - Bangkok Tel: 66-2-694-1351

Fax: 66-2-694-1350

#### EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Dusseldorf Tel: 49-2129-3766400

Germany - Karlsruhe Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

**Italy - Milan** Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Venice Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Poland - Warsaw Tel: 48-22-3325737

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

06/23/16