


# TP 3150S - Touch panel



2400458

<https://www.phoenixcontact.com/us/products/2400458>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel with 38.1 cm/15" TFT display (analog resistive (polyester)), 1024 x 768 pixel(s) (XGA), 65536 colors, Arm<sup>®</sup> Cortex<sup>®</sup>-A8, 800 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows<sup>®</sup> Embedded Compact 7 and user software: Visu+ / AX OPC Server. (bus system: without)

## Your advantages

- Acoustic warning from alarms via integrated buzzer (85 dB)
- Energy efficient due to LED backlighting
- Visu+ RT and AX OPC server integrated as standard in all devices
- Easy IP address allocation and active connection monitoring thanks to PROFINET-Device according to Conformance Class B
- Display available in sizes from 14.5 cm (5.7") to 39.05 cm (15.4")
- Versatile communication options, even with third-party systems, thanks to numerous drivers and interfaces
- Easy installation, low installation depth, and compact design
- Short startup time

## Commercial data

Item number	2400458
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR17
Product key	DRCABC
Catalog page	Page 472 (C-6-2019)
GTIN	4055626055923
Weight per piece (including packing)	2,300 g
Weight per piece (excluding packing)	3,768 g
Customs tariff number	84714100
Country of origin	DE

# TP 3150S - Touch panel



2400458

<https://www.phoenixcontact.com/us/products/2400458>

## Technical data

### Product properties

Product type	Operator panel
--------------	----------------

### Computer data

Processor	Arm® Cortex®-A8, 800 MHz
Operating system	Windows® Embedded Compact 7
RAM	512 MB RAM
Data storage system	Flash, 1 GB
Slots	1x SD

### Display

Display type	38.1 cm/15" TFT
Screen resolution	1024 x 768 Pixel(s) (XGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	480 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	65536 colors
Reading angle left	80 °
Reading angle right	80 °
Reading angle top	65 °
Reading angle bottom	80 °

### Software

User software	Visu+ AX OPC Server
---------------	------------------------

### System requirements

Runtime system	Visu+ Runtime
----------------	---------------

### Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without

### System properties

User software	Visu+ AX OPC Server
---------------	------------------------

### System requirements

Runtime system	Visu+ Runtime
----------------	---------------

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

# TP 3150S - Touch panel



2400458

<https://www.phoenixcontact.com/us/products/2400458>

## Supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Power supply unit	24 V DC $\pm$ 20 %
Typical current consumption	0.6 A

## Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

## Supply

Power consumption	typ. 14.4 W
-------------------	-------------

## Mounting

Mounting type	Front mounting
---------------	----------------

## Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	20 % ... 85 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

## Dimensions

### External dimensions

Width / Height / Depth	400 mm / 329 mm / 5 mm (Dimensions of the front plate)
------------------------	--

### Installation dimensions

Width / Height / Installation depth	372 mm / 301 mm / 55 mm (Installation cutout)
-------------------------------------	---

# TP 3150S - Touch panel

2400458

<https://www.phoenixcontact.com/us/products/2400458>



## Classifications

### ECLASS

ECLASS-11.0

27330201

### ETIM

ETIM 8.0

EC001412

### UNSPSC

UNSPSC 21.0

43211900

# TP 3150S - Touch panel

2400458

<https://www.phoenixcontact.com/us/products/2400458>



## Environmental product compliance

REACH SVHC	Lead 7439-92-1
	Diazene-1,2-dicarboxamide (C,C'-azodi(formamide)) (ADCA) 123-77-3
China RoHS	Environmentally Friendly Use Period = 15;
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

# TP 3150S - Touch panel

2400458

<https://www.phoenixcontact.com/us/products/2400458>



## Accessories

### TOUCH PEN - Touch pen

2701379

<https://www.phoenixcontact.com/us/products/2701379>



Touch pen for analog-resistive HMI's, silver coated. Delivery includes self-adhesive pen holder.

---

### USB FLASH DRIVE - USB memory stick

2402809

<https://www.phoenixcontact.com/us/products/2402809>



USB memory stick, 8 GB

# TP 3150S - Touch panel

2400458

<https://www.phoenixcontact.com/us/products/2400458>



## SD FLASH 2GB - Program / configuration memory

2988162

<https://www.phoenixcontact.com/us/products/2988162>



Program and configuration memory, for extending the internal flash memory, pluggable, 2 GB.

---

## HMI BATTERY - Battery/accumulator

2701383

<https://www.phoenixcontact.com/us/products/2701383>

Lithium battery



# TP 3150S - Touch panel

2400458

<https://www.phoenixcontact.com/us/products/2400458>



## HMI SCB MOUNTING KIT 4 - Mounting material

2701384

<https://www.phoenixcontact.com/us/products/2701384>



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

---

## HMI SCB MOUNTING KIT 6 - Mounting material

2701385

<https://www.phoenixcontact.com/us/products/2701385>



HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.



# TP 3150S - Touch panel

2400458

<https://www.phoenixcontact.com/us/products/2400458>



## HMI SCB MOUNTING KIT 8 - Mounting material

2701387

<https://www.phoenixcontact.com/us/products/2701387>




HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

## MC 1,5/ 3-STF-3,5 BD:1-3 - PCB connector

1751312

<https://www.phoenixcontact.com/us/products/1751312>



PCB connector, nominal cross section: 1.5 mm<sup>2</sup>, color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MC 1,5/...-STF, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting: Screw flange, type of packaging: packed in cardboard

# TP 3150S - Touch panel

2400458

<https://www.phoenixcontact.com/us/products/2400458>




## 15,0" DISPLAY PROTECTIVE FOIL - Protective foil

2701378

<https://www.phoenixcontact.com/us/products/2701378>

Protective film set comprising 10 pieces of film for a 15" display. Including a squeegee to apply film and instructions.



---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)