

ADJUSTABLE PRECISION SHUNT REGULATORS

Description

The AN431 series ICs are three-terminal adjustable shunt regulators with guaranteed thermal stability over a full operation range. These ICs feature sharp turn-on characteristics, low temperature coefficient and low output impedance, which make them ideal substitutes for Zener diodes in applications such as switching power supply, charger and other adjustable regulators.

The output voltage of these ICs can be set to any value between V_{REF} (2.5V) and the maximum cathode voltage (36V).

The AN431 precision reference is offered in two voltage tolerance: 0.5% and 1.0%.


These ICs are available in SOT-23 package.

Features

- Programmable Precise Output Voltage from 2.5V to 36V
- High Stability under Capacitive Load
- Low Temperature Deviation: 4.5mV Typical
- Low Equivalent Full-range Temperature Coefficient with 20PPM°C Typical
- Low Dynamic Output Resistance: 0.15Ω Typical
- Sink Current Capacity from 1mA to 100mA
- Low Output Noise
- Wide Operating Range of -40 to +125°C
- Lead-Free Packages: SOT-23
 - Totally Lead-Free; RoHS Compliant (Notes 1 & 2)
- Lead-Free Packages, Available in "Green" Molding Compound: SOT-23
 - Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
 - Halogen and Antimony Free. "Green" Device (Note 3)

Pin Assignments

(Top View)



SOT-23


Applications

- Charger
- Voltage Adapter
- Switching Power Supply
- Graphic Card
- Precision Voltage Reference

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


Typical Applications Circuit




Shunt Regulator




Typical Applications Circuit (Cont.)



High Current Shunt Regulator




Current Source or Current Limit



Precision 5V 1A Regulator




Typical Applications Circuit (Cont.)




PWM Converter with Reference

Functional Block Diagram







Absolute Maximum Ratings (Note 4)

Symbol	Parameter	Rating	Unit
V _{KA}	Cathode Voltage	40	V
I _{KA}	Cathode Current Range (Continuous)	-100 to 150	mA
I _{REF}	Reference Input Current Range	10	mA
P _D	Power Dissipation	370	mW
TJ	Junction Temperature	+150	°C
T _{STG}	Storage Temperature Range	-65 to +150	°C
ESD ESD (Human Body Model)		2000	V

Note 4: Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V _{KA}	Cathode Voltage	V _{REF}	36	V
I _{KA}	Cathode Current	1.0	100	mA
T _A	Operating Ambient Temperature Range	-40	+125	°C






AN431

Electrical Characteristics (@TA=+25°C, unless otherwise specified.)


Symbol	Param	eter	Test Circuit	Conditions		Min	Min Typ Max Unit		Unit
.,	Reference	0.5%	4	V _{KA} =V _{REF} , I _{KA} =10mA		2.487	2.500	2.512	V
V _{REF}	Voltage	1.0%	4			2.475	2.500	2.525	
	Deviation of Reference Voltage Over Full Temperature Range		4	V _{KA} =V _{REF} , I _{KA} =10mA	0 to +70°C	_	4.5	8	mV
ΔV_{REF}					-40 to +85°C	_	4.5	10	
					-40 to +125°C	_	4.5	16	
ΔV _{REF} /	Ratio of Change in Reference Voltage to the Change in Cathode Voltage		_	I _{KA} =10mA	ΔV_{KA} =10V to V_{REF}	_	-1.0	-2.7	mV/V
ΔV_KA			5		ΔV _{KA} =36V to 10V		-0.5	-2.0	
I _{REF}	Reference Current		5	I _{KA} =10mA, R1=10KΩ, R2=∞		_	0.7	4	μA
ΔI_{REF}	Deviation of Reference Current Over Full Temperature Range		5	I _{KA} =10mA, R T _A =-40 to +1	1=10KΩ, R2=∞, 25°C	-	0.4	1.2	μA
I _{KA} (Min)	Minimum Cathode Current for Regulation		4	V _{KA} =V _{REF}		-	0.4	1.0	mA
I _{KA} (Off)	Off-state Cathode (Current	6	6 V _{KA} =36V, V _{REF} =0		_	0.05	1.0	μΑ
Z _{KA}	Dynamic Impedance	e	4	$V_{KA}=V_{REF}$, $I_{KA}=1$ to 100mA, $f\leq 1.0kHz$		_	0.15	0.5	Ω
θЈС	Thermal Resistance	e	-	SOT-23		_	135	_	°C/W




Electrical Characteristics (Cont.)



Test Circuit 4 for V_{KA} = V_{REF}



Test Circuit 5 for V_{KA} > V_{REF}




Test Circuit 6 for I_{OFF}




Performance Characteristics


Reference Voltage vs. Ambient Temperature




Cathode Current vs. Cathode Voltage




Off-state Cathode Current vs. Ambient Temperature




Reference Current vs. Ambient Temperature



Cathode Current vs. Cathode Voltage




Ratio of Delta Reference Voltage to the Ratio of Delta Cathode Voltage







Performance Characteristics (Cont.)


Small Signal Voltage Gain vs. Frequency







Reference Impedance vs. Frequency





Stability Boundary Conditions vs. Load Capacitance









Performance Characteristics (Cont.)


Pulse Response of Input and Output Voltage







Ordering Information






D I		Temperature	O a sa altiti a sa	Part Number		Marking ID			
	Package	Range	Condition	Lead Free	Green	Lead Free	Green	Packing	
	SOT-23	23 -40 to +125°C	0.5%	AN431AN- ATRE1	AN431AN- ATRG1	EB1	GB1	3000/ Tape & Reel	
			1.0%	AN431BN- ATRE1	AN431BN- ATRG1	EB2	GB2	3000/ Tape & Reel	

Marking Information






A : Logo

XXX : Marking ID (See Ordering Information)



Package Outline Dimensions (All dimensions in mm(inch).)

(1) Package Type: SOT-23




Downloaded from **Arrow.com**.



Suggested Pad Layout

(1) Package Type: SOT-23



Dimensions Z (mm)/(inch)		G	X	Y	E
		(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)
Value	2.900/0.114	1.100/0.043	0.800/0.031	0.900/0.035	0.950/0.037

– E –



AN431

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

www.diodes.com