


PIPE-TO-PIPE AND STUD CONNECTORS


Ø
16.5
25
40



PLUG-IN REDUCER


| Transair® | ØD1 | ØD2 | ØG | Z | L | Kg |
|------------|-----|------|------|----|-------|-------|
| 6666 17 25 | 25 | 16.5 | 34 | 51 | 77 | 0.052 |
| 6666 25 40 | 40 | 25 | 44.5 | 71 | 100.5 | 0.126 |

Ø
50
63



| Transair® | ØD1 | ØD2 | ØG | L | Kg |
|------------|-----|-----|----|-----|-------|
| 6666 25 50 | 50 | 25 | 45 | 97 | 0.210 |
| 6666 40 50 | 50 | 40 | 67 | 116 | 0.317 |
| 6666 40 63 | 63 | 40 | 67 | 120 | 0.373 |
| 6666 50 63 | 63 | 50 | 80 | 125 | 0.520 |


Ø
76
100
168



| Transair® | ØD1 | ØD2 | L | Kg |
|------------|-----|-----|-------|-------|
| RX64 L1 50 | 76 | 50 | 220 | 0.530 |
| RX64 L1 63 | 76 | 63 | 230 | 0.584 |
| RX64 L3 50 | 100 | 50 | 343 | 1.290 |
| RX64 L3 63 | 100 | 63 | 250 | 0.850 |
| RX66 L3 L1 | 100 | 76 | 192.5 | 0.702 |
| RA66 L8 L1 | 168 | 76 | 210 | 1.388 |
| RA66 L8 L3 | 168 | 100 | 210 | 1.502 |

Use 1 connector RR01 to connect plug-in reducer RX64, RX66 and RA66 to Transair® aluminium pipe Ø76 or Ø100 and 1 pipe-to-pipe connector (6606) to connect to Transair® aluminium pipe Ø50 or Ø63.

Ø
16.5
25
40




VENTED END CAP

| Transair® | ØD | E | ØG | H | L | Kg |
|------------|------|------|----|------|------|-------|
| 6625 17 00 | 16.5 | 25.5 | 34 | 45.5 | 62.5 | 0.145 |
| 6625 25 00 | 25 | 33 | 45 | 47 | 75 | 0.061 |
| 6625 40 00 | 40 | 34.5 | 67 | 54 | 98.5 | 0.180 |

Model Ø16.5: supplied with Ø6mm plug
Models Ø25 and Ø40: supplied with Ø8mm plug


Ø
50
63



| Transair® | ØD | ØG | H | L | Kg |
|------------|----|----|------|-----|-------|
| 6625 50 00 | 50 | 80 | 67 | 107 | 0.423 |
| 6625 63 00 | 63 | 91 | 72.5 | 111 | 0.496 |

Supplied with Ø8mm plug

Ø
76
100
168



| Transair® | ØD | L | Kg |
|------------|-----|-----|-------|
| RA25 L1 04 | 76 | 123 | 0.642 |
| RA25 L3 04 | 100 | 123 | 0.929 |
| RA25 L8 04 | 168 | 116 | 1.200 |

Use 1 connector RR01 to connect end cap RA25 to Transair® aluminium pipe Ø76, Ø100 or Ø168.
Supplied with 1/2" threaded plug.