

1-1337451-0 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

BNC RF Connectors

BNC BHSkt 50Ohm Silver Pltd

1-1337451-0

TE Internal Number: 1-1337451-0

Product Highlights [View All](#)

- Connector - RF
- Jack
- Connector Style = Jack
- Body Style = Bulkhead
- Not Surface Mountable

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

Product Drawings

[BNC BULKHEAD SOCKET FRONT MOUNT 50 OHM LESS SOLDER TAG](#) (PDF, English) [.tif available](#)

Product Environmental Compliance

TE Material Declaration

[MD_1-1337451-0_11162011331](#) (PDF, English)

Please Note:

Use the Product Drawing for all design activity

Product Type Features		Contact Features	
Product Type Help information about Product Type	Connector - RF	Center Contact Material Help information about Center Contact Material	Brass
Gender	Jack	Center Contact Plating Help information about Center Contact Plating	Silver
Grade Help information about Grade	Professional	Housing Features	
Sealed Help information about Sealed	No	Connector Style	Jack
Isolated Help information about Isolated	No	Configuration Features	
Dielectric Material Help information about Dielectric Material	PTFE	Number of Ports	1
Flats Dimension	11.0 A/F	Solder Terminal	With
Mechanical Attachment		Industry Standards	
Surface Mountable	No	Government/Industry Qualification	No
Hardware Included Help information about Hardware Included	No	RoHS/ELV Compliance Help information about RoHS/ELV Compliance	RoHS compliant, ELV compliant
Panel Mount Retention Help information about Panel Mount Retention	With	Lead Free Solder Processes Help information about Lead Free Solder Processes	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
Panel Mount Retention Type	Hex Nut	RoHS/ELV Compliance History	Converted to comply with RoHS directive
Panel Attachment Style	Front Mount	Military Style Number	UG-1094/U
Panel Cutout	8.9mm x 9.7mm D-Shape	Environmental	
Flange Dimension [Dia.] (mm [in])	12.5 [0.492]	Operating Temperature (Max.) (°C)	165
Electrical Characteristics		Packaging Features	
Connector Impedance (Ω) Help information about Connector Impedance (Ω)	50	Packaging Method	Individual
Frequency	DC - 4 GHz	Packaging Quantity	50
Dimensions		Other	
Panel Thickness (mm [in])	1.50 - 2.90 [0.059 - 0.114]	Brand	Greenpar
Body Features		Comment	Without Solder Tag
Body Style	Bulkhead		
Body Material Help information about Body Material	Brass		
Body Plating Help information about Body Plating	Silver		
Polarized Help information about Polarized	No		
Flange and Thread Material	Brass		
Lockwasher Material	Brass		
Lockwasher Plating	Silver		
Product Compliance			

[Converted to EU RoHS/ELV Compliant](#) [Help information about](#) These products comply with the substance restrictions of the Restriction of Hazardous Substances Directive 2011/65/EU (RoHS2). These products also comply with the End of Life Vehicles Directive 2000/53/EC (ELV). The RoHS2 Directive requires certain electrical and electronic products be free (except for trace impurities) of mercury, cadmium, hexavalent chromium, PBB, PBDE and lead. Certain exemptions are allowed such as lead used as an alloying additive in copper, steel and aluminum. Finished electrical and electronic products will be CE marked as required by Directive 2011/65/EU (RoHS2). Components may not be CE marked.

EU RoHS/ELV Compliance

[Statement of Compliance](#)

[View All Product Compliance](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

