



Specification:
 1. Electrical Char
 Insulation Resistance: 500MΩ min, 500V DC for 1 minute
 Contact Resistance: 20mΩ max.
 Rating Current: 1.5A max.
 Rating Voltage: 120V AC
 Dielectric Voltage: 1000 Vrms at 1MA 60 sec. min.

2. Physical Char
 Housing: PBT Glass filled (UL 94V-0) Color: Black
 Soldering Temperature: 235°C for 5 sec.
 Spring Wire: 0.45mm Dia Phosphor Bronze
 6u" Gold plating over Nickel
 Temperature Range: -40°C to +85°C
 Durability: 550 mating cycles min.

3. Packing: Tray

RoHS compliant
 Unit:mm

Scale	Free						
TOLERANCE							
.XX	±0.20					Drawn	04.08.2016
.XXX	±0.13					Approved	04.08.2016
.XXXX	±0.05						
DIM	TOL						
Angle	+0°30'	Id.	①	Drawn	Winnie		
		Modification		Date	04.08.2016	Name	Winnie

Customer-No.	Date	Name	Customer-No.	Drawing-No.	Replace	SHEET
ASSMANN WSW-No.	04.08.2016	Winnie	A-2004-1-4-LP-N-R	ASSMANN	ASS 7320 CO	rev00
				WSW components		

1	2	3	4	5	6	7
1	2	3	4	5	6	7
H	G	F	E	D	C	B
H	G	F	E	D	C	B