


SERIES


**DC780R
DC780**



High Current Power Line Chokes



Actual Size



Physical Parameters

	Inches	Millimeters
A	0.775 ± 0.025	19.6 ± 0.6
B (C/L to C/L)	See Characteristics table	
C	0.750 Min.	19.05 Min.
D	0.815 ± 0.015	20.7 ± 0.4
E (Ref. only)	0.195 Max.	4.95 Max.
F	Clearance Hole for 4/40 Screw	

Leads Tinned to within 1/16" of Body

Inductance Measured @ 1 KHz with 0 Amps dc

Mechanical Configuration Center hole allows for mechanical mounting; insulated bobbins.

Operating Temperature

-55°C to +125°C;
-55°C to +80°C @ full rated current

Current Rating at 80°C Ambient 45°C Rise

Incremental Current Minimum current which causes a 5% max. change in Inductance

Power Dissipation at 80°C 1.400 Watts Max.

Dielectric Withstanding Voltage 1000 V RMS Min.

Marking DELEVAN; DC780; dash number with tolerance letter. Note: An R after DC780 indicates a RoHS component.

Example: DC780R-103K

DELEVAN
DC780R
103K

Packaging Bulk only

*Internal Bobbin may be green or black.

MAXIMUM (OHMS) @ 25°C
DC RESISTANCE
CURRENT RATING (A DC)
INCREMENTAL CURRENT (A DC)
(Inches, Reference)
DIMENSION B
(Inches, Reference)
LEAD DIAMETER
(Inches, Reference)

	SERIES DC780						
DASH NUMBER*	NOMINAL INDUCTANCE (µH)	TOLERANCE	DC RESISTANCE MAXIMUM (OHMS) @ 25°C	CURRENT RATING (A DC)	INCREMENTAL CURRENT (A DC)	DIMENSION B (Inches, Reference)	LEAD DIAMETER (Inches, Reference)
-102L	1.0	± 15%	0.003	11.4	110.0	0.620	0.051
-122L	1.2	± 15%	0.003	11.4	108.0	0.620	0.051
-152L	1.5	± 15%	0.003	11.4	89.0	0.620	0.051
-182L	1.8	± 15%	0.003	11.4	81.0	0.620	0.051
-222L	2.2	± 15%	0.004	11.4	73.0	0.620	0.051
-272L	2.7	± 15%	0.005	11.4	66.0	0.620	0.051
-332L	3.3	± 15%	0.005	11.4	60.0	0.620	0.051
-392L	3.9	± 15%	0.005	11.4	55.0	0.620	0.051
-472L	4.7	± 15%	0.005	11.4	50.0	0.620	0.051
-562L	5.6	± 15%	0.006	11.4	46.0	0.620	0.051
-682L	6.8	± 15%	0.007	11.4	42.0	0.620	0.051
-822L	8.2	± 15%	0.007	11.4	38.0	0.620	0.051
-103K	10.0	± 10%	0.009	11.4	34.5	0.620	0.051
-123K	12.0	± 10%	0.009	11.4	31.5	0.620	0.051
-153K	15.0	± 10%	0.013	9.0	28.2	0.625	0.045
-183K	18.0	± 10%	0.018	7.2	25.7	0.630	0.045
-223K	22.0	± 10%	0.019	7.2	23.3	0.630	0.045
-273K	27.0	± 10%	0.026	5.5	21.0	0.546	0.040
-333K	33.0	± 10%	0.029	5.5	19.0	0.546	0.036
-393K	39.0	± 10%	0.030	5.5	17.5	0.594	0.036
-473K	47.0	± 10%	0.035	5.5	15.9	0.625	0.036
-563K	56.0	± 10%	0.039	5.5	14.6	0.625	0.036
-683K	68.0	± 10%	0.053	4.8	13.2	0.656	0.036
-823K	82.0	± 10%	0.060	4.8	12.1	0.656	0.036
-104K	100	± 10%	0.080	4.0	10.9	0.593	0.036
-124K	120	± 10%	0.090	4.0	10.0	0.593	0.036
-154K	150	± 10%	0.098	4.0	8.9	0.593	0.032
-184K	180	± 10%	0.110	4.0	8.1	0.593	0.032
-224K	220	± 10%	0.150	2.8	7.4	0.593	0.029
-274K	270	± 10%	0.213	2.0	6.6	0.562	0.025
-334K	330	± 10%	0.305	1.6	6.0	0.590	0.025
-394K	390	± 10%	0.320	1.6	5.5	0.590	0.025
-474K	470	± 10%	0.355	1.6	5.0	0.590	0.025
-564K	560	± 10%	0.388	1.6	4.6	0.590	0.023
-684K	680	± 10%	0.430	1.6	4.2	0.590	0.023
-824K	820	± 10%	0.590	1.3	3.8	0.590	0.023
-105K	1,000	± 10%	0.818	1.0	3.5	0.590	0.020
-125K	1,200	± 10%	1.140	0.8	3.2	0.590	0.018
-155K	1,500	± 10%	1.260	0.8	2.8	0.590	0.018
-185K	1,800	± 10%	1.390	0.8	2.6	0.590	0.018
-225K	2,200	± 10%	1.540	0.8	2.3	0.590	0.018

*Complete part # must include series # PLUS the dash #

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delevan:](#)

[DC780R-123K](#) [DC780R-125K](#) [DC780R-333K](#) [DC780R-334K](#) [DC780R-332L](#) [DC780R-392L](#) [DC780R-394K](#)
[DC780R-393K](#) [DC780R-155K](#) [DC780R-153K](#) [DC780R-152L](#) [DC780R-154K](#) [DC780R-102L](#) [DC780R-104K](#)
[DC780R-103K](#) [DC780R-105K](#) [DC780R-122L](#) [DC780R-124K](#) [DC780R-182L](#) [DC780R-184K](#) [DC780R-183K](#)
[DC780R-185K](#) [DC780R-473K](#) [DC780R-474K](#) [DC780R-472L](#) [DC780R-824K](#) [DC780R-822L](#) [DC780R-823K](#)
[DC780R-682L](#) [DC780R-684K](#) [DC780R-683K](#) [DC780R-563K](#) [DC780R-562L](#) [DC780R-564K](#) [DC780-105K](#) [DC780-](#)
[474K](#) [DC780-332L](#) [DC780-182L](#) [DC780-153K](#) [DC780-682L](#) [DC780-684K](#) [DC780-274K](#) [DC780-333K](#) [DC780-392L](#)
[DC780-155K](#) [DC780-102L](#) [DC780-822L](#) [DC780-185K](#) [DC780-224K](#) [DC780-393K](#) [DC780-122L](#) [DC780-824K](#)
[DC780-125K](#) [DC780-272L](#) [DC780-472L](#) [DC780R-224K](#) [DC780R-222L](#) [DC780R-225K](#) [DC780R-223K](#) [DC780R-](#)
[273K](#) [DC780R-274K](#) [DC780R-272L](#) [DC780-184K](#) [DC780-563K](#) [DC780-222L](#) [DC780-183K](#) [DC780-104K](#) [DC780-](#)
[152L](#) [DC780-564K](#) [DC780-225K](#) [DC780-823K](#) [DC780-154K](#) [DC780-683K](#) [DC780-273K](#) [DC780-394K](#) [DC780-123K](#)
[DC780-334K](#) [DC780-473K](#) [DC780-124K](#) [DC780-223K](#) [DC780-562L](#) [DC780-103K](#)