









## UNCONTROLLED

Part Number	Colour	Mounting Hole Dia	Max Panel Thickness	D	h	Part ID
462737	White	22.2	3.2	25.8	11.5	1036595



## ESSENTRA

## essentracomponents.com

© 2013 Essentra Components. All rights reserved. Registered in England, Company No. 547495. Registered Office: Avebury House, 201-249 Avebury Boulevard, Milton Kevnes, MK9 1AU

Condition of Sale can be found on our website: essentra.com.

Essentra Components does not warrant that the files will be error free and may create new versions ("Upgrades") at any time, which may correct such errors. Essentra Components has no obligation to notify you of such upgrades. Any upgraded file will be published to the website, when it becomes available.

You are not permitted to load any of the files on to a network server for the purposes of distribution to one or more other computer(s) on that network or to effect such distribution. Essentra Components shall not be liable for any loss or damage whatsoever or however caused, arising directly or indirectly from the use of the files.

UNLESS OTHERWISE STATED									
ALL DIMEN	NSIONS IN r	nm	DC	DO NOT SCALE					
LINEAR <sup>-</sup>	TOLERANO	Æ	THIRD ANGLE PROJECTION						
0-10mm ± 10-30mm ± 30-50mm ±	$\begin{array}{c} \underline{0} & (\underline{0.0}) \\ \pm 0.5 & \pm 0.15 \\ \pm 0.5 & \pm 0.20 \\ \pm 0.5 & \pm 0.30 \\ \pm 0.8 & \pm 0.50 \end{array}$	(0.00) $\pm 0.10$ $\pm 0.15$ $\pm 0.20$ $\pm 0.25$	¢						
100-200mm ± 200-300mm ± 300-500mm ±	$\pm 0.8 \pm 0.30$ $\pm 1.5 \pm 0.80$ $\pm 2.0 \pm 1.20$ $\pm 3.0 \pm 2.00$ $\pm 5.0 \pm 3.00$	±0.40	UNSPECIFIED DRAFT ANGL DIMENSIONS IN INCHES F	DLERANCE ±0.5 DEGREES D RADII 0.25mm E 0.5 DEGREES D IN BRACKETS [] ARE OR REFERENCE ONLY					
ORG.SCALE	ITS		CREATE DATE. 18/Dec/2014						
MATERIAL NYLON									
ITEM NO. 462737									
DOMED BLANKING PLUGS									
DWG.No.	)5000	0-1	1	ISSUE No.					