
<mark>МацокУ</mark> Mallory Sonalert Products, Inc. Sales Outline Drawing				Part #: JT028-RG-CDL	
				Revisio	D
Specifications:					
Stack Number:	1	2			
LED Color:	RED	GREEN			
Connection Wires:	Red and Brown	Green and Brown			
LED Current Draw:	<50 mA	<40 mA			
Rated Voltage:	24 VAC/DC				
Operating Voltage:			20-28 VAC/DC		
Sound Level Category:	Loud	Loud	Loud		Loud
Mode of Operation:	Continuous	Medium Pulse (5PPS)	Double Pulse (0.5PPS)		Continuous for 5 sec then 0.1s beep until reset
Connection:	Black and Gray Wires	Black and Gray Wires;	Black and Gray Wires	; Purple	Black and Gray wires; Orange ar
		Orange wire connected	wire connected	to	Purple wires connected to
		to Green/Yellow wire	Green/Yellow wi	re	Green/Yellow wire
Sound Current Draw:	40mA Max.	40mA Max.	40mA Max.		40mA Max.
Loudness @ 1m:	80-85 dB(A) Typ.				
Frequency:	2000 ± 500 Hz				
Total Max Current:	<130mA with all LED's and sound unit working				
Operating Temperature:	-25° ~ +60°C				
Lens Color:	Opaque White				
Material:	ABS FR15U				
Mounting Method:	Direct Mount using 1/2" NPT Stainless Steel Pipe and Nut				
Weight Typical (g):	315				
NEMA 12:	Approved				
Options:	Please contact factory.				
Dimensions: Inches (m	m)	cUL Recogn	ized		ROHS Complian
	<b>PATENT</b> 5.2 [132	NUMBER(S) D898600	10309594		
	5.2 [132	.0.1			



LED OPERATION: | CONNECT STACK COLOR WIRE TO POWER AND BROWN WIRE TO POWER.

SOUND OPERATION: CONNECT GRAY AND BLACK WIRES TO POWER FOR CONTINUOUS SOUND.

FOR MEDIUM PULSE, CONNECT GRAY & BLACK TO POWER AND ORANGE WIRE TO GREEN/YELLOW WIRE.
FOR DOUBLE PULSE, CONNECT GRAY & BLACK TO POWER AND PURPLE WIRE TO GREEN/YELLOW WIRE.
FOR CONT/BEEP, CONNECT GRAY & BLACK TO POWER AND ORANGE & PURPLE TO GREEN/YELLOW WIRE.