



Lock nuts in nickel-plated brass



Lock nuts nickel-plated brass


Material: nickel-plated brass
Execution: hexagonal design
Operating temperatures: -40 to +200°C



| |  |  | M |
|----------------|---|---|----------|
| Article number | G | mm | mm |

Metrical thread

| | | | |
|------------|----------|-----|------|
| A8000.06.1 | M 6x0,75 | 9 | 2,8 |
| A8000.06 | M 6x1,0 | 9 | 2,8 |
| A8000.08.1 | M 8x1,0 | 11 | 2,8 |
| A8000.08 | M 8x1,25 | 11 | 2,8 |
| A8000.10.1 | M 10x1,0 | 13 | 2,8 |
| A8000.10 | M 10x1,5 | 13 | 2,8 |
| A8000.12 | M 12x1,5 | 15 | 3,0 |
| A8000.17 | M 16x1,5 | 19 | 3,0 |
| A8000.20 | M 20x1,5 | 24 | 3,5 |
| A8000.25 | M 25x1,5 | 30 | 4,0 |
| A8000.32 | M 32x1,5 | 36 | 4,0 |
| A8000.40 | M 40x1,5 | 46 | 5,0 |
| A8000.50 | M 50x1,5 | 55 | 5,5 |
| A8000.63 | M 63x1,5 | 70 | 6,0 |
| A8000.75 | M 75x1,5 | 80 | 6,0 |
| A8000.080 | M 80x2,0 | 95 | 8,0 |
| A8000.085 | M 85x2,0 | 95 | 8,0 |
| A8000.095 | M 95x2,0 | 110 | 9,0 |
| A8000.100 | M100x3,0 | 115 | 9,0 |
| A8000.105 | M105x3,0 | 120 | 9,0 |
| A8000.115 | M115x3,0 | 125 | 10,0 |



Pg thread

| | | | |
|----------|-------|----|-----|
| A8007 | Pg 7 | 15 | 3,0 |
| A8009 | Pg 9 | 18 | 3,0 |
| A8011 | Pg 11 | 21 | 3,0 |
| A8013 | Pg 13 | 23 | 3,0 |
| A8016 | Pg 16 | 26 | 3,0 |
| A8021 | Pg 21 | 32 | 3,5 |
| A8029 | Pg 29 | 41 | 4,0 |
| A8036 | Pg 36 | 51 | 5,0 |
| A8042 | Pg 42 | 60 | 5,0 |
| A8048.48 | Pg 48 | 64 | 5,5 |

Gas thread

| | | | |
|----------|----------|----|-----|
| A803/8G | G 3/8" | 19 | 3,0 |
| A801/2G | G 1/2" | 24 | 3,0 |
| A805/8G | G 5/8" | 26 | 3,0 |
| A803/4G | G 3/4" | 30 | 3,5 |
| A801G | G 1" | 38 | 4,5 |
| A8011/4G | G 1 1/4" | 46 | 5,0 |
| A8011/2G | G 1 1/2" | 51 | 5,0 |
| A8048 | G 2" | 64 | 5,5 |