

## Switches, Special Use - Component

[See General Information for Switches, Special Use - Component](#)

**ARCOLECTRIC LIMITED**

E45221

61 CENTRAL AVE

WEST MOLESEY, SURREY KT8 2RF UNITED KINGDOM

Cat. No.	Amps	V	Frequency	HP
110 f/b 0,1 aa	0.125	125	60	—
	0.125	45	DC	—
T1100AA AAA,	0.125	125	60	—
T1101AA AAA	0.125	45	DC	—
12 f/b 00, 50 aa	10	250	60	—
	—	125	60	½
	16	250 RES	60	—
	1	30	DC	—
13 f/b 00, 03, 30, 50, 53	20	250	60	1
	—	125	60	½
1330, 1350, aa	14	36"T"	DC	—
	7	72"T"	DC	—
14 or 15 f/b 00, 10, 50	16	250 RES	60	1
60 aa; 17 f/b 50, 60 aa	—	125	60	1/2
1403, 1453, 1503, 1553 aa				
1500 or 1510 aa	10	14	DC	—
14 or 15 f/b 20, 70 aa 1770 aa	16	250 RES	60	—
	—	125/250	60	½
	—	125	60	¼
14 or 15 f/b 01, 02, 11, 21,	16	250 RES	60	—
22, 51, 52, 61, 63,	—	250	60	—

64, 71, 72 aa, 1458, 1490,	—	125	60	—
1558, 1590 aa				
17 f/b 00, 10 aa	20	250RES	60	—
	—	250	60	1
	—	125	60	½
1720 aa	20	250RES	60	—
	—	250	60	½
	—	125	60	¼
17 f/b 84-89	5	250 RES	60	—
2 f/b 2-5, f/b 0-9 or A-Z	12	250	60	—
f/b 0-9, or A-Z, f/b 0-9 or A-Z	4	300	60	—
f/b A-Z aa				
2 f/b 2-5, f/b 0-9 or A-Z	16	250	60	—
f/b 0-9, or A-Z, f/b 0-9 or A-Z	4	300	60	—
f/b A-Z aa				
3101, 3102, 3111, 3141 aa	5	250	60	—
3145, 3146	5	250	60	—
550 f/b 0, 3, 5, 8 aa	15	250	60	1
540 f/b 0, 3, 5, 8 aa	—	125	60	½
55 f/b 50-60, 62, 64	15	250	60	—
66, 68, 90-92aa				
60 f/b 00, 01, 02, 03, 08,09,	20	277	60	—
10, 11, 50, 53, 56, 57, 58,				
60, 62, 66, 67, 68, 90, 91,	—	125	60	1
92, 94 w/aa		250		1-1/2
60, f/b 51 or 52,	20	277	60	—
w/aa		125	—	1
		250	—	1-1/2
700, 705 f/b 0, 1, 3, 4 aa	16	250RES	60	—
	—	250	60	1
	—	125	60	½
82 f/b 00, 01, 50, 51 aa	12	250	60	1


	—	125	60	½
83 f/b 00, 01, 03, 04 aa	13	250	60	1
	—	125	60	½
83 f/b 50, 51, 53, 54 aa	12	250	60	1
	—	125	60	½
85 f/b 00, 03, 50, 53 aa	14	250	60	½
	—	125	60	¼
	15	250RES	60	—
	10	277	60	—
86 f/b 00, 10, 50, 60 aa	10	277	60	½
	—	125	60	¼
86 f/b 00	16	250	60	½
	—	277	60	½
	—	125	60	¼
8601, 8602 aa	6	277	60	—
	16	250	60	—
86 f/b 11, 51, 52, 53, 61 aa	6	277	60	—
8620 aa	15	277	60	—
	—	277	60	½
	—	250	60	½
	—	125	60	¼
86 f/b 70, 71, 72 aa	10	277	60	½
8700 aa	0.5	250	60	—
8800 aa	15	250	60	—
	—	125	60	½
9000 ww/o aa	1	250	60	—
9 f/b 2-6, f/b 00-99 ww/o aa	20	277RES	60	—
	250	60	2	
		125	60	1
3900, 3950 aa	20	277	60	—
f/b 00-01, -02				
-10, -11, -20 thru -22 incl.				

-51, -52, -50, -61,	—	250	60	1
-70, -71, -72	14	36	DC	—
		125	60	1
V4	3A	125/250 Vac	60 Hz	—
	5A	125/250 Vac	60 Hz	—
V3	—	250 Vac	60 Hz	3/4
	10.1	125VL	60 Hz	—

aa = With prefixes and suffixes.

f/b = Followed by.

Marking: Company name, and either electrical rating or catalog number (or both) marked on switch. When electrical rating or catalog number (one or the other) is not marked on switch, it is indicated on the shipping container.

UL Recognized Component Mark  is on the switch or smallest shipping container. When the Mark is not on the switch, the company name and catalog number appear with Mark on the container.

Cat. No.	Temp C	POL/THR	Per Pole	Endurance	SPCOA
110 f/b 0,1 aa	100	1/1	—	6K	A3
T1100AA AAA,	65	1/1	—	6K	—
T1101AA AAA					
12 f/b 00, 50 aa	100	1,2/1	PP	6K	—
13 f/b 00, 03, 30, 50, 53	85	1,2/1,2	—	6K	—
1330, 1350, aa	85	2/1	—	6K	—
14 or 15 f/b 00, 10, 50	85	1,2/1,2	—	6K	—
60 aa; 17 f/b 50, 60 aa					
1403, 1453, 1503, 1553 aa					
1500 or 1510 aa	85	1/1	—	6K	2
14 or 15 f/b 20, 70 aa, 1770 aa	85	1,2/1,2	—	6K	—
14 or 15 f/b 01, 02, 11, 21,	85	1,2/1,2	—	6K	—
22, 51, 52, 61, 63,					
64, 71, 72 aa, 1458, 1490,					

1558, 1590 aa					
17 f/b 00, 10 aa	85	1/1,2	—	6K	—
1720 aa	85	1/2	—	6K	—
17 f/b 84-89	85	1/1	—	6K	—
2 f/b 2-5, f/b 0-9 or A-Z	65	1,2/M	—	6K	2
f/b 0-9, or A-Z, f/b 0-9 or A-Z f/b A-Z aa					
2 f/b 2-5, f/b 0-9 or A-Z	65	1/2/M	—	6K	2
f/b 0-9, or A-Z, f/b 0-9 or A-Z f/b A-Z aa					
3101, 3102, 3111, 3141aa	85	1/1,2	—	6K	—
3145, 3146	85	1/1	—	6K	—
550 f/b 0, 3, 5, 8 aa	85	1/1	—	6K	—
540 f/b 0, 3, 5, 8 aa					
55 f/b 50-60, 62, 64, 66, 68, 90-92aa	85	1,2/1,2	—	6K	1
60 f/b 00, 01, 02, 03, 08, 09, 10, 11, 50, 53, 56, 57, 58, 60, 62, 66, 67, 68, 90, 91, 92, 94, w/aa	100	1,2/1,2	6K		2
60, f/b 51 or 52, w/aa	100	2/1	—	6K	—
700, 705 f/b 0, 1, 3, 4 aa	65	1 or 2/1	—	6K	2
82 f/b 00, 01, 50, 51 aa	85	1,2/1,2	—	6K	2
83 f/b 00, 01, 03, 04 aa	85	1,2/1,2	—	6K	2
83 f/b 50, 51, 53, 54 aa	85	1,2/1,2	—	6K	2
85 f/b 00, 03, 53 aa	105	1,2/1	—	6K	2
86 f/b 00, 10, 50, 60 aa	65	1,2/1,2	—	6K	2
8601, 8602 aa	65	1/1	—	6K	—
86 f/b 00	65	1,2/1,2	—	6K	—
86 F/B 11, 51, 52, 53, 61 aa	6	277	60	—	
8620 aa	90	1,2	—	6K	—
86 f/b 70, 71, 72 aa	90	1,2	—	6K	—
8700 aa	100	1/1	—	6K	—

8800 aa	100	1,2/1	—	6K	—
9000 aa	105	1,2/1	—	6K	—
9 f/b 2-6, f/b 00-99 aa	85	1 or 2/1	—	6K	a3
39	20	277	60	—	a3
	—	250	—	—	a3
	—	125	—	—	a3
	7	72	DC	—	a3
	14	36	DC	—	a3
39 f/b -01, -02, -10	65	1,2/1,23	—	6K	—
-11, -20 thru -22 @@					
3900, 3950 @@	65	1,2/1	—	6K	—

aa = With or without additional prefixes and/or suffixes.

f/b = Followed by.

**Last Updated** on 2005-05-17

This page and all contents are Copyright © 2005 by Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2005 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

