Put-Ups —



- **Economical And Easy** To Install
- Resists Gasoline. **Engine Chemicals And Cleaning Solvents**
- **Complete Coverage**
- **Cut And Abrasion** Resistant

Nominal Size	Part #	Expansion Range		Bulk	Shop	Available	Lbs/
		Min	Max	Spool	Spool	Colors	100′
1/8"	PTT0.13	1/16"	1/4"	1,000′	225′	5	0.29
1/4"	PTT0.25	11/64"	11/32"	1,000′	200′	5	0.36
5/16"	PTT0.31	1/4"	3/8"	1,000′	200′	5	0.58
1/2"	PTT0.50	11/32"	5/8″	500′	100′	5	0.84
3/4"	PTT0.75	1/2"	13/16"	250′	75′	5	1.10
1"	PTT1.00	5/8"	1 1/8"	250′	65′	5	1.23
1 1/4"	PTT1.25	1"	1 11/16"	250′	50′	5	1.30
1 1/2"	PTT1.50	1 1/8"	2"	200′	40′	5	1.95
1 3/4"	PTT1.75	1 1/2"	2 5/8"	200′	30′	5	2.60
2"	PTT2.00	1 3/4"	3 1/8"	200′	50′	5	3.43
2 1/2"	PTT2.50	2"	3 1/2"	100′	50′	5	3.60

Cut Cleanly Hot Knife

The FLEXO® Tight Weave original braided from 10 mil polyethylene terepthalate (PET) monofilament yarns. The material has a wide operating temperature range, is resistant to chemical degradation, UV radiation, and abrasion. Tight Weave is designed for use in applications where optimum coverage and abrasion resistance is required. The tight braid construction increases the coverage, wear factor and improves harness security.

Tight Weave for Extra Coverage

Used in electronics, automotive, marine and industrial wire harnessing applications where cost efficiency and durability are critical.

Material

Polyethylene Terepthalate

Grade

PTT

Monofilament Diameter

.010"

Drawing Number

TF001PET-WD

High thermal and chemical resistance and extra coverage make FLEXO® TIGHT WEAVE ideal for customizing and protecting the wires, hoses and cables.



Black & Neon Blue(BNB), Black & Neon Red(BNR), Black and Neon Orange(BNO), Black and Neon Yellow(BNY), and Black (BK)



104 Demarest Road • Sparta, NJ 07871








Colors

Available:

BK, BNY, BNB, BNO, BNR











Abrasion Resistance High

Abrasion Test Machine Taber 5150

Abrasion Test Wheel Calibrase H-18

Abrasion Test Load 500g

Room Temperature 77°F

Humidity 72%

Two Broken Filament 300 Test Cycles

Approximately 6 Broken **Filaments 500 Test Cycles**

Material Destroyed - Very Visible Hole In Matérial 1,150 Test Cycles

Pre-Test Weight 4,547.4 mg

Post-Test Weight 4,133.9 mg


Test End Loss Of Mass Point Of Destruction 413.5 mg

Rating	 UL94VO, FAR25		
	FMVSS-302		




1=No Effect 2=Little Effect 4=More Affected 5=Severely Affected

3=Affected



SVHC _____



www.techflex.com

PHYSICAL **PROPERTIES**

Monofilament Diameter ASTM D-204	010
Flammability Rating FMVSS-302 Approved	UL94
Recommended Cutting	_Hot Knife
Colors	5
Wall Thickness	
Tensile Strength (Yarn) ASTM D-2256 Lbs	7.5
Specific Gravity ASTM D-792	38
Moisture Absorption % ASTM D- 570	12
Hard Vacuum Data ASTM E-595 at 10-5 torr	
TML	19
CVCM	00
WVR	16
Smoke D-Max ASTM E-662	56
Outgassing	Med
Oxygen Index	21

None