

# MOSFET – Dual, P-Channel, POWERTRENCH

## 30 V

## FDS4935A

### General Description

This P-Channel MOSFET is a rugged gate version of ON Semiconductor's advanced POWERTRENCH<sup>®</sup> process. It has been optimized for power management applications requiring a wide range of gate drive voltage ratings (4.5 V – 20 V).

### Features

- -7 A, -30 V.  $R_{DS(ON)} = 23 \text{ m}\Omega @ V_{GS} = -10 \text{ V}$   
 $R_{DS(ON)} = 35 \text{ m}\Omega @ V_{GS} = -4.5 \text{ V}$
- Low Gate Charge (15 nC Typical)
- Fast Switching Speed
- High Performance Trench Technology for Extremely Low  $R_{DS(ON)}$
- High Power and Current Handling Capability
- This is a Pb-Free Device

### Features

- Power Management
- Load Switch
- Battery Protection

### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Symbol         | Parameter  | Ratings         | Unit             |
|----------------|--|-----------------|------------------|
| $V_{DS}$       | Drain-Source Voltage   | -30             | V                |
| $V_{GSS}$      | Gate-Source Voltage  | $\pm 20$        | V                |
| $I_D$          | Drain Current – Continuous (Note 1a)<br>– Pulsed                           | -7<br>-30       | A                |
| $P_D$          | Power Dissipation for Dual Operation                                       | 2               | W                |
| $P_D$          | Power Dissipation (Note 1a)<br>for Single Operation (Note 1b)<br>(Note 1c) | 1.6<br>1<br>0.9 | W                |
| $T_J, T_{STG}$ | Operating and Storage Junction Temperature Range                           | -55 to +150     | $^\circ\text{C}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


### THERMAL CHARACTERISTICS

| Symbol          | Parameter   | Ratings | Unit                      |
|-----------------|---|---------|---------------------------|
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient (Note 1a) | 78      | $^\circ\text{C}/\text{W}$ |
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case (Note 1)     | 40      | $^\circ\text{C}/\text{W}$ |




ON Semiconductor<sup>®</sup>

[www.onsemi.com](http://www.onsemi.com)




SOIC8  
CASE 751EB

### MARKING DIAGRAM



FDS4935A = Specific Device Code  
A = Assembly Site  
L = Wafer Lot Number  
YW = Assembly Start Week

### ELECTRICAL CONNECTION



### ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

# FDS4935A

## ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Symbol                               | Parameter                                 | Test Condition   | Min | Typ | Max  | Unit                 |
|--------------------------------------|---|--|-----|-----|------|----------------------|
| <b>OFF CHARACTERISTICS</b>           |   |  |     |     |      |                      |
| $BV_{DSS}$                           | Drain-Source Breakdown Voltage            | $V_{GS} = 0\text{ V}, I_D = -250\ \mu\text{A}$               | -30 | -   | -    | V                    |
| $\frac{\Delta BV_{DSS}}{\Delta T_J}$ | Breakdown Voltage Temperature Coefficient | $I_D = -250\ \mu\text{A}$ , Referenced to $25^\circ\text{C}$ | -   | -24 | -    | mV/ $^\circ\text{C}$ |
| $I_{DSS}$                            | Zero Gate Voltage Drain Current           | $V_{DS} = -24\text{ V}, V_{GS} = 0\text{ V}$                 | -   | -   | -10  | $\mu\text{A}$        |
| $I_{GSSF}$                           | Gate-Body Leakage Current, Forward        | $V_{GS} = -20\text{ V}, V_{DS} = 0\text{ V}$                 | -   | -   | -100 | nA                   |
| $I_{GSSR}$                           | Gate-Body Leakage Current, Reverse        | $V_{GS} = 20\text{ V}, V_{DS} = 0\text{ V}$                  | -   | -   | 100  | nA                   |

## ON CHARACTERISTICS (Note 2)

|  |  |  |     |                |                |                      |
|--|--|--|-----|----------------|----------------|----------------------|
| $V_{GS(th)}$                           | Gate Threshold Voltage                         | $V_{DS} = V_{GS}, I_D = -250\ \mu\text{A}$   | -1  | -1.6           | -3             | V                    |
| $\frac{\Delta V_{GS(th)}}{\Delta T_J}$ | Gate Threshold Voltage Temperature Coefficient | $I_D = -250\ \mu\text{A}$ , Referenced to $25^\circ\text{C}$   | -   | 4.4            | -              | mV/ $^\circ\text{C}$ |
| $R_{DS(on)}$                           | Static Drain-Source On-Resistance              | $V_{GS} = -10\text{ V}, I_D = -7\text{ A}$<br>$V_{GS} = -4.5\text{ V}, I_D = -5.5\text{ A}$<br>$V_{GS} = -10\text{ V}, I_D = -7\text{ A}, T_J = 125^\circ\text{C}$ | -   | 19<br>28<br>26 | 23<br>35<br>34 | m $\Omega$           |
| $I_{D(on)}$                            | On-State drain Current                         | $V_{GS} = -10\text{ V}, V_{DS} = -5\text{ V}$  | -30 | -              | -              | A                    |
| $g_{FS}$                               | Forward Transconductance                       | $V_{DS} = -5\text{ V}, I_D = -7\text{ A}$  | -   | 19             | -              | S                    |

## DYNAMIC CHARACTERISTICS

|            |                              |  |   |      |   |    |
|------------|------------------------------|--|---|------|---|----|
| $C_{iss}$  | Input Capacitance            | $V_{DS} = -15\text{ V}, V_{GS} = 0\text{ V}$<br>$f = 1.0\text{ MHz}$ | - | 1233 | - | pF |
| $C_{oss}$  | Output Capacitance           |  | - | 311  | - | pF |
| $C_{riss}$ | Reverse Transfer Capacitance |  | - | 152  | - | pF |

## SWITCHING CHARACTERISTICS (Note 2)


|              |                     |  |   |     |    |    |
|--------------|---------------------|--|---|-----|----|----|
| $t_{d(on)}$  | Turn-On Delay Time  | $V_{DD} = -15\text{ V}, I_D = -1\text{ A}$<br>$V_{GS} = -10\text{ V}, R_{GEN} = 6\ \Omega$ | - | 13  | 23 | ns |
| $t_r$        | Turn-On Rise Time   |  | - | 10  | 20 | ns |
| $t_{d(off)}$ | Turn-Off Delay Time |  | - | 48  | 77 | ns |
| $t_f$        | Turn-Off Fall Time  |  | - | 25  | 40 | ns |
| $Q_g$        | Total Gate Charge   | $V_{DS} = -15\text{ V}, I_D = -7\text{ A}$<br>$V_{GS} = -5\text{ V}$                       | - | 15  | 21 | nC |
| $Q_{gs}$     | Gate-Source Charge  |  | - | 4.4 | -  | nC |
| $Q_{gd}$     | Gate-Drain Charge   |  | - | 4.5 | -  | nC |

## DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS


|          |   |   |   |       |      |   |
|----------|---|---|---|-------|------|---|
| $I_S$    | Maximum Continuous Drain-Source Diode Forward Current | -   | - | -2.1  | A    |   |
| $V_{SD}$ | Drain-Source Diode Forward Voltage                    | $V_{GS} = 0\text{ V}, I_S = -2.1\text{ A}$ (Note 2) | - | -0.75 | -1.2 | V |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.


- $R_{\theta JA}$  is the sum of the junction-to-case and case-to-ambient resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a)  $78^\circ\text{C/W}$  when mounted on a  $0.5\text{ in}^2$  pad of 2 oz. Copper.



b)  $125^\circ\text{C/W}$  when mounted on a  $0.02\text{ in}^2$  pad of 2 oz. copper.



c)  $135^\circ\text{C/W}$  when mounted on a minimum pad.

- Pulse Test Pulse Width  $< 300\ \mu\text{s}$ , Duty Cycle  $< 2.0\%$

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance Variation with Gate-to-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature

TYPICAL CHARACTERISTICS (continued)




Figure 7. Gate-Charge Characteristics




Figure 8. Capacitance Characteristics




Figure 9. Maximum Safe Operating Area




Figure 10. Single Pulse Maximum Power Dissipation




Figure 11. Transient Thermal Response Curve

Thermal characterization performed using the conditions described in Note 1c.  
 Transient thermal response will change depending on the circuit board design.

# FDS4935A

## ORDERING INFORMATION

| Device Marking | Device   | Package Type       | Reel Size | Tape Width | Shipping <sup>†</sup> |
|----------------|----------|--------------------|-----------|------------|-----------------------|
| FDS4935A       | FDS4935A | SOIC8<br>(Pb-Free) | 13"       | 12 mm      | 2500 / Tape & Reel    |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

# MECHANICAL CASE OUTLINE






## PACKAGE DIMENSIONS

ON Semiconductor®



SOIC8  
CASE 751EB  
ISSUE A

DATE 24 AUG 2017



- NOTES:
- A) THIS PACKAGE CONFORMS TO JEDEC MS-012, VARIATION AA.
  - B) ALL DIMENSIONS ARE IN MILLIMETERS.
  - C) DIMENSIONS DO NOT INCLUDE MOLD FLASH OR BURRS.
  - D) LANDPATTERN STANDARD: SOIC127P600X175-8M

|                  |             |  |
|------------------|-------------|--|
| DOCUMENT NUMBER: | 98AON13735G | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SOIC8       | PAGE 1 OF 1  |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**onsemi Website:** [www.onsemi.com](http://www.onsemi.com)

### TECHNICAL SUPPORT

**North American Technical Support:**

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

**Europe, Middle East and Africa Technical Support:**

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

