



- Perfect for Grounding and Shielding
- 100% Copper Braid
- Provides Excellent Current Transmission

Put Ups

Nominal Size	Part #	Wall Thickness	Min Exp.	Max Exp.	Bulk Spool	Shop Spool	Available Colors	Lbs/100'
1/8"	MBC0.13CP	.015"	1/8"	1/4"	250'	25'	Copper	0.90
1/4"	MBC0.25CP	.025"	1/4"	3/8"	100'	25'	Copper	3.00
3/8"	MBC0.38CP	.018"	3/8"	3/4"	100'	25'	Copper	3.10
1/2"	MBC0.50CP	.020"	1/2"	1"	100'	25'	Copper	4.10




Cut Cleanly
Shears

Bare Copper Braid for a Wide Variety of Applications!

Techflex® high purity Copper Sleeve is a 100% copper braid for grounding, shielding, and many other unique projects. Our copper series of metal braids are pure metal with no fillers or coating to provide many years of continuous use. Our braid is suitable for hoses, wires, and other lines on a wide variety of applications. Techflex® Bar Copper braid will provide high flexibility and excellent current transmission for your demanding uses.

Colors Available:
Copper (CP)



Material
Copper

Grade
MBC

Wall Thickness
0.13" - 0.38"


Drawing Number
TF001MBC-WD



www.techflex.com

1 (833) SLEEING • (973) 300-9242 • fax: (973) 300-9409
104 Demarest Road • Sparta, NJ 07871





FLAMMABILITY


Rating _____ Non Flammable

CHEMICAL RESISTANCE

1=No Effect 4=More Affected
2=Little Effect 5=Severely Affected
3=Affected

Aromatic Solvents _____	1
Aliphatic Solvents _____	1
Chlorinated Solvents _____	1
Weak Bases _____	1
Salts _____	1
Strong Bases _____	2
Salt Water 0-S-1926 _____	1
Hydraulic Fluid MIL-H-5606 _____	1
Lube Oil MIL-L-7808 _____	1
De-Icing Fluid MIL-A-8243 _____	1
Strong Acids _____	5
Strong Oxidants _____	5
Esters/Ketones _____	1
UV Light _____	2
Petroleum _____	2
Fungus ASTM G-21 _____	2
Halogen Free _____	Yes
RoHS _____	Yes

Melt Point
ASTM D-2117
1,981°F (1,083°C)



www.techflex.com

PHYSICAL PROPERTIES

Monofilament Thickness _____ .005"
ASTM D-204
Flammability Rating _____ Non Flammable
Recommended Cutting _____ Shears
Colors _____ 1
Wall Thickness _____ .013-.038"

© 2021 Techflex® - Any unauthorized reproduction, in whole or part, in any medium whatsoever, without the express written permission of Techflex® is strictly forbidden.

Techflex® product names and logos are registered trademarks of Techflex®, unless otherwise attributed. The contents and illustrations contained herein are believed to be reliable. Techflex® makes no warranties as to their accuracy or completeness and disclaims any liability in connection with their use. Techflex's® only obligations are those in standard terms of sale for these products and Techflex® will not be liable for any consequential or other damages arising due to misuse of these products or typographical errors or omissions. Users should make their own evaluation to determine the suitability of these products for their unique and specific applications.