


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022288024](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Breakaway Header, Right-Angle Surface Mount Compatible, 2 Circuits, 0.76µm Gold (Au) Selective Plating, Mating Pin Length 6.20mm

Documents:

Drawing (PDF)	Packaging Specification PK-40873-0041-001 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-22-28-8021-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification PS-10-07-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link

Application Tooling Part Link	11-20-1230
-------------------------------	------------

General

Product Family	PCB Headers
Series	42377
Application	Board-to-Board, Signal, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 254
UPC	800753809529

Physical

Breakaway	Yes
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.151/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	See Product Specification

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42377 Series](#)

Mates With

KK Crimp Housing [2695](#) , [6471](#) , [7880](#) , KK
PC Board Connector [4455](#)

Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 500V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 235

Material Info

Engineering Number 42377-0282

Reference - Drawing Numbers

Packaging Specification PK-40873-0041-001
Product Specification PS-10-07-001
Sales Drawing SD-42377-001-000, SD-42377-001-002
Symbol/Footprint Data SYM-22-28-8021-001

This document was generated on 12/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-28-8024](#)