

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0026481122](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 396 Breakaway Header, Right-Angle, 12 Circuits, Tin (Sn) Plating

Documents:

| | |
|--|--|
| 3D Model | Packaging Specification PK-41662-001-001 (PDF) |
| Drawing (PDF) | Symbol Footprint Data SYM-26-48-1122-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-08-50-001 (PDF) | |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Application tooling part link


| | |
|-------------------------------|------------|
| Application Tooling Part Link | 11-20-0901 |
|-------------------------------|------------|

General

| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 41662 |
| Application | Board-to-Board, Power, Wire-to-Board |
| Overview | KK Interconnect Solutions |
| Product Name | KK 396 |
| UPC | 800753586604 |

Physical

| | |
|--------------------------------|---------------------------|
| Breakaway | Yes |
| Circuits (Loaded) | 12 |
| Circuits (maximum) | 12 |
| Color - Resin | Black |
| Durability (mating cycles max) | 25 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | None |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Resin | Polyester |
| Net Weight | 4.382/g |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PC Tail Length | 4.67mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Bag |
| Pitch - Mating Interface | 3.96mm |
| Pitch - Termination Interface | 3.96mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Shrouded | Partial |
| Stackable | No |
| Temperature Range - Operating | See Product Specification |
| Termination Interface: Style | Through Hole |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[41662](#) Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

Electrical

Current - Maximum per Contact 7.0A
Voltage - Maximum 250V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 235

Material Info

Engineering Number A-41662-B12A197

Reference - Drawing Numbers

Packaging Specification PK-41662-001-001
Product Specification PS-08-50-001
Sales Drawing SD-41662-001-001, SD-41662-001-002
Symbol/Footprint Data SYM-26-48-1122-001

This document was generated on 12/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-48-1122](#)