

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is and its officers, employees, even if such claim any manner.

www.fairchildsemi.com



February 2011

FOD3184 3A Output Current, High Speed MOSFET/IGBT Gate Driver Optocoupler

Features


- High noise immunity characterized by 50kV/µs (Typ.) common mode rejection @ V_{CM} = 2,000V
- Guaranteed operating temperature range of -40°C to +100°C
- 3A peak output current for medium power MOSFET/IGBT
- Fast switching speed

FAIRCHILD

SEMICONDUCTOR

- 210ns max. propagation delay65ns max pulse width distortion
- Fast output rise/fall time
 - Offers lower dynamic power dissipation
- 250kHz maximum switching speed
- Wide V_{DD} operating range from 15V to 30V
- Use of P-Channel MOSFETs at output stage enables output voltage swing close to the supply rail (rail-to-rail output)
- Under voltage lockout protection (UVLO) with hysteresis – optimized for driving IGBTs
- Safety and regulatory approvals
 - UL1577, 5,000 VAC_{RMS} for 1 min.
 - DIN EN/IEC 60747-5-2, 1,414 peak working insulation voltage
 - Minimum creepage distance of 8.0mm
 - Minimum clearance distance of 8mm to 16mm (option TV or TSV)
 - Minimum insulation thickness of 0.5mm

Functional Block Diagram



Note:

A 0.1µF bypass capacitor must be connected between pins 5 and 8.

©2005 Fairchild Semiconductor Corporation FOD3184 Rev. 1.0.4

Applications


- Plasma Display Panel
- High performance DC/DC convertor
- High performance switch mode power supply
- High performance uninterruptible power supply
- Isolated Power MOSFET/IGBT gate drive

Description

The FOD3184 is a 3A Output Current, High Speed MOSFET/IGBT Gate Drive Optocoupler. It consists of a aluminium gallium arsenide (AIGaAs) light emitting diode optically coupled to a CMOS detector with PMOS and NMOS output power transistors integrated circuit power stage. It is ideally suited for high frequency driving of power MOSFETS/IGBT used in Plasma Display Panels (PDPs), motor control inverter applications and high performance DC/DC converters.

The device is packaged in an 8-pin dual in-line housing compatible with 260°C reflow processes for lead free solder compliance.

Package Outlines



Truth Table

LED	V _{DD} -V _{SS} "Positive Going" (Turn-on)	V _{DD} -V _{SS} "Negative Going" (Turn-off)	v _o
Off	0V to 30V	0V to 30V	Low
On	0V to 11.5V	0V to 10V	Low
On	11.5V to 13.5V	10V to 12V	Transition
On	13.5V to 30V	12V to 30V	High

Pin Definitions

Pin #	Name	Description
1	NC	Not Connected
2	Anode	LED Anode
3	Cathode	LED Cathode
4	NC	Not Connected
5	V _{SS}	Negative Supply Voltage
6	V _{O2}	Output Voltage 2 (internally connected to V _{O1})
7	V ₀₁	Output Voltage 1
8	V _{DD}	Positive Supply Voltage

Safety and Insulation Ratings

As per DIN EN/IEC 60747-5-2. This optocoupler is suitable for "safe electrical insulation" only within the safety limit data. Compliance with the safety ratings shall be ensured by means of protective circuits.

Symbol	Parameter	Min.	Тур.	Max.	Unit
	Installation Classifications per DIN VDE 0110/1.89 Table 1				
	For Rated Mains Voltage < 150Vrms		I–IV		
	For Rated Mains Voltage < 300Vrms		I–IV		
	For Rated Mains Voltage < 450Vrms		I–III		1
	For Rated Mains Voltage < 600Vrms		I–III		1
	For Rated Mains Voltage < 1000Vrms (Option T, TS)		I–III		
	Climatic Classification		40/100/21		
	Pollution Degree (DIN VDE 0110/1.89)		2		
CTI	Comparative Tracking Index	175			
V _{PR}	Input to Output Test Voltage, Method b, $V_{IORM} \times 1.875 = V_{PR}$, 100% Production Test with tm = 1 sec., Partial Discharge < 5pC	2651			
	Input to Output Test Voltage, Method a, $V_{IORM} \times 1.5 = V_{PR}$, Type and Sample Test with tm = 60 sec.,Partial Discharge < 5 pC	2121			
VIORM	Max Working Insulation Voltage	1,414			V _{peak}
V _{IOTM}	Highest Allowable Over Voltage	6000			V _{peak}
	External Creepage	8			mm
	External Clearance	7.4			mm
	External Clearance (for Option T or TS - 0.4" Lead Spacing)	10.16			mm
	Insulation Thickness	0.5			mm
	Safety Limit Values – Maximum Values Allowed in the Event of a Failure				
T _{Case}	Case Temperature	150			°C
I _{S,INPUT}	Input Current	25			mA
P _{S,OUTPUT}	Output Power	250			mW
R _{IO}	Insulation Resistance at T _S , V _{IO} = 500V	10 ⁹			Ω

3

Absolute Maximum Ratings (T_A = 25°C unless otherwise specified)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Value	Units
T _{STG}	Storage Temperature	-40 to +125	°C
T _{OPR}	Operating Temperature	-40 to +100	°C
TJ	Junction Temperature	-40 to +125	°C
T _{SOL}	Lead Solder Temperature – Wave solder (Refer to Reflow Temperature Profile, pg. 22)	260 for 10 sec.	°C
I _{F(AVG)}	Average Input Current ⁽¹⁾	25	mA
I _{F(tr, tf)}	LED Current Minimum Rate of Rise/Fall	250	ns
V _R	Reverse Input Voltage	5	V
I _{OH(PEAK)}	"High" Peak Output Current ⁽²⁾	3	А
I _{OL(PEAK)}	"Low" Peak Output Current ⁽²⁾	3	А
$V_{DD} - V_{SS}$	Supply Voltage	-0.5 to 35	V
V _{O(PEAK)}	Output Voltage	0 to V _{DD}	V
Po	Output Power Dissipation ⁽³⁾	250	mW
PD	Total Power Dissipation ⁽³⁾	295	mW

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

Symbol	Parameter	Value	Units
$V_{DD} - V_{SS}$	Power Supply	15 to 30	V
I _{F(ON)}	Input Current (ON)	10 to 16	mA
V _{F(OFF)}	Input Voltage (OFF)	-3.0 to 0.8	V

4

Electrical-Optical Characteristics (DC)

Apply over all recommended conditions, typical value is measured at V_{DD} = 30V, V_{SS} = 0V, T_A = 25°C, unless otherwise specified.

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
I _{OH}	High Level Output Current	$V_{OH} = (V_{DD} - V_{SS} - 1V)$		-0.9	-0.5	А
		$V_{OH} = (V_{DD} - V_{SS} - 6V)$			-2.5	
I _{OL}	Low Level Output Current	$V_{OL} = (V_{DD} - V_{SS} + 1V)$	0.5	1		А
		$V_{OL} = (V_{DD} - V_{SS} + 6V)$	2.5			
V _{OH}	High Level Output Voltage ⁽⁴⁾⁽⁵⁾	I _O = -100mA, I _F = 10mA	$V_{DD} - 0.5$			V
		I _O = -2.5A, I _F = 10mA	$V_{DD} - 7$			
V _{OL}	Low Level Output Voltage ⁽⁴⁾⁽⁵⁾	$I_{O} = 100 \text{mA}$, $I_{F} = 0 \text{mA}$			V _{SS} + 0.5	V
		I _O = 2.5A, I _F = 0mA			V _{SS} + 7	
I _{DDH}	High Level Supply Current	Output Open, I _F = 10 to 16mA		2.6	3.5	mA
I _{DDL}	Low Level Supply Current	Output Open, V _F = -3.0 to 0.8V		2.5	3.5	mA
I _{FLH}	Threshold Input Current Low to High	$I_{O} = 0$ mA, $V_{O} > 5V$		3.0	7.5	mA
V _{FHL}	Threshold Input Voltage High to Low	$I_{O} = 0mA, V_{O} < 5V$	0.8			V
V _F	Input Forward Voltage	I _F = 10mA	1.1	1.43	1.8	V
$\Delta V_F/T_A$	Temperature Coefficient of Forward Voltage	I _F = 10mA		-1.5		mV/°C
V _{UVLO+}	UVLO Threshold	$V_{O} > 5V, I_{F} = 10mA$	11.5	13.0	13.5	V
V _{UVLO}		V _O < 5V, I _F = 10mA	10.0	11.5	12.0	V
UVLO _{HYST}	UVLO Hysteresis			1.5		V
BV _R	Input Reverse Breakdown Voltage	I _R = 10μA	5			V
C _{IN}	Input Capacitance	$f = 1MHz, V_F = 0V$		25		pF

5

Switching Characteristics

Apply over all recommended conditions, typical value is measured at V_{DD} = 30V, V_{SS} = 0V, T_A = 25°C, unless otherwise specified.

Symbol	Parameter	Test Conditions	Min.	Тур.*	Max.	Unit
t _{PLH}	Propagation Delay Time to High Output Level ⁽⁶⁾	I _F = 10mA,	50	120	210	ns
t _{PHL}	Propagation Delay Time to Low Output Level ⁽⁶⁾	$R_g = 10\Omega$, f = 250kHz,	50	145	210	ns
P _{WD}	Pulse Width Distortion ⁽⁷⁾	Duty Cycle = 50% ,		35	65	ns
P _{DD} (t _{PHL} – t _{PLH})	Propagation Delay Difference Between Any Two Parts ⁽⁸⁾	C _g = 10nF	-90		90	ns
t _r	Rise Time	C _L = 10nF,		38		ns
t _f	Fall Time	$R_g = 10\Omega$		24		ns
t _{UVLO ON}	UVLO Turn On Delay			2.0		μs
t _{UVLO OFF}	UVLO Turn Off Delay			0.3		μs
I CM _H I	Output High Level Common Mode Transient Immunity ^{(9) (10)}	$\label{eq:transform} \begin{array}{l} T_A = +25^\circ C, \\ I_f = 10 mA \mbox{ to } 16 mA, \\ V_{CM} = 2 kV, \\ V_{DD} = 30 V \end{array}$	35	50		kV/µs
I CM _L I	Output Low Level Common Mode Transient Immunity ^{(9) (11)}		35	50		kV/µs

*Typical values at $T_A = 25^{\circ}C$


Isolation Characteristics

Symbol	Parameter	Test Conditions	Min.	Тур.*	Max.	Unit
V _{ISO}	Withstand Isolation Voltage ^{(12) (13)}	$\label{eq:transformation} \begin{split} T_A &= 25^\circ C, \\ R.H. &< 50\%, \ t = 1 \text{min.}, \\ I_{I-O} &\leq 10 \mu A \end{split}$	5000			V _{rms}
R _{I-O}	Resistance (input to output) ⁽¹³⁾	V _{I-O} = 500V		10 ¹¹		Ω
C _{I-O}	Capacitance (input to output)	Freq. = 1MHz		1		pF


*Typical values at $T_A = 25^{\circ}C$

Notes:


- 1. Derate linearly above +79°C free air temperature at a rate of 0.37mA/°C.
- 2. Maximum pulse width = $10\mu s$.
- 3 Derate linearly above +79°C, free air temperature at the rate of 5.73mW/°C.
- In this test, V_{OH} is measured with a dc load current of 100mA. When driving capacitive load V_{OH} will approach V_{DD} as I_{OH} approaches zero amps.
- 5. Maximum pulse width = 1ms, maximum duty cycle = 20%.
- t_{PHL} propagation delay is measured from the 50% level on the falling edge of the input pulse to the 50% level of the falling edge of the V_O signal. t_{PLH} propagation delay is measured from the 50% level on the rising edge of the input pulse to the 50% level of the rising edge of the V_O signal.
- 7. PWD is defined as | t_{PHL} t_{PLH} | for any given device.
- 8. The difference between t_{PHL} and t_{PLH} between any two FOD3184 parts under same operating conditions, with equal loads.
- 9. Pin 1 and 4 need to be connected to LED common.
- 10. Common mode transient immunity in the high state is the maximum tolerable dV_{CM}/dt of the common mode pulse V_{CM} to assure that the output will remain in the high state (i.e. $V_O > 15V$).
- 11. Common mode transient immunity in a low state is the maximum tolerable dV_{CM}/dt of the common mode pulse, V_{CM} , to assure that the output will remain in a low state (i.e. $V_O < 1.0V$).
- 12. In accordance with UL 1577, each optocoupler is proof tested by applying an insulation test voltage > 6000Vrms, 60Hz for 1 second (leakage detection current limit $I_{I-O} < 10\mu$ A).
- 13. Device considered a two-terminal device: pins on input side shorted together and pins on output side shorted together.




©2005 Fairchild Semiconductor Corporation FOD3184 Rev. 1.0.4




FOD3184 Rev. 1.0.4




@2005 Fairchild Semiconductor Corporation FOD3184 Rev. 1.0.4




FOD3184 Rev. 1.0.4







©2005 Fairchild Semiconductor Corporation

FOD3184 Rev. 1.0.4








Ordering Information


Part Number	Package	Packing Method
FOD3184	DIP 8-Pin	Tube (50 units per tube)
FOD3184S	SMT 8-Pin (Lead Bend)	Tube (50 units per tube)
FOD3184SD	SMT 8-Pin (Lead Bend)	Tape and Reel (1,000 units per reel)
FOD3184V	DIP 8-Pin, DIN EN/IEC 60747-5-2 option	Tube (50 units per tube)
FOD3184SV	SMT 8-Pin (Lead Bend), DIN EN/IEC 60747-5-2 option	Tube (50 units per tube)
FOD3184SDV	SMT 8-Pin (Lead Bend), DIN EN/IEC 60747-5-2 option	Tape and Reel (1,000 units per reel)
FOD3184TV	DIP 8-Pin, 0.4" Lead Spacing, DIN EN/IEC 60747-5-2 option	Tube (50 units per tube)
FOD3184TSV	SMT 8-Pin, 0.4" Lead Spacing, DIN EN/IEC 60747-5-2 option	Tube (50 units per tube)
FOD3184TSR2V	SMT 8-Pin, 0.4" Lead Spacing, DIN EN/IEC 60747-5-2 option	Tape and Reel (700 units per reel)

Marking Information




Definitions 1 Fairchild logo

1	Fairchild logo
2	Device number
3	VDE mark (Note: Only appears on parts ordered with DIN EN/IEC 60747-5-2 option – See order entry table)
4	Two digit year code, e.g., '11'
5	Two digit work week ranging from '01' to '53'
6	Assembly package code




Symbol	Description	Dimension in mm
W	Tape Width	16.0 ± 0.3
t	Tape Thickness	0.30 ± 0.05
P ₀	Sprocket Hole Pitch	4.0 ± 0.1
D ₀	Sprocket Hole Diameter	1.55 ± 0.05
E	Sprocket Hole Location	1.75 ± 0.10
F	Pocket Location	7.5 ± 0.1
P ₂		2.0 ± 0.1
Р	Pocket Pitch	12.0 ± 0.1
A ₀	Pocket Dimensions	10.30 ±0.20
B ₀		10.30 ±0.20
K ₀		4.90 ±0.20
W ₁	Cover Tape Width	13.2 ± 0.2
d	Cover Tape Thickness	0.1 max
	Max. Component Rotation or Tilt	10°
R	Min. Bending Radius	30



Symbol	Description	Dimension in mm
W	Tape Width	24.0 ± 0.3
t	Tape Thickness	0.40 ± 0.1
P ₀	Sprocket Hole Pitch	4.0 ± 0.1
D ₀	Sprocket Hole Diameter	1.55 ± 0.05
E	Sprocket Hole Location	1.75 ± 0.10
F	Pocket Location	11.5 ± 0.1
P ₂		2.0 ± 0.1
Р	Pocket Pitch	16.0 ± 0.1
A ₀	Pocket Dimensions	12.80 ± 0.1
B ₀		10.35 ± 0.1
κ _o		5.7 ±0.1
W ₁	Cover Tape Width	21.0 ± 0.1
d	Cover Tape Thickness	0.1 max
	Max. Component Rotation or Tilt	10°
R	Min. Bending Radius	30

©2005 Fairchild Semiconductor Corporation FOD3184 Rev. 1.0.4



Profile Freature	Pb-Free Assembly Profile
Temperature Min. (Tsmin)	150°C
Temperature Max. (Tsmax)	200°C
Time (t _S) from (Tsmin to Tsmax)	60–120 seconds
Ramp-up Rate (t _L to t _P)	3°C/second max.
Liquidous Temperature (T _L)	217°C
Time (t_L) Maintained Above (T_L)	60–150 seconds
Peak Body Package Temperature	260°C +0°C / -5°C
Time (t _P) within 5°C of 260°C	30 seconds
Ramp-down Rate (T_P to T_L)	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

(1.78)1.500 Δ 1 <u>Ø1.00</u> (TYP) 6 35-6 86 (13.00) (9.96) 5 8 9.40-9.91 LAND PATTERN RECOMMENDATION 1.14-1.78 3.68-3.94 5.08 Max 0.510(Min) 2.54 (Typ) (0.775)NOTES:

FAIRCHILD

0.40(Min)

(BOTH SIDES)

10.16

12.60(Max)

(1.52)


0.20-0.40


(2.54)


(0.76)

7.62(Typ)

- A) NO STANDARD APPLIES TO THIS PACKAGE
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSION D) DWG FILENAME AND REVISION: MKT-N08Lrev2.







ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

Downloaded from Arrow.com.