

STP5NK80Z STP5NK80ZFP

N-channel 800V - 1.9Ω - 4.3A - TO-220/TO-220FP Zener-protected SuperMESH™ Power MOSFET

General features

Туре	V _{DSS} (@Tjmax)	R _{DS(on)}	I _D
STP5NK80Z	800 V	< 2.4 Ω	4.3 A
STP5NK80ZFP	800 V	< 2.4 Ω	4.3 A


- 100% avalanche tested
- Gate charge minimized
- Very low intrinsic capacitances
- Very good manufacturing repeatibility

Description


The SuperMESH™ series is obtained through an extreme optimization of ST's well established strip-based PowerMESH™ layout. In addition to pushing on-resistance significantly down, special care is taken to ensure a very good dv/dt capability for the most demanding applications. Such series complements ST full range of high voltage MOSFETs including revolutionary MDmesh™ products.

Applications

■ Switching application



Internal schematic diagram



Order codes

Part number	Marking	Package	Packaging
STP5NK80Z	P5NK80Z	TO-220	Tube
STP5NK80ZFP	P5NK80ZFP	TO-220FP	Tube

Contents

1	Electrical ratings
2	Electrical characteristics 5
	2.1 Electrical characteristics (curves)
3	Test circuit
4	Package mechanical data11
5	Packaging mechanical data12

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Val	ue	Unit
		TO-220	TO-220FP	
V _{DS}	Drain-source voltage (V _{GS} = 0)	80	00	V
V _{GS}	Gate-source voltage	± (30	V
I _D	Drain current (continuous) at T _C = 25°C	4.3	4.3 (1)	Α
I _D	Drain current (continuous) at T _C =100°C	2.7 2.7 (1)		Α
I _{DM} ⁽²⁾	Drain current (pulsed)	17.2 17.2 ⁽¹⁾		Α
P _{TOT}	Total dissipation at T _C = 25°C	I dissipation at T _C = 25°C 110 30		W
	Derating factor	0.88	0.24	W/°C
V _{ESD(G-S)}	Gate source ESD (HBM-C=100pF, R=1.5KΩ)	35	00	V
dv/dt (3)	Peak diode recovery voltage slope	4.	5	V/ns
V _{ISO}	Insulation withstand voltage (RMS) from all three leads to external heat sink (t=1s; T _c = 25°C)	- 2500		V
T _J T _{stg}	Operating junction temperature Storage temperature	-55 to	°C	

- 1. Limited only by maximum temperature allowed
- 2. Pulse width limited by safe operating area
- $3. \quad I_{SD} \leq \!\! 4.3 \text{A, di/dt 200A/} \mu\text{s, V}_{DD} \leq \!\! V_{(BR)DSS}, T_j \leq \!\! T_{JMAX}.$

Table 2. Thermal data

Symbol	Parameter	Val	Unit	
		TO-220	TO-220FP	
R _{thj-case}	Thermal resistance junction-case max	1.14	4.2	°C/W
R _{thj-a}	Thermal resistance junction-ambient max	62	°C/W	
T _I	Maximum lead temperature for soldering purpose	300		°C

Table 3. Avalanche characteristics

Symbol	Parameter	Value	Unit
I _{AR}	Avalanche current, repetitive or not-repetitive (pulse width limited by Tj Max)	4.3	Α
E _{AS}	Single pulse avalanche energy (starting Tj=25°C, Id=Iar, Vdd=50V)	190	mJ

Table 4. Gate-source zener diode

	Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
Ī	BV_{GSO}	Gate-source breakdown voltage	Igs=± 1mA (Open Drain)	30			V

1.1 Protection features of gate-to-source zener diodes

The built-in back-to-back Zener diodes have specifically been designed to enhance not only the device's ESD capability, but also to make them safely absorb possible voltage transients that may occasionally be applied from gate to source. In this respect the Zener voltage is appropriate to achieve an efficient and cost-effective intervention to protect the device's integrity. These integrated Zener diodes thus avoid the usage of external components.

2 Electrical characteristics

(T_{CASE}=25°C unless otherwise specified)

Table 5. On/off states

Symbol	Parameter Test conditions		Min.	Тур.	Max.	Unit
V _{(BR)DSS}	Drain-source breakdown voltage	I _D = 1mA, V _{GS} = 0	800			V
I _{DSS}	Zero gate voltage drain current (V _{GS} = 0)	V_{DS} = Max rating, V_{DS} = Max rating, T_{C} = 125°C			1 50	μ Α μ Α
I _{GSS}	Gate body leakage current (V _{GS} = 0)	V _{GS} = ± 20V			±10	μΑ
V _{GS(th)}	Gate threshold voltage	$V_{DS} = V_{GS}, I_{D} = 100 \mu A$	3	3.75	4.5	V
R _{DS(on)}	Static drain-source on resistance	$V_{GS} = 10V, I_D = 2.15 A$		1.9	2.4	Ω

Table 6. Dynamic

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
g _{fs} ⁽¹⁾	Forward transconductance	$V_{DS} = 15V, I_D = 2.15A$		4.25		S
C _{iss} C _{oss} C _{rss}	Input capacitance Output capacitance Reverse transfer capacitance	V _{DS} =25V, f=1 MHz, V _{GS} =0		910 98 20		pF pF pF
C _{osseq} (2)	Equivalent output capacitance	V _{GS} =0, V _{DS} =0V to 400V		40		pF
$\begin{array}{c} t_{\text{d(on)}} \\ t_{\text{r}} \\ t_{\text{d(off)}} \\ t_{\text{r}} \end{array}$	Turn-on delay time Rise time Turn-on delay time fall time	V_{DD} =400 V, I_{D} = 2 A, R_{G} =4.7 Ω , V_{GS} =10V (see <i>Figure 18</i>)		18 25 45 30		ns ns ns
Q _g Q _{gs} Q _{gd}	Total gate charge Gate-source charge Gate-drain charge	V _{DD} =640V, I _D = 4.3A V _{GS} =10V		32.4 5 18.5	45.5	nC nC nC
t _{d(Voff)}	Off-voltage rise time Fall time Cross-over time	V_{DD} =640 V, I_{D} = 4.3 A, R_{G} =4.7 Ω , V_{GS} =10V (see <i>Figure 20</i>)		22 10 32		ns ns ns

^{1.} Pulsed: pulse duration=300µs, duty cycle 1.5%

^{2.} $C_{\rm oss\ eq.}$ is defined as a constant equivalent capacitance giving the same charging time as $C_{\rm oss}$ when $V_{\rm DS}$ increases from 0 to 80% $V_{\rm DSS}$

Table 7. Source drain diode

Symbol	Parameter	Test conditions	Min	Тур.	Max	Unit
I _{SD}	Source-drain current				4.3	Α
I _{SDM} ⁽¹⁾	Source-drain current (pulsed)				17.2	Α
V _{SD} ⁽²⁾	Forward on voltage	I _{SD} = 4.3 A, V _{GS} =0			1.6	V
t _{rr} Q _{rr} I _{RRM}	Reverse recovery time Reverse recovery charge Reverse recovery current	I_{SD} = 4.3 A, di/dt = 100A/ μ s, V_{DD} =40 V, Tj = 150°C (see <i>Figure 20</i>)		500 3 12		ns μC Α

^{1.} Pulse width limited by safe operating area

^{2.} Pulsed: pulse duration=300µs, duty cycle 1.5%

2.1 Electrical characteristics (curves)

Figure 1. Safe operating area for TO-220

Figure 2. Thermal impedance for TO-220




Figure 3. Safe operating area for TO-220FP (HV11720)

Figure 4. Thermal impedance for TO-220FP




Figure 5. Output characterisics

Figure 6. Transfer characteristics




Figure 7. Transconductance

Figure 8. Static drain-source on resistance




Figure 9. Gate charge vs gate-source voltage Figure 10. Capacitance variations




Figure 11. Normalized gate threshold voltage Figure 12. Normalized on resistance vs vs temperature temperature





Figure 13. Source-drain diode forward characteristics

Figure 14. Normalized BVdss vs temperature







Figure 15. Avalanche energy vs temperature



3 Test circuit

Figure 16. Unclamped Inductive load test circuit

Figure 17. Unclamped Inductive waveform




Figure 18. Switching times test circuit for resistive load

Figure 19. Gate charge test circuit





Figure 20. Test circuit for inductive load switching and diode recovery times




4 Package mechanical data

In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a Lead-free second level interconnect . The category of second level interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com


TO-220FP MECHANICAL DATA

DIM		mm.			inch	
DIM.	MIN.	TYP	MAX.	MIN.	TYP.	MAX.
Α	4.4		4.6	0.173		0.181
В	2.5		2.7	0.098		0.106
D	2.5		2.75	0.098		0.108
Е	0.45		0.7	0.017		0.027
F	0.75		1	0.030		0.039
F1	1.15		1.7	0.045		0.067
F2	1.15		1.7	0.045		0.067
G	4.95		5.2	0.195		0.204
G1	2.4		2.7	0.094		0.106
Н	10		10.4	0.393		0.409
L2		16			0.630	
L3	28.6		30.6	1.126		1.204
L4	9.8		10.6	.0385		0.417
L5	2.9		3.6	0.114		0.141
L6	15.9		16.4	0.626		0.645
L7	9		9.3	0.354		0.366
Ø	3		3.2	0.118		0.126



TO-220 MECHANICAL DATA

DIM.		mm.			inch	
DIW.	MIN.	TYP	MAX.	MIN.	TYP.	MAX.
Α	4.40		4.60	0.173		0.181
b	0.61		0.88	0.024		0.034
b1	1.15		1.70	0.045		0.066
С	0.49		0.70	0.019		0.027
D	15.25		15.75	0.60		0.620
E	10		10.40	0.393		0.409
е	2.40		2.70	0.094		0.106
e1	4.95		5.15	0.194		0.202
F	1.23		1.32	0.048		0.052
H1	6.20		6.60	0.244		0.256
J1	2.40		2.72	0.094		0.107
L	13		14	0.511		0.551
L1	3.50		3.93	0.137		0.154
L20		16.40			0.645	
L30		28.90			1.137	
øΡ	3.75		3.85	0.147		0.151
Q	2.65		2.95	0.104		0.116



5 Revision history

Table 8. Revision history

Date	Revision	Changes
09-Sep-2004	2	Preliminary version
06-Sep-2005	3	Final version
16-Aug-2006	4	New template, no content change

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2006 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics:
STP5NK80Z STP5NK80ZFP