

Electrical Characteristics Data

0402 NPO 2pF 50V (0402N2R0B500CT)

1. Dimension



Size Inch (mm)	L (mm)	W (mm)	T (mm)
0402 (1005)	1.00±0.05	0.50±0.05	0.50±0.05


2. Cap, DF, IR @25°C

(Cap, DF @ 1MHz, 1Vrms ; IR @ 50V, 120sec)

Item	Spec
Cap [pF]	2(±0.1 pF)
DF	≤0.227%
IR [G-ohm]	>10 min

3. Impedance/ESR-Frequency

(Equipment: 4287A)



4. Capacitance – Temperature Characteristics


(Equipment: 4284A)

≤ 10 pF, The TCC measurement is unstable and high deviation

5. Capacitance – DC Voltage Characteristics

(Equipment: 4284A; DC charge 60±5sec)

24V :0% ; 50V :0%



6. Capacitance – AC Voltage Characteristics

(Equipment: 4284A; AC charge 60±5sec)

