


THROUGH-HOLE .025" SQ POST SOCKET

(2.54 mm) .100" PITCH • SSW/SSQ SERIES



SSW/SSQ

Mates:

TSW, MTSW, MTLW,
DW, EW, ZW, TSS, ZSS,
TSM, TSSH, HTSS

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer (-S & -D) or
Black High Temperature Thermoplastic (-T)

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Current Rating (SSW/TSM):

4.7 A per pin

(2 pins powered)

Current Rating (SSQ/TSW):

6.3 A per pin

(2 pins powered)

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Insertion Depth:

(3.68 mm) .145" to

(6.35 mm) .250"

Max Cycles:

100 with 10 μ" (0.25 μm) Au

Voltage Rating:

465 VAC / 655 VDC

PROCESSING

Lead-Free Solderable:

Yes:

-S and -D row option

No, Lead Wave only:

-P, -T and -Q row option

| SERIES | 1 | NO. PINS PER ROW | LEAD STYLE | PLATING OPTION | ROW OPTION | TAIL OPTION | OTHER OPTION |
|--------|---|------------------|------------|----------------|------------|-------------|--------------|
|--------|---|------------------|------------|----------------|------------|-------------|--------------|

SSW
= Solder Tail

01 thru 50

Specify
LEAD STYLE
from chart

-F
= Gold flash on contact,
Matte Tin on tail

-S
= Single Row

Leave blank for straight pin version)

-LL
= Locking Lead

Available on tails from

(2.29 mm)

.090" to

(7.87 mm)

.310" only.

Not Available

with single

row 1 or 2

positions)

"XXX"

= Polarized
(Specify "XXX" as position number)

SSQ
= Square Tail

-L
= 10 μ" (0.25 μm)
Gold on contact,
Matte Tin on tail

-P
= Single Row
(36 pins max)

-RA
= Right-angle

-G
= 20 μ" (0.51 μm)
Gold on contact,
Gold flash on tail

-D
= Double Row

-T
= Triple Row





-Q
= Double Row
.200"
(5.08 mm)
row space
(outer rows filled only)

-T
= Matte Tin
(-T N/A on LIF contacts)

| THROUGH-HOLE | | |
|--------------------------|----------------------|---------------------------|
| LEAD STYLE | | SINGLE DOUBLE OR TRIPLE A |
| Standard Insertion Force | Low Insertion Force* | |
| -01 | -21 | (2.64) .104 |
| -02 | -22 | (4.93) .194 |
| -03 | -23 | (10.00) .394 |
| -04 | -24 | (14.83) .584 |
| -06** | N/A | (3.15) .124 |


* LIF not available with Tin Plating

**Style -06 Not available with SSQ



Through-hole


Right-angle



Straight Pin Versions

| RIGHT-ANGLE | | | | |
|--------------------------|----------------------|--------------|-------------|-------------|
| LEAD STYLE | | SINGLE | DOUBLE | TRIPLE |
| Standard Insertion Force | Low Insertion Force* | (-S) B | (-D) B | (-T & -Q) B |
| -02 | -22 | (2.54) .100 | (2.54) .100 | (2.54) .100 |
| -03 | -23 | (7.62) .300 | (7.62) .300 | N/A |
| -04 | -24 | (12.45) .490 | N/A | N/A |

*LIF not available with Tin Plating



Right-angle Versions

Note:

Some lengths, styles and options are non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SSW-102-01-G-S](#) [SSW-104-01-T-D](#) [SSW-110-01-G-D](#) [SSW-103-01-F-S](#) [SSW-103-01-G-D](#) [SSW-108-01-T-D](#)
[SSW-110-01-F-D](#) [SSW-125-01-S-D](#) [SSW-105-01-F-D](#) [SSW-107-01-G-D](#) [SSW-108-01-S-D](#) [SSW-117-01-G-D](#) [SSW-](#)
[106-01-T-D](#) [SSW-117-02-S-D-RA](#) [SSW-106-02-G-S-RA](#) [SSW-105-01-S-D](#) [SSW-113-01-T-S](#) [SSW-102-01-G-D](#)
[SSW-104-01-G-S](#) [SSW-103-01-T-S](#) [SSW-104-02-G-D-RA](#) [SSW-108-01-S-S](#) [SSW-109-02-T-D-RA](#) [SSW-112-01-S-S](#)
[SSW-111-01-S-D](#) [SSW-108-01-G-S](#) [SSW-136-06-G-D](#) [SSW-104-01-S-D](#) [SSW-130-06-S-D](#) [SSW-106-01-T-S](#)
[SSW-113-01-G-D](#) [SSW-113-22-F-D-VS-K](#) [SSW-105-02-G-T-RA](#) [SSW-102-01-T-D](#) [SSW-114-01-G-S](#) [SSW-110-02-G-](#)
[S-RA](#) [SSW-106-02-T-S-RA](#) [SSW-104-02-T-S](#) [SSW-110-02-G-D](#) [SSW-105-01-L-D](#) [SSW-113-01-F-D](#) [SSW-108-01-T-](#)
[S](#) [SSW-106-01-F-D](#) [SSW-126-02-F-S-RA](#) [SSW-110-02-F-S-RA](#) [SSW-120-01-G-D](#) [SSW-106-01-G-D](#) [SSW-116-01-](#)
[G-D](#) [SSW-109-01-T-D](#) [SSW-110-02-S-S-RA](#) [SSW-103-01-F-D](#) [SSW-108-01-F-D](#) [SSW-112-01-G-D](#) [SSW-120-01-S-](#)
[D](#) [SSW-106-01-G-S](#) [SSW-121-01-G-D](#) [SSW-120-01-T-D](#) [SSW-110-01-S-D](#) [SSW-110-01-T-S](#) [SSW-117-01-S-D](#)
[SSW-113-01-S-D](#) [SSW-107-01-T-D](#) [SSW-102-01-S-S](#) [SSW-112-01-F-D](#) [SSW-102-02-G-D-RA](#) [SSW-103-01-S-S](#)
[SSW-105-01-T-S](#) [SSW-107-01-S-D](#) [SSW-108-02-G-D](#) [SSW-132-01-S-D](#) [SSW-109-01-F-D](#) [SSW-108-01-G-D](#) [SSW-](#)
[125-01-F-D](#) [SSW-108-02-T-D](#) [SSW-107-01-F-D](#) [SSW-110-01-F-S](#) [SSW-107-02-S-D](#) [SSW-105-01-S-S](#) [SSW-116-01-](#)
[T-S](#) [SSW-124-01-S-D](#) [SSW-110-01-T-D](#) [SSW-105-01-T-D](#) [SSW-112-01-S-D](#) [SSW-104-01-F-D](#) [SSW-105-01-G-D](#)
[SSW-106-01-S-D](#) [SSW-112-01-T-D](#) [SSW-125-01-G-D](#) [SSW-108-01-L-D](#) [SSW-125-02-S-D](#) [SSW-103-22-S-D-VS](#)
[SSW-117-02-G-D-RA](#) [SSW-103-02-G-S-RA](#) [SSW-102-03-G-S](#) [SSW-103-01-T-D](#) [SSW-108-02-G-S-RA](#) [SSW-110-02-](#)
[T-S](#) [SSW-118-01-S-S](#) [SSW-116-22-G-S](#) [SSW-120-02-F-D-RA](#)