



POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH
3	1300630042	C03006A48M020	32	2M +89-0MM (6'7"+3.50-0)
4	1300630150	C04006A48M020	32	2M +89-0MM (6'7"+3.50-0)

FACE VIEW-MALE INSERT





SPECS:
 OVERMOLD: GRAY PVC W/BLACK STRIP
 INSERT: BLACK PVC
 COUPLING NUT: ANODIZED ALUMINUM
 CABLE: #10AWG GRAY PVC
 DUAL RATED UL TC/OPEN WIRING & ST00W
 ELECTRICAL: 600V AC/DC

UPDATED PROFILE EC NO: IPG2014-1160 DRWG:GGUSTAFSON 2013/12/23 CHKD:VOU 2014/01/15 APPR:WOODMAN 2014/05/12	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± .005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.13</td> <td>± .010</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.25</td> <td>± .020</td> </tr> </tbody> </table> ANGULAR ±1/2°		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± 0.13	± .010	1 PLACE	± 0.25	± .020	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
			mm	INCH																	
	4 PLACES		± ---	± ---																	
	3 PLACES		± ---	± .005																	
2 PLACES	± 0.13	± .010																			
1 PLACE	± 0.25	± .020																			
	IN/MM	NTS	INCH																		
	DRAWN BY	DATE	TITLE																		
	B.RUPERT	01/12/2010	QUICK CHANGE MALE STRAIGHT 3 & 4 POLE PORTABLES																		
	CHECKED BY	DATE	MOLEX INCORPORATED																		
	B. WOODMAN	01/12/2010	SD-130063-042																		
	APPROVED BY	DATE	SHEET NO.																		
	JFMURPHY	2010/01/15	1 OF 1																		
	MATERIAL NO.	SEE CHART	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
	DOCUMENT NO.																				

POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH
3	1300630042	C03006A48M020	32	2M +89-0MM (6'7"+3.50-0)
4	1300630150	C04006A48M020	32	2M +89-0MM (6'7"+3.50-0)

FACE VIEW-MALE INSERT



SPECS:
 OVERMOLD: GRAY PVC W/BLACK STRIP
 INSERT: BLACK PVC
 COUPLING NUT: ANODIZED ALUMINUM
 CABLE: #10AWG GRAY PVC
 DUAL RATED UL TC/OPEN WIRING & ST00W
 ELECTRICAL: 600V AC/DC

UPDATED PROFILE EC NO: IFG2014-1160 DRWG:GGUSTAFSON 2013/12/23 CHKD:VOU 2014/01/15 APPR:WOODMAN 2014/05/12	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION															
	$\nabla=0$ $\nabla=0$	<table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± .005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.13</td> <td>± .010</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.25</td> <td>± .020</td> </tr> </tbody> </table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± 0.13	± .010	1 PLACE	± 0.25	± .020	IN/MM	NTS	INCH	
		mm	INCH																		
	4 PLACES	± ---	± ---																		
3 PLACES	± ---	± .005																			
2 PLACES	± 0.13	± .010																			
1 PLACE	± 0.25	± .020																			
<table border="1"> <thead> <tr> <th>REV</th> <th>DESCRIPTION</th> </tr> </thead> <tbody> <tr> <td>B</td> <td></td> </tr> </tbody> </table>	REV	DESCRIPTION	B		<table border="1"> <thead> <tr> <th>DRAWN BY</th> <th>DATE</th> </tr> </thead> <tbody> <tr> <td>B. RUPERT</td> <td>01/12/2010</td> </tr> <tr> <th>CHECKED BY</th> <th>DATE</th> </tr> <tr> <td>B. WOODMAN</td> <td>01/12/2010</td> </tr> <tr> <th>APPROVED BY</th> <th>DATE</th> </tr> <tr> <td>JFMURPHY</td> <td>2010/01/15</td> </tr> </tbody> </table>	DRAWN BY	DATE	B. RUPERT	01/12/2010	CHECKED BY	DATE	B. WOODMAN	01/12/2010	APPROVED BY	DATE	JFMURPHY	2010/01/15	TITLE QUICK CHANGE MALE STRAIGHT 3 & 4 POLE PORTABLES			
REV	DESCRIPTION																				
B																					
DRAWN BY	DATE																				
B. RUPERT	01/12/2010																				
CHECKED BY	DATE																				
B. WOODMAN	01/12/2010																				
APPROVED BY	DATE																				
JFMURPHY	2010/01/15																				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-130063-042	SHEET NO. 1 OF 1																
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		