

#### PROTECTION PRODUCTS - TransClamp™

#### Description

A TransClamp™ is a low capacitance TVS array designed to protect high speed data interfaces. This series has been specifically designed to protect sensitive components which are connected to data and transmission lines from overvoltage caused by **ESD** (electrostatic discharge), **CDE** (Cable Discharge Events), and **Lightning**.

These devices integrate low capacitance, surge-rated compensation diodes with a high power transient voltage suppressor (TVS). The compensation diodes are arranged in a bridge pattern allowing the device to be connected in common mode and/or differential mode. This allows the designer maximum flexibility and reduces parts count. The capacitance of the device is limited to 12pF maximum from line-to-line to ensure correct signal transmission on high-speed lines.

These devices may be used to meet Bellcore GR-1089-CORE short-haul (intra-building) surge requirements and will withstand a minimum 100 A surge for a 2/10µs pulse.

The TClamp™0602N is in a 10-pin, RoHS/WEEE compliant, SLP2626P10 package. It measures 2.6 x 2.6 x 0.60mm. The leads are spaced at a pitch of 0.5mm and are finished with lead-free NiPdAu. They are particularly well suited for applications where board space is at a premium such as integrated connectors/magnetics and T1/E1 equipment.

#### Features

- ◆ Transient protection for high-speed data lines to **Bellcore 1089 (Intra-Building) 100A (2/10µs)**  
**IEC 61000-4-2 (ESD) ±15kV (air), ±8kV (contact)**  
**IEC 61000-4-4 (EFT) 40A (5/50ns)**  
**IEC 61000-4-5 (Lightning) L5, 95A (8/20µs)**
- ◆ Protects two lines in common and differential mode
- ◆ Low capacitance (12pF line-to-line)
- ◆ Low operating voltages (6V)
- ◆ Low clamping voltage
- ◆ Small SLP Package saves board space
- ◆ Solid-state technology


#### Mechanical Characteristics

- ◆ SLP2626P10 10L package
- ◆ RoHS/WEEE Compliant
- ◆ Nominal Dimensions: 2.6 x 2.6 x 0.60 mm
- ◆ Lead Pitch: 0.5mm
- ◆ Molding compound flammability rating: UL 94V-0
- ◆ Marking: Marking Code
- ◆ Packaging: Tape and Reel


#### Applications

- ◆ T1/E1
- ◆ T3/E3
- ◆ 10/100 Ethernet
- ◆ Integrated Magnetics
- ◆ Carrier Class Equipment
- ◆ ISDN Interfaces

#### Circuit Diagram



#### Package Configuration



**PROTECTION PRODUCTS**
**Absolute Maximum Rating**

| Rating   | Symbol    | Value       | Units |
|--|-----------|-------------|-------|
| Peak Pulse Power (tp = 8/20μs)                                 | $P_{pk}$  | 2500        | Watts |
| Peak Pulse Current (tp = 2/10μs)                               | $I_{pp}$  | 120         | A     |
| Peak Pulse Current (tp = 8/20μs)                               | $I_{pp}$  | 95          | A     |
| ESD per IEC 61000-4-2 (Air)<br>ESD per IEC 61000-4-2 (Contact) | $V_{ESD}$ | 30<br>30    | kV    |
| Operating Temperature  | $T_J$     | -55 to +125 | °C    |
| Storage Temperature  | $T_{STG}$ | -55 to +150 | °C    |


**Electrical Characteristics (T=25°C)**

| <b>TClamp0602N</b>        |           |   |         |         |         |       |
|---------------------------|-----------|---|---------|---------|---------|-------|
| Parameter                 | Symbol    | Conditions  | Minimum | Typical | Maximum | Units |
| Reverse Stand-Off Voltage | $V_{RWM}$ |   |         |         | 6       | V     |
| Reverse Breakdown Voltage | $V_{BR}$  | $I_t = 1mA$                                       | 6.8     |         |         | V     |
| Reverse Leakage Current   | $I_R$     | $V_{RWM} = 6V, T=25^\circ C$                      |         |         | 5       | μA    |
| Clamping Voltage          | $V_C$     | $I_{pp} = 100A, tp = 2/10\mu s$<br>Line-to-Ground |         |         | 25      | V     |
| Clamping Voltage          | $V_C$     | $I_{pp} = 100A, tp = 2/10\mu s$<br>Line-to-Line   |         |         | 29      | V     |
| Junction Capacitance      | $C_J$     | Line-to-Gnd<br>$V_R = 0V, f = 1MHz$               |         |         | 25      | pF    |
|                           |           | Line-to-Line<br>$V_R = 0V, f = 1MHz$              |         |         | 12      | pF    |


PROTECTION PRODUCTS

Typical Characteristics


Non-Repetitive Peak Pulse Power vs. Pulse Time




Power Derating Curve




Clamping Voltage vs. Peak Pulse Current  
Line-to-Ground



Clamping Voltage vs. Peak Pulse Current  
Line-to-Line



Normalized Junction Capacitance  
vs. Reverse Voltage




## PROTECTION PRODUCTS

### Applications Information


#### Device Connection Options for Protection of Two High-Speed Data Lines

These devices are designed to protect two high-speed data lines (one differential pair) from transient over-voltages which result from lightning and ESD. They can be configured to protect in differential (Line-to-Line) and common (Line-to-Ground) mode. Data line inputs/outputs are connected at pins 1, 2 and 3, and 8, 9 and 10 as shown. For proper operation, pins 1 - 3 must be connected together and pins 8 - 10 must be connected together. Pins 4, 5, 6, and 7 left unconnected. For differential operation, the center tab is also left not connected. For common mode operation, the center tab is connected to ground. The ground connection should be made directly to a ground plane on the board for best results. The use of multiple vias is recommended for reduced ground loop inductance.

**Circuit Diagram**




**Pin Configuration (Top Side View)**



| Pin        | Identification |
|------------|----------------|
| 1, 2, 3    | Line 1 in/out  |
| 8, 9, 10   | Line 2 in/out  |
| 4, 5, 6, 7 | No Connect     |
| Center Tab | Ground         |

PROTECTION PRODUCTS

Applications Information - Spice Model




TClamp0602N Spice Model

| TClamp0602N Spice Parameters |       |          |           |           |
|------------------------------|-------|----------|-----------|-----------|
| Parameter                    | Unit  | D1 (TVS) | D2 (LCRD) | D3 (LCRD) |
| IS                           | Amp   | 1.4E-11  | 1.001E-20 | 1.001E-20 |
| BV                           | Volt  | 8.3      | 150       | 150       |
| VJ                           | Volt  | 0.56     | 0.59      | 0.59      |
| RS                           | Ohm   | 0.029    | 0.075     | 0.064     |
| IBV                          | Amp   | 1E-3     | 1E-3      | 1E-3      |
| CJO                          | Farad | 300e-12  | 11.0E-12  | 11.0E-12  |
| TT                           | sec   | 2.541E-9 | 2.541E-9  | 2.541E-9  |
| M                            | --    | 0.256    | 0.01      | 0.01      |
| N                            | --    | 1.1      | 1.1       | 1.1       |
| EG                           | eV    | 1.11     | 1.11      | 1.11      |

PROTECTION PRODUCTS

Outline Drawing - SLP2626P10




| DIM | DIMENSIONS |      |      |             |      |      |
|-----|------------|------|------|-------------|------|------|
|     | INCHES     |      |      | MILLIMETERS |      |      |
|     | MIN        | NOM  | MAX  | MIN         | NOM  | MAX  |
| A   | .020       | .024 | .026 | 0.50        | 0.60 | 0.65 |
| A1  | .000       | .001 | .002 | 0.00        | 0.03 | 0.05 |
| A2  | (.007)     |      |      | (0.17)      |      |      |
| b   | .007       | .010 | .012 | 0.20        | 0.25 | 0.30 |
| D   | .098       | .102 | .106 | 2.50        | 2.60 | 2.70 |
| D1  | .079       | .085 | .089 | 2.00        | 2.15 | 2.25 |
| E   | .098       | .102 | .106 | 2.50        | 2.60 | 2.70 |
| E1  | .044       | .050 | .054 | 1.11        | 1.26 | 1.36 |
| e   | .020 BSC   |      |      | 0.50 BSC    |      |      |
| L   | .011       | .014 | .016 | 0.30        | 0.35 | 0.40 |
| N   | 10         |      |      | 10          |      |      |
| aaa | .003       |      |      | 0.08        |      |      |
| bbb | .004       |      |      | 0.10        |      |      |

NOTES:

1. CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).
2. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

Land Pattern - SLP2626P10




| DIM | DIMENSIONS |             |
|-----|------------|-------------|
|     | INCHES     | MILLIMETERS |
| B   | .081       | 2.05        |
| C   | .100       | 2.50        |
| F   | .050       | 1.26        |
| G   | .073       | 1.85        |
| P   | .020       | 0.50        |
| X   | .012       | 0.30        |
| Y   | .025       | 0.65        |
| Z   | .124       | 3.15        |

NOTES:

1. THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY. CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR COMPANY'S MANUFACTURING GUIDELINES ARE MET.

## PROTECTION PRODUCTS

### Marking



YY = year  
WW = Week



### Ordering Information

| Part Number     | Qty per Reel | Reel Size |
|-----------------|--------------|-----------|
| TClamp0602N.TCT | 3,000        | 7 Inch    |

Note: Lead finish is lead-free NiPdAu

TransClamp and TClamp are marks of Semtech Corporation

### Tape and Reel Specification



Pin 1 Location

→ User Direction of feed

### Device Orientation in Tape

| A0              | B0              | K0              |
|-----------------|-----------------|-----------------|
| 2.77 +/-0.05 mm | 2.77 +/-0.05 mm | 0.80 +/-0.05 mm |

| Tape Width | B, (Max)      | D                     | D1           | E            | F           | K (MAX) | P          | P0         | P2          | T(MAX) | W                        |
|------------|---------------|-----------------------|--------------|--------------|-------------|---------|------------|------------|-------------|--------|--------------------------|
| 8 mm       | 4.2 mm (.165) | 1.5 + 0.1 mm - 0.0 mm | 1.0 mm ±0.05 | 1.750±.10 mm | 3.5±0.05 mm | 2.4 mm  | 4.0±0.1 mm | 4.0±0.1 mm | 2.0±0.05 mm | 0.4 mm | 8.0 mm + 0.3 mm - 0.1 mm |

### Contact Information

Semtech Corporation  
Protection Products Division  
200 Flynn Rd., Camarillo, CA 93012  
Phone: (805)498-2111 FAX (805)498-3804