

5

4

3

2

1

D



Description: 9 Pin Crimp Type Plug
 Part No: 40-9809M
 Application: 98 Series D-Sub Connector
 Crimp Tool: N/A
 Impedance: N/A
 Frequency Range: N/A
 Material: Shell Steel, Nickel plated
 Insulator PBT+Fiber-grass and nylon-66,
 UL94-V0 Black

RoHS Compliance: Yes

Technical Detail: N/A

DRAWING NO.
40-9809M-CUST(SEE TABLE I)

REVISIONS

01		OFFICIAL RELEASE				
11-26-09	Y	U	Y	T	H	
02		CHANGE SHELL PLATING FROM YELLOW ZINC TO NICKEL				
10-15-10	J	J	Y	T	H	ECO-10-0166
03		CHANGE DIMENSIONS: 10.60 TO 11.0±0.25; D DIMENSION FOR 40-9825M FROM 41.28 TO 41.10; ADD DIMENSION: 10.90±0.25; DELETE DIMENSION: 1.35MAX.				
03-24-11	J	J	J	D		ECO-11-0054

D


C

C

TABLE I

Part Number	Description	A (mm)	B (mm)	C (mm)	D (mm)
40-9809M	9 Pin Crimp Type Plug	30.80	24.99	16.92	19.20
40-9815M	15 Pin Crimp Type Plug	39.15	33.32	25.25	27.70
40-9825M	25 Pin Crimp Type Plug	53.00	47.04	38.96	41.10
40-9837M	37 Pin Crimp Type Plug	69.30	63.50	55.42	57.30


B



B

A

A



DIM OUTLINE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY JEAN.JIN	DATE 03-24-11
DECIMALS	mm	CHECKED BY JEAN.JIN	DATE 03-24-11
X	± 0.5	APPROVED BY DONALD	DATE 03-24-11
X.X	± 0.3	U/M	mm
X.XX	± 0.2		
ANGLES	± 0.5°		

		Connectivity Solutions	
TITLE 98 SERIES CRIMP STYLE PANEL & CABLE MOUNT D-SUB CONNECTORS			
SHEET 1 OF 1	DRAWING NO. 40-9809M-CUST (SEE TABLE I)	SIZE A	

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[40-9809M](#)