

**M12 male 0° with cable F&B Pro**

TPE-S 5x0.34 bu robot+drag chain 5m

Plug Connectors for Food & Beverage

Male straight

M12 F&B Pro

5-pole

Screw, Stainless Steel 1.4404 (V4A)

without cable sleeves



IP69K

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.


[Link to Product](#)

**Illustration**

stay connected



Male



Product may differ from Image

**Approvals**



\* only for products with UL/CSA approved cable

**Form**

Form 12041

**Cables**

Cable number 339

No./diameter of wires 5 x 0.34 mm<sup>2</sup>

|                                    |  |
|------------------------------------|--|
| Wire isolation                     | PP (br, wh, bl, bk, gnye)  |
| C-track properties                 | 4 Mio.   |
| Jacket Color                       | pastel blue  |
| Material (jacket)                  | TPE (UL)   |
| Outer Ø                            | 5.0 mm ±5%   |
| Bend radius (moving)               | 10× outer Ø  |
| Temperature range (fixed)          | -40...+105 °C  |
| Temperature range (mobile)         | -25...+105 °C  |
| Cable identification               | 339  |
| Approval (cable)                   | UL (AWM-Style 22126/11558), CE conform   |
| Cable weight [g/m]                 | 35,20  |
| Material (wire)                    | Cu wire, bare  |
| Resistor (core)                    | max. 58 Ω/km (20 °C)   |
| Single wire Ø (core)               | 0.1 mm   |
| Construction (core)                | 42× 0.1 mm (multi-strand wire class 6)   |
| Diameter (core)                    | 5× 0.34 mm <sup>2</sup>  |
| AWG                                | similar to AWG 22  |
| Material (wire isolation)          | PP   |
| Material property (wire isolation) | CFC-, halogen-, cadmium-, silicone- and lead-free  |
| Shore hardness (wire isolation)    | 64 ±3 D  |
| Wire-Ø incl. isolation             | 1.27m ±5%  |
| Color/numbering of wires           | br, bk, bl, wh, gnye longitudinally striped  |
| Stranding combination              | 5 wires twisted around central filler  |
| Shield                             | no   |
| Material (jacket)                  | TPE-S (laser-markable)   |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 47 ±5 D  |
| Outer-Ø (jacket)                   | 5.0 mm ±5%   |
| Color (jacket)                     | pastel blue  |
| Nominal voltage                    | 300 V AC   |
| Test voltage                       | 3000 V AC  |
| Current load capacity              | to DIN VDE 0298-4  |
| Temperature range (fixed)          | -40...+105 °C  |
| Temperature range (mobile)         | -25...+105 °C  |
| Bend radius (fixed)                | 5× outer Ø   |
| Bend radius (moving)               | 10× outer Ø  |
| No. of bending cycles (C-track)    | max. 4 Mio. (25 °C)  |
| Traversing distance (C-track)      | max. 10 m  |
| Travel speed (C-track)             | max. 3 m/s   |
| Acceleration (C-track)             | max. 10 m/s <sup>2</sup>   |
| Torsion stress                     | ±180°/m  |
| No. of torsion cycles              | max. 2 Mio. (25 °C)  |
| Torsion speed                      | 35 cycles/min  |
| <b>Technical Data</b>              |  |
| Operating voltage                  | max. 125 V AC/DC   |
| Operating voltage (only UL listed) | max. 30 V AC/DC  |
| Rated surge voltage                | 1.5 kV   |
| Operating current per contact      | max. 4 A   |
| No. of poles                       | 5-pole   |

|   |  |
|---|--|
| Material group                            | IEC 60664-1, category I  |
| Coding                                    | A-coded  |
| LED display                               | no   |
| Locking of ports                          | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                         | M12 (SW14)   |
| Protection                                | IP65, IP68, IP69K inserted and tightened (EN 60529)              |
| Material                                  | PP   |
| Locking material                          | Stainless steel 1.4404 (V4A)                                     |
| suitable for corrugated tube (internal Ø) | without  |

**General data**

|                            |   |
|----------------------------|---|
| Standards                  | DIN EN 61076-2-101 (M12), FDA conform     |
| Mounting method            | inserted, tightened                       |
| Material (contact)         | Copper alloy                              |
| Material (contact surface) | Au  |
| Material (contact carrier) | PP, ice blue                              |
| Pollution Degree           | 3   |
| Stripping length (jacket)  | 20 mm                                     |
| Temperature range          | -40...+105 °C, depending on cable quality |

**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879690140 |
| eClass                | 27279218      |
| Packaging unit        | 1             |