



www.niccomp.com/pcn | Technical Support: tpmg@niccomp.com

Issued: March 29th, 2019
SUB: EOL Notice

Product Type: Surface Mount UV LEDs
NIC Series: NUVA and NUVC Series

Notification: End of Life Notification

The following is notification of the end of life for the NUVA and NUVC series of surface mount UV LEDs effective March 29th, 2019. A list of the affected parts numbers can be found in table #1.

Last Order Date: September 29th, 2019 for established customers with existing business on these part numbers
Last Ship Date: March 29th, 2020 for established customers with existing business on these part numbers


Reason for Discontinuation: Low Demand
Prepared by: Technical Product Marketing Group / tpmg@niccomp.com

| Series | Discontinued Part Numbers | Size | Wavelength |
|--------|---------------------------|----------------|------------|
| NUVA33 | NUVA33R365TRF | 3.4x3.4x2.37mm | 365nm |
| NUVA33 | NUVA33R365TRSF | 3.4x3.4x2.37mm | 365nm |
| NUVA33 | NUVA33HP1R7R365TRF | 3.4x3.4x2.37mm | 365nm |
| NUVA33 | NUVA33T385TRF | 3.4x3.4x2.37mm | 385nm |
| NUVA33 | NUVA33U395TRF | 3.4x3.4x2.37mm | 395nm |
| NUVA33 | NUVA33V405TRF | 3.4x3.4x2.37mm | 405nm |
| NUVA35 | NUVA35R365TRF | 3.4x3.4x3.34mm | 365nm |
| NUVA35 | NUVA35T385TRF | 3.4x3.4x3.34mm | 385nm |
| NUVA35 | NUVA35U395TRF | 3.4x3.4x3.34mm | 395nm |
| NUVA35 | NUVA35V405TRF | 3.4x3.4x3.34mm | 405nm |
| NUVA66 | NUVA66R365TRF | 6.0x6.0x1.20mm | 365nm |
| NUVA66 | NUVA66R365STAR1F | 6.0x6.0x1.20mm | 365nm |
| NUVA66 | NUVA66HP2R365TRF | 6.0x6.0x1.20mm | 365nm |
| NUVA66 | NUVA66T385TRF | 6.0x6.0x1.20mm | 385nm |
| NUVA66 | NUVA66HP2T385TRF | 6.0x6.0x1.20mm | 385nm |
| NUVA66 | NUVA66U395TRF | 6.0x6.0x1.20mm | 395nm |
| NUVA66 | NUVA66HP2U395TRF | 6.0x6.0x1.20mm | 395nm |
| NUVA66 | NUVA66V405TRF | 6.0x6.0x1.20mm | 405nm |
| NUVA66 | NUVA66HP2V405TRF | 6.0x6.0x1.20mm | 405nm |
| NUVA77 | NUVA77R365TRF | 6.8x6.8x1.45mm | 365nm |
| NUVA77 | NUVA77T385TRF | 6.8x6.8x1.45mm | 385nm |
| NUVA77 | NUVA77U395TRF | 6.8x6.8x1.45mm | 395nm |
| NUVA77 | NUVA77HP6U395TRF | 6.8x6.8x1.45mm | 395nm |
| NUVA77 | NUVA77V405TRF | 6.8x6.8x1.45mm | 405nm |
| NUVC66 | NUVC66DW278TRF | 6.0x6.0x1.35mm | 278nm |

➔ Follow NIC PCN alerts to get email notifications of EOL and PCN announcements at www.niccomp.com/pcn

FEATURES

- SURFACE MOUNT 3.4mm x 3.4mm x 2.37mm
- WAVELENGTH 365 ~ 405nm FOR UV CURING, PHOTO CATALYST & SENSOR LIGHTING
- RoHS COMPLIANT
- COMPATIBLE WITH REFLOW SOLDERING
- TAPE AND REEL PACKAGING




| SPECIFICATIONS | Case Sizes |
|--|---|
| | 33 (3.4x3.4x2.37mm) |
| Wavelength | 365nm ~ 405nm (nominal) |
| Forward Current | 500mA |
| Radiant Flux | 870mW ~ 1,110mW (typical) |
| Power Dissipation | 3.08W (365nm), 2.66W (385, 395 & 405nm) |
| Operating Temperature* | -10°C ~ +85°C |
| Junction Temperature (Tj) | +90°C ~ +125°C max. |
| Thermal Resistance (Typical) ^{Note 1} | 4.5°C/W |
| Viewing Angle (2 θ 1/2) | 120° (365nm) 130° (385, 395 & 405nm) |

Note 1 - Rthj-c = Thermal Resistance (Junction - Case)

*After soldering storage temperature is -40°C ~ +100°C

PART NUMBERING SYSTEM



* See page 2 for definitions


WAVELENGTH CODES

| Code | Nominal Wavelength |
|------|--------------------|
| R | 365nm |
| T | 385nm |
| U | 395nm |
| V | 405nm |

COMPONENT DIMENSIONS



| Item | Dimension (mm) |
|------|----------------|
| L | 3.40 |
| R | φ3.10 |
| H1 | 2.37 |
| H2 | 0.68 |
| H3 | 0.82 |
| W | 3.40 |
| T1 | 1.30 |
| T2 | 2.30 |
| T3 | 3.20 |
| Wt | 3.20 |

Tolerance: ±0.13



| Termination | Connection |
|-------------|-------------|
| 1 | Anode |
| 2 | Thermal Pad |
| 3 | Cathode |

Internal Circuit Diagram







PART NUMBERS AND RANKING CODES (Forward Current - 500mA)

| Part Numbers | Ranking Codes (Note 2) | Wavelength (nm) | Radiant Flux (mW) | | Voltage (V) | | Thermal Resistance (Typical) ^{Note 1} | Junction Temperature | Spectrum Half Width (Typical) | Viewing Angle (Typical) |
|---------------|---------------------------|--------------------|----------------------|------|----------------|------|---|----------------------|----------------------------------|----------------------------|
| | | | Min. | Max. | Min. | Max. | Rth j-c | °C | $\Delta\lambda$ | 2 θ 1/2 |
| NUVA33R365TRF | P12-V2 | 360 ~ 370 | 870 | 960 | 3.4 | 3.6 | 4.5°C/W | <90°C | 9.0nm | 120° |
| | P12-V3 | | | | 3.6 | 3.8 | | | | |
| | P13-V2 | | 960 | 1060 | 3.4 | 3.6 | | | | |
| | P13-V3 | | | | 3.6 | 3.8 | | | | |
| | P14-V2 | | 1060 | 1170 | 3.4 | 3.6 | | | | |
| P14-V3 | 3.6 | 3.8 | | | | | | | | |
| NUVA33T385TRF | HP12-V1 | 380 ~ 390 | 1000 | 1100 | 3.2 | 3.4 | | <125°C | | 130° |
| | HP12-V2 | | | | 3.4 | 3.6 | | | | |
| | HP12-V3 | | | | 3.6 | 3.8 | | | | |
| | HP13-V1 | | 1100 | 1210 | 3.2 | 3.4 | | | | |
| | HP13-V2 | | | | 3.4 | 3.6 | | | | |
| | HP13-V3 | | 1210 | 1330 | 3.6 | 3.8 | | | | |
| | HP14-V1 | | | | 3.2 | 3.4 | | | | |
| | HP14-V2 | | | | 3.4 | 3.6 | | | | |
| HP14-V3 | 3.6 | 3.8 | | | | | | | | |
| NUVA33U395TRF | HP12-V1 | 390 ~ 400 | 1000 | 1100 | 3.2 | 3.4 | 4.5°C/W | | 130° | |
| | HP12-V2 | | | | 3.4 | 3.6 | | | | |
| | HP12-V3 | | | | 3.6 | 3.8 | | | | |
| | HP13-V1 | | 1100 | 1210 | 3.2 | 3.4 | | | | |
| | HP13-V2 | | | | 3.4 | 3.6 | | | | |
| | HP13-V3 | | 1210 | 1330 | 3.6 | 3.8 | | | | |
| | HP14-V1 | | | | 3.2 | 3.4 | | | | |
| | HP14-V2 | | | | 3.4 | 3.6 | | | | |
| HP14-V3 | 3.6 | 3.8 | | | | | | | | |
| NUVA33V405TRF | HP12-V1 | 400 ~ 410 | 1000 | 1100 | 3.2 | 3.4 | | 4.5°C/W | 130° | |
| | HP12-V2 | | | | 3.4 | 3.6 | | | | |
| | HP12-V3 | | | | 3.6 | 3.8 | | | | |
| | HP13-V1 | | 1100 | 1210 | 3.2 | 3.4 | | | | |
| | HP13-V2 | | | | 3.4 | 3.6 | | | | |
| | HP13-V3 | | 1210 | 1330 | 3.6 | 3.8 | | | | |
| | HP14-V1 | | | | 3.2 | 3.4 | | | | |
| | HP14-V2 | | | | 3.4 | 3.6 | | | | |
| HP14-V3 | 3.6 | 3.8 | | | | | | | | |





Note 1 - Rthj-c = Thermal Resistance (Junction - Case)

Note 2 - Actual ranking code will be specified by NIC on reel label.





FORWARD VOLTAGE VS. FORWARD CURRENT @ +25°C







FORWARD CURRENT VS. RELATIVE RADIANT FLUX @ +25°C







SPECTRUM @ +25°C & 500mA







FORWARD CURRENT VS. PEAK WAVELENGTH @ +25°C







RADIATION CHARACTERISTICS
 (Angle of Beam Spread, Directivity)
 +25°C, 500mA If







AMBIENT TEMPERATURE VS. PEAK WAVELENGTH @ 500mA If




AMBIENT TEMPERATURE VS. RELATIVE RADIANT FLUX @ 500mA If




AMBIENT TEMPERATURE VS. FORWARD VOLTAGE @ 500mA If



DERATING CURVES




NUVA33R365TRF: $T_j = 090^{\circ}\text{C}$, $R_{th\ j-a} \sim 10^{\circ}\text{C/W}$



NUVA33T385TRF: $T_j = 125^{\circ}\text{C}$, $R_{th\ j-a} \sim 10^{\circ}\text{C/W}$
 NUVA33U395TRF: $T_j = 125^{\circ}\text{C}$, $R_{th\ j-a} \sim 10^{\circ}\text{C/W}$
 NUVA33V405TRF: $T_j = 125^{\circ}\text{C}$, $R_{th\ j-a} \sim 10^{\circ}\text{C/W}$


LAND PATTERN DIMENSIONS

| Item | Dimension (mm) |
|------|----------------|
| a | 3.3 ± 0.13 |
| b | 1.3 ± 0.13 |
| c | 2.3 ± 0.13 |
| d | 3.3 ± 0.13 |
| e | 0.5 ± 0.13 |
| f | 0.5 ± 0.13 |
| g | 0.5 ± 0.13 |



| Land Pad | Connection |
|----------|-------------|
| 1 | Anode |
| 2 | Thermal Pad |
| 3 | Cathode |

REFLOW SOLDERING PROFILE




RELIABILITY DATA

| Item | Conditions | Failure Criteria |
|--|--|---|
| Load Life 1 | +25°C, 500mA for 1,000 hours | Forward Voltage (Vf): ±10 of initial value Radiant Flux (φe): ±30 of initial value |
| Load Life 2 | +25°C, 700mA for 1,000 hours | |
| High Temperature Load Life (1,000 hours) | For 365nm at +85°C, 100mA For 385nm ~ 405nm at +85°C, 300mA | |
| Humidity Load Life | 365nm at +60°C, 90% RH, 350mA for 500 hours 385nm ~ 405nm at +60°C, 90% RH, 450mA for 500 hours | |
| Load Temperature Load Life | -10°C, 500mA for 1,000 hours | |
| High Temperature Storage | +100°C for 1,000 hours | |
| Low Temperature Storage | -40°C for 1,000 hours | |
| Temperature Cycling 100 Cycles | -40°C (30 minutes) ~ +25°C (5 minutes) +100°C (30 minutes) ~ +25°C (5 minutes) | |
| Resistance to Vibration | 100Hz ~ 1,000Hz ~ 100Hz for 4 minutes, 200m/s ² , 3 directions for 48 minutes total | |
| ESD (Human Body Model) | R = 1.5KΩ, C = 100pF Test Voltage = 2KV 3 times negative/positive | |
| Moisture Sensitivity (MSL) | 3 time reflow with peak temperature +260°C Pre-conditioning: +60°C, 60% RH for 168 hours | |

EMBOSED PLASTIC TAPE DIMENSIONS (mm)


| Type | Size | A ± 0.10 | B ± 0.10 | D +0.1/-0 | E ± 0.10 | F ± 0.1 | P ₀ ± 0.1 | P ₁ ± 0.1 | P ₂ ± 0.1 | W ± 0.3 | T ± 0.1 |
|--------|-----------|----------|----------|-----------|----------|---------|----------------------|----------------------|----------------------|---------|---------|
| NUVA33 | 3.4 x 3.4 | 3.80 | 3.80 | 1.50 | 1.75 | 5.50 | 2.0 | 4.0 | 12.0 | 12.0 | 2.50 |




TAPE LEADER: 150mm ~ 600mm
 EMPTY CARRIER AT START OF REEL: 400mm min.
 EMPTY CARRIER AT END OF REEL: 200mm min.

REEL DIMENSIONS (mm)



| Type | A ± 2.0 | B ± 2.0 | C ± 2.0 | D ± 0.8 | W ± 2.0 | Qty/Reel |
|--------|---------|---------|---------|---------|---------|----------|
| NUVA33 | φ203 | φ60 | φ13.0 | φ21.0 | 13.0 | 500 max. |





NIC Components Corp.

(1P) Model No.: NUVA33


Ranking Code: T-HP11-V2

(Q) QTY: 500 (9D) DATE CODE: YYWW
 

(1T) LOT: XXXXXXXXXXXXXXXX
 **RoHS Compliant**

FACTORY INTERNAL REFERENCE INFORMATION FIELD 

Precautions for storage, handling and use of UV LED components**Storage Conditions:**

Before opening moisture barrier bag: 5°C ~ 30°C 50% RH. Use within 1 year from the delivery date

After opening moisture barrier bag: 5°C ~ 30°C 60% RH. Solder with 672 hours

Baking conditions: 65°C ± 5° 10% RH 10 ~ 24 hours

ESD Precautions:

LEDs are sensitive to static electricity or surge voltage and current. Electrostatic discharge can damage LED components and affect component reliability. When handling LEDs the following measures against ESD are recommended :

1. Wear a wrist strap, anti-static clothes, foot wear and gloves.
 2. Set up a grounded or anti-static paint floors, a grounded or the ability to surge protection workstation equipment and tools.
 3. Work tables and benches should have surface mat made of a conductive materials. Appropriate grounding is required for all devices, equipment, and machinery used in the product assembly.
 4. Incorporate surge protection when reviewing the design of products (Curing Module, etc).
 5. If tools or equipment contain insulating materials such as glass or plastics are used the following measures against ESD are strongly recommended :
 - a. Dissipating static charge with conductive materials
 - b. Preventing charge generation with moisture
 - c. Plug in the ionizing blowers(ionizer) for neutralizing the charge
 - d. The customer is advised to check if the LEDs are damaged by ESD when performing the characteristics inspection of the LEDs in the application.
 - e. Damage of LED can be detected with a forward voltage checking(measuring) at low current($\leq 1\text{mA}$). LEDs damaged by ESD may have a current flow at a low voltage.
- * Failure Criteria : $V_F < 2.0\text{V}$ at $I_f = 0.5\text{mA}$.

Cleaning:

1. Do not use brushes for cleaning or organic solvents (i.e. Acetone, TCE, etc..) for washing as they may damage the resin of the LEDs.
2. Isopropyl Alcohol(IPA) is the recommended solvent for cleaning the LEDs under the following conditions.
3. Cleaning Condition : IPA, 25°C max. × 60sec max.
4. Ultrasonic cleaning is **not** recommended.
5. Pretests should be conducted with the actual cleaning process to validate that the process will not damage the LEDs.

Manual handling and soldering:

1. Use Teflon-type tweezers to grab the base of the LED and do not apply mechanical pressure on the surface of the encapsulant.
2. The recommended soldering iron condition is 260°C for <5 seconds. For higher temperatures a short contact time is required (reduce duration 1 second for every 10°C increase in temperature).
3. The power dissipation of the soldering iron should be lower than 15W and the surface temperature of the device should be controlled to $\leq 230^{\circ}\text{C}$

Usage:

1. The LED should not come into direct contact with hazardous materials such as sulfur, chlorine, phthalate, etc.
2. The metal parts on the LED can rust when exposed to corrosive gases. Therefore, exposure to corrosive gases must be avoided during operation and storage.
3. The silver-plated metal parts also can be affected not only by the corrosive gases emitted inside of the end-products but by the gases penetrated from outside environment.
4. Extreme environments such as sudden ambient temperature changes or high humidity that can cause condensation must be avoided.
5. Do not directly look at the light when the LEDs are on. Proceed with caution to avoid the risk of damage to the eyes when examining the LEDs with optical instruments.