

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Round cable set; connection 1: IDC/FLK socket strip (1x 14-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 1.5 m



## Commercial Data

Item number	2288927
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	C421
Product Key	CK2131
Catalog Page	Page 536 (C-5-2019)
GTIN	4017918057312
Weight per Piece (including packing)	97.033 g
Weight per Piece (excluding packing)	94.8 g
Customs tariff number	85444290
Country of origin	DE

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

## Technical Data

### Product properties

Product type	System cable
--------------	--------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

### Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

#### Supported controller SIEMENS S7-1500

Suitable I/O card	6ES7521-1BH00-0AB0
	6ES7521-1BH10-0AA0
	6ES7521-1BH50-0AA0
	6ES7521-1BL00-0AB0
	6ES7522-1BH00-0AB0
	6ES7522-1BH01-0AB0
	6ES7522-1BH10-0AA0
	6ES7522-1BL00-0AB0
	6ES7522-1BL01-0AB0
	6ES7531-7KF00-0AB0
	6ES7531-7LH00-0AB0
	6ES7531-7MH00-0AB0
	6ES7531-7NF00-0AB0
	6ES7531-7NF10-0AB0
	6ES7531-7PF00-0AB0
	6ES7532-5HF00-0AB0
	6ES7532-5HD00-0AB0
6ES7532-5ND00-0AB0	

#### Supported controller SIEMENS S7-300 / ET 200 M

Suitable I/O card	CPU 312C
	CPU 313C

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

	CPU 313C-2DP
	CPU 313C-2PiP
	CPU 314C-2DP
	CPU 314C-2PiP
	6ES7321-1BH02-0AA0
	6ES7321-1BH10-0AA0
	6ES7321-1BH50-0AA0
	6ES7321-1BL00-0AA0
	6ES7321-7BH01-0AB0
	6ES7322-1BH01-0AA0
	6ES7322-1BH10-0AA0
	6ES7322-1BL00-0AA0
	6ES7322-8BF00-0AB0
	6ES7322-8BH01-0AB0
	6ES7323-1BH01-0AA0
	6ES7323-1BL00-0AA0
	6ES7331-7HF01-0AB0
	6ES7331-7KB02-0AB0
	6ES7331-7KF02-0AB0
	6ES7331-7NF00-0AB0
	6ES7331-7PF01-0AB0
	6ES7331-7PF11-0AB0
	6ES7332-5HD01-0AB0
	6ES7332-5HB01-0AB0
	6ES7332-7ND02-0AB0
	6ES7332-8TF01-0AB0
	6ES7334-0CE01-0AA0
	6ES7334-0KE00-0AB0
	6ES7335-7HG01-0AB0
	6ES7336-4GE00-0AB0
	6ES7338-4BC01-0AB0
	6ES7350-1AH03-0AE0
	6ES7350-2AH01-0AE0
	6ES7351-1AH01-0AE0
	6ES7352-1AH02-0AE0
	6ES7353-1AH01-0AE0
	6ES7354-1AH01-0AE0
	6ES7355-0VH10-0AE0
	6ES7355-1VH10-0AE0
	6ES7357-4AH01-0AE0

Supported controller ALLEN-BRADLEY ControlLogix

Suitable I/O card	1756-IN16
	1756-IA8D

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

	1756-IA16
	1756-IB16
	1756-IC16
	1756-OB16E
	1756-IR6I
	1756-IT6I
	1756-OF4
	1756-OF6CI
	1756-OF8
	1756-PLS

## Supported controller HONEYWELL Experion PKS C200

Suitable I/O card	TC-IDX 081
	TC-IDA 161
	TC-IAH 061
	TC-IXR 061
	TC-IXL 061
	TC-OAH 061
	TC-OAV 061
	TC-OAV 081

## Supported controller SCHNEIDER ELECTRIC Modicon TSX QUANTUM

Suitable I/O card	DDI 353
	DDI 853
	DAI 453
	DDO 353

## Cable/line

Cable length	1.5 m
--------------	-------

### 14X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	14
Shielded	no
Cable type	14X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	14x 0.14 mm <sup>2</sup>
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	6.4 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	55 mm
Smallest bending radius, movable installation	104 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

## color code

IDC/FLK14 (1)	IDC/FLK14 (1) = black
IDC/FLK14 (2)	IDC/FLK14 (2) = brown
IDC/FLK14 (3)	IDC/FLK14 (3) = red
IDC/FLK14 (4)	IDC/FLK14 (4) = orange
IDC/FLK14 (5)	IDC/FLK14 (5) = yellow
IDC/FLK14 (6)	IDC/FLK14 (6) = green
IDC/FLK14 (7)	IDC/FLK14 (7) = blue
IDC/FLK14 (8)	IDC/FLK14 (8) = violet
IDC/FLK14 (9)	IDC/FLK14 (9) = gray
IDC/FLK14 (10)	IDC/FLK14 (10) = white
IDC/FLK14 (11)	IDC/FLK14 (11) = white-black
IDC/FLK14 (12)	IDC/FLK14 (12) = white-brown
IDC/FLK14 (13)	IDC/FLK14 (13) = white-red
IDC/FLK14 (14)	IDC/FLK14 (14) = white-orange

## Connection data

### Connection 1

Connection in acc. with standard	Based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	14
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

### Connection 2

Connection in acc. with standard	Based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	14
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

## Notes

General

For proper use, the specifications of the installation directive (see Downloads) must be observed.

## Drawings

Diagram



Maximum permissible current per path in uncoiled state

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2288927>



### EAC

Approval ID: RU\*-DE.HB\*35.B00385



### UL Listed

Approval ID: FILE E 238705

	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $\text{mm}^2$
	125 V	1 A	-	-



### cUL Listed

Approval ID: FILE E 238705

	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $\text{mm}^2$
	125 V	1 A	-	-



# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

## Classifications

### ECLASS

ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

### ETIM

ETIM 8.0	EC000237
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# FLK 14/EZ-DR/ 150/KONFEK - Cable



2288927

<https://www.phoenixcontact.com/us/products/2288927>

## Accessories

KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/us/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, lettering field size: 20 x 8 mm

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)