



Part Number : [733910080](#)

Product Description : 50 Ohms, SMA Right-Angle PCB Jack, Nickel (Ni) Plated, 80 Pieces Per Tray

Series Number : 73391

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[Drawing 733910080_sd.pdf](#)

3D Models and Design Files


[3D Model PDF 733910080.pdf](#)

[3D Model 733910080_stp.zip](#)

[HFSS Model SMA_RA_TH_Connector_73391-008x.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73391
Description	50 Ohms, SMA Right-Angle PCB Jack, Nickel (Ni) Plated, 80 Pieces Per Tray
Product Family	SMA RF Connectors
Product Name	SMA
Style	PCB
Type	Subminiature
UPC	756054714959

Electrical

Frequency	18 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	2.952/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
--------------	----

Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260

This document was generated on Sep 02, 2023