



MQS

TE Internal #: 966658-2
PCB Mount Header, Vertical, Wire-to-Board, 32 Position, 2.54 mm [.1 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Signal, Blue

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles > Signal Header



Connector System: **Wire-to-Board**
Number of Positions: **32**
Centerline (Pitch): **2.54 mm [.1 in]**
Sealable: **No**
PCB Mount Orientation: **Vertical**

[All Signal Header \(295\)](#)

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Header Type	Fully Shrouded
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Sections	1
Number of Signal Positions	32
Number of Positions	32
PCB Mount Orientation	Vertical
Number of Rows	2

Electrical Characteristics

Nominal Voltage Architecture	12 V
------------------------------	------

Body Features

Primary Product Color	Blue
-----------------------	------



Connector & Keying Code	C-D
Contact Features	
Contact Size	.63mm
Contact Type	Tab
Mating Tab Width	.63 mm[.024 in]
Mating Tab Thickness	.63 mm[.024 in]
Contact Mating Area Plating Material	Tin
Termination Features	
Termination Method to PCB	Through Hole - Solder
Mechanical Attachment	
Mating Retention	With
Mating Alignment	With
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Mating Retention Type	Locking Interface
Housing Features	
Centerline (Pitch)	2.54 mm[.1 in]
Dimensions	
Connector Length	57.6 mm[2.26 in]
Connector Width	15.6 mm[.614 in]
Profile Height from PCB	20.2 mm[.795 in]
Usage Conditions	
Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C[149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F]
Operating Temperature Range	-30 – 100 °C[-22 – 212 °F]
Operation/Application	
Shielded	No
Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94HB



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1420000-1
32POS MQS REC



TE Part # 1989718-1
COVER ASSY MQS HSG 2X16 POSN.



TE Part # 966661-3
TSP/MOD STVERB2X16P

Customers Also Bought



TE Part #282526-6
20P 070 MLK CAP HEAD ASSY

TE Part #925590-4
MINI SPRING REC.

TE Part #3-967618-2
Signal Header

TE Part #1544113-4
CLIP DRAP. 6,3 G1

TE Part #2329531-3
20POS,TAB0.63X0.63,HDR ASSY,
90DEG,SLDR

TE Part #2349217-1
1 PORT,MATENET,HDR ASSY,COD A,
TOP LATCH

TE Part #2196135-1
C LEAF SPRING

TE Part #2330860-1
HSD-USB CABLE ASSY DACAR535

Documents

Product Drawings

32pos MQS .63 header 180deg

English

CAD Files

Customer View Model

ENG_CVM_CVM_966658-2_G1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_966658-2_G1.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_966658-2_G1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English