



Part Number : [357470410](#)

Product Description : VersaBlade Male Crimp Terminal, 24 AWG, Type B

Series Number : 35747

Status : Active

Product Category : Crimp Terminals



Documents & Resources

Drawings

[Drawing 357470410_sd.pdf](#)

3D Models and Design Files

[3D Model 357470410_stp.zip](#)

Specifications

[Application Specification 351500000AS_ENG-000.pdf](#)

[Packaging Specification PK-35747-001-001.pdf](#)

[Product Specification PS-35150-003-001.pdf](#)

[Product Specification 351800400-001.pdf](#)

[Product Specification 351800600-001.pdf](#)

Tooling Specifications

[Crimp Specification CS-35745-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	35747
Description	VersaBlade Male Crimp Terminal, 24 AWG, Type B
Application	Power, Wire-to-Wire
Product Family	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	822348431038

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.266/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.45mm max.
Wire Size (AWG)	24
Wire Size mm ²	0.29

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500300.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500304.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351500309.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500310.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500314.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351500319.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500400.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500404.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351500409.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500410.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Red	/content/molex/molex-dot-com/us/en/products/product-page.html/351500412.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500414.html

VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351500419.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500600.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500604.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351500609.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351500610.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Red	/content/molex/molex-dot-com/us/en/products/product-page.html/351500612.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351500614.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351500619.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Yellow, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351503309.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Yellow, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351503319.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Yellow, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351503419.html
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351503609.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351503619.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351504319.html

VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351504419.html
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351504619.html
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/351510410.html
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue	/content/molex/molex-dot-com/us/en/products/product-page.html/351510414.html
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351510419.html
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/351514419.html
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/2026500909.html
VersaBlade Multi-Module 2-2 Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/2041020429.html
VersaBlade Multi-Module 4-2 Hybrid Receptacle Housing, 6 Circuits, Natural, Glow-Wire Capable	/content/molex/molex-dot-com/us/en/products/product-page.html/2041020609.html
VersaBlade Multi-Module Hybrid Receptacle Housings	<u>35180</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u>35524</u>

Application Tooling

Global

Description	Part Number
Extraction and Activation Tool	<u>0638132700</u>
Hand Crimp Tool for Industry Standard 1.78mm Tab Terminals, 24-26 AWG Wire	<u>0638196900</u>
FineAdjust Applicator for .070 Male and Female Crimp Terminals, 24 AWG	<u>0639044200</u>

T2 Terminator for .070 Female Crimp Terminal	<u>0639120700</u>
---	-------------------

This document was generated on Dec 11, 2023