### CLL2003

### **SURFACE MOUNT** HIGH VOLTAGE SILICON **SWITCHING DIODE**



www.centralsemi.com

# **DESCRIPTION:**

The CENTRAL SEMICONDUCTOR CLL2003 type is a silicon switching diode manufactured by the epitaxial planar process, designed for applications requiring high voltage capability.

**MARKING: CATHODE BAND** 



MAXIMUM RATINGS: (T <sub>A</sub> =25°C)	SYMBOL		UNITS
Continuous Reverse Voltage	$v_R$	250	V
Peak Repetitive Reverse Voltage	$V_{RRM}$	250	V
Average Forward Current	IO	200	mA
Continuous Forward Current	I <sub>F</sub>	250	mA
Peak Repetitive Forward Current	I <sub>FRM</sub>	625	mA
Peak Forward Surge Current, tp=1.0µs	I <sub>FSM</sub>	4.0	Α
Peak Forward Surge Current, tp=1.0s	I <sub>FSM</sub>	1.0	Α
Power Dissipation	$P_{D}$	500	mW
Operating and Storage Junction Temperature	T <sub>J</sub> , T <sub>stg</sub>	-65 to +200	°C
Thermal Resistance	$\Theta_{\sf JA}$	350	°C/W
ELECTRICAL CHARACTERISTICS: (T <sub>A</sub> =25°C ur	nless otherwise noted)		

# SYMBOL TEST CONDITIONS MIN


SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS
$I_{R}$	V <sub>R</sub> =200V		100	nA
$I_{R}$	V <sub>R</sub> =200V, T <sub>A</sub> =150°C		100	μΑ
$BV_R$	I <sub>R</sub> =100μA	250		V
$V_{F}$	I <sub>F</sub> =100mA		1.00	V
$V_{F}$	I <sub>F</sub> =200mA		1.25	V
$C_T$	$V_R$ =0, f=1.0 MHz		5.0	pF
t <sub>rr</sub>	$I_F = I_R = 30$ mA, Rec. to 3.0mA,			
	$R_L=100\Omega$		50	ns

# **CLL2003**

## SURFACE MOUNT HIGH VOLTAGE SILICON SWITCHING DIODE



# **SOD-80 CASE - MECHANICAL OUTLINE**



**MARKING: CATHODE BAND** 

DIMENSIONS							
	INCHES		MILLIMETERS				
SYMBOL	MIN	MAX	MIN	MAX			
Α	0.130	0.146	3.30	3.71			
В	0.014		0.35				
C (DIA)	0.049	0.067	1.25	1.70			

SOD-80 (REV:R2)

### **OUTSTANDING SUPPORT AND SUPERIOR SERVICES**



#### PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- · Inventory bonding
- · Consolidated shipping options

- · Custom bar coding for shipments
- · Custom product packing

#### **DESIGNER SUPPORT/SERVICES**

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free guick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- · Custom electrical curves
- · Environmental regulation compliance
- · Customer specific screening
- · Up-screening capabilities

- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- · Application and design sample kits
- · Custom product and package development

### REQUESTING PRODUCT PLATING

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- 2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

#### **CONTACT US**

#### Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA

Main Tel: (631) 435-1110 Main Fax: (631) 435-1824

Support Team Fax: (631) 435-3388

www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

**Worldwide Distributors:** 

www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: <a href="https://www.centralsemi.com/terms">www.centralsemi.com/terms</a>

www.centralsemi.com (001)