# xckt2145p16

limit switch XCKT - th.plastic roller lever var.length - 1NC+1NO - snap - M16





#### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch
Device short name	XCKT
Sensor design	Compact
Body type	Fixed
Head type	Rotary head
Material	Plastic
Body material	Plastic
Head material	Zamak
Fixing mode	By the body
Movement of operating head	Rotary
Type of operator	Spring return roller lever thermoplastic (variable length)
Type of approach	Lateral approach 2 directions
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contacts operation	Snap action

#### **Complementary**

By 30° cam
Screw-clamp terminals, clamping capacity: 1 x 0.342 x 1.5 mm <sup>2</sup>
2 entries tapped for M16 x 1.5 cable gland, cable outer diameter: 48 mm
Zb
With
0.25 N.m
0.1 N.m
1.5 m/s
0.1 mm on the tripping points with 1 million operating cycles
Q300, DC-13 (Ue = 250 V, Ie = 0.27 A) conforming to EN/IEC 60947-5-1 appendix A A300, AC-15 (Ue = 240 V, Ie = 3 A) , Ithe = 10 A conforming to EN/IEC 60947-5-1 appendix A
500 V degree of pollution 3 conforming to IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14
<= 25 MOhm conforming to IEC 60255-7 category 3
6 kV conforming to IEC 60664 6 kV conforming to IEC 60947-1
10 A by gG cartridge fuse
5000000 cycles, DC-13, 120 V, 4 W, operating rate: <= 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13, 24 V, 10 W, operating rate: <= 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13, 48 V, 7 W, operating rate: <= 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C
10000000 cycles
58 mm
51 mm
30 mm

Product weight	0.155 kg	
Terminals description ISO n°1	(13-14)NO (21-22)NC	

### **Environment**

Shock resistance	50 gn (duration = 11 ms) conforming to IEC 60068-2-27	
Vibration resistance	25 gn (f = 10500 Hz) conforming to IEC 60068-2-6	
IP degree of protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529	
IK degree of protection	IK04 conforming to EN 50102	
Class of protection against electric shock	Class II conforming to IEC 61140 Class II conforming to NF C 20-030	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4070 °C	
Protective treatment	TC	
Product certifications	CCC CSA UL	
Standards	EN/IEC 60204-1 EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14	

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 1002 - Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available

