

Aluminum Electrolytic Capacitors

Surface Mount Type

S series

High temperature Lead-Free reflow (suffix : A*)



Features


- Endurance : 85 ℃ 2000 h
- Vibration-proof product (30G guaranteed) is available upon request. (Ø8 ≦)
- AEC-Q200 compliant
- RoHS compliant

Specifications											
Category temp. range	-40 ℃ to +85 ℃										
Rated voltage range	6.3 V to 50 V										
Capacitance range					1 μF t	o 15	00 μF	=			
Capacitance tolerance								20 ℃)			
Leakage current	I ≤ 0.01							(Whichever is great	er)		
Dissipation factor (tan δ)		Plea	ase se	ee th	e atta	ched	l char	acteristics list			
Characteristics	Rated voltage (V)	6.3	10	16	25	35	50				
	Z (-25 °C) / Z (+20 °C)	4	3	2	2	2	2	(Impedance	e ratio at 120 Hz)		
at low temperature	Z (-40 °C) / Z (+20 °C)	8	6	4	4	3	3				
	After applying rated working										
	at $+85~\%~\pm~2~\%$ and then being stabilized at $+20~\%$, capacitors shall meet the following limits.										
	Within ±20 % of the initial value										
Endurance	Capacitance change	Size code Cap			Ca	pacitance change					
Lituarance	Capacitance change	D8 (ø6.3)				2000 hours ±25 %					
		≦ D (ø6.3) Miniature				ıre	10	1000 hours ±30 %			
	Dissipation factor (tan δ)	≤ 2	00 %	of th	ne init	ial lir	nit				
	Leakage current	_		_	ial lin						
	After storage for 1000 h at								eing		
Shelf life	stabilized at +20 ℃, capa	citors	shall	mee	et the	limit	s spe	cified in endurance.			
	(With voltage treatment)										
	After reflow soldering and	then	being	g stal	oilized	l at +	-20 °C	C, capacitors shall m	eet the		
Resistance to	following limits.										
	Capacitance change	With	nin ±	10 %	of th	e init	tial va	alue			
soldering heat	Dissipation factor (tan δ)	With	ոin th	e init	ial lin	nit					
	Leakage current Within the initial limit										


Frequency correction factor for ripple current

Trequency correction factor for rippic current										
Frequency (Hz)	50, 60	120	1 k	10 k to						
Correction factor	0.70	1.00	1 30	1 70						

Marking



Dimensions




< Size code : E, F, G, H13, J16, K16, K21 >

Dimensions (Vibration-proof products)


* The size and shape are different from standard products. Please inquire details of our company.

< Size code : D, D8 >



Supportive Terminals () Reference size

*1 : E to G : L±0.3 H13 to K21 : L±0.5



Supportive Terminals () Reference size


Unit : mm

Size code	øD	L	А, В	H max.	F	I	W	Р	K	R	S	Т
D	6.3	6.1	6.6	7.8	0 to +0.15	2.4	0.65±0.1	2.2	$0.35 \begin{array}{c} +0.15 \\ -0.20 \end{array}$	1.1±0.2	3.3	1.05±0.2
D8	6.3	8.0	6.6	7.8	0 to +0.15	2.4	0.65±0.1	2.2	$0.35 \begin{array}{c} +0.15 \\ -0.20 \end{array}$	1.1±0.2	3.3	1.05±0.2
Е	8.0	6.5	8.3	9.5	0 to +0.15	3.4	0.7±0.1	2.2	$0.35 \begin{array}{c} +0.15 \\ -0.20 \end{array}$	0.70±0.2	5.3	1.7±0.2
F	8.0	10.5	8.3	10.0	0 to +0.15	3.4	1.2±0.2	3.1	0.70±0.2	0.70±0.2	5.3	1.3±0.2
G	10.0	10.5	10.3	12.0	0 to +0.15	3.5	1.2±0.2	4.6	0.70±0.2	0.70±0.2	6.9	1.3±0.2
H13	12.5	13.8	13.5	15.0	-0.1 to +0.15	4.7	1.2±0.2	4.4	0.70±0.3	2.2±0.2	7.1	2.4±0.2
J16	16.0	16.8	17.0	19.0	-0.1 to $+0.15$	5.5	1.4±0.2	6.7	0.70±0.3	3.0 ± 0.2	9.0	1.9±0.2
K16	18.0	16.8	19.0	21.0	-0.1 to +0.15	6.7	1.4±0.2	6.7	0.70±0.3	3.0±0.2	11.0	1.9±0.2
K21	18.0	21.8	19.0	21.0	-0.1 to +0.15	6.7	1.4±0.2	6.7	0.70±0.3	3.0±0.2	11.0	1.9±0.2

Land / Pad pattern

The circuit board land/pad pattern size for chip capacitors is specified in the following table. The land pitch influences installation strength and consider it.

Standard products





Land space




Vibration-proof products


< Size code : D, D8 >





< Size code : E, F, G, H, J, K >





(Table of board land size vs. capacitor size)

(Table of board faild	Unit : mm		
Size code	а	b	С
B (ø4)	1.0	2.5	1.6
C (ø5)	1.5	2.8	1.6
D (ø6.3)	1.8	3.2	1.6
D8 (ø6.3x7.7L)	1.8	3.2	1.6
E (ø8x6.2L)	2.2	4.0	1.6
F (ø8x10.2L)	3.1	4.0	2.0
G (ø10x10.2L)	4.6	4.1	2.0
H (ø12.5)	4.0	5.7	2.0
J (ø16)	6.0	6.5	2.5
K (ø18)	6.0	7.5	2.5

When size "a" is wide, back fi llet can be made, decreasing fi tting strength.

(Table of board land size vs. capacitor size)

Size code	Α	В	С	D	Е	F	G	Н
D (ø6.3xL6.1)	1.2	3.6	3.2	2.0	0.95	0.65	1.0	1.2
D8 (ø6.3xL8.0)	1.2	3.6	3.2	2.0	0.95	0.65	1.0	1.2
E (ø8x6.5L)	1.8	4.2	5.0	1.3	1.5	1.4	1.5	2.0
F (ø8x10.5L)	2.7	4.0	4.7	1.3	1.0	1.7	1.1	2.5
- / >								

	E (Ø8X6.5L)	1.8	4.2	5.0	1.3	1.5	1.4	1.5	2.0
	F (ø8x10.5L)	2.7	4.0	4.7	1.3	1.0	1.7	1.1	2.5
Ī	G (ø10)	3.9	4.4	4.7	1.3	1.2	1.9	1.1	2.5
Ī	H (ø12.5)	3.9	6.0	6.9	2.8	1.3	1.9	2.2	2.5
Ī	J (ø16)	5.8	6.8	6.2	3.6	1.3	1.9	1.7	2.8
	K (ø18)	5.8	7.3	6.2	3.6	1.8	1.9	1.7	2.8

When size "A" is wide, back fi llet can be made, decreasing fi tting strength.

- *Take mounting conditions, solderability and fi tting strength into consideration when selecting parts for your company's design.
- * The vibration-proof capacitors of size ø6.3 has support terminals extending from the bottom side to the lead edge. Then, make sure to find appropriate soldering conditions to form fillet on the support terminals if required for appearance inspection.

Unit: mm

Aluminum Electrolytic Capacitors (SMD Type)

S series (High temp. reflow)

Characteristics list

		iotico								
Case size					Chacification			Min.		
		(mm)				Specification				Packaging
Rated	Capacitance		,	Size						Q'ty (pcs)
voltage	(±20 %)			code*1	Ripple		Endurance	Part No.	Reflow	
(V)	(µF)	øD	L	5545	current*2	tanδ ^{*3}	(hours)			Taping
					(mA rms)		(Hours)			raping
	22	4.0	5.4	В	29	0.30	2000	EEE0JA220AR	(5)	2000
	33	4.0	5.4	(B)	22	0.35	1000	EEE0JA330WAR	(5)	2000
	47	5.0	5.4	(b)	46	0.30	2000	EEE0JA330WAR EEE0JA470AR	(5)	1000
	47	5.0	5.4	(C)	47	0.40	1000	EEE0JA101WAR	(5)	1000
	100	6.3	5.4	(C)	71	0.40	2000	EEE0JA101WAR EEE0JA101AP	(5)	1000
6.3		6.3	7.7	D8	188	0.30	2000		(5)	900
	330	8.0	6.2	E	300	0.35	2000	EEE0JA331XAP		1000
	470	8.0	10.2		380			EEE0JA331AP	(7)	500
				(F)		0.35	1000	EEE0JA471UAP	(7)	
	1000	10.0	10.2	G (C)	700	0.35	2000	EEE0JA102AP	(7)	500
	1500	10.0	10.2	(G)	750	0.50	1000	EEE0JA152UAP	(7)	500
	22	4.0	5.4	(B)	28	0.30	1000	EEE1AA220WAR	(5)	2000
	33	4.0	5.4	(B)	29	0.30	1000	EEE1AA330WAR	(5)	2000
		5.0	5.4	C	43	0.22	2000	EEE1AA330AR	(5)	1000
	47	5.0	5.4	(C)	47	0.30	1000	EEE1AA470WAR	(5)	1000
	100	5.0	5.4	(C)	50	0.30	1000	EEE1AA101WAR	(5)	1000
10		6.3	5.4	D	70	0.26	2000	EEE1AA101AP	(5)	1000
10	220	6.3	7.7	D8	173	0.22	2000	EEE1AA221XAP	(5)	900
		8.0	6.2	Е	250	0.26	2000	EEE1AA221AP	(7)	1000
	330	8.0	10.2	F	390	0.26	2000	EEE1AA331AP	(7)	500
	470	8.0	10.2	(F)	390	0.26	1000	EEE1AA471UAP	(7)	500
		10.0	10.2	G	400	0.26	2000	EEE1AA471AP	(7)	500
	1000	10.0	10.2	(G)	580	0.35	1000	EEE1AA102UAP	(7)	500
	10	4.0	5.4	В	28	0.16	2000	EEE1CA100AR	(5)	2000
	22	4.0	5.4	(B)	28	0.26	1000	EEE1CA220WAR	(5)	2000
	22	5.0	5.4	С	39	0.16	2000	EEE1CA220AR	(5)	1000
	33	5.0	5.4	(C)	35	0.26	1000	EEE1CA330WAR	(5)	1000
	47	5.0	5.4	(C)	39	0.26	1000	EEE1CA470WAR	(5)	1000
	47	6.3	5.4	D	70	0.16	2000	EEE1CA470AP	(5)	1000
16	100	6.3	5.4	(D)	70	0.26	1000	EEE1CA101WAP	(5)	1000
10	100	8.0	6.2	Е	200	0.20	2000	EEE1CA101AP	(7)	1000
	220	6.3	7.7	D8	162	0.20	2000	EEE1CA221XAP	(5)	900
	220	8.0	10.2	(F)	280	0.20	1000	EEE1CA221UAP	(7)	500
	330	8.0	10.2	(F)	320	0.20	1000	EEE1CA331UAP	(7)	500
	330	10.0	10.2	G	380	0.20	2000	EEE1CA331AP	(7)	500
	470	8.0	10.2	(F)	350	0.26	1000	EEE1CA471UAP	(7)	500
	4/0	10.0	10.2	G	420	0.20	2000	EEE1CA471AP	(7)	500
	4.7	4.0	5.4	В	22	0.14	2000	EEE1EA4R7AR	(5)	2000
	10	4.0	5.4	(B)	22	0.20	1000	EEE1EA100WAR	(5)	2000
	10	5.0	5.4	C	28	0.14	2000	EEE1EA100AR	(5)	1000
	22	5.0	5.4	(C)	35	0.20	1000	EEE1EA220WAR	(5)	1000
	22	6.3	5.4	Ď	55	0.14	2000	EEE1EA220AP	(5)	1000
	22	5.0	5.4	(C)	42	0.20	1000	EEE1EA330WAR	(5)	1000
	33	6.3	5.4	Ď	65	0.14	2000	EEE1EA330AP	(5)	1000
25	47	6.3	5.4	(D)	70	0.20	1000	EEE1EA470WAP	(5)	1000
25		8.0	6.2	(E)	91	0.16	1000	EEE1EA101UAP	(7)	1000
	100	6.3	7.7	D8	143	0.16	2000	EEE1EA101XAP	(5)	900
		8.0	10.2	F	180	0.16	2000	EEE1EA101AP	(7)	500
	222	8.0	10.2	(F)	230	0.20	1000	EEE1EA221UAP	(7)	500
	220	10.0	10.2	G	310	0.16	2000	EEE1EA221AP	(7)	500
	222	8.0	10.2	(F)	270	0.20	1000	EEE1EA331UAP	(7)	500
	330	10.0	10.2	G	340	0.16	2000	EEE1EA331AP	(7)	500
	470	10.0	10.2	(G)	380	0.25	1000	EEE1EA471UAP	(7)	500
	0			(5)	230	0.20			(')	

^{*1:} Size code(): Miniaturization product

^{*2:} Ripple current (120 Hz / +85 ℃)

^{*3:} tanδ (120 Hz / +20 °C)

[•] Please refer to the page of "Refl ow Profi le" and "The Taping Dimensions".

 $[\]cdot$ When requesting vibration-proof product, please put the last "V" instead to "P"

Aluminum Electrolytic Capacitors (SMD Type)

S series (High temp. reflow)

Characteristics list

Rated	Capacitance	Case size Specification					Min. Packaging			
voltage (V)	(±20 %) (μF)	øD	L	Size code ^{*1}	Ripple current ^{*2} (mA rms)	tanδ ^{*3}	Endurance (hours)	Part No.	Reflow	Q'ty (pcs) Taping
	4.7	4.0	5.4	В	22	0.12	2000	EEE1VA4R7AR	(5)	2000
	10	4.0	5.4	(B)	22	0.16	1000	EEE1VA100WAR	(5)	2000
	10	5.0	5.4	С	30	0.12	2000	EEE1VA100AR	(5)	1000
	22	5.0	5.4	(C)	36	0.16	1000	EEE1VA220WAR	(5)	1000
	22	6.3	5.4	D	60	0.12	2000	EEE1VA220AP	(5)	1000
	33	6.3	5.4	(D)	60	0.16	1000	EEE1VA330WAP	(5)	1000
	33	8.0	6.2	Е	130	0.14	2000	EEE1VA330AP	(7)	1000
35	47	6.3	5.4	(D)	70	0.16	1000	EEE1VA470WAP	(5)	1000
	77	8.0	6.2	Е	165	0.14	2000	EEE1VA470AP	(7)	1000
		6.3	7.7	D8	132	0.14	2000	EEE1VA101XAP	(5)	900
	100	8.0	10.2	(F)	140	0.14	1000	EEE1VA101UAP	(7)	500
		10.0	10.2	G	210	0.14	2000	EEE1VA101AP	(7)	500
	220	8.0	10.2	(F)	200	0.14	1000	EEE1VA221UAP	(7)	500
		10.0	10.2	G	310	0.14	2000	EEE1VA221AP	(7)	500
	330	10.0	10.2	(G)	350	0.30	1000	EEE1VA331UAP	(7)	500
	1	4.0	5.4	В	10	0.12	2000	EEE1HA1R0AR	(5)	2000
	2.2	4.0	5.4	В	16	0.12	2000	EEE1HA2R2AR	(5)	2000
	3.3	4.0	5.4	В	16	0.12	2000	EEE1HA3R3AR	(5)	2000
	4.7	4.0	5.4	(B)	18	0.14	1000	EEE1HA4R7WAR	(5)	2000
	7.7	5.0	5.4	С	23	0.12	2000	EEE1HA4R7AR	(5)	1000
	10	5.0	5.4	(C)	27	0.14	1000	EEE1HA100WAR	(5)	1000
	10	6.3	5.4	D	35	0.12	2000	EEE1HA100AP	(5)	1000
	22	6.3	5.4	(D)	40	0.14	1000	EEE1HA220WAP	(5)	1000
50	22	8.0	6.2	Е	120	0.12	2000	EEE1HA220AP	(7)	1000
30		8.0	6.2	(E)	65	0.12	1000	EEE1HA330UAP	(7)	1000
	33	6.3	7.7	D8	65	0.14	2000	EEE1HA330XAP	(5)	900
		8.0	10.2	F	110	0.12	2000	EEE1HA330AP	(7)	500
		6.3	7.7	D8	105	0.14	2000	EEE1HA470XAP	(5)	900
	47	8.0	10.2	(F)	110	0.12	1000	EEE1HA470UAP	(7)	500
		10.0	10.2	G	130	0.12	2000	EEE1HA470AP	(7)	500
	100	8.0	10.2	(F)	200	0.18	1000	EEE1HA101UAP	(7)	500
	100	10.0	10.2	G	250	0.12	2000	EEE1HA101AP	(7)	500
	220	10.0	10.2	(G)	300	0.18	1000	EEE1HA221UAP	(7)	500

^{*1:} Size code() : Miniaturization product

^{*2:} Ripple current (120 Hz / +85 °C)

^{*3:} tanδ (120 Hz / +20 °C)

[•] Please refer to the page of "Refl ow Profi le" and "The Taping Dimensions".

[•] When requesting vibration-proof product, please put the last "V" instead to "P"

Guidelines and precautions regarding the technical information and use of our products described in this online catalog.

- If you want to use our products described in this online catalog for applications requiring special qualities or reliability, or for applications where the failure or malfunction of the products may directly jeopardize human life or potentially cause personal injury (e.g. aircraft and aerospace equipment, traffic and transportation equipment, combustion equipment, medical equipment, accident prevention, anti-crime equipment, and/or safety equipment), it is necessary to verify whether the specifications of our products fit to such applications. Please ensure that you will ask and check with our inquiry desk as to whether the specifications of our products fit to such applications use before you use our products.
- The quality and performance of our products as described in this online catalog only apply to our products when used in isolation. Therefore, please ensure you evaluate and verify our products under the specific circumstances in which our products are assembled in your own products and in which our products will actually be used.
- If you use our products in equipment that requires a high degree of reliability, regardless of the application, it is recommended that you set up protection circuits and redundancy circuits in order to ensure safety of your equipment.
- The products and product specifications described in this online catalog are subject to change for improvement without prior notice. Therefore, please be sure to request and confirm the latest product specifications which explain the specifications of our products in detail, before you finalize the design of your applications, purchase, or use our products.
- The technical information in this online catalog provides examples of our products' typical operations and application circuits. We do not guarantee the non-infringement of third party's intellectual property rights and we do not grant any license, right, or interest in our intellectual property.
- If any of our products, product specifications and/or technical information in this online catalog is to be exported or provided to non-residents, the laws and regulations of the exporting country, especially with regard to security and export control, shall be observed.

< Regarding the Certificate of Compliance with the EU RoHS Directive/REACH Regulations>

- The switchover date for compliance with the RoHS Directive/REACH Regulations varies depending on the part number or series of our products.
- When you use the inventory of our products for which it is unclear whether those products are compliant with the RoHS Directive/REACH Regulation, please select "Sales Inquiry" in the website inquiry form and contact us.

We do not take any responsibility for the use of our products outside the scope of the specifications, descriptions, guidelines and precautions described in this online catalog.



Notices

■ Applicable laws and regulations

- •This product complies with the RoHS Directive (Restriction of the use of certain hazardous substances in electrical and electronic equipment (DIRECTIVE 2011/65/EU and (EU)2015/863)).
- No Ozone Depleting Chemicals(ODC's), controlled under the Montreal Protocol Agreement, are used in producing this product.
- We do not use PBBs or PBDEs as brominated flame retardants.
- Export procedure which followed export related regulations, such as foreign exchange and a foreign trade method, on the occasion of export of this product.
- These products are not dangerous goods on the transportation as identified by UN(United Nations) numbers or UN classification.

■ Limited applications

- This capacitor is designed to be used for electronics circuits such as audio/visual equipment, home appliances, computers and other office equipment, optical equipment, measuring equipment.
- An advanced specification must be signed individually for high-reliability use that might threaten human life or property due to a malfunction of the capacitor.

■ Intellectual property rights and licenses

• The technical information in this specification provides examples of our products' typical operations and application circuits. We do not guarantee the non-infringement of third party's intellectual property rights and we do not grant any license, right, or interest in our intellectual property.

Items to be observed

■ For specification

- This specification guarantees the quality and performance of the product as individual components. The durability differs depending on the environment and the conditions of usage. Before use, check and evaluate their compatibility with actual conditions when installed in the products. When safety requirements cannot be satisfied in your technical examination, inform us immediately.
- Do not use the products beyond the specifications described in this document.

Upon application to products where safety is regarded as important

Install the following systems for a failsafe design to ensure safety if these products are to be used in equipment where a defect in these products may cause the loss of human life or other signification damage, such as damage to vehicles (automobile, train, vessel), traffic lights, medical equipment, aerospace equipment, electric heating appliances, combustion/ gas equipment, rotating rotating equipment, and disaster/crime prevention equipment.

- (1) The system is equipped with a protection circuit and protection device.
- (2) The system is equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault.

■ Conditions of use

- Before using the products, carefully check the effects on their quality and performance, and determined whether or not they can be used. These products are designed and manufactured for general-purpose and standard use in general electronic equipment. These products are not intended for use in the following special conditions.
 - (1) In liquid, such as Water, Oil, Chemicals, or Organic solvent.
 - (2) In direct sunlight, outdoors, or in dust.
 - (3) In vapor, such as dew condensation water of resistive element, or water leakage, salty air, or air with a high concentration corrosive gas, such as Cl₂, H₂S, NH₃, SO₂, or NOx.
 - (4) In an environment where strong static electricity or electromagnetic waves exist.
 - (5) Mounting or placing heat-generating components or inflammables, such as vinyl-coated wires, near these products.
 - (6) Sealing or coating of these products or a printed circuit board on which these products are mounted, with resin and other material.
 - (7) Using resolvent, water or water-soluble cleaner for flux cleaning agent after soldering. (In particular, when using water or a water-soluble cleaning agent, be careful not to leave water residues)
 - (8) Using in the atmosphere where strays acid or alkaline.
 - (9) Using in the atmosphere where there are excessive vibration and shock.
 - (10) Using in the atmosphere where there are low pressure or decompression.
- Please arrange circuit design for preventing impulse or transitional voltage.
 Do not apply voltage, which exceeds the full rated voltage when the capacitors receive impulse voltage, instantaneous high voltage, high pulse voltage etc.
- Our products there is a product are using an electrolyte solution. Therefore, misuse can result in rapid deterioration of characteristics and functions of each product. Electrolyte leakage damages printed circuit and affects performance, characteristics, and functions of customer system.



Application guidelines (SMD Type)

1. Circuit design

1.1 Operating temperature and frequency

Electrical characteristics of the capacitor are likely to change due to variation in temperature and/or frequency. Circuit designers should take these changes into consideration.

(1) Effects of operating temperature on electrical parameters

At higher temperatures : leakage current and capacitance increase while equivalent series resistance

(ESR) decreases.

At lower temperatures : leakage current and capacitance decrease while equivalent series resistance

(ESR) increases.

(2) Effects of frequency on electrical parameters

At lower frequencies : heat generated by ripple current will rise due to an increase in equivalent

series resistance (ESR).

1.2 Operating temperature and life expectancy

(1) Expected life is affected by operating temperature. Generally, each 10 °C reduction in temperature will double the expected life. Use capacitors at the lowest possible temperature below the upper category temperature.

(2) If operating temperatures exceed the upper category limit, rapid deterioration of electrical parameter will occur and irreversible damage will result.

Measure not only the ambient temperature but also the surface temperature of the capacitor's case top, which has effects of ripple current and radiated heat from power transistors, IC's, and/or resistors.

Avoid placing components, which could conduct heat to the capacitor from the back side of the circuit board.

(3) The formula for calculating expected life is as follows;

$$L2 = L1 \times 2^{\frac{|11-|2|}{10}} \qquad \text{where } T1 \ge T2$$

L₁ : Guaranteed life (h) at temperature, T₁ ℃

L₂ : Expected life (h) at temperature, T₂ °C

 T_1 : Upper category temperature ($^{\circ}$ C)

 T_2 : Actual operating temperature, ambient temperature + temperature rise due to ripple current ($^{\circ}$ C)

(4) Using the capacitor beyond the rated lifetime will result in short circuit, electrolyte leak, vent open, and large deterioration of characteristics. The lifetime cannot exceed 15 years due to aging of sealing rubber.

1.3 Load conditions to avoid

The following load conditions will cause rapid deterioration of capacitor's electrical characteristics.

In addition, instantaneous heating and gas generation within the capacitor may cause an operation of pressure relief vent, and that results in electrolyte leaks, explosion and/or fire ignition.

The leaked electrolyte is combustible and electrically conductive.

(1) Reverse voltage

DC capacitors have polarity. Therefore, do not apply the reverse voltage. Find the correct polarity before insertion.

(2) Charge / Discharge applications

General purpose capacitors are not suitable for use in repeating charge/discharge applications.

For such applications, consult a sales representative with actual application condition. Rush current must not exceed 100 A.

(3) ON-OFF circuit

When using capacitors in circuit where ON-OFF switching is repeated more than 10,000 times a day, consult a sales representative with actual application condition for an appropriate choice of capacitors.

(4) Over voltage

Do not apply a voltage exceeding the rated voltage. The rated surge voltage can be applied only for a short time. Make sure that a sum of the DC voltage and the superimposed AC ripple voltage does not exceed the rated voltage.



(5) Ripple current

Do not apply ripple currents exceeding the rated value.

Make sure that rated ripple currents superimposed on low DC bias voltages do not cause reverse voltage conditions. Even if the current is below the rated ripple current, using the capacitor for longer than the rated lifetime will cause ESR increase and internal generation of heat, which may eventually lead to vent open, bulging of case/rubber, electrolyte leak, short circuit, explosion, or ignition in the worst case.

1.4 Connections in series or parallel

(1) Capacitors connected in parallel

Because the impedance of the capacitor and PCB's wiring are very close, various impedance values may cause unbalanced ripple current loads among parallel capacitors. Combine the same part number and wire them carefully to minimize the potential risk of an excessive ripple current concentrating to one capacitor of the smallest impedance.

(2) Capacitors connected in series

Voltage being applied to each capacitor must be smaller than the rated voltage. Unbalanced voltages to the series capacitors may exceed the rated voltage. Voltage-divider resistors considering leakage currents could prevent the over-voltage to the series capacitors. Conductive polymer hybrid aluminum electrolytic capacitors are not allowed to be connected in series.

1.5 Capacitor mounting considerations

- (1) For double sided circuit boards, avoid wiring patterns passing between the mounted capacitor and the circuit board. When a radial lead type capacitor is dipped into a solder bath, an excess solder may deposit under the capacitor by capillary action, causing short circuit between anode and cathode terminals. Also, lead holes must be placed with special care for radial lead type capacitors because laminate on capacitor's surface may become damaged during flow process.
- (2) The pitch between circuit board holes should match the lead wire pitch of the radial lead type capacitors within the specified tolerances. Unmatched pitch may cause an excessive stress on lead wires during the insertion process and result in short/open circuit, increased leakage current, or electrolyte leak.
- (3) Clearance for case mounted pressure relief
 - Capacitors with case mounted pressure relief require sufficient clearance to allow for proper pressure relief operation. The minimum clearance are dependent on capacitor diameters as follows.
 - (Ø 10 mm to Ø 16 mm: 2 mm minimum, Ø 18 mm: 3 mm minimum)
- (4) Wiring near the pressure relief
 - Avoid locating high voltage or high current wiring or circuit board paths above the pressure relief. Flammable, high temperature gas that exceeds 100 °C may be released which could dissolve the wire insulation and ignite.
- (5) Circuit board patterns under the capacitor
 - Avoid circuit board runs under the capacitor, as an electrical short can occur due to an electrolyte leakage.
- (6) Resonant vibration after circuit board's production may make a heavy load on the capacitor and cause rapid change in characteristics and/or capacitor's break.

1.6 Electrical isolation

Electrically isolate the capacitor's case from cathode terminals, as well as circuit patterns.

1.7 Capacitor coating

The laminate coating is intended for marking and identification purposes and is not meant to electrically insulate the capacitor.

2. Capacitor handling techniques

2.1 Considerations before using

- (1) Capacitors have a finite life. Do not reuse or recycle capacitors from used equipment.
- (2) Transient recovery voltage may be generated in the capacitor due to dielectric absorption. If required, this voltage can be discharged with a resistor with a value of about $1 \text{ k}\Omega$.
- (3) Capacitors stored for a long period of time may exhibit an increase in leakage current. This can be corrected by gradually applying rated voltage in series with a resistor of approximately $1 \text{ k}\Omega$.
- (4) If capacitors are dropped, they can be damaged mechanically or electrically. Avoid using dropped capacitors.
- (5) Dented or crushed capacitors should not be used.

The seal integrity can be damaged and loss of electrolyte/ shortened life can result.



2.2 Capacitor insertion

- (1) Verify the correct capacitance and rated voltage of the capacitor.
- (2) Verify the correct polarity of the capacitor before insertion.
- (3) Verify the correct terminal dimension and land pattern size for surface mount type, or holes' pitch for radial lead type before mount to avoid short circuit, stress on the terminals, and/or lack of terminal strength.
- (4) Excessive mounting pressure can cause high leakage current, short circuit, or disconnection.
- (5) When using a mounter for radial lead type, avoid cutter wear and acute angle of lead-bending with respect to circuit board. That may create excessive stress and pull the lead to damage the capacitor.

2.3 Reflow soldering (for surface mount type)

- (1) Surface-mount type capacitor are exclusively for reflow soldering.
 - When reflow solder is used an ambient heat condition system such as the simultaneous use of infrared and hot-air is recommended.
- (2) Observe proper soldering conditions (temperature, time, etc.). Do not exceed the specified limits. If the peak temperature is high or if the heating time is long, it may cause deterioration of the electrical characteristics and life characteristics.
 - Recommended soldering condition is a guideline for ensuring the basic characteristics of the components, but not for the stable soldering conditions. Conditions for proper soldering should be set up according to individual onditions.
 - The Temperature on Capacitor top shall be measured by using thermal couple that is fixed firmly by epoxy glue.
- (3) In case of use in 2 times reflow, 2nd reflow must be done when the capacitor's temperature return back to normal level.
- (4) In our recommended reflow condition , the case discoloration and the case swelling might be slightly generated. But please acknowledge that these two phenomena do not influence the reliability of the product.
- (5) The crack on top marking might be occurred by reflow heat stress.

 But please acknowledge that it does not influence the reliability of the product.
- (6) VPS (Vapor Phase Soldering) reflow can cause significant characteristics change and/ or mounting failure due to deformation by acute temperature rise.
 - VPS is acceptable provided that the process does not exceed recommended reflow profile and temperature rise is less than 3 $^{\circ}$ C/sec.
 - Please contact Panasonic for detailed conditions.
- (7) The vibration-proof capacitors of size ø6.3 has support terminals extending from the bottom side to the lead edge. Then, make sure to find appropriate soldering conditions to form fillet on the support terminals if required for appearance inspection. However, even if sufficient solder fillets are not observed, the reliability of vibration-proof will not be lowered because the support terminals on the bottom side enhance the solder joint to PCB.

2.4 Flow soldering (for radial lead type)

- (1) Radial lead type capacitors cannot apply to reflow soldering.
- (2) Do not immerse the capacitor body into the solder bath as excessive internal pressure could result.
- (3) Apply proper soldering conditions (temperature, time, etc.). Do not exceed the specified limits.
- (4) Do not allow other parts or components to touch the capacitor during soldering.

2.5 Manual soldering

- (1) Apply soldering conditions (temperature and time) based on the specification, or do not exceed temperature of 350 ℃ for 3 seconds.
- (2) If a soldered capacitor must be removed and reinserted, avoid excessive stress on the capacitor leads.
- (3) Avoid physical contacts between the tip of the soldering iron and capacitors to prevent or capacitor failure.
- (4) When bending lead wires of radial type capacitors to match the hole pitch on PCB, avoid applying excessive stress to the capacitor body.

2.6 Capacitor handling after soldering

- (1) Avoid moving the capacitor after soldering to prevent excessive stress on the lead wires where they enter the seal. The capacitor may break from element portion due to a torque at outer rim, causing a large stress to terminals.
- (2) Do not use the capacitor as a handle when moving the circuit board assembly. The total weight of the board would apply to element portion through terminals, and the capacitor may break.
- (3) Avoid striking the capacitor after assembly to prevent failure due to excessive shock. The capacitor may break due to excessive shock or load above specified range.



2.7 Circuit board cleaning

(1) Circuit boards can be immersed or ultrasonically cleaned using suitable cleaning solvents for up to 5 minutes and up to 60 °C maximum temperatures. The boards should be thoroughly rinsed and dried. The use of ozone depleting cleaning agents is not recommended for the purpose of protecting our environment.

[Target solvent]

Pine Alpha ST-100S, Aqua Cleaner 210SEP, Clean-thru 750H / 750L / 710M, Sunelec B-12, Sunelec B-12, Cold Cleaner P3-375, Techno Cleaner 219, DK Be-clear CW-5790, Telpene Cleaner EC-7R, Technocare FRW-17 / FRW-1 / FRV-1

- (2) Avoid using the following solvent groups unless specifically allowed in the specification;
 - (a) Halogenated based solvents: may permeate the seal and cause internal corrosion. Especially, 1-1-1 trichloroethane must not be used on any aluminum electrolytic capacitors.

(b) Alkaline based solvents : may dissolve and react to the aluminum case.

(c) Petroleum based solvents : may deteriorate the sealing rubber.(d) Xylene : may deteriorate the sealing rubber.

(e) Acetone : may erase the markings on the capacitor top.

- (3) A thorough drying after cleaning is required to remove residual cleaning solvents that may be trapped between the capacitor and the circuit board. Avoid drying temperatures, which exceed the upper category temperature of the capacitor.
- (4) Monitor the contamination levels of the cleaning solvents during use in terms of electrical conductivity, pH, specific gravity, and water content. Inside the capacitor may corrode with high density of chlorine. Control the flux density in the cleaning agent to be less than 2 mass%.
- (5) Depending on the cleaning method, the marking on a capacitor may be erased or blurred.
- ** Please consult us if you are not certain about acceptable cleaning solvents or cleaning methods.

2.8 Mounting adhesives and coating agents

When using mounting adhesives or coating agents to control humidity, avoid using materials containing halogenated solvents. Also, avoid the use of chloroprene based polymers.

Cure or dry out the coating agents thoroughly, and do not leave any solvents. Make sure to dry out cleaning agents completely immediately after washing the circuit board if the capacitors are mounted afterward, so that the solvents are not left under the capacitor body. Also, leave more than 1/3 of the sealing portion open, and do not cover that portion with any adhesives or coating.

2.9 Potting and molding

Potting and molding processes cannot be recommended. They have potential risks to change the capacitor's performance and reliability due to injection pressure, diffused material into the capacitor, as well as heat accumulation by covered resin. Also, evaporated electrolyte may remain inside the resin, then turn to liquid, and possibly short circuit PCB patterns.

2.10 Fumigation

In exporting electronic appliances with aluminum electrolytic capacitors, in some cases fumigation treatment using such halogen compound as methyl bromide is conducted for wooden boxes.

If such boxes are not dried well, the halogen left in the box is dispersed while transported and enters in the capacitors inside. This possibly causes electrical corrosion of the capacitors. Therefore, after performing fumigation and drying make sure that no halogen is left. Don't perform fumigation treatment to the whole electronic appliances packed in a box.

2.11 Flux

If you use a halogen type (Chlorine type, Bromine type, etc.) high-activity flux, please use it after confirmation in advance, as it may have an impact on performance and reliability of this product due to the residue of the flux.

3. Precautions for using capacitors

3.1 Environmental conditions

Capacitors should not be stored or used in the following environments.

- (1) Exposure to temperatures above the upper category or below the lower category temperature of the capacitor.
- (2) Direct contact with water, salt water, or oil.
- (3) High humidity conditions where water could condense on the capacitor.
- (4) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid, chlorine, chlorine compound, bromine, bromine compound or ammonia.
- (5) Exposure to ozone, radiation, or ultraviolet rays.
- (6) Vibration and shock conditions exceeding specified requirements.

Even within the specified requirements, a large vibration acceleration may be applied due to resonance, so be sure to evaluate and confirm with the actual product.



3.2 Electrical precautions

- (1) Avoid touching the terminals of a capacitor as a possible electric shock could result. The exposed aluminum case is not insulated and could also cause electric shock if touched.
- (2) Avoid short circuiting the area between the capacitor terminals with conductive materials including liquids such as acids or alkaline solutions.
- (3) A low-molecular-weight-shiroxane which is included in a silicon material shall causes abnormal electrical characteristics.

4. Emergency procedures

(1) If the pressure relief of the capacitor operates, immediately turn off the equipment and disconnect from the power source.

This will minimize an additional damage caused by the vaporizing electrolyte.

(2) Avoid contact with the escaping electrolyte gas, which can exceed 100 ℃ temperatures.

If electrolyte or gas enters the eye, immediately flush the eye with large amounts of water.

If electrolyte or gas is ingested by mouth, gargle with water.

If electrolyte contacts the skin, wash with soap and water.

5. Long term storage

(1) Leakage current of a capacitor tends to increase after a long-term storage due to dielectric dissolution, and very high current may flow at the first voltage load. However, applying voltage will form the dielectric, and the leakage current will decrease. Expiration date is 42 months from the outgoing inspection date for part numbers listed below, and it is 12 month for part numbers not listed below.

Series	Expiration date
S (Only high temperature reflow)	42 months from
HA (Only high temperature reflow)	
HB (Only high temperature reflow and 5.4 mm height)	outgoing
HC, HD, FCA, FC, FKA, FK, FKS, FN, FP, FT, FH, TG, TK,TP, TC, TCU, TQ	inspection date

Storage condition is to keep in room temperature (5 $^{\circ}$ C to 35 $^{\circ}$ C) and humidity (45 $^{\circ}$ 6 to 85 $^{\circ}$ 6) with no direct sunshine.

(2) Environmental conditions

Do not store under condition outside the area described in the specification, and also under conditions listed below.

- (a) Exposure to temperatures above the upper category or below the lower category temperature of the capacitor.
- (b) Direct contact with water, salt water, or oil.
- (c) High humidity conditions where water could condense on the capacitor.
- (d) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid, chlorine, Chlorine compound, Bromine, Bromine compound or ammonia.
- (e) Exposure to ozone, radiation, or ultraviolet rays.
- (f) Vibration and shock conditions exceeding specified requirements.

6. Capacitor disposal

When disposing capacitors, use one of the following methods.

- (1) Incinerate after crushing the capacitor or puncturing the can wall (to prevent explosion due to internal pressure rise).
- (2) Dispose as solid waste.

NOTE: Local laws may have specific disposal requirements which must be followed.

The precautions in using aluminum electrolytic capacitors follow the "Safety application guide for the use in fixedaluminum electrolytic capacitors for electronic equipment", RCR-2367D issued by JEITA in October 2017.

Please refer to the above application guide for details.

■ AEC-Q200 compliant

The products are tested based on all or part of the test conditions and methods defined in AEC-Q200. Please consult with Panasonic for the details of the product specification and specific evaluation test results, etc., and please review and approve Panasonic's product specification before ordering.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

EEE-0JA101AP EEE-0JA101WAR EEE-0JA102AP EEE-0JA220AR EEE-0JA330WAR EEE-0JA331AP EEE-0JA331XAP EEE-0JA470AR EEE-1AA101AP EEE-1AA101WAR EEE-1AA102UAP EEE-1AA220WAR EEE-1AA221AP EEE-1AA221XAP EEE-1AA330AR EEE-1AA330WAR EEE-1AA331AP EEE-1AA470WAR EEE-1AA471AP EEE-1AA471UAP EEE-1CA100AR EEE-1CA101AP EEE-1CA101WAP EEE-1CA220AR EEE-1CA220WAR EEE-1CA221AP EEE-1CA221XAP EEE-1CA330WAR EEE-1CA331AP EEE-1CA331UAP EEE-1CA470AP EEE-1CA470WAR EEE-1CA471AP EEE-1CA471UAP EEE-1EA100AR EEE-1EA100WAR EEE-1EA101AP EEE-1EA101UAP EEE-1EA101XAP EEE-1EA220AP EEE-1EA220WAR EEE-1EA221AP EEE-1EA221UAP EEE-1EA330AP EEE-1EA330WAR EEE-1EA331AP EEE-1EA331UAP EEE-1EA4R7AR EEE-1EA470WAP EEE-1EA471UAP EEE-1HAR10AR EEE-1HAR22AR EEE-1HAR33AR EEE-1HAR47AR EEE-1HA1R0AR EEE-1HA100AP EEE-1HA100WAR EEE-1HA101AP EEE-1HA101UAP EEE-1HA2R2AR EEE-1HA220AP EEE-1HA220WAP EEE-1HA221UAP EEE-1HA3R3AR EEE-1HA330AP EEE-1HA330UAP EEE-1HA330XAP EEE-1HA4R7AR EEE-1HA4R7WAR EEE-1HA470AP EEE-1HA470UAP EEE-1HA470XAP EEE-1VA100AR EEE-1VA100WAR EEE-1VA101AP EEE-1VA101UAP EEE-1VA101XAP EEE-1VA220AP EEE-1VA220WAR EEE-1VA221AP EEE-1VA221UAP EEE-1VA330AP EEE-1VA330WAP EEE-1VA331UAP EEE-1VA4R7AR EEE-1VA470AP EEE-1VA470WAP EEE-0JA152UAP EEE-0JA471UAP EEE-1CA221UAP EEE-1AA221A EEE-1CA100SA EEE-1EA221UA