



Part Number : [643193211](#)

Product Description : [.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Black Coding, Mat Sealed](#)

Series Number : [64319](#)

Status : Active

Product Category : [Connector Housings](#)



Documents & Resources

Drawings

[Drawing 643193211_sd.pdf](#)

3D Models and Design Files

[3D Model 643193211_stp.zip](#)

Specifications

[Application Specification AS-64319-002-001.pdf](#)

[Application Specification AS-64319-002-CH-001.pdf](#)

[Application Specification AS-64319-002-FR-001.pdf](#)

[Application Specification AS-64319-002-SP-001.pdf](#)

[Application Specification 984200002-AS-KR-000.pdf](#)

[Application Specification AS-98420-002-001.pdf](#)

[Application Specification AS-98420-002-CH-001.pdf](#)

[Application Specification AS-98420-002-FR-001.pdf](#)


[Application Specification AS-98420-002-SP-001.pdf](#)

[Packaging Specification PK-64319-001-001.pdf](#)

[Product Specification PS-64319-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	64319
Description	.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Black Coding, Mat Sealed
Application	Automotive, Power, Wire-to-Board
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C; Current max = 6.0A for 0.635mm Terminal (0.75mm ² wire) and 12.0A for 1.50mm Terminal (2.00mm ² wire)
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Product Family	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	883906131135

Electrical

Current - Maximum per Contact	12.0A, 2.5A
-------------------------------	-------------

Physical

Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Circuits (maximum)	32
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	29.426/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.50mm, 3.70mm CMC Header, Right-Angle, 32 Circuits, 1 Port, Black	<u>0643340100</u>
CMC Header 112-circuit, 3-pocket, Solder Tail	<u>0643330100</u>
2.50mm, 3.50mm, 3.70mm CMC Header, Right-Angle, 80 Circuits	<u>5022250801</u>

Use with Part(s)

Description	Part Number
CMC Wire Cap for 32 Circuits, CMC Receptacle Mat Sealed	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/643191201.html</u>

CMC 0.635mm Blind Cavity Plug	/content/molex/molex-dot-com/us/en/products/product-page.html/643251010.html
CMC 1.50mm Blind Cavity Plug	/content/molex/molex-dot-com/us/en/products/product-page.html/643251023.html
CMC CP Female Terminals	<u>64322</u>
1.50mm CMC CP Female Terminals	<u>64323</u>

Application Tooling

Global

Description	Part Number
Continuity Test Pen Assembly	<u>0638121100</u>
Unlocking Tool for CMC and CMX Receptacle Connector	<u>0638241200</u>