



**Part Number :** [02091117](#)

**Product Description :** 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Reel

**Series Number :** 1381

**Status :** Active

**Product Category :** Crimp Terminals

**Engineering Number :** 1381-A(P901)

**Packaging Alternative :** 0002091119 (Bag)



---

## Documents & Resources

### Drawings

[Drawing\\_002091117\\_sd.pdf](#)

### Specifications

[Product Specification PS-43660-9999-001.pdf](#)

[Test Summary 11890000-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	1381
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Reel
Application	Power, Wire-to-Wire
Product Family	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
UPC	800753746312

### Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	384.000/mg
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	N/A

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Use with Part(s)

Description	Part Number
Standard .093" Pin and Socket Dual Row Connector Housings	<u>1261</u>
Standard .093" Pin and Socket 3 Row Connector Housings	<u>1292</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1396</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1490</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1545</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1619</u>

## Application Tooling

### Global

Description	Part Number
Insertion Tool for Standard .093" Pin and Socket Terminals	<u>0011020003</u>
Extraction Tool for Standard .093" Pin and Socket Terminals	<u>0011030006</u>
Terminator Die	<u>0011402002</u>
Extractor Tool for .093 and HCS-125 Product Series	<u>0638240200</u>
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 18 AWG	<u>0638280900</u>
Hand Crimp Tool for .093" Pin and Socket Crimp Terminals, 22 AWG	<u>0638281400</u>
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 20 AWG	<u>0638281700</u>
Mini-Mac Applicator for Standard .093" Pin and Socket Terminals, for 18-22 AWG Wire with Insulation Diameter no greater than 2.29mm MAX	<u>0638924000</u>

Mini-Mac Applicator for Standard .093" Pin and Socket Terminals, for 18-22 AWG Wire with Insulation Diameter no greater than 3.05mm MAX	<u>0638927000</u>
-----------------------------------------------------------------------------------------------------------------------------------------------------	-------------------

---

This document was generated on Feb 07, 2024