

## Har-speed M12 malecont. Crimp AWG 23-26



Part number	21 01 100 9019
Specification	Har-speed M12 malecont. Crimp AWG 23-26
HARTING eCatalogue	https://b2b.harting.com/21011009019

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact
Version	
Gender	Male
Manufacturing process	Turned contacts
Technical characteristics	
Conductor cross-section	0.13 0.25 mm²
Conductor cross-section	AWG 26 AWG 23
Performance level	1
Material properties	
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

Page 1 / 2 | Creation date 2022-01-08 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



## Material properties

REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead
Commercial data	
Packaging size	100
Net weight	0.1 g
Country of origin	Switzerland
European customs tariff number	85369010
eCl@ss	27440204 Contact for industrial connectors

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING: 21011009019