

## Specification Sheet

Part Number: 156-02224



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Two-piece assembly allows the mount to slide along the strap ensuring proper orientation.

2-Piece Cable Tie & Edge Clip, 8.0" Long, EC5B, 1–3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 100/pkg

**Article Number** 156-02224

**Type** T50REC5B

**Color** Black (BK)

**Quantity Per** bag

**Product Description** HellermannTyton's Two-Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. NOTE: UL Listing applies to 1-2mm panel thicknesses only.

<b>Short Description</b>	2-Piece Cable Tie & Edge Clip, 8.0" Long, EC5B, 1–3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 100/pkg
<b>Global Part Name</b>	T50REC5B-PA66HIRHSUVR5/PA66HIRHSUV-BK
<b>Minimum Tensile Strength (Imperial)</b>	50.0
<b>Minimum Tensile Strength (Metric)</b>	225
<b>Length L (Imperial)</b>	8.0
<b>Length L (Metric)</b>	203.2
<b>Fixation Method</b>	EdgeClip, sideways, assembled, 2 piece
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.18
<b>Width W (Metric)</b>	4.6
<b>Bundle Diameter Min (Imperial)</b>	0.20
<b>Bundle Diameter Min (Metric)</b>	5.0
<b>Bundle Diameter Max (Imperial)</b>	2.0

**Bundle Diameter Max (Metric)** 50.0

**Thickness T (Imperial)** 0.05

**Thickness T (Metric)** 1.2

**Height H (Imperial)** 0.61

**Height H (Metric)** 15.5

**Panel Thickness Min (Imperial)** 0.04

**Panel Thickness Max (Imperial)** 0.12

**Panel Thickness Min (Metric)** 1.0

**Panel Thickness Max (Metric)** 3.0

**Material** Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Polyamide 6.6, high impact modified, heat and UV-stabilized, proprietary blend (PA66HIRHSUVR5)

**Material Shortcut** PA66HIRHSUVR5 PA66HIRHSUV

**Material Cable Tie** Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

**Flammability** UL 94 HB

**Operating Temperature** -40°F to +239°F (-40°C to +115°C) -40°F to +230°F (-40°C to +110°C)

**ROHS Compliant** Yes

**UL Listed (US and Canada)** Yes

**UL Listed (US)** Yes

**Package Quantity (Imperial)** 100

**Package Quantity (Metric)** 100

**Customs Number** 3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02224](#)