


- PNP
- Normally open (NO)
- 1.50 mm
- Flush (shielded)
- Cable, PUR, 5.00 m



General attributes

Approvals / Conformity	CE cULus EAC
Basic standard	IEC 60947-5-2
Enclosure Type per IEC 60529	IP68 according to BWN PR 20
Function indicator	Yes
Polarity reversal protected	Yes
Power indicator	No
Protection Class	II
Short circuit protected	Yes
MTTF	830 a

Electrical attributes

Connection type	Cable
Eff. operating current I _e	200 mA
Eff. operating voltage U _e DC	24.0 V
Electrical version	DC, direct current
Load capacitance max. (at U _e)	0.500 µF
Max. no-load cur. I _o undamped	3.0 mA
Minimum operating current I _m	0 mA
No-load current I _o damped max.	9.0 mA
Operating voltage U _B max. DC [V]	30.0 V
Operating voltage U _B min. DC [V]	10.0 V
Rated insulation voltage U _i	250 VAC
Rated short circuit current	100 A
Ripple max. (% of U _e)	15 %
Switching freq. f max. (at U _e)	3000 Hz
Switching function	Normally open (NO)
Switching output	PNP

Voltage drop static max. 2.5 V

Mechanical attributes

Ambient temperature T _a max.	70 °C
Ambient temperature T _a min.	-25 °C
Assured operating distance S _a	1.20 mm
Cable diameter D max.	3.1 mm
Cable jacket material	PUR
Cable length	5.00 m
Conductor cross-section	0.14 mm ²
Depth	30.0 mm
Diameter d1	M08x1
Eff. operating distance S _r	1.50 mm
Housing material	Stainless steel
Mech. installation condition	Flush (shielded)
Mounting length	29.0 mm
Number of conductors	3
Rated operating distance S _n [mm]	1.50 mm
Sensing face material	PBT
Tightening torque	8 Nm

Remarks

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.

