
SLVS011D - OCTOBER 1982 - REVISED AUGUST 2003

- 3-Terminal Regulators
- Output Current Up To 100 mA
- No External Components Required
- Internal Thermal-Overload Protection
- Internal Short-Circuit Current Limiting
- Direct Replacement for Industry-Standard MC79L00 Series
- Available in 5% or 10% Selections

description/ordering information

This series of fixed negative-voltage integrated-circuit voltage regulators is designed for a wide range of applications. These include on-card regulation for elimination of noise and distribution problems associated with single-point



† Internally connected NC – No internal connection

LP PACKAGE (TOP VIEW)



regulation. In addition, they can be used to control series pass elements to make high-current voltage-regulator circuits. One of these regulators can deliver up to 100 mA of output current. The internal current-limiting and thermal-shutdown features essentially make the regulators immune to overload. When used as a replacement for a Zener-diode and resistor combination, these devices can provide an effective improvement in output impedance of two orders of magnitude, with lower bias current.

ORDERING INFORMATION

TJ	OUTPUT VOLTAGE TOLERANCE	NOMINAL OUTPUT VOLTAGE (V)	PACKAG	Ε [†]	ORDERABLE PART NUMBER	TOP-SIDE MARKING		
			COIC (D)	Tube of 75	MC79L05ACD	701.054		
		_	SOIC (D)	Reel of 2500	MC79L05ACDR	79L05A		
		-5	TO 000 / TO 00 // D)	Bulk of 1000	MC79L05ACLP	701.0540		
	5%		TO-226 / TO-92 (LP)	Reel of 2000	MC79L05ACLPR	79L05AC		
		-12	0010 (D)	Tube of 75	MC79L12ACD	701.404		
			SOIC (D)	Reel of 2500	MC79L12ACDR	79L12A		
0°C to 125°C				Bulk of 1000	MC79L12ACLP	701.404.0		
			TO-226 / TO-92 (LP)	Reel of 2000	MC79L12ACLPR	79L12AC		
				Bulk of 1000	MC79L15ACLP			
		-15	TO-226 / TO-92 (LP)	Ammo of 2000	MC79L15ACLPM	79L15AC		
				Reel of 2000	MC79L15ACLPR			
	400/	-12	TO-226 / TO-92 (LP)	Bulk of 1000	MC79L12CLP	79L12C		
	10%	-15	SOIC (D) Tube of 75 MC79L15CD		79L15C			


[†] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



equivalent schematic



absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Input voltage: MC79L05	30 V
MC79L12, MC79L15	35 V
Package thermal impedance, θ _{JA} (see Notes 1 and 2): D package	97°C/W
LP package	140°C/W
Operating free-air, case, or virtual junction temperature	150°C
Lead temperature 1.6 mm (1/16 inch) from case for 10 seconds	260°C
Storage temperature range, T _{stg}	-65°C to 150°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions

			MIN	MAX	UNIT
Vi		MC79L05	-7	-20	
	Input voltage	MC79L12	-14.5	-27	V
		MC79L15	-17.5	-30	
lo	Output current			100	mA
TJ	Operating virtual junction temperature		0	125	°C



NOTES: 1. Maximum power dissipation is a function of $T_J(max)$, θ_{JA} , and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_J(max) - T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can affect reliability.

^{2.} The package thermal impedance is calculated in accordance with JESD 51-7.

electrical characteristics at specified virtual junction temperature, $V_I = -10 \text{ V}$, $I_O = 40 \text{ mA}$ (unless otherwise noted)

DADAMETED	TTOT COMPLETIONS!	-	M	C79L05	С	МС	79L05A	C	UNIT
PARAMETER	TEST CONDITIONS†	TJ	MIN	TYP	MAX	MIN	TYP	MAX	UNII
		25°C	-4.6	-5	-5.4	-4.8	-5	-5.2	
Output voltage‡	$V_I = -7 \text{ V to } -20 \text{ V},$ $I_O = 1 \text{ mA to } 40 \text{ mA}$	0°C to 125°C	-4.5		-5.5	-4.75		-5.25	V
	$V_I = -10 \text{ V}, I_O = 1 \text{ mA to } 70 \text{ mA}$	0°C to 125°C	-4.5		-5.5	-4.75		-5.25	
Input regulation	V _I = -7 V to -20 V	2500			200			150	.,
	$V_{I} = -8 \text{ V to } -20 \text{ V}$	25°C			150			100	mV
Ripple rejection	$V_I = -8 \text{ V to } -18 \text{ V, f} = 120 \text{ Hz}$	25°C	40	49		41	49		dB
Outrast as audation	I _O = 1 mA to 100 mA	0500			60			60	>/
Output regulation	$I_O = 1 \text{ mA to } 40 \text{ mA}$	25°C			30			30	mV
Output noise voltage	f = 10 Hz to 100 kHz	25°C		40			40		μV
Dropout voltage	I _O = 40 mA	25°C		1.7			1.7		V
5:		25°C			6			6	•
Bias current		125°C			5.5			5.5	mA
5:	V _I = -8 V to -20 V	2021 1250			1.5		1.5		
Bias current change	$I_O = 1 \text{ mA to } 40 \text{ mA}$	0°C to 125°C			0.2			0.1	mA

[†] All characteristics are measured with a 0.33-µF capacitor across the input and a 0.1-µF capacitor across the output. Pulse-testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. ‡ This specification applies only for dc power dissipation permitted by absolute maximum ratings.

electrical characteristics at specified virtual junction temperature, $V_I = -19 \text{ V}$, $I_O = 40 \text{ mA}$ (unless otherwise noted)

242445752		_	M	C79L12	С	МС	79L12A	C	
PARAMETER	TEST CONDITIONS†	TJ	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
		25°C	-11.1	-12	-12.9	-11.5	-12	-12.5	
Output voltage‡	$V_I = -14.5 \text{ V to } -27 \text{ V},$ $I_O = 1 \text{ mA to } 40 \text{ mA}$	0°C to 125°C	-10.8		-13.2	-11.4		-12.6	V
	$V_I = -19 \text{ V}, I_O = 1 \text{ mA to } 70 \text{ mA}$	0°C to 125°C	-10.8		-13.2	-11.4		-12.6	
Input regulation	$V_{I} = -14.5 \text{ V to } -27 \text{ V}$	0500			250			250	.,
	V _I = -16 V to -27 V	25°C			200			200	mV
Ripple rejection	$V_I = -15 \text{ V to } -25 \text{ V, f} = 120 \text{ Hz}$	25°C	36	42		37	42		dB
0	I _O = 1 mA to 100 mA	0500			100			100	
Output regulation	I _O = 1 mA to 40 mA	25°C			50			50	mV
Output noise voltage	f = 10 Hz to 100 kHz	25°C		80			80		μV
Dropout voltage	I _O = 40 mA	25°C		1.7			1.7		V
5.		25°C			6.5			6.5	•
Bias current		125°C			6			6	mA
D'an annual alcana	V _I = -16 V to -27 V	000 1- 40500			1.5			1.5	A
Bias current change	I _O = 1 mA to 40 mA	0°C to 125°C			0.2			0.1	mA

[†] All characteristics are measured with a 0.33-µF capacitor across the input and a 0.1-µF capacitor across the output. Pulse-testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. ‡ This specification applies only for dc power dissipation permitted by absolute maximum ratings.



MC79L00 SERIES NEGATIVE-VOLTAGE REGULATORS

SLVS011D - OCTOBER 1982 - REVISED AUGUST 2003

electrical characteristics at specified virtual junction temperature, $V_I = -23~V,\,I_O = 40~mA$ (unless otherwise noted)

DADAMETED	TEGT CONDITIONS	_	M	C79L15	С	МС	79L15 <i>A</i>	/C	UNIT
PARAMETER	TEST CONDITIONS†	TJ	MIN	TYP	MAX	MIN	TYP	MAX	UNII
		25°C	-13.8	-15	-16.2	-14.4	-15	-15.6	
Output voltage‡	$V_I = -17.5 \text{ V to } -30 \text{ V},$ $I_O = 1 \text{ mA to } 40 \text{ mA}$	0°C to 125°C	-13.5		-16.5	-14.25		-15.75	V
	$V_1 = -23 \text{ V}, I_0 = 1 \text{ mA to } 70 \text{ mA}$	0°C to 125°C	-13.5		-16.5	-14.25		-15.75	
Input regulation	$V_I = -17.5 \text{ V to } -30 \text{ V}$	0500			300			300	\/
	$V_{I} = -17.5 \text{ V to } -30 \text{ V}$	25°C			250			250	mV
Ripple rejection	V _I = -18.5 V to -28.5 V, f = 120 Hz	25°C	33	39		34	39		dB
Outside as and office	I _O = 1 mA to 100 mA	0500			150			150	
Output regulation	I _O = 1 mA to 40 mA	25°C			75			75	mV
Output noise voltage	f = 10 Hz to 100 kHz	25°C		90			90		μV
Dropout voltage	I _O = 40 mA	25°C		1.7			1.7		V
		25°C			6.5			6.5	
Bias current		125°C			6			6	mA
D'an annual alam	V _I = -20 V to -30 V	000 1- 40500			1.5			1.5	4
Bias current change	$I_O = 1 \text{ mA to } 40 \text{ mA}$	0°C to 125°C			0.2			0.1	mA

[†] All characteristics are measured with a 0.33-µF capacitor across the input and a 0.1-µF capacitor across the output. Pulse-testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. ‡ This specification applies only for dc power dissipation permitted by absolute maximum ratings.



www.ti.com 6-Oct-2023

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
MC79L05ACD	LIFEBUY	SOIC	D	8	75	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L05A	
MC79L05ACDE4	LIFEBUY	SOIC	D	8	75	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L05A	
MC79L05ACDG4	LIFEBUY	SOIC	D	8	75	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L05A	
MC79L05ACDR	LIFEBUY	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L05A	
MC79L05ACDRE4	LIFEBUY	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L05A	
MC79L05ACDRG4	LIFEBUY	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L05A	
MC79L05ACLP	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L05AC	
MC79L05ACLPE3	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L05AC	
MC79L05ACLPR	LIFEBUY	TO-92	LP	3	2000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L05AC	
MC79L12ACD	LIFEBUY	SOIC	D	8	75	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L12A	
MC79L12ACDE4	LIFEBUY	SOIC	D	8	75	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L12A	
MC79L12ACDR	LIFEBUY	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 125	79L12A	
MC79L12ACLP	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L12AC	
MC79L12ACLPE3	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L12AC	
MC79L12ACLPR	LIFEBUY	TO-92	LP	3	2000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L12AC	
MC79L12ACLPRE3	LIFEBUY	TO-92	LP	3	2000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L12AC	
MC79L12CLP	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L12C	
MC79L15ACLP	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L15AC	
MC79L15ACLPE3	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L15AC	
MC79L15ACLPR	LIFEBUY	TO-92	LP	3	2000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L15AC	
MC79L15ACLPRE3	LIFEBUY	TO-92	LP	3	2000	RoHS & Green	SN	N / A for Pkg Type	0 to 125	79L15AC	

⁽¹⁾ The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".



PACKAGE OPTION ADDENDUM

www.ti.com 6-Oct-2023

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 25-Oct-2023

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device		Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
MC79L05ACDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
MC79L12ACDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1

www.ti.com 25-Oct-2023



*All dimensions are nominal

Device	Package Type	Package Drawing Pins		SPQ	Length (mm)	Width (mm)	Height (mm)	
MC79L05ACDR	SOIC	D	8	2500	340.5	338.1	20.6	
MC79L12ACDR	SOIC	D	8	2500	340.5	338.1	20.6	

PACKAGE MATERIALS INFORMATION

www.ti.com 25-Oct-2023

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
MC79L05ACD	D	SOIC	8	75	507	8	3940	4.32
MC79L05ACDE4	D	SOIC	8	75	507	8	3940	4.32
MC79L05ACDG4	D	SOIC	8	75	507	8	3940	4.32
MC79L12ACD	D	SOIC	8	75	507	8	3940	4.32
MC79L12ACDE4	D	SOIC	8	75	507	8	3940	4.32



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040001-2/F



TO-92 - 5.34 mm max height

TO-92



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.
- 3. Lead dimensions are not controlled within this area.4. Reference JEDEC TO-226, variation AA.
- 5. Shipping method:

 - a. Straight lead option available in bulk pack only.
 b. Formed lead option available in tape and reel or ammo pack.
 - c. Specific products can be offered in limited combinations of shipping medium and lead options.
 - d. Consult product folder for more information on available options.



TO-92





TO-92





IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated