

# Dimmable Constant Voltage LED Driver 156W 12V 13A RS HLG-185-12B

RS Stock number 721-1932



- Features:
- Universal AC input / Full range
- Built-in active PFC function
- High efficiency up to 94%
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Cooling by free air convection
- OCP point adjustable through output cable or internal potential meter
- IP67 / IP65 design for indoor or outdoor installations
- Three in one dimming function (1~10Vdc or PWM signal or resistor)
- Suitable for LED lighting and street lighting applications
- Compliance to worldwide safety regulations for lighting
- Suitable for dry / damp / wet locations



#### SPECIFICATION


SPECIFICA	ATION		_						_					
MODEL			HLG-185-12				HLG-185-30		HLG-185-42	HLG-185-48	HLG-185-54			
	DC VOLTAGE		12V	15V	20V	24V	30V	36V	42V	48V	54V			
ОИТРИТ	CONSTANT CURRENT REGION Note.4		6 ~12V	7.5 ~ 15V	10~20V	12 ~ 24V	15 ~ 30V	18~36V	21 ~ 42V	24~48V	27 ~ 54V			
	RATED CURRENT		13A	11.5A	9.3A	7.8A	6.2A	5.2A	4.4A	3.9A	3.45A			
	RATED POWER		156W	172W	186W	187.2W	186W	187.2W	184.8W	187.2W	186.3W			
	RIPPLE & NOISE (max.) Note.2		150mVp-p	150 mVp-p	150mVp-p	150mVp-p	200mVp-p	200mVp-p	200mVp-p	200mVp-p	200mVp-p			
	VOLTAGE ADJ. RANGE Note.6		10.8 ~ 13.5V	13.5~17V	17~22V	22 ~ 27V	27 ~ 33V	33~40V	38 ~ 46V	43~53V	49 ~ 58V			
	CURRENT ADJ. RANGE		Can be adjust	ed by internal p	otential meter	or through out	put cable							
	CURRENT ADJ. R	ANGE	6.5 ~ 13A	5.75 ~ 11.5A	4.65 ~ 9.3A	3.9 ~ 7.8A	3.1 ~ 6.2 A	2.6 ~ 5.2A	2.2~4.4A	1.95 ~ 3.9A	1.72~3.45A			
	VOLTAGE TOLERA	ANCE Note.3	±2.5%	±2.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%			
	LINE REGULATIO	N	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%			
	LOAD REGULATION	ON	±2.0%	±1.5%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%			
	SETUP, RISE TIME	Note.8	2500ms, 80ms	s at full load	230VAC / 115V	AC; B type 2	500ms, 200ms	at 95% load	230VAC / 115	VAC				
	HOLD UP TIME (T)	yp.)	16ms at full lo	ad 230VAC/	115 VAC									
	VOLTAGE RANGE	Note.5	90~264VAC	127 ~ 370	OVDC									
	FREQUENCY RANGE		47~63Hz											
	POWER FACTOR		PF≥0.95/230	VAC PF	≥0.98/115VAC	at full load and	irated output v	oltage PF	≥0.9 at 50 ~	100% load				
INPUT	EFFICIENCY (Typ.)		92%	93%	93.5%	94%	94%	94%	94%	94%	94%			
INFOI	AC CUIDDENT	12V	1.8A / 115 VAC	1.8A/115VAC										
	AC CURRENT	15V~54V	2.1A / 115 VAC 0.9A / 230 VAC											
	INRUSH CURREN	T(Typ.)	COLD START 75A/230VAC											
	LEAKAGE CURRENT		<0.75mA / 240VAC											
	OVER CURRENT Note 4		95~108%											
			Protection type: Constant current limiting, recovers automatically after fault condition is removed											
	SHORT CIRCUIT		Constant current limiting, recovers automatically after fault condition is removed											
PROTECTION	OVERVOLENCE		14~17V	18 ~ 21V	23~27V	28 ~ 34V	34~38V	41 ~ 46V	47 ~ 53V	54 ~ 60V	59 ~ 65V			
	OVERVOLTAGE		Protection type: Shut down o/p voltage with auto-recovery or re-power on to recovery											
	OVER TEMPERAT	UDE	100°C ±10°C (RTH2)											
	OVERTEMPERAT	UKE	Protection type: Shut down o/p voltage, recovers automatically after temperature goes down											
	WORKING TEMP.		-40 ~ +60 °C @ full load ; +70 °C @ 60% load (Refer to derating curve)											
	WORKING HUMID	ITY	20 ~ 95% RH non-condensing											
ENVIRONMENT	STORAGE TEMP.,	HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH											
	TEMP. COEFFICIE	NT	±0.03%/°C (0~50°C)											
	VIBRATION		10 ~ 500Hz, 5G 12min./1cycle, period for 72min. each along X,Y,Z axes											
	SAFETY STANDA	RDS Note.7	UL8750, EN61347-1, EN61347-2-13 independent IP65 or IP67 approved ; Design refer to UL60950-1, TUV EN60950-1											
	WITHSTAND VOL	TAGE	I/P-O/P:3.75KVAC I/P-FG:1.88KVAC O/P-FG:0.5KVAC											
SAFETY &	ISOLATION RESIS	STANCE	I/P-O/P, I/P-FG, O/P-FG:100 M O hms / 500 V D C / 25°C / 70% RH											
EMC	EMI CONDUCTION 8	RADIATION	Complian œ to EN55015, EN55022 (CISPR22) Class B											
	HARMONIC CURR	ENT	Complian œ to EN61000-3-2 Class C (≥50% load); EN61000-3-3											
	E110 11111111111171		Complian ce to EN61000-4-2,3,4,5,6,8,11; ENV50204, EN61547, EN55024, heavy industry level (surge 4KV), criteria A											
	EMS IMMUNITY		192.2Khrs min. MIL-HDBK-217F (25°C)											
	MTBF		192.2Khrs mi	n. MIL-HDB	K-217F (25°C)									
OTHERS			192.2Khrs mi 228*68*38.8n		K-217F (25°C)									



## ■ Mechanical Specification


Case No.994D Unit:mm

Blank: (HLG-185)




※IP67 rated. Cable for I/O connection.

### A Type: (HLG-185-\_A)





B Type:(HLG-185-\_B)



- X IP67 rated. Output constant current level can be adjusted through output cable by connecting a resistor or 1 ~ 10V dc or 10V PWM signal between DIM+ and DIM-.
- ※ Please DO NOT connect "DIM-" to "-V".
- ※ Reference resistance value for output current adjustment (Typical)

Resistance value	10K $\Omega$	$\mathbf{20K}\Omega$	$\mathbf{30K}\Omega$	$\mathbf{40K}\Omega$	50K $Ω$	$\mathbf{60K}\Omega$	<b>70K</b> Ω	$80 \mathrm{K}\Omega$	$90 \mathrm{K}\Omega$	<b>100K</b> Ω	OPEN
Percentage of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	102%~108%


※ 1 ~ 10V dimming function for output current adjustment (Typical)


Dimming value	1V	2V	3V	4V	5V	6V	7V	8V	9V	10V	OPEN
Percentage of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	102%~108%

\* 10V PWM signal for output current adjustment (Typical): Frequency range: 100HZ ~ 3KHz

Duty value	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	OPEN
Percentage of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	102%~108%










#### ■ Power Factor Characteristic


Power factor will be higher than 0.9 when output loading is 50% or higher.

#### **Constant Current Mode**




### ■ EFFICIENCY vs LOAD (48V Model)

HLG-185 series possess superior working efficiency that up to 94% can be reached in field applications.



## ■ DRIVING METHODS OF LED MODULE



Typical LED power supply I-V curve



#### O Direct driving:

Under direct driving, the power supply will work in "constant current mode (CC)" and output voltage of the power supply will be clamped by sum of forward voltage (VF) of the LED strip.

The total forward voltage of series connecting LEDs is suggested for 60%~95% of power supply rated output voltage due to concern of the best PF value and efficiency.




#### With LED driver :

Using additional driver, the power supply will work in "constant voltage mode (CV)" and output voltage of the power supply will be kept in rated value. In this drive mode, several design issues need to be considered:

- 1.Output voltage of PSU must be higher than total forward voltage of series connecting LEDs by 3V minimum.
- Input capacitor (Cin) of LED driver circuit should use 47uF ~ 100uF(typ.) of rating depends on the operating frequency of the LED driver.

The higher the operating frequency is used, the smaller value of Cin should be chosen, and vice versa.


3.Do not use B type with LED driver.



#### ■ DIMMING OPERATION(for B-type only)

Using the built-in dimming function on B-type model can't turn the lighting fixture totally dark. Please refer to the connection method below to achieve 0% brightness of the lighting fixture connecting to the LED power supply unit.

O Dimming connection diagram for turning the lighting fixture ON/OFF:




Using a switch and relay can turn ON/OFF the lighting fixture.

- 1. Output constant current level can be adjusted through output cable by connecting a resistor or 1~10Vdc or 10V PWM signal between DIM+ and DIM-.
- 2. The LED lighting fixture can be turned ON/OFF by the switch.



### ■ EMI DEBUG SUGGESTION




- A. Add a common mode ferrite choke on output wires to reduce the common emission between 10M ~ 300MHz per lighting EMI regulation.
- B. Chassis of LED lamp and chassis of HLG-185 or the FG wire should be connected to the safety ground to reduce the EMI noise, including the conduction and radiation emission.
- C. The additional X-Cap and discharge resistor can reduce the low frequency conduction noise between 9K ~ 1MHz per lighting EMI regulation.
- D. L-C filter should be added at the DC input of LED constant current driver to avoid the differential emission and high frequency noise generated by the CC driver.

#### ■ WATERPROOF CONNECTION

Waterproof connector

Waterproof connector can be assembled on the output cable of HLG-185 to operate in dry/wet/damp or outdoor environment.



#### Cable Joiner

