



- Unit purifies air up to 2 workplaces
- 100–240 power supply for global use
- Filter alarm and 3 steps speed control
- Small foot print design
- The fume extraction unit MG 130 is easy to install and operate. Is supplied complete ready to place close to the workbench.

MG 130

Code No.: 130-1000-ESD

Dimensions W x D x H (mm)	460 x 210 x 500
Dimensions W x D x H (Inch)	18,11 x 8,26 x 19,68
Weight (ca) in kg	11
Voltage	100 - 240 V, 50/60 Hz
Heating output	100 W
Noise level (distance 1 m) dB(A)	
Max. vacuum	---
Capacity m ³ /h	140
Pre filter	Pre filter mat class F7
Cartridge Volume Extraction	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1-2 workplaces
Interface RS232 (Remote control)	1 x RS232 (TTL)
USB interface	---
WX compatible	---