

Product Summary

B320A-B340A:								
V _{RRM} (V)	l _o (A)	V _{F(MAX)} @ 3A (V)	I _{R(MAX)} @ V _{RRM} (mA)					
20, 30, 40	3.0	0.50	0.5					

B350-B360A:

V _{RRM} (V)	I _O (A)	V _{F(typ)} @ +125°C (V)	I _{R(MAX)} @ V _{RRM} (mA)
50, 60	3.0	0.70	0.5

Description and Applications

For use in low-voltage, high-frequency inverters, freewheeling, DC-DC converters, and polarity protection applications.

Features

- Guard Ring Die Construction for Transient Protection
- Ideally Suited for Automated Assembly
- Low Power Loss, High Efficiency
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Notes 3 & 4)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data

- Case: SMA
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Plating (Matte-Tin Finish).
 Solderable per MIL-STD-202, Method 208 (3)
- Polarity: Cathode Band
- Weight: 0.064 grams (Approximate)

SMA



Bottom View

Ordering Information (Note 5)

Part Number*	Compliance	Case	Packaging
B3XXA-13-F	Standard	SMA	5,000/Tape & Reel

* XX = Device Type, e.g. B320A-13-F (SMA Package).

Marking Information (Note 6)



B3x0A = Product Type Marking Code, ex: B320A) | | = Manufacturers' Code Marking YWW = Date Code Marking Y = Last Digit of Year (ex: 15 for 2015) WW = Week Code (01 to 53)

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
 - 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 - 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 - 4. Products manufactured with Date Code 0924 (week 24, 2009) and newer are built with Green Molding Compound.
- 5. For packaging details, go to our website at http://www.diodes.com/products/packages.html.
- 6. Device has a cathode band (as shown above) and may also have a cathode notch.



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitance load, derate current by 20%.

Characteristic		Symbol	B320A	B330A	B340A	B350A	B360A	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		V _{RRM} V _{RWM} V _R	20	30	40	50	60	V
Average Rectified Output Current @ T _T = +100°C		Ιo	3.0					А
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load		I _{FSM}			80			А

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Maximum Total Power Dissipation - Steady State, TA = +25°C (Note 7)	PD	850	mW
Typical Thermal Resistance, Junction to Ambient (Note 7)	R _{0JA}	140	°C/W
Typical Thermal Resistance, Junction to Terminal (Note 8)	R _{θJT}	25	°C/W
Typical Thermal Resistance, Junction to Ambient (Note 8)	R _{θJA}	100	°C/W
Operating Temperature Range	TJ	-55 to +150	°C
Storage Temperature Range	T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic		Symbol	Min	Тур	Max	Unit	Test Condition
Forward Valtage Drop	B320A, B330A, B340A	VF		-	0.50	V	I _F = 3.0A, T _A = +25°C
Forward Voltage Drop	B350A, B360A	۷F	V _F	_	0.70		
Lookogo Curropt (Noto 0)	akage Current (Note 9)		_	-	0.5	mA	@ Rated V _R , T _A = +25°C
Leakage Current (Note 9)			_		20		@ Rated V _R , T _A = +100°C
Total Capacitance		Ст		200	_	pF	$V_R = 4V, f = 1MHz$


Notes:

7. Device mounted on FR-4 PCB, with minimum recommended pad layout.


8. Device mounted on glass epoxy substrate with 2x3mm copper pad.

9. Short duration pulse test used to minimize self-heating effect.













Fig. 8 Non-Repetitive Forward Surge Current Derating Curve






POWER (W)



Package Outline Dimensions


Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for the latest version.



SMA						
Dim	Min	Max				
Α	2.29	2.92				
В	4.00	4.60				
С	1.27	1.63				
D	0.15	0.31				
ш	4.80	5.59				
G	0.05	0.20				
Н	0.76	1.52				
J	1.96	2.40				
All Dimensions in mm						

Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.



Dimensions	Value (in mm)			
С	4.00			
G	1.50			
Х	2.50			
X1	6.50			
Y	1.70			

SMA

SMA



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: B360A-13-F